


# NS12565T101MNV



### ■ Features

- Item Summary  
100 μH(±20%), 2.23A, 1.81A
- Lifecycle Stage  
Mass Production
- AEC-Q200 qualified
- Standard packaging quantity (minimum)  
Taping 2000pcs(500pcs\*4reel)

### ■ Products characteristics table

CaseSize (EIA/JIS)	-/12565
Inductance	100 μH(±20%)
Inductance Measuring Frequency	100kHz
Rated Current -Saturation Current	2.23A
Rated Current -Temperature Rise Current	1.81A
DC Resistance (max)	0.1476Ω
Avg. of DC.Resistance	0.123Ω
Temperature Range	-40°C to 125°C
Self-resonant Frequency (min)	5.5MHz
RoHS Compliance	Yes
Halogen Free	Yes
Soldering Method	Reflow


### ■ External Dimensions

L	12.5mm ±0.3
W	12.5mm ±0.3
H	6.5mm ±0.35

### ■ Recommended Land Patterns

【推奨ランドパターン】  
 実装上の注意  
 ・実装状態を確認の上ご使用ください。また、ご購入の際は、  
 ・本製品のはんだ付けはリフローはんだ工法にのみ対応しています。

【Recommended Land Patterns】  
 Surface Mounting  
 ・Mounting and soldering conditions should be checked beforehand.  
 ・Applicable soldering process to these products is reflow soldering only.



SMD Power Inductors (NS series)

Type	A	B	C
NS 10145	2.5	5.6	3.2
NS 10155	2.5	5.6	3.2
NS 10165	2.5	5.6	3.2
NS 12555	2.5	8.6	3.2
NS 12565	2.5	8.6	3.2
NS 12575	2.5	8.6	3.2

unit:mm