

Integra Cil



Crompton Instruments Integra Ci1 Energy Meter

The Integra Ci1 energy meter is specially designed and developed as a cost effective watt hour and VAr hour meter to complement the current Crompton Instruments Ci meter series. The Integra Ci1 self-contained 96mm DIN panel mounted watt hour, VAr hour meter measures the real consumption of active and reactive energy to Class 1.0 accuracy.

The backlit LCD screen displays 8 character counter indicating watt hour or VAr hour units. The optional modules enable transfer of energy measurements to building management systems (BMS) via pulsed or digital communication options.

Programmable functions

The Integra Ci1 energy meter provides simple programming to suit single-phase, three-phase three-wire and three-phase four-wire un-balanced system configurations, CT ratio settings and configuration of selected communication options. To prevent unauthorised access to the product configuration settings, all set-up screens offer password protection.

Plug in modules

Plug in modules allows to fit either maximum of two isolated pulsed output relays or a RS-485 communication module + one isolated pulsed output relay. The communication output module can be programmed internally to respond either to Modbus® RTU or Johnson Controls.

Display

The four push buttons give direct access to display the programmed set CT ratio, watt hours import and export, VAr hours import and export and the phase sequence test routine for both voltage and current phases. During the accumulation of the Wh or VArh the running icon will flash at a rate dependant on the displayed parameter.



Self-explanatory standard international icons on the display allow to read at a glance what parameters are measured and what system configuration (Wh or VAhr) is.

Features

- DIN 96 enclosure
- Backlit LCD screen
- Bezel depth 6.1mm
- Plug-in output modules
- Programmable CT ratio
- User programmable system configuration
- Phase diagnostic indication
- System running indication
- Removable energy threshold (1%)

Benefits

- Cost effective
- Intuitive navigation
- Crompton Instruments brand quality
- UK manufactured
- Easy 'clip-in' panel mounting

Standards

IEC 61326 IEC 61010-1 IEC 62053-21 RoHS Compliant




Specifications

Input		
Nominal input voltage	100-289V ac L-N (173-500V ac L-L)	
Max. continuous input overload voltage	120% of nominal	
Max. short duration input voltage	2 x range maximum (1 second application repeated 5 times at 5 min intervals)	
Nominal input voltage burden	< 0.2VA per phase	
Nominal input current	5A ac rms	
Max. continuous input overload current	120% of nominal	
Max. short duration input current	10 x range maximum (1 second application repeated 5 times at 5 min intervals)	
Frequency	45-66Hz	
Auxiliary		
Operating range	110-400V ac nominal +/- 10% (99-440V ac absolute limits) or 120-350V dc +/- 20% (96-420V dc absolute limits)	
Auxiliary burden	5 VA (Max)	
Accuracy		
Active energy (Wh)	Class 1 (IEC 62053-21)	
Reactive energy (VArh)	+/- 1% of range	
Display LCD	8 character backlit counter (########) After the maximum reading is reached the digits will return to zero	
Output modules (optional)		
Pulsed output relays	1 per module (2 modules fitted per Ci1)	
Contact rating	50mA max at 250V ac	
Туре	Solid state relay	
RS485 output module	1 RS-485 communication module (maximum of 1 module fitted per Ci1)	
Туре	2-wire half duplex	
Baud rate	2400, 4800, 9600, 19200, 38400	
Enclosure		
Enclosure style	DIN 96 panel mount	
Dimensions	96x96x64.1mm (depth behind panel without module 58mm, with module 82.5mm)	
Panel cut-out	92x92mm	
Panel thickness	1-5mm	
Front protection rating	IP52	



Parameters

Button	Screen	Parameters
CT	1	CT Ratio
Wh	2 3	IMPORT Wh EXPORT Wh
Wh	4 5	IMPORT VArh EXPORT VArh
TEST	6	Phase sequence diagnostic



Product Codes

Description	Part number
Integra Ci1 base unit	CI1-01
Options	
Pulsed output	CI-PUL-01
Modbus® RS485	CI-MOD-01
Accessories	
IP65 protective cover	3 G365 O2
IP54 panel gasket	3 C345 O1

While TE has made every reasonable effort to ensure the accuracy of the information in this catalog, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications. TE connectivity (logo) and TE Connectivity are trademarks of the TE Connectivity Ltd. family of companies. Crompton is a trademark of Crompton Parkinson and is used by TE Connectivity Ltd. under a licence. Other logos, product and Company names mentioned herein may be trademarks of their respective owners.

TE Energy - innovative and economical solutions for the electrical power industry: cable accessories, connectors & fittings, insulators & insulation, surge arresters, switching equipment, street lighting, power measurement and control.



TE Energy Freebournes Road Witham, Essex CM8 3AH Phone: +44 (0)870 870 7500 Fax: +44 (0)870 240 5287 Email: electrical@te.com www.crompton-instruments.com http://energy.te.com

