

# Excel range

## section 4

Cat No.

Please note that not all products are available ex-stock and are made to order.  
For availability please check with your nearest HPM of ce.

Std  
Pk

XL770/1



XL770/2H



XL770/1



XLW770V1



XL1036



XLTD770/1



Cat No.	Description	Std Pk
<b>Excel Range switches 230 - 240V a.c.</b>		
<i>Switches are supplied with Cat. No. 770M unless otherwise speci ed. These are interchangeable with any 770, 769, 707 series mechanism. Available to PWD speci cation with rear-screwed plate mounting of mechanisms.</i>		
<b>Vertical standard size switches</b>		
<i>Plate size: 73 x 117mm. Mounting centres: 84mm.</i>		
XL770/0	Blank grid with blank cover	10
XL770/1	10A 1 gang standard size switch	10
XL770/2	10A 2 gang standard size switch	10
XL770/3	10A 3 gang standard size switch	10
XL770/4	10A 4 gang standard size switch	10
XL770/5	10A 5 gang standard size switch	10
XL770/6	10A 6 gang standard size switch	10
<b>Horizontal standard size switches</b>		
<i>Plate size: 117 x 73mm. Mounting centres: 84mm.</i>		
XL770/1H	10A 1 gang standard size switch	10
XL770/2H	10A 2 gang standard size switch	10
XL770/3H	10A 3 gang standard size switch	10
XL770/4H	10A 4 gang standard size switch	10
XL770/5H	10A 5 gang standard size switch	10
XL770/6H	10A 6 gang standard size switch	10
<b>Architrave switches</b>		
<i>Plate size: 35 x 84mm. Mounting centres: 70mm. Suitable for horizontal and vertical mounting.</i>		
XL770/1	10A 1 gang architrave switch, 35 x 84mm, 70mm mounting centres	10
XL770/2	10A 2 gang architrave switch, 35 x 84mm, 70mm mounting centres	10
XL770/3	10A 3 gang architrave switch, 35 x 110mm, 95mm mounting centres	10
XL770/4	10A 4 gang architrave switch, 35 x 135mm, 120mm mounting centres	10
<b>Standard size weatherproof switches, IP56</b>		
<i>Plate size: 73 x 117mm. Mounting centres: 84mm. Weatherproof to IP56, in one or two-gang arrangement.</i>		
XLW770H1	10A 1 gang standard size switch for horizontal mounting	3
XLW770H2	10A 2 gang standard size switch for horizontal mounting	3
XLW770V1	10A 1 gang standard size switch for vertical mounting	3
XLW770V2	10A 2 gang standard size switch for vertical mounting	3
<b>Heavy duty rocker switches, range switch isolators</b>		
<i>Plate size: 73 x 117mm. Mounting centres: 84mm. Mechanism size 41 x 63 x 13mm deep from back of plate.</i>		
XL1036	40A, 240V ac single pole switch with looping terminals	10
XL1036N	40A, 240V ac single pole switch with neon indicator	10
XL1036P	40A, 415V ac double pole switch & terminal for common neutral & earth	10
XL1036PN	40A, 415V ac double pole switch with neon indicator & terminal for common neutral & earth	10
<b>Time delay switches</b>		
<i>Plate size: 73 x 117mm. Mounting centres: 84mm. EMC compliant. Available in white only. Cover plates in various colours are sold separately - refer to Excel accessories, switch cover plates.</i>		
XLTX770/1	10A time delay switch, 3-wire. Push start/push restart. 1 sec to 239 hrs time adjustment.	3
XLTX770/1A	10A time delay switch, 2-wire. Push start/push restart. 1 sec to 239 hrs time adjustment.	3
XLTX770/1NC	10A time delay switch, 3-wire. Push start/push restart, normally-closed contacts. 1 sec to 239 hrs time adjustment.	3
XLTX770/2	10A time delay switch, 3-wire. Push start/push stop. 1 sec to 239 hrs time adjustment.	3
XLTX770/2A	10A time delay switch, 2-wire. Push start/push stop. 1 sec to 239 hrs time adjustment.	3
XLTX770/2NC	10A time delay switch, 3-wire. Push start/push stop, normally-closed contacts. 1 sec to 239 hrs time adjustment.	3
XLTX770/3	10A repeat cycle timer, 3-wire. Choice of 8 time cycles - 15s, 1 min, 5 min, 15 min, 1 hr, 4 hrs, 12 hrs, 24 hrs.	3
XLTX770/3A	10A repeat cycle timer, 2-wire. Choice of 8 time cycles - 15s, 1 min, 5 min, 15 min, 1 hr, 4 hrs, 12 hrs, 24 hrs.	3
XLTF770/1	Fan time delay, 2-wire: 3, 10 & 20 minutes	3
XLTD770/1	2.5A time delay switch, 2-wire. 1, 3 & 10 minutes, push start/push restart	3

# Excel range

## section 4

Cat No.

Please note that not all products are available ex-stock and are made to order. For availability please check with your nearest HPM of ce.

Std Pk

XL770TH



XL770T

**Light switch with timer**

Plate size: 117 x 73mm. Mounting centres: 84mm.

Available in white only.

Auto, manual or random operation. 500W incand. 500VA dichroic/ uoro/fan motors. 7VA min load. EMC compliant.

1 gang light switch with programmable digital 24hr & 7 day timer. Vertical mounting.

3

XL770TH

1 gang light switch with programmable digital 24hr & 7 day timer. Horizontal mounting.

3

XL632



XL632

**Automatic light switch**

Plate size: 73 x 117mm. Mounting centres: 84mm

Available in white only. Cover plates in various colours are sold separately - refer to Excel Range accessories/switch cover plates.

Automatic light switch for internal use. Rated 600VA, min load 7VA. Vertical mounting. EMC compliant.

Light switches on automatically when someone enters the room and switches off after a preset time if no further movement detected. Manual override.

3

XL770/2RX



XL770/2RX

**Remote controlled switch**

Plate size: 73 x 117mm. Mounting centres: 84mm.

Available in white only.

Cover plates in various colours are sold separately - refer to Excel Range accessories/switch cover plates.

Remote/touch switch rated 600VA, min load 7VA. Remote control (included) range up to 9m. EMC compliant

3

Section 4

XL770/1KLIO



XL770/1KLI

**Keylock Switches**

Plate size: 73 x 117mm. Mounting centres: 84mm.

Supplied with Cat. No. 770M mechanism. Also available in 15A and in 20A. Specify.

Note: For common keys, add CK to Cat. No. no of switch required eg XL770/1KLICK.

10A keylock switch with key removable in on position

10

XL770/1KLO

10A keylock switch, with key removable in off position

10

XL770/1KLIO

10A keylock switch, with key removable in on or off position

10

XL770KT1



XL770KT1

**KeyTag switches**

Plate size: 73 x 117mm. Mounting centres: 84mm.

Available in white only.

Supplied with Cat. No. 770/20KTM switches inside pockets, Cat. No. 707M neons (opal in pocket, red outside), Cat. No. 770T3 blank tag. The KeyTag mechanisms supplied are interchangeable with other mechs. detailed below,

Base pocket style KeyTags are available with plastic cover plates only.

2 x 20A switches & neon in base pocket

10

XL770KT2 2 x 20A switches & neon in base pocket, 10A independent switch above

10

XL770KT3 2 x 20A switches & neon in base pocket, 10A independent switch & neon above

10

XL770KT4 3 x 20A switches in base pocket

10

XL770KT5 3 x 20A switches in base pocket, 10A independent switch above

10

XL770KT6 3 x 20A switches in base pocket, 10A independent switch & neon above

10

XL770KT7 2 x 20A switches & neon in top pocket

10

XL770KT8 2 x 20A switches & neon in top pocket, 10A independent switch below

10

XL770KT9 2 x 20A switches & neon in top pocket, 10A independent switch & neon below

10

XL770KT10 3 x 20A switches in top pocket

10

XL770KT11 3 x 20A switches in top pocket, 10A independent switch below

10

XL770KT12 3 x 20A switches in top pocket, 10A independent switch & neon below

10

XL770KT13 3 x 20A switches & neon in base pocket

10

XL770KT14 4 x 20A switches in base pocket

10

XL770KT15 3 x 20A switches & neon in top pocket

10

XL770KT16 4 x 20A switches in top pocket

10

**KeyTags**

770T3

KeyTag, 100mm long, with removable insert

10

# Excel range

section

# 4

Cat No.

Please note that not all products are available ex-stock and are made to order.  
For availability please check with your nearest HPM of ce.

Std  
Pk

XL770VCKT7



XL770KM1



XL787



XL787X



XL787/2X



### VingCard KeyTag switches

Plate size: 73 x 117mm. Mounting centres: 84mm.

Available in white only.

Activated by insertion of a VingCard (not supplied).

Base pocket style KeyTags are available with plastic cover plates only.

XL770VCKT1	2 x 20A switches & neon in base pocket	10
XL770VCKT3	2 x 20A switches & neon in base pocket, 10A independent switch & neon above	10
XL770VCKT4	3 x 20A switches in base pocket	10
XL770VCKT5	3 x 20A switches in base pocket, 10A independent switch above	10
XL770VCKT6	3 x 20A switches in base pocket, 10A independent switch & neon above	10
XL770VCKT7	2 x 20A switches & neon in top pocket	10
XL770VCKT8	2 x 20A switches & neon in top pocket, 10A independent switch below	10
XL770VCKT9	2 x 20A switches & neon in top pocket, 10A independent switch & neon below	10
XL770VCKT10	3 x 20A switches in top pocket	10
XL770VCKT11	3 x 20A switches in top pocket, 10A independent switch below	10
XL770VCKT12	3 x 20A switches in top pocket, 10A independent switch & neon below	10
XL770VCKT13	3 x 20A switches & neon in base pocket	10
XL770VCKT14	4 x 20A switches in base pocket	10
XL770VCKT15	3 x 20A switches & neon in top pocket	10
XL770VCKT16	4 x 20A switches in top pocket	10

### KeyCard switches

Plate size: 73 x 117mm. Mounting centres: 84mm

Available in white only.

Activated by insertion of a room access card, (not supplied).

Base pocket style KeyCards are available with plastic cover plates only.

XL770KM1	2 x 20A switches & neons in base pocket	10
XL770KM2	2 x 20A switches & neons in base pocket, 10A independent switch above	10
XL770KM3	2 x 20A switches & neons in base pocket, 10A independent switch & neon above	10
XL770KM7	2 x 20A switches & neons in top pocket	10
XL770KM8	2 x 20A switches & neons in top pocket, 10A independent switch below	10
XL770KM9	2 x 20A switches & neons in top pocket, 10A independent switch & neon below	10

### Excel Range powerpoints 230 - 240V a.c.

#### Single powerpoints

Plate size: 117 x 73mm. Mounting centres: 84mm.

XL787	10A single powerpoint	10
XL787S	10A single powerpoint with safety shutter	10
XL787NS	10A single powerpoint with neon & safety shutter	10
XL787R	10A single powerpoint with round earth	10
XL787RS	10A single powerpoint with round earth & safety shutter	10
XL787RNS	10A single powerpoint with round earth, neon & safety shutter	10
XL787/15	15A single powerpoint	10
XL787/15S	15A single powerpoint with shutters	10
XL787/15NS	15A single powerpoint with neon & safety shutter	10
XL787/20	20A single powerpoint	10
XL787/20N	20A single powerpoint with neon	10
XL787/25	25A single powerpoint	10
XL787/25N	25A single powerpoint with neon	10
XL787/32	32A single powerpoint	10

#### Single powerpoints, double pole

Plate size: 117 x 73mm. Mounting centres: 84mm.

XL787P	10A single powerpoint, double pole	10
XL787PN	10A single powerpoint, double pole, with neon	10
XL787PR	10A single powerpoint, double pole, with round earth	10

#### Single powerpoints with extra switch

Plate size: 117 x 73mm. Mounting centres: 84mm.

XL787X	10A single powerpoint with extra switch	5
XL787XS	10A single powerpoint with extra switch & safety shutter	5
XL787XNS	10A single powerpoint with extra switch, neon, safety shutter	5
XL787XR	10A single powerpoint with extra switch & round earth	5
XL787XRS	10A single powerpoint, extra switch, round earth & safety shutter	10
XL787XNV	10A single powerpoint with extra switch, no volt	5
XL787XNV15	15A single powerpoint with extra switch, no volt	5

#### Single powerpoints with 2 extra switches

Plate size: 117 x 73mm. Mounting centres: 84mm.

XL787/2X	10A single powerpoint with 2 extra switches	5
XL787/2XS	10A single powerpoint with 2 extra switches & safety shutter	10

Section 4

# Excel range

## section 4

Cat No.

Please note that not all products are available ex-stock and are made to order.  
For availability please check with your nearest HPM of ce.

Std  
Pk

XL787XI



XL787XI

**Single powerpoints with engraved inserts**

Plate size: 117 x 73mm. Mounting centres: 84mm.

10A single powerpoint, 'Not safety switch protected' insert

10

XL787ID



XL787ID

**Single powerpoints with blanking inserts**

Plate size: 117 x 73mm. Mounting centres: 84mm.

10A single powerpoint with white ID insert

5

XL787IDCL

10A single powerpoint with clear ID insert

5

XL787B



XL787B

**Power monitor**

Plate size: 117 x 73mm. Mounting centres: 84mm.

10A power monitor. Brownout protecting single powerpoint

10

XL787B15

15A power monitor. Brownout protecting single powerpoint

10

XLV787



XLV787

**Vertical single powerpoints**

Plate size: 73 x 117mm. Mounting centres: 84mm.

10A vertical single powerpoint

10

XLV787S

10A vertical single powerpoint with safety shutter

10

XLV787NS

10A vertical single powerpoint with neon & safety shutter

10

XLV787R

10A vertical single powerpoint with round earth

10

XLV787RS

10A vertical single powerpoint with round earth & safety shutter

10

XLV787/15

15A vertical single powerpoint

5

**Vertical single powerpoints with extra switch**

Plate size: 73 x 117mm. Mounting centres: 84mm.

XLV787X

10A vertical single powerpoint with extra switch

5

XLV787XS

10A vertical single powerpoint with extra switch & safety shutter

5

XLV787XNS

10A vertical single powerpoint, extra switch, neon & safety shutter

10

**Vertical single powerpoints with 2 extra switches**

Plate size: 73 x 117mm. Mounting centres: 84mm.

XLV787/2X



XLV787/2X

10A vertical single powerpoint with 2 extra switches

5

XLV787/2XS

10A vertical single powerpoint with 2 extra switches & safety shutters

10

XL777



XL777

**Double powerpoints**

Plate size: 117 x 73mm. Mounting centres: 84mm.

10A double powerpoint

10

XL777DD

10A dovetail dolly double powerpoint, 2 blank DD inserts, 1 lock

10

XL777S

10A double powerpoint with safety shutters

10

XL777NS

10A double powerpoint, neons & safety shutters

10

XL777R

10A double powerpoint with round earths

10

XL777RS

10A double powerpoint with round earths & safety shutters

10

XL777RNS

10A double powerpoint, round earth, neons & safety shutters

10

XL777/1015

Double powerpoint with 10 & 15A outlets

10

XL777/1015S

Double powerpoint with 10 & 15A outlets & safety shutters

10

XL777/1015NS

Double powerpoint with 10 & 15A outlets, neons & safety shutters

10

XL777CH

10A double powerpoint, chemical resistant  
Available in white only

10

XL777/15

15A double powerpoint

10

XL777/15S

15A double powerpoint with safety shutters

10

XL777/15NS

15A double powerpoint, neons & safety shutters

10

**Double powerpoints, double pole**

Plate size: 117 x 73mm. Mounting centres: 84mm.

XL777P

10A double pole double powerpoint

10

# Excel range

section

# 4

Cat No.

Please note that not all products are available ex-stock and are made to order.  
For availability please check with your nearest HPM of ce.

Std  
Pk

XL777X



XL777ID



XLV777



XLV777X



XL792B15



XL7774



XL7775



XL777F	<b>Double powerpoints, shrouded</b> <i>Plate size: 117 x 73mm. Mounting centres: 84mm.</i> 10A shrouded double powerpoint	8
XL777X	<b>Double powerpoints with extra switch</b> <i>Plate size: 117 x 73mm. Mounting centres: 84mm.</i> 10A double powerpoint with extra switch	10
XL777XS	10A double powerpoint with extra switch & safety shutters	10
XL777XNS	10A double powerpoint with extra switch, 2 neons & safety shutters	10
XL777X3NS	10A double powerpoint with extra switch, 3 neons & safety shutters	10
XL777XCH	10A double powerpoint, chemical resistant	1
XL777XD	10A double powerpoint with extra duo switch	10
XL777X15	15A double powerpoint with extra switch	10
XL777X15NS	15A double powerpoint with extra switch, 2 neons & safety shutters	10
XL777ID	<b>Double powerpoints with blanking inserts</b> <i>Plate size: 117 x 73mm. Mounting centres: 84mm.</i> 10A double powerpoint with white ID insert	10
XL777IDCL	10A double powerpoint with clear ID insert	10
XLV777	<b>Vertical double powerpoints</b> <i>Plate size: 73 x 117mm. Mounting centres: 84mm.</i> 10A double powerpoint	10
XLV777S	10A double powerpoint with safety shutters	10
XLV777NS	10A double powerpoint, neons & safety shutters	10
XLV777R	10A double powerpoint with round earth	10
XLV777RS	10A double powerpoint with round earth & safety shutters	10
XLV777/1015	Double powerpoint with 10 & 15 amp outlets	10
XLV777/1015S	Double powerpoint with 10 & 15 amp outlets & safety shutters	10
XLV777/1015NS	Double powerpoint, 10 & 15 A outlet, neons & safety shutters	10
XLV777/15	15A double powerpoint	10
XLV777/15NS	15A double powerpoint, neons & safety shutters	10
XLV777X	<b>Vertical double powerpoints with extra switch</b> <i>Plate size: 73 x 117mm. Mounting centres: 84mm.</i> 10A double powerpoint with extra switch	10
XLV777XS	10A double powerpoint with extra switch & safety shutters	10
XLV777XNS	10A double powerpoint with extra switch, 2 neons & safety shutters	10
XLV777X15	15A double powerpoint with extra switch	10
XL792B	<b>Double slimline powerpoints</b> <i>Plate size: 157 x 50mm. Mounting centres: 137mm.</i> 10A double slimline powerpoint with busbar link	5
XL792B15	15A double slimline powerpoint with busbar link	5
XL792NS	10A double slimline powerpoint, 2 neons & safety shutters with busbar link	5
XL792/15	15A double slimline powerpoint with busbar link	5
XL792/15NS	15A double slimline powerpoint, 2 neons & safety shutters with busbar link	5
XL792/OA	Double slimline grid & cover, at blank 34 x 57 x 2.5mm thick may be punched or drilled (no mechs)	1
XL7774	<b>Four-in-one powerpoint</b> <i>Plate size: 190.5 x 72.5mm. Mounting centres: 84mm.</i> <i>Available in white only. Suits 137/1 mounting block</i> 10A Four-in-one powerpoint	5
XL7775	<b>Multiple powerpoints, 5 gang</b> <i>Plate size: 250 x 72.5mm. Mounting centres: 84mm</i> <i>Available in white only. Includes mounting block and conduit adapter.</i> 10A 5 gang powerpoint with 5 switched outlets	10
XL7775/1	10A 5 gang powerpoint with 4 switched outlets plus 1 x 10A switch	10
XL7775/2	10A 5 gang powerpoint with 4 switched outlets plus 2 x 10A switches	10
XL7775/3	5 gang powerpoint with 4 x 10A switched outlets plus 1 x 15A switched outlet	10

Section 4

# Excel range

## section 4

Cat No.

Please note that not all products are available ex-stock and are made to order.  
For availability please check with your nearest HPM of ce.

Std  
Pk

XL777PA



XL777EL10



XL777EL30



XL798/0



XL798/777EL



XL300E



Cat No.	Description	Std Pk
<b>Surge protecting double powerpoints</b> <i>Plate size: 117 x 73mm. Mounting centres: 84mm.</i>		
XL777PA	10A surge arrester double powerpoint with buzzer	2
XL777PANB	10A surge arrester double powerpoint without buzzer	2
XL777PAM	Replacement module	10
<b>Electresafe powerpoints, 10mA tripping</b> <i>Plate size: 117 x 73mm. Mounting centres: 84mm.</i>		
XL777EL10	10mA Electresafe powerpoint, 10A	2
XL777EL10N	10mA Electresafe powerpoint with 'supply available' neon, 10A	2
XL777EL10N2	10mA Electresafe powerpoint with switched outlet neons, 10A	2
XL777EL10N3	10mA Electresafe powerpoint with 3 neons, 10A	2
XL777EL10/1015	10mA Electresafe powerpoint with 10A & 15A outlets	2
<b>Electresafe powerpoints, 30mA tripping</b> <i>Plate size: 117 x 37mm. Mounting centres: 84mm.</i>		
XL777EL30	30mA Electresafe powerpoint, 10A	2
XL777EL30N	30mA Electresafe powerpoint with 'supply available' amber neon, 10A	2
XL777EL30N2	30mA Electresafe powerpoint with switched outlet neons, 10A	2
XL777EL30R	30mA Electresafe powerpoint with round earths, 10A	2
XL777EL30/1015	30mA Electresafe powerpoint with 10A & 15A outlets	2
XL777EL30G	30mA Electresafe powerpoint for generators, 10A.	2
XL777EL30G1015	30mA Electresafe powerpoint for generators, 10A & 15A outlets.	1
<b>Excel shaver supply outlets</b> <i>Plate size: 117 x 73mm. Mounting centres: 84mm.</i>		
XL798/0	Excel shaver outlet	10
<b>Excel shaver supply outlets with double powerpoint</b> <i>Plate size: 114 x 117mm. Mounting centres: 84mm.</i> <i>Available in white only</i>		
XL798/777	Excel shaver outlet & double powerpoint	1
XL798/777EL30	Excel shaver outlet & double powerpoint with 30mA safety switch	1
XL798/777X	Excel shaver outlet & double powerpoint and extra switch	1
<b>Excel Range dimmers and fan controllers 230 - 240V a.c.</b>		
<b>Leading edge light dimmers, EMC compliant</b> <i>Plate size: 73 x 117mm Mounting centres: 84mm</i> <i>Refer to technical section at front of Section 8 for more information.</i>		
XL200E	200VA light dimmer, leading edge	3
XL300E	300VA light dimmer, leading edge	3
XL400L	400VA light dimmer, leading edge	3
XL700L	700VA light dimmer, leading edge	3
XL1000L	1000VA light dimmer, leading edge	1
XL1000ERC	1000VA light dimmer/fan controller, leading edge, for remote mounting <i>Available in white only.</i> <i>Control plate suits all standard-sized mounting accessories - 84mm centres. Plate size 117mm H x 73mm W x 13mm D from back of plate.</i> <i>Remote unit 190mm H x 100mm W x 46mm D overall.</i>	1
XL2000ERC	2000VA light dimmer/fan controller, leading edge, for remote mounting <i>Available in white only.</i> <i>Control plate suits all standard-sized mounting accessories - 84mm centres. Plate size 117mm H x 73mm W x 13mm D from back of plate.</i> <i>Remote unit 190mm H x 100mm W x 46mm D overall.</i>	3



# Excel range

## section 4

Cat No.

Please note that not all products are available ex-stock and are made to order.  
For availability please check with your nearest HPM of ce.

Std  
Pk

XL400T



XL400T

**Trailing edge light dimmers, EMC compliant**

Plate size: 73 x 117mm Mounting centres: 84mm  
Refer to technical section at front of Section 8 for more information.

400VA light dimmer, trailing edge

3

XL700T

700VA light dimmer, trailing edge

3

XL1000T

1000VA light dimmer, trailing edge

3

XL400ESD



XL400ESD

**Superdimmer, EMC compliant**

Plate size: 73 x 117mm. Mounting centres: 84mm.  
Refer to technical section at front of Section 8 for more information.

400VA light dimmer operated by infra-red remote control (included), or metallic touch plate, leading edge

3

Superdimmer, switch and dimmer with user-adjustable ramp-up/down times. Four combinations available:  
suf x MSWE - matt silver touch plate with white cover plate; MSMS matt silver touch and cover plates;  
PBWE - polished brass touch plate with white cover plate; PBPB - polished brass touch plate and cover plate.

XL300F



XL300F

**Fan controllers, EMC compliant**

Plate size: 73 x 117mm. Mounting centres: 84mm.  
230 - 240V ac. Must be matched to fan type.

300VA fan controller

3

XL650ET

650VA timed fan speed controller with auto switch-off  
Min load 60VA. Timer switches off load after approximately 2 hours, manually resettable. Also suited for controlling resistive loads. Suitable for ceiling sweep & ceiling exhaust fans.

3

XL475

100VA de-hummer 3-speed fan controller

3

XL475/1

100VA de-hummer 3-speed fan controller

3

XL475/2

100VA de-hummer 3-speed fan controller

3

XL770/1CX



XL770/1CX

**Excel Range outlets**

**Standard size TV and FM-TV outlets**  
Plate size: 73 x 117mm. Mounting centres: 84mm.

75 ohm coax outlet

10

XL770/1FCX

75 ohm coax to F connector

10

XL770/1TV

300 ohm TV outlet

10

XL770/2FMTV

FM-TV outlet (300/300 ohm)

10

XL770/2FMTV300

FM-TV outlet with 2 x 300 ohm outlets

10

XL770/2FMTV75

FM-TV outlet (75/75 ohm)

10

XLA770/1CX



XLA770/1CX

**Architrave TV and FM-TV outlet**

Plate size: 32 x 68mm. Mounting centres: 70mm.

75 ohm coax outlet

10

XL770F



XL770F

**F connector pay-TV outlet**

Plate size: 73 x 117mm. Mounting centres: 84mm.

F connector for cable, microwave & satellite TV. 75 ohm

10

XL770/1RJ2



XL770/1RJ2

**Modular series RJ outlets**

Plate size: 117 x 73mm. Mounting centres: 84mm.

Single RJ45 outlet (phone/data, Cat 5E)

10

XL770/2RJ2

Double RJ45 outlet (phone.data, Cat 5E)

10

# Excel range

section

# 4

Cat No.

Please note that not all products are available ex-stock and are made to order.  
For availability please check with your nearest HPM of ce.

Std  
Pk

XL222/2T



**XL222/2T**  
10A double powerpoint, 2 x F connectors and 2 x RJ45 sockets (8P8C - Cat 5E), 2 horizontal plates tall

1

**XL222PA/2T**  
10A double powerpoint with surge protection, 2 x F connectors and 2 x RJ45 sockets (8P8C - Cat 5E), 2 horizontal plates tall

1

**XLV222/2W**  
10A double powerpoint, 2 x F connectors and 2 x RJ45 sockets (8P8C - Cat 5E), 2 vertical plates wide

1

**XLV048/2W**  
8 x F connectors and 4 x RJ45 sockets (8P8C - Cat 5E), 2 vertical plates wide

1

**Triple size communication outlet combinations**

Plate size: 117 x 219mm.

**XLV424/3W**  
2 x 10A double powerpoint, 4 x F connectors and 2 x RJ45 sockets (8P8C - Cat 5E), 3 vertical plates wide

1

**XL422PA/3T**  
1 x 10A double powerpoint with surge protection, 1 x 10A double powerpoint, 2 x F connectors and 2 x RJ45 sockets (8P8C - Cat 5E), 3 horizontal plates tall

1

**XLV6/3W**  
3 x 10A double vertical powerpoints. 3 vertical plates wide

1

XL422PA/3T



**Excel Range cover plates & grids with cover plates**

Available in various colour and metallic finishes - please refer to colour options page at the beginning of this section for details of codes and surcharges.

Please note that not all plates are available in every colour and/or metallic finish.

Not all plates have been listed, however, plates are available for all products.

**Standard size switch cover plate only**

Plate size: 73 x 117mm. Mounting centres: 84mm.

Plates available for all Excel products (not all listed). Can be used for horizontal and vertical switches.

**XL770/0PL**  
Blank cover plate only

10

**XL770/1PL**  
Cover plate only for 1 gang switch

10

**XL770/2PL**  
Cover plate only for 2 gang switch

10

**XL770/3PL**  
Cover plate only for 3 gang switch

10

**XL770/4PL**  
Cover plate only for 4 gang switch

10

**XL770/5PL**  
Cover plate only for 5 gang switch

10

**XL770/6PL**  
Cover plate only for 6 gang switch

10

XL770/1PL



**Standard size grids and cover plate only (no mechs)**

Plate size: 73 x 117mm. Mounting centres: 84mm.

Colour surcharges might apply - please see Colour options and surcharges page. Please note that not all plates are available in every colour.

Not all plates have been listed, however, plates are available for all Excel and Standard Range products.

**XL770/1GPL**  
1 gang standard size grid & cover plate only

10

**XL770/2GPL**  
2 gang standard size grid & cover plate only

10

**XL770/3GPL**  
3 gang standard size grid & cover plate only

10

**XL770/4GPL**  
4 gang standard size grid & cover plate only

10

**XL770/5GPL**  
5 gang standard size grid & cover plate only

10

**XL770/6GPL**  
6 gang standard size grid & cover plate only

10

XL770/3GPL



**Architrave switch cover plate only (matt only)**

Plate size: 35 x 84mm. Mounting centres: 70mm.

**XLA770/1PL**  
Cover plate only for 1 gang switch

20

**XLA770/2PL**  
Cover plate only for 2 gang switch

20

**XLA770/3PL**  
Cover plate only for 3 gang switch

20

**XLA770/4PL**  
Cover plate only for 4 gang switch

20

**Architrave switch grids and cover plate only (no mechs)**

**XLA770/1GPL**  
1 gang architrave grid & cover plate only

20

**XLA770/2GPL**  
2 gang architrave grid & cover plate only

20

**XLA770/3GPL**  
3 gang architrave grid & cover plate only

10

**XLA770/4GPL**  
4 gang architrave grid & cover plate only

10

**Heavy duty rocker cover plate only**

**XL1036PL**  
Cover plate only for heavy duty rocker switch

20

**Slimline grids and cover plate only (no mechs)**

Plate size: 157 x 50mm. Mounting centres: 137mm.

**XL792/0A**  
Double slimline grid & cover, at blank 34 x 57 x 2.5mm thick. May be punched or drilled

10

**XL792/02A**  
Double slimline 2 gang grid & cover, at blank 34 x 57 x 2.5mm thick

10

**XL792/4**  
Four gang grid & cover. Accepts 4 x RJ sockets with adaptor, or other mechs

10

XL792/4





# Excel range

section

# 4

Cat No.

Please note that not all products are available ex-stock and are made to order.  
For availability please check with your nearest HPM of ce.

Std  
Pk

XL787PL




	<b>Single powerpoint cover plate only</b> <i>Plate size: 117 x 73mm. Mounting centres: 84mm.</i>	
XL787PL	Cover plate only for single powerpoint	10
XL787XPL	Cover plate only for single powerpoint with extra switch	10
XL787NSPL	Cover plate only for single powerpoint with neon	20
XL787/2XPL	Cover plate only for single powerpoint with 2 extra switches	10

XLDCPL



	<b>Double powerpoint cover plate only</b> <i>Plate size: 117 x 73mm. Mounting centres: 84mm.</i>	
XL777PL	Cover plate only for double powerpoint	10
XL777XPL	Cover plate only for double powerpoint with extra switch	10
XL777NSPL	Cover plate only for double powerpoint with neon	20

XL770U



	<b>Double size cover plate only (matt only)</b> <i>Plate size: 144 x 116.5mm or 116.5 x 114mm, 230.5 x 72.5mm or 72.5 x 230.5mm. Mounting centres: 84mm.</i> <i>Enables 2 x Excel units to be mounted side by side or one above each other. Choose from 4 different layouts. Specify layout and cover function when ordering. Please contact us for an order form.</i>	
XLDC	Double size cover plate only	10

XL770TOPL



	<b>Triple size cover plate only (matt only)</b> <i>Plate size: 117 x 213mm or 213 x 117mm. Mounting centres: 84mm.</i> <i>Enables 3 x Excel standard size units to be mounted side by side or above each other. Choose from 2 different layouts. Specify layout and cover functions when ordering. Please contact us for an order form</i>	
XLTC	Triple size cover plate only	1

XL770/1D3



	<b>Four-in-one powerpoint cover plate only</b> <i>Plate size: 190.5 x 72.5mm. Mounting centres: 84mm.</i>	
XL774PL	Cover plate only for Four-in-one powerpoint	5

	<b>Universal cover plate only</b> <i>Plate size: 117 x 73mm. Mounting centres: 84mm</i> <i>A multi-purpose plate, used by electronics manufacturers as a base for a variety of electronic switching applications.</i>	
XL770U	Excel universal plate	10

	<b>Telephone outlet cover plate only</b> <i>Plate size: 117 x 73mm. Mounting centres: 84mm.</i>	
XL770TOPL	Telephone outlet plate	10

	<b>Computer grids and plates only</b> <i>Plate size: 117 x 73mm. Mounting centres: 84mm.</i>	
XL770FPL	F, BNC, TNC or ST bre optic adaptor, plate only. Hole dia. 9.5mm	10
XL770/1D1	Computer outlet plate for 1 x 9 pin (CP9) D connector socket	10
XL770/2D1	Computer outlet plate for 2 x 9 pin (CP9) D connector sockets	10
XL770/1D2	Computer outlet plate for 1 x 15 pin (CP15) D connector socket	10
XL770/2D2	Computer outlet plate for 2 x 15 pin (CP15) D connector sockets	10
XL770/1D3	Computer outlet plate for 1 x 25 pin (CP25) D connector socket	10
XL770/2D3	Computer outlet plate for 2 x 25 pin (CP25) D connector sockets	10

800/2CL



	<b>Circuit identification &amp; plain caps</b>	
	<b>Plain blank flush caps</b> Plain blank flush caps only. (Packet of 100.) Specify colour.	100

	<b>Engraved flush caps</b> Engraved flush caps. <i>Available in figures 1-99, letters A-Z. (10 of each number or letter in each pack). Black engraving standard or specify red, yellow.</i>	10
--	---	----

	<b>Identification products</b>	
	<b>Identification products</b>	
800	Blanking piece, suits all 770 series switch plates	10
800LH	Blanking piece with hole for potentiometer mounting, suits all 770 series switch plates.	10
800ID	Blanking piece engraved - Not Safety Switch Protected. Suits all 770 series switch plates.	10
800/2	Blanking insert with opaque cap. Add Suits all 770 series switch plates.	50
800/2CL	Blanking insert with clear cap. Add Suits all 770 series switch plates.	50
800/2CL1	Die cut labels for circuit identification to suit Cat. No. 800/2CL	50
800/2CL3	Blank die-cut paper for Cat. No. 800/2CL2 circuit ID kit <i>10 sheets per pack. Specify: WE (white); BU (blue); RED (red); or YE (yellow).</i>	1

	<b>Paint blisters</b>	
XL1FB	Paint blister	1

Section 4