MultiModem[®] IND



V.92 Industrial Modem

The MultiModem® IND industrial modem is designed for rugged industrial and outdoor applications. The metal chassis and industrial-grade components allow for operation over a temperature range of -40° to +85° C and meet the reliability specifications for vibration and shock. With V.92/56K modem

speeds, the MultiModem IND industrial modem provides the fastest, reliable dial-up rates for modem communication in applications under extreme temperatures and conditions.


Features

- V.92/56K download speeds and 48K upload speeds when connecting with V.92 servers
- · Rugged, industrial metal chassis
- Operates over the industrial temperature range of -40° to +85° C
- GR 1089 Clause 4 lightning and AC power fault compliant
- · Meets reliability specifications for vibration and shock
- Supports dial-up or 2-wire leased line operation
- V.44 compression improves data throughput rates
- Class 1.0 and Class 2.1 faxing at speeds to V.34/33.6K bps (Super G3)
- Error Correction Mode (ECM) provides fast and reliable fax transmissions
- Windows Plug-and-Play operation
- · U.S. Caller ID reporting
- Remote configuration for centralized setup and control
- · Callback Security for network security and reduced telephone toll charges
- Global approvals in many countries for worldwide use
- Country localization kits available with power cords, phone cords and telco adapters
- Desktop or panel mounting
- Flash memory for easy updates
- Two-year warranty



Benefits

- Withstands extreme temperatures and conditions
- V.92/56K modem speeds
- Global approvals



Specifications

Rates

Data: V.92/56K downloads & 48K upload speeds from V.92 servers; V.90/56K downloads from V.90/K56flex servers; 33.6K bps transfers with other servers

Fax: 33.6K/14.4K bps

Standards

Data: V.92, V.90, enhanced V.34 & below

Error Correction: V.42

Data Compression: V.44, V.42bis, MNP® Class 5

Fax: V.34, Class 2.1 & Class 1.0, V.17, Group 3, Class 1 & Class 2, Error

Correction Mode (ECM)

Connectors

1 RJ-11 & DB9

Operation

Async/230.4K bps

Dial-up or 2-wire leased line

Operating System Support

Windows 3.1x/95/98/NT/Me/2000/XP, Linux, SCO OpenServer, & others

Power Requirements

6V to 48VDC; 155mA typical @ 9VDC, 180mA maximum @ 9VDC

Physical Description

4.3" w x 2.4" h x 0.94" d; 4.1 oz.

(11 cm x 6.1 cm x 2.4 cm; 115 g)

Operating Environment/Reliability

Temperature Range: -40° to +85° C

EN 60068-2-6: Vibration - 10 - 500Hz sine vibration 5g

EN 60068-2-30: Temp/Humidity Damp Heat cycling

EN 60068-2-1: Cold (-40° C)

EN 60068-2-2: Dry Heat (+85° C)

EN 60068-2-14: Change of Temperature (-40° C to +85° C)

IEC 68-2-27: Shock - 3 shocks/3mS duration 50g

Approvals

EMC: FCC Part 15 Class B, EN 55022 Class B, EN 55024, EN 61000-6-2

Safety: UL 60950-1, EN 60950-1, GR 1089 (Clause 4 lightning & AC power fault

compliant)

Ordering Information

Product	Description	Region
MT5634IND*	V.92 Data/Fax Industrial Modem	Global

^{*} Specify country when ordering.

Services & Warranty

Multi-Tech's comprehensive Support
Services programs offer a full array of
options to suit your specific needs. These
services are aimed at protecting your
investment, extending the life of your
solution or product, and reducing total
cost of ownership. Our seasoned technical
experts, with an average tenure of more
than 10 years, can walk you through smooth
installations, troubleshoot issues and help
you with configurations. Products include a
2-year warranty that can be extended up to
5 years via Multi-Tech's Extended Warranty
program, which offers the convenience of
Overnight Service* for optimal uptime.

Extended Warranty & Overnight Services

To give you peace-of-mind and protect your investment, our Extended Warranty Service Plans ensure your Multi-Tech products are covered for 1, 2, or 3 years beyond the manufacturer's warranty with an optional Overnight Service plan*.

Installation Support

Multi-Tech's Installation Support Service delivers priority service with the ability to work one-on-one with an experienced Multi-Tech technical support engineer, to guide you through the installation process for our products.

Technical Support Services

At Multi-Tech, we're committed to providing you personalized attention and quality service while providing you a quick response to your product support needs. We have several options of support for you to choose from.

For additional information on Support Services as well as other service offerings, please contact your Multi-Tech representative or visit www.multitech.com/support.go.

* Overnight replacement service is currently available for U.S. customers.

World Headquarters

Multi-Tech Systems, Inc. 2205 Woodale Drive Mounds View, MN 55112 U.S.A. Tel: 763-785-3500 Toll-Free: 800-328-9717 Email: sales@multitech.com www.multitech.com

EMEA Headquarters

Multi-Tech Systems (EMEA) Unit 1, Thames Court 2 Richfield Avenue Reading, Berkshire RG1 8EQ United Kingdom Tel: +(44) 118 959 7774 Email: sales@multitech.co.uk



Produced in the U.S. of U.S. and non-U.S. components. Features and specifications are subject to change without notice.

Trademarks and Registered Trademarks: Multi-Tech and the Multi-Tech logo, MultiModem: Multi-Tech Systems, Inc. All other products and technologies are the trademarks or registered trademarks of their respective holders.