

Moeller HPL0211-2004/2005

	Phases	Rated operational current $I_e$ A	Type Article no.	Std. pack	Notes	
<b>Commoning busbars, 1.25 mm thick</b>						
For miniature circuit-breakers <b>without</b> auxiliary contacts						
With fork connectors, for combination box terminal						
	1	85	<b>FAZ-XIS1/2</b> 212121	20 off	–	  
	1	85	<b>FAZ-XIS1/6</b> 212122	–	–	
	1	85	<b>FAZ-XIS1/12</b> 212123	–	–	
	2	100	<b>FAZ-XIS2/4</b> 212124	10 off	2- and 4-pole version can also be used for FI switches	
	2	100	<b>FAZ-XIS2/6</b> 212125			
	2	100	<b>FAZ-XIS2/12</b> 212126			
	3	100	<b>FAZ-XIS3/6</b> 212127	–	–	
	3	100	<b>FAZ-XIS3/12</b> 212128	–	–	
	4	100	<b>FAZ-XIS4/8</b> 212129	5 off	2- and 4-pole version can also be used for FI switches	
	4	100	<b>FAZ-XIS4/12</b> 212130			
For miniature circuit-breakers <b>with</b> auxiliary contacts						
	1	85	<b>FAZ-XIS1/2-HI</b> 212131	20 off	–	  
	1	85	<b>FAZ-XIS1/6-HI</b> 212132	–	–	
	1	85	<b>FAZ-XIS1/9-HI</b> 212133	–	–	
	2	100	<b>FAZ-XIS2/4-HI</b> 212134	10 off	–	
	2	100	<b>FAZ-XIS2/6-HI</b> 212135			
	2	100	<b>FAZ-XIS2/10-HI</b> 212136			
	3	100	<b>FAZ-XIS3/6-HI</b> 212137	–	–	
	3	100	<b>FAZ-XIS3/12-HI</b> 212138	–	–	
	3	100	<b>FAZ-XIS31/6-HI</b> 212139	1 auxiliary contact per pole	–	
	3	100	<b>FAZ-XIS31/8-HI</b> 212140			
	3	100	<b>FAZ-XIS31/9-HI</b> 212141			

