


Spec Sheet

SMD Power Inductors for Industrial / Automotive Comfort and Safety Applications (NR series H type / V type / S type)

NRS4018T1R0NDGJV



Features

- Item Summary
1.0 μ H($\pm 30\%$), 4000mA, 3200mA
- Lifecycle Stage
Mass Production
- AEC-Q200 qualified
- Standard packaging quantity (minimum)
Taping 3500pcs

Products characteristics table


CaseSize (EIA/JIS)	~4018
Inductance	1.0 μ H($\pm 30\%$)
Inductance Measuring Frequency	100kHz
Rated Current -Saturation Current	4000mA
Rated Current -Temperature Rise Current	3200mA
DC Resistance (max)	0.0324 Ω
Avg. of DC.Resistance	0.027 Ω
Temperature Range	-40°C to 125°C
Self-resonant Frequency (min)	90MHz
RoHS Compliance	Yes
Halogen Free	Yes
Soldering Method	Reflow

External Dimensions

L	4mm ± 0.2
W	4mm ± 0.2
H	1.8mm max

Recommended Land Patterns

【推奨ランドパターン】 実装上の注意 ・実装状態を確認の上ご使用くださいようお願いいたします。 ・本製品のはんだ付けはリフローはんだ工法に限りま。
【Recommended Land Patterns】 Surface Mounting ・Mounting and soldering conditions should be checked beforehand. ・Applicable soldering process to these products is reflow soldering only.



SMD Power Inductors (NR series/NR series H type/S type/V type)			
Type	A	B	C
NR 4010, NRS4010,	1.2	2.8	3.7
NR 4012, NRS4012,			
NR 4018, NRS4018			

unit:mm

2014.01.23

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.
 TAIYO YUDEN reserves the right to make change to the Date at any time without notice.
 Before making final selection, please check product specification.