



## Material Safety Data Sheet

Copyright, 2011, 3M Company All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

### SECTION 1: PRODUCT AND COMPANY IDENTIFICATION

**PRODUCT NAME:** 3M™ Scotch-Weld™ High Performance Industrial Plastic Adhesive 4693H  
**MANUFACTURER:** 3M  
**DIVISION:** Industrial Adhesives and Tapes Division  
**ADDRESS:** 3M Center, St. Paul, MN 55144-1000

**EMERGENCY PHONE: 1-800-364-3577 or (651) 737-6501 (24 hours)**

**Issue Date:** 05/03/11  
**Supersedes Date:** 05/02/11

**Document Group:** 07-9492-5

**Product Use:**

Specific Use: Plastic Adhesive  
 Intended Use: Industrial use

### SECTION 2: INGREDIENTS

<u>Ingredient</u>	<u>C.A.S. No.</u>	<u>% by Wt</u>
CYCLOHEXANE	110-82-7	50 - 60
STYRENE-BUTADIENE POLYMER	9003-55-8	5 - 15
POLYTERPENE RESIN	31393-98-3	7 - 13
DIPENTENE POLYMER	9003-73-0	7 - 13
HYDROCARBON RESIN	100199-62-0	1 - 5
ACETONE	67-64-1	1 - 5
STABILIZER	2440-22-4	< 0.15

### SECTION 3: HAZARDS IDENTIFICATION

#### 3.1 EMERGENCY OVERVIEW

**Odor, Color, Grade:** colorless to light amber

**General Physical Form:** Liquid

**Immediate health, physical, and environmental hazards:** Closed containers exposed to heat from fire may build pressure and explode. Extremely flammable liquid and vapor. Vapors may travel long distances along the ground or floor to an ignition source and flash back. May cause allergic skin reaction. May cause target organ effects.

### 3.2 POTENTIAL HEALTH EFFECTS

**Eye Contact:**

Mild Eye Irritation: Signs/symptoms may include redness, pain, and tearing.

**Skin Contact:**

Moderate Skin Irritation: Signs/symptoms may include localized redness, swelling, itching, and dryness.

Prolonged or repeated exposure may cause:

Allergic Skin Reaction (non-photo induced): Signs/symptoms may include redness, swelling, blistering, and itching.

**Inhalation:**

Respiratory Tract Irritation: Signs/symptoms may include cough, sneezing, nasal discharge, headache, hoarseness, and nose and throat pain.

May be absorbed following inhalation and cause target organ effects.

**Ingestion:**

Gastrointestinal Irritation: Signs/symptoms may include abdominal pain, stomach upset, nausea, vomiting and diarrhea.

May be absorbed following ingestion and cause target organ effects.

**Target Organ Effects:**

Central Nervous System (CNS) Depression: Signs/symptoms may include headache, dizziness, drowsiness, incoordination, nausea, slowed reaction time, slurred speech, giddiness, and unconsciousness.

Prolonged or repeated exposure may cause:

Liver Effects: Signs/symptoms may include loss of appetite, weight loss, fatigue, weakness, abdominal tenderness and jaundice.

Kidney/Bladder Effects: Signs/symptoms may include changes in urine production, abdominal or lower back pain, increased protein in urine, increased blood urea nitrogen (BUN), blood in urine, and painful urination.

## SECTION 4: FIRST AID MEASURES

### 4.1 FIRST AID PROCEDURES

The following first aid recommendations are based on an assumption that appropriate personal and industrial hygiene practices are followed.

**Eye Contact:** Flush eyes with large amounts of water. If signs/symptoms persist, get medical attention.

**Skin Contact:** Remove contaminated clothing and shoes. Immediately flush skin with large amounts of water. Get medical attention. Wash contaminated clothing and clean shoes before reuse.

**Inhalation:** Remove person to fresh air. If signs/symptoms develop, get medical attention.

**If Swallowed:** Do not induce vomiting unless instructed to do so by medical personnel. Give victim two glasses of water. Never give anything by mouth to an unconscious person. Get medical attention.

## SECTION 5: FIRE FIGHTING MEASURES

### 5.1 FLAMMABLE PROPERTIES

**Autoignition temperature**

*No Data Available*

**Flash Point**

1 °F [*Test Method: Closed Cup*]

**Flammable Limits(LEL)**

1.35 % volume

**Flammable Limits(UEL)**

8.35 % volume

## 5.2 EXTINGUISHING MEDIA

Use fire extinguishers with class B extinguishing agents (e.g., dry chemical, carbon dioxide).

## 5.3 PROTECTION OF FIRE FIGHTERS

**Special Fire Fighting Procedures:** Water may not effectively extinguish fire; however, it should be used to keep fire-exposed containers and surfaces cool and prevent explosive rupture. Wear full protective equipment (Bunker Gear) and a self-contained breathing apparatus (SCBA).

**Unusual Fire and Explosion Hazards:** Closed containers exposed to heat from fire may build pressure and explode. Extremely flammable liquid and vapor. Vapors may travel long distances along the ground or floor to an ignition source and flash back.

**Note: See STABILITY AND REACTIVITY (SECTION 10) for hazardous combustion and thermal decomposition information.**

## SECTION 6: ACCIDENTAL RELEASE MEASURES

### 6.1. Personal precautions, protective equipment and emergency procedures

### 6.2. Environmental precautions

Place in a metal container approved for transportation by appropriate authorities.

### Clean-up methods

Refer to other sections of this MSDS for information regarding physical and health hazards, respiratory protection, ventilation, and personal protective equipment. Call 3M-HELPS line (1-800-364-3577) for more information on handling and managing the spill. Clean up residue with an appropriate solvent selected by a qualified and authorized person. Ventilate the area with fresh air. Read and follow safety precautions on the solvent label and MSDS.

**In the event of a release of this material, the user should determine if the release qualifies as reportable according to local, state, and federal regulations.**

## SECTION 7: HANDLING AND STORAGE

### 7.1 HANDLING

Do not eat, drink or smoke when using this product. Wash exposed areas thoroughly with soap and water. Keep away from heat, sparks, open flame, pilot lights and other sources of ignition. Ground containers securely when transferring contents. Wear low static or properly grounded shoes. Avoid breathing of vapors, mists or spray. Avoid static discharge. Avoid eye contact with vapors, mists, or spray. Keep out of the reach of children. Vapors may ignite explosively. May cause flash fire. Prevent build-up of vapors - open all windows and doors. Maintain vapor concentrations below recommended exposure limits. Use only with cross-ventilation. Without adequate ventilation, vapors may settle in low-lying areas. Keep away from heat, sparks, and open flame. Do not smoke or ignite matches, lighters, etc. For industrial or professional use only. Avoid contact with oxidizing agents. Use general dilution ventilation and/or local exhaust ventilation to control airborne exposures to below Occupational Exposure Limits. If ventilation is not adequate, use respiratory protection equipment.

### 7.2 STORAGE

Store away from acids. Store away from heat. Store out of direct sunlight. Keep container in well-ventilated area. Keep container tightly closed. Store away from oxidizing agents.

**SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION**

**8.1 ENGINEERING CONTROLS**

Provide appropriate local exhaust ventilation on open containers. Use general dilution ventilation and/or local exhaust ventilation to control airborne exposures to below Occupational Exposure Limits and/or control mist, vapor, or spray. If ventilation is not adequate, use respiratory protection equipment.

**8.2 PERSONAL PROTECTIVE EQUIPMENT (PPE)**

**8.2.1 Eye/Face Protection**

Avoid eye contact with vapors, mists, or spray.

The following eye protection(s) are recommended: Safety Glasses with side shields  
Indirect Vented Goggles

**8.2.2 Skin Protection**

Avoid skin contact.

Select and use gloves and/or protective clothing to prevent skin contact based on the results of an exposure assessment. Consult with your glove and/or protective clothing manufacturer for selection of appropriate compatible materials.

Gloves made from the following material(s) are recommended: Fluoroelastomer  
Polymer laminate

**8.2.3 Respiratory Protection**

Avoid breathing of vapors, mists or spray.

Select one of the following NIOSH approved respirators based on airborne concentration of contaminants and in accordance with OSHA regulations: Half facepiece or fullface air-purifying respirator with organic vapor cartridges

Select and use respiratory protection to prevent an inhalation exposure based on the results of an exposure assessment. Consult with your respirator manufacturer for selection of appropriate types of respirators.

**8.2.4 Prevention of Swallowing**

Do not eat, drink or smoke when using this product. Wash exposed areas thoroughly with soap and water.

**8.3 EXPOSURE GUIDELINES**

<u>Ingredient</u>	<u>Authority</u>	<u>Type</u>	<u>Limit</u>	<u>Additional Information</u>
ACETONE	ACGIH	TWA	500 ppm	
ACETONE	ACGIH	STEL	750 ppm	
ACETONE	OSHA	TWA	2400 mg/m3	
CYCLOHEXANE	ACGIH	TWA	100 ppm	
CYCLOHEXANE	OSHA	TWA	1050 mg/m3	

SOURCE OF EXPOSURE LIMIT DATA:

ACGIH: American Conference of Governmental Industrial Hygienists

CMRG: Chemical Manufacturer Recommended Guideline

OSHA: Occupational Safety and Health Administration

AIHA: American Industrial Hygiene Association Workplace Environmental Exposure Level (WEEL)

**SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES**

<b>Odor, Color, Grade:</b>	colorless to light amber
<b>General Physical Form:</b>	Liquid
<b>Autoignition temperature</b>	<i>No Data Available</i>
<b>Flash Point</b>	1 °F [ <i>Test Method:</i> Closed Cup]
<b>Flammable Limits(LEL)</b>	1.35 % volume
<b>Flammable Limits(UEL)</b>	8.35 % volume
<b>Boiling Point</b>	>=176 °F
<b>Density</b>	0.84 g/ml
<b>Vapor Density</b>	2.90 [ <i>Ref Std:</i> AIR=1]
<b>Vapor Pressure</b>	77 mmHg [ <i>@</i> 68 °F]
<b>Specific Gravity</b>	.84 [ <i>Ref Std:</i> WATER=1]
<b>pH</b>	<i>Not Applicable</i>
<b>Melting point</b>	<i>Not Applicable</i>
<b>Solubility in Water</b>	Slight (less than 10%)
<b>Evaporation rate</b>	>=2.00 [ <i>Ref Std:</i> WATER=1]
<b>Hazardous Air Pollutants</b>	<=0.0 lb HAPS/lb solids [ <i>Test Method:</i> Calculated]
<b>Hazardous Air Pollutants</b>	<=0 % weight [ <i>Test Method:</i> Calculated]
<b>Volatile Organic Compounds</b>	<=505 g/l [ <i>Details:</i> EU VOC content]
<b>Kow - Oct/Water partition coef</b>	<i>No Data Available</i>
<b>Percent volatile</b>	60 - 70 % weight
<b>VOC Less H2O &amp; Exempt Solvents</b>	<=492 g/l [ <i>Test Method:</i> calculated SCAQMD rule 443.1]
<b>VOC Less H2O &amp; Exempt Solvents</b>	<=4.11 lb/gal [ <i>Test Method:</i> calculated SCAQMD rule 443.1]
<b>VOC Less H2O &amp; Exempt Solvents</b>	<=56.1 % [ <i>Test Method:</i> calculated per CARB title 2]
<b>Viscosity</b>	2600 centipoise [ <i>@</i> 73.4 °F]
<b>Solids Content</b>	>=27.8 %

## SECTION 10: STABILITY AND REACTIVITY

**Stability:** Stable.

### Materials and Conditions to Avoid:

#### 10.1 Conditions to avoid

Heat  
Sparks and/or flames

#### 10.2 Materials to avoid

Strong oxidizing agents

**Hazardous Polymerization:** Hazardous polymerization will not occur.

### Hazardous Decomposition or By-Products

<u>Substance</u>	<u>Condition</u>
Aldehydes	During Combustion
Hydrocarbons	During Combustion
Carbon monoxide	During Combustion
Carbon dioxide	During Combustion
Ketones	During Combustion

## SECTION 11: TOXICOLOGICAL INFORMATION

Please contact the address listed on the first page of the MSDS for Toxicological Information on this material and/or its components.

## SECTION 12: ECOLOGICAL INFORMATION

### ECOTOXICOLOGICAL INFORMATION

Not determined.

### CHEMICAL FATE INFORMATION

Not determined.

## SECTION 13: DISPOSAL CONSIDERATIONS

**Waste Disposal Method:** Incinerate in a permitted hazardous waste incinerator. As a disposal alternative, dispose of waste product in a permitted hazardous waste facility.

**EPA Hazardous Waste Number (RCRA):** D001 (Ignitable)

Since regulations vary, consult applicable regulations or authorities before disposal.

## SECTION 14: TRANSPORT INFORMATION

**ID Number(s):**

62-4495-2631-8, 62-4495-2635-9

For Transport Information, please visit <http://3M.com/Transportinfo> or call 1-800-364-3577 or 651-737-6501.

## SECTION 15: REGULATORY INFORMATION

### US FEDERAL REGULATIONS

Contact 3M for more information.

**311/312 Hazard Categories:**

Fire Hazard - Yes Pressure Hazard - No Reactivity Hazard - No Immediate Hazard - Yes Delayed Hazard - Yes

**Section 313 Toxic Chemicals subject to the reporting requirements of that section and 40 CFR part 372 (EPCRA):**

<u>Ingredient</u>	<u>C.A.S. No</u>	<u>% by Wt</u>
CYCLOHEXANE	110-82-7	50 - 60

### STATE REGULATIONS

Contact 3M for more information.

### CHEMICAL INVENTORIES

The components of this product are in compliance with the chemical notification requirements of TSCA.

All applicable chemical ingredients in this material are listed on the European Inventory of Existing Chemical Substances (EINECS),

or are exempt polymers whose monomers are listed on EINECS. Contact 3M for more information.

## INTERNATIONAL REGULATIONS

Contact 3M for more information.

This MSDS has been prepared to meet the U.S. OSHA Hazard Communication Standard, 29 CFR 1910.1200.

## SECTION 16: OTHER INFORMATION

### NFPA Hazard Classification

Health: 2 Flammability: 3 Reactivity: 0 Special Hazards: None

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

### Revision Changes:

Section 1: Emergency phone information was deleted.

Company Logo was deleted.

Copyright was deleted.

Section 16: Disclaimer (second paragraph) was modified.

Section 16: Web address heading was deleted.

Section 8: Skin protection - recommended gloves information was modified.

Section 14: Transportation legal text was modified.

Section 15: Inventories information was modified.

Section 9: Vapor pressure value was modified.

Section 9: Boiling point information was modified.

Section 5: Flammable limits (UE) information was modified.

Section 5: Flammable limits (LEL) information was modified.

Section 9: Property description for optional properties was modified.

Section 8: Respiratory protection - recommended respirators guide was modified.

Section 1: Address line 1 was deleted.

Section 1: Address line 2 was deleted.

Section 9: Flammable limits (LEL) information was modified.

Section 9: Flammable limits (UEL) information was modified.

Section 2: Ingredient table was modified.

Section 6: 6.2. Environmental precautions heading was modified.

Section 6: 6.1. Personal precautions, protective equipment and emergency procedures heading was modified.

Section 16: Web address was added.

Section 1: Address was added.

Copyright was added.

Company logo was added.

Telephone header was added.

Company Telephone was added.

Section 1: Emergency phone information was added.

DISCLAIMER: The information in this Material Safety Data Sheet (MSDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a

particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the MSDS available directly from 3M

**3M USA MSDSs are available at [www.3M.com](http://www.3M.com)**





# Transport Information Document

**Date:** March 05, 2012

**3M ID Number:** 62-4495-2631-8

**Product Description:** 3M(TM) Scotch-Weld(TM) High Performance Industrial Plastic Adhesive 4693H Clear, 5 oz, 36 per case

**Transport Protective Service:** PROTECTIVE SERVICE NOT REQUIRED

**NMFC Item:** 004620

**NMFC Sub:** 06

**NMFC Class:** 060.0

**Flash Point (Closed-cup):** 1°F/-17°C

## UNITED STATES DEPARTMENT OF TRANSPORTATION - GROUND (U.S. DOT, 49 CFR)

CONSUMER COMMODITY, ORM-D OR LIMITED QUANTITY

## UNITED STATES DEPARTMENT OF TRANSPORTATION - VESSEL (U.S. DOT, 49 CFR)

UN1133, ADHESIVES, 3, II, LIMITED QUANTITY, -017C

## INTERNATIONAL AIR TRANSPORT ASSOCIATION (IATA)

UN1133, ADHESIVES, 3, II

## INTERNATIONAL MARITIME ORGANIZATION (IMO)

UN1133, ADHESIVES, 3, II, LIMITED QUANTITY, -017C

The classification is authorized by the Competent Authority of the United States of America and may not meet the requirements of other competent authorities.

These transportation classifications are provided as a customer service. AS THE SHIPPER YOU REMAIN RESPONSIBLE FOR COMPLYING WITH ALL THE APPLICABLE LAWS AND REGULATIONS, INCLUDING PROPER TRANSPORTATION CLASSIFICATION AND PACKAGING. 3M's transportation classifications are based on product formulations, packaging, 3M policies and 3M's understanding of applicable current regulations and is valid for the original 3M package only. 3M does not guarantee the accuracy of this classification information. This information applies only to transportation classification and NOT THE PACKAGING, LABELING, OR MARKING REQUIREMENTS. The original 3M package is certified for U.S. ground shipment only. If you are shipping by air or ocean, the package may not meet applicable regulatory requirements.

For Transport Information, please visit [3M.com/Transportinfo](http://3M.com/Transportinfo)

or call 1-800-364-3577 or 651-737-6501 for assistance.