


# Spec Sheet

SMD Power Inductors for Industrial / Automotive Comfort and Safety Applications (NR series H type / V type / S type)

## NRS6020TOR8NMGGV



### ■ Features

- Item Summary  
0.8  $\mu$ H( $\pm$ 30%), 6400mA, 4100mA
- Lifecycle Stage  
Mass Production
- AEC-Q200 qualified
- Standard packaging quantity (minimum)  
Taping 2500pcs

### ■ Products characteristics table

CaseSize (EIA/JIS)	-/6020
Inductance	0.8 $\mu$ H( $\pm$ 30%)
Inductance Measuring Frequency	100kHz
Rated Current -Saturation Current	6400mA
Rated Current -Temperature Rise Current	4100mA
DC Resistance (max)	0.024 $\Omega$
Avg. of DC.Resistance	0.02 $\Omega$
Temperature Range	-40°C to 125°C
Self-resonant Frequency (min)	110MHz
RoHS Compliance	Yes
Halogen Free	Yes
Soldering Method	Reflow


### ■ External Dimensions

L	6mm $\pm$ 0.2
W	6mm $\pm$ 0.2
H	2mm max

### ■ Recommended Land Patterns

【推奨ランドパターン】  
実装上の注意  
・実装状態を確認の上ご使用くださいようお願いいたします。  
・本製品のはんだ付けはリフローはんだ工法に限ります。

【Recommended Land Patterns】  
Surface Mounting  
・Mounting and soldering conditions should be checked beforehand.  
・Applicable soldering process to these products is reflow soldering only.



Type	A	B	C
NRS601.0			
NR 601.2, NRS601.2			
NRS601.4	1.6	4.7	5.7
NR 6020, NRS6020			
NR 6038, NRS6038			
NR 6045, NRS6045			

unit: mm

2014.01.23

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.  
TAIYO YUDEN reserves the right to make change to the Date at any time without notice.  
Before making final selection, please check product specification.