



Revision Number: 006.0

Issue date: 01/11/2012

1. PRODUCT AND COMPANY IDENTIFICATION

Product name:	LOCTITE® 242™ THREADLOCKER	IDH number:	135354
	MEDIUM STRENGTH		
Product type:	Anaerobic Sealant	Item number:	24221
		Region:	United States
Company address:	Contact information:		
Henkel Corporation	Telephone: 860.571.5100		
One Henkel Way	MEDICAL EMERGENCY Phone: Poison Control Center		
Rocky Hill, Connecticut 06067	1-877-671-4608 (toll free) or 1-303-592-1711		
	TRANSPORT EMERGENCY Phone: CHEMTREC		
	1-800-424-9300 (toll free) or 1-703-527-3887		
	Internet: www.henkelna.com		

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW

Physical state:	Liquid	HEALTH:	*2
Color:	Blue	FLAMMABILITY:	1
Odor:	Mild	PHYSICAL HAZARD:	1
		Personal Protection:	See MSDS Section 8

WARNING: CAUSES EYE IRRITATION.
MAY CAUSE SKIN IRRITATION.
MAY CAUSE ALLERGIC SKIN REACTION.
MAY CAUSE RESPIRATORY TRACT IRRITATION.

Relevant routes of exposure: Skin, Inhalation, Eyes

Potential Health Effects

Inhalation:	May cause respiratory tract irritation.
Skin contact:	May cause allergic skin reaction. May cause skin irritation.
Eye contact:	Contact with eyes will cause irritation.
Ingestion:	Not expected to be harmful by ingestion.

Existing conditions aggravated by exposure: Eye, skin, and respiratory disorders.

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

See Section 11 for additional toxicological information.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous components	CAS NUMBER	%
Polyglycol dimethacrylate	25852-47-5	60 - 100
Oleic acid 5.5EO	9004-96-0	10 - 30
Saccharin	81-07-2	1 - 5
Silica, amorphous, fumed, crystal-free	112945-52-5	1 - 5
Cumene hydroperoxide	80-15-9	1 - 5
Propanediol-1,2	57-55-6	1 - 5
Titanium dioxide	13463-67-7	0.1 - 1
Cumene	98-82-8	0.1 - 1

4. FIRST AID MEASURES

Inhalation:	Move to fresh air. If breathing is difficult, give oxygen. If breathing has stopped, give artificial respiration. Keep warm and quiet. Get medical attention.
Skin contact:	Wash with soap and water. Remove contaminated clothing and footwear. Wash clothing before reuse. If symptoms develop and persist, get medical attention.
Eye contact:	Flush with copious amounts of water, preferably, lukewarm water for at least 15 minutes, holding eyelids open all the time. Get medical attention.
Ingestion:	Do not induce vomiting. Keep individual calm. Get medical attention.

5. FIRE FIGHTING MEASURES

Flash point:	> 93.3 °C (> 199.94 °F) Tagliabue closed cup
Flame projection:	Not applicable
Autoignition temperature:	Not determined
Flammable/Explosive limits - lower:	2.6 % (propylene glycol)
Flammable/Explosive limits - upper:	12.5 % (propylene glycol)
Extinguishing media:	Foam, dry chemical or carbon dioxide.
Special firefighting procedures:	None
Unusual fire or explosion hazards:	None
Hazardous combustion products:	Oxides of carbon. Oxides of sulfur. Oxides of nitrogen. Irritating organic vapours.

6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

Environmental precautions:	Do not allow product to enter sewer or waterways.
Clean-up methods:	Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Store in a partly filled, closed container until disposal.

7. HANDLING AND STORAGE

Handling:	Prevent contact with eyes, skin and clothing. Do not breathe vapor and mist. Wash thoroughly after handling.
Storage:	For safe storage, store at or below 38 °C (100.4 °F) Keep in a cool, well ventilated area away from heat, sparks and open flame. Keep container tightly closed until ready for use.

For information on product shelf life contact Henkel Customer Service at (800) 243-4874.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous components	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Polyglycol dimethacrylate	None	None	None	None
Oleic acid 5.5EO	None	None	None	None
Saccharin	None	None	None	None
Silica, amorphous, fumed, crystal-free	10 mg/m3 TWA Inhalable dust. 3 mg/m3 TWA Respirable fraction.	20 MPPCF TWA 0.8 mg/m3 TWA	None	None
Cumene hydroperoxide	None	None	1 ppm (6 mg/m3) TWA (SKIN)	None
Propanediol-1,2	None	None	10 mg/m3 TWA Aerosol.	None
Titanium dioxide	10 mg/m3 TWA	15 mg/m3 TWA Total dust.	None	None
Cumene	50 ppm TWA	50 ppm (245 mg/m3) TWA (SKIN)	None	None

Engineering controls:

No specific ventilation requirements noted, but forced ventilation may still be required if concentrations exceed occupational exposure limits.

Respiratory protection:

Use NIOSH approved respirator if there is potential to exceed exposure limit(s).

Eye/face protection:

Safety goggles or safety glasses with side shields.

Skin protection:

Use impermeable gloves and protective clothing as necessary to prevent skin contact. Neoprene gloves. Butyl rubber gloves. Natural rubber gloves.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state:	Liquid
Color:	Blue
Odor:	Mild
Odor threshold:	Not available.
pH:	Not applicable
Vapor pressure:	< 5 mm hg (27 °C (80.6 °F))
Boiling point/range:	> 149 °C (> 300.2 °F)
Melting point/ range:	Not available.
Specific gravity:	1.1 at 23.9 °C (75.02 °F)
Vapor density:	Not available.
Flash point:	> 93.3 °C (> 199.94 °F) Tagliabue closed cup
Flame projection:	Not applicable
Flammable/Explosive limits - lower:	2.6 % (propylene glycol)
Flammable/Explosive limits - upper:	12.5 % (propylene glycol)
Autoignition temperature:	Not determined
Evaporation rate:	Not available.
Solubility in water:	Slight
Partition coefficient (n-octanol/water):	Not available.
VOC content:	4.48 %; 49.3 g/l EPA Method 24

10. STABILITY AND REACTIVITY

Stability:	Stable
Hazardous reactions:	Will not occur.
Hazardous decomposition products:	Oxides of carbon. Oxides of sulfur. Oxides of nitrogen. Irritating organic vapours.
Incompatible materials:	Strong oxidizing agents. Free radical initiators. Strong reducing agents. Alkalis. Oxygen scavengers. Other polymerization initiators. Copper. Iron. Zinc. Aluminum. Rust.
Conditions to avoid:	See "Handling and Storage" (Section 7) and "Incompatibility" (Section 10).

11. TOXICOLOGICAL INFORMATION

Acute oral product toxicity:	LD50 (rat) > 10,000 mg/kg
Acute dermal product toxicity:	LD50 (rabbit) > 5,000 mg/kg

Hazardous components	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Polyglycol dimethacrylate	No	No	No
Oleic acid 5.5EO	No	No	No
Saccharin	No	No	No
Silica, amorphous, fumed, crystal-free	No	No	No
Cumene hydroperoxide	No	No	No
Propanediol-1,2	No	No	No
Titanium dioxide	No	Group 2B	No
Cumene	No	Group 2B	No

Hazardous components	Health Effects/Target Organs
Polyglycol dimethacrylate	Irritant, Allergen
Oleic acid 5.5EO	Irritant
Saccharin	No Target Organs
Silica, amorphous, fumed, crystal-free	Nuisance dust
Cumene hydroperoxide	Allergen, Central nervous system, Corrosive, Irritant, Mutagen
Propanediol-1,2	Irritant
Titanium dioxide	Irritant, Respiratory, Some evidence of carcinogenicity
Cumene	Central nervous system, Irritant, Lung

12. ECOLOGICAL INFORMATION

Ecological information:	Not available.
--------------------------------	----------------

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Follow all local, state, federal and provincial regulations for disposal.

Hazardous waste number: Not a RCRA hazardous waste.

14. TRANSPORT INFORMATION

The shipping classifications in this sections are for non-bulk packaging only (unless otherwise specified). Shipping classification may be different for bulk packaging.

U.S. Department of Transportation Ground (49 CFR)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

International Air Transportation (ICAO/IATA)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

Water Transportation (IMO/IMDG)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

15. REGULATORY INFORMATION

United States Regulatory Information

TSCA 8 (b) Inventory Status: All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.

TSCA 12(b) Export Notification: None above reporting de minimus

CERCLA/SARA Section 302 EHS: None above reporting de minimus
CERCLA/SARA Section 311/312: Immediate Health, Delayed Health
CERCLA/SARA 313: This product contains the following toxic chemicals subject to the reporting requirements of section 313 of the Emergency Planning and Community Right-To-Know Act of 1986 (40 CFR 372). Cumene hydroperoxide (CAS# 80-15-9).

California Proposition 65: This product contains a chemical known in the State of California to cause cancer. This product contains a chemical known to the State of California to cause birth defects or other reproductive harm.

Canada Regulatory Information

CEPA DSL/NDL Status: All components are listed on or are exempt from listing on the Canadian Domestic Substances List.

WHMIS hazard class: D.2.A, D.2.B

16. OTHER INFORMATION

This material safety data sheet contains changes from the previous version in sections: 3, 8, 11

Prepared by: Kyra Kozak Woods, Manager, Regulatory Affairs

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.