

**RTV133
SILICONE SEALANT****1. CHEMICAL PRODUCT AND COMPANY IDENTIFICATION**

Manufactured By: Momentive performance material
260 Hudson River Rd
Waterford NY 12188

Revised: 09/24/2010
Preparer: PRODUCT STEWARDSHIP COMPLIANCE AND STANDARDS
CHEMTREC 1-800-424-9300

Chemical Family/Use: Sealant
Formula: Mixture

HMIS

Flammability: 1 Reactivity: 0 Health: 0

NFPA

Flammability: 1 Reactivity: 0 Health: 1

2. HAZARDS IDENTIFICATION**EMERGENCY OVERVIEW**

CAUTION! May cause skin, eye, and respiratory tract irritation. Attention: Not for injection into humans.

Form: Paste**Color:** black**Odor:** sweet**POTENTIAL HEALTH EFFECTS****INGESTION**

May cause stomach discomfort. Not an anticipated route of exposure.

SKIN

Uncured product contact will irritate lips, gums and tongue. Skin irritation is possible after contact with the uncured product.

INHALATION

Irritating to respiratory system. Applies in uncured state.

EYES

Eye irritation on contact with the uncured product.

MEDICAL CONDITIONS AGGRAVATED

None known.

SUBCHRONIC (TARGET ORGAN)

None known.

CHRONIC EFFECTS / CARCINOGENICITY

This product or one of its ingredients present at 0.1% or more is NOT listed as a carcinogen or

**RTV133
SILICONE SEALANT**

suspected carcinogen by NTP, IARC, or OSHA.

ROUTES OF EXPOSURE

Eyes; dermal

3. COMPOSITION/INFORMATION ON INGREDIENTS

<u>PRODUCT COMPOSITION</u>	<u>CAS REG NO.</u>	<u>WGT. %</u>
<u>A. HAZARDOUS</u>		
2-Propanol	67-63-0	0.1 - 1 %
Vinyltrimethoxysilane	2768-02-7	1 - 5 %
TITANIUM, BIS(ETHYL ACETOACETATO)-	27858-32-8	1 - 5 %
<u>B. NON-HAZARDOUS</u>		
Dimethylpolysiloxane	70131-67-8	30 - 60 %
QUARTZ	14808-60-7	10 - 30 %
Treated Silica	68937-51-9	10 - 30 %
VinylStopped Phenylmethyl Polymer	68951-96-2	5 - 10 %

4. FIRST AID MEASURES**INGESTION**

Do not induce vomiting. If victim is conscious, give 1-3 glasses of water to drink. Never give anything by mouth to an unconscious person. Get medical attention if irritation persists.

SKIN

To clean from skin, remove completely with a dry cloth or paper towel, before washing with detergent and water. If skin irritation persists, call a physician.

INHALATION

If inhaled, remove to fresh air. If not breathing give artificial respiration using a barrier device. If breathing is difficult give oxygen. Get medical attention.

EYES

In case of contact, immediately flush eyes with plenty of water for at least 15 minutes and get medical attention if irritation persists.

**RTV133
SILICONE SEALANT**

NOTE TO PHYSICIAN

Treatment is symptomatic and supportive.

5. FIRE-FIGHTING MEASURES

FLAMMABLE LIMITS IN AIR - LOWER (%): No data available.

FLAMMABLE LIMITS IN AIR - UPPER (%): No data available.

SENSITIVITY TO MECHANICAL IMPACT: No

SENSITIVITY TO STATIC DISCHARGE

Sensitivity to static discharge is not expected.

EXTINGUISHING MEDIA

All standard extinguishing agents are suitable.

SPECIAL FIRE FIGHTING PROCEDURES

Firefighters must wear NIOSH/MSHA approved positive pressure self-contained breathing apparatus with full face mask and full protective clothing.

6. ACCIDENTAL RELEASE MEASURES**ACTION TO BE TAKEN IF MATERIAL IS RELEASED OR SPILLED**

Wipe, scrape or soak up in an inert material and put in a container for disposal. Wear proper protective equipment as specified in the protective equipment section. Increase area ventilation.

7. HANDLING AND STORAGE**PRECAUTIONS TO BE TAKEN IN HANDLING AND STORAGE**

Keep container closed when not in use. Avoid contact with skin and eyes. Remove contact lenses before using sealant. Do not handle lenses until all sealant has been cleaned from the fingertips, nails and cuticles. Residual sealant may remain on fingers for several days and transfer to lenses and cause severe eye irritation. Product releases methanol during application and curing. Keep away from children.

STORAGE

Store away from heat, sources of ignition, and incompatibles. Keep container tightly closed.

**RTV133
SILICONE SEALANT****8. EXPOSURE CONTROLS/PERSONAL PROTECTION****ENGINEERING CONTROLS**

Eyewash stations; Showers; Ventilation and other forms of engineering controls are preferred for controlling exposures. Respiratory protection may be needed for non-routine or emergency situations.

RESPIRATORY PROTECTION

If exposure limits are exceeded or respiratory irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Supplied air respirators may be required for non-routine or emergency situations. Respiratory protection must be provided in accordance with OSHA regulations (see 29CFR 1910.134).

PROTECTIVE GLOVES

Rubber gloves

EYE AND FACE PROTECTION

Safety glasses

OTHER PROTECTIVE EQUIPMENT

Wear suitable protective clothing and eye/face protection.

Exposure Guidelines

Component	CAS RN	Source	Value
------------------	---------------	---------------	--------------

Absence of values indicates none found

PEL - OSHA Permissible Exposure Limit; TLV - ACGIH Threshold Limit Value; TWA - Time Weighted Average; INTL REL - Internal Recommended Exposure Limit

OSHA revoked the Final Rule Limits of January 19, 1989 in response to the 11th Circuit Court of Appeals decision (AFL-CIO v. OSHA) effective June 30, 1993. See 29 CFR 1910.1000 (58 FR 35338).

9. PHYSICAL AND CHEMICAL PROPERTIES

BOILING POINT - C & F:	No data available.
VAPOR DENSITY (AIR=1):	No data available.
PHYSICAL STATE:	Paste
ODOR:	sweet
COLOR:	black
SPECIFIC GRAVITY (WATER=1):	ca. 1.23
DENSITY:	ca. 1,230 g/cm ³
ACID / ALKALINITY (MEQ/G):	No data available.
pH:	No data available.
SOLUBILITY IN WATER (20 C):	insoluble
SOLUBILITY IN ORGANIC SOLVENT (STATE SOLVENT):	insoluble
VOLATILE ORGANIC CONTENT:	4.9 %(m)
VOC EXCL. H₂O & EXEMPTS (G/L):	60 g/l

**RTV133
SILICONE SEALANT**

10. STABILITY AND REACTIVITY**STABILITY**

Stable

HAZARDOUS POLYMERIZATION

Hazardous polymerisation does not occur.

HAZARDOUS THERMAL DECOMPOSITION / COMBUSTION PRODUCTS

Carbon dioxide (CO₂); Carbon monoxide; Methanol; Silicon dioxide.; formaldehyde; This product contains methylpolysiloxanes which can generate formaldehyde at approximately 300 degrees Fahrenheit (150°C) and above, in atmospheres which contain oxygen. Formaldehyde is a skin and respiratory sensitizer, eye and throat irritant, acute toxicant, and potential cancer hazard. A MSDS for formaldehyde is available from Momentive.

INCOMPATIBILITY (MATERIALS TO AVOID)

None known.

CONDITIONS TO AVOID

None known.

11. TOXICOLOGICAL INFORMATION**ACUTE ORAL**

Remarks: Unknown

ACUTE DERMAL

Remarks: Unknown

ACUTE INHALATION

Remarks: No data available.

OTHER

None.

SENSITIZATION

No data available.

SKIN IRRITATION

No data available.

EYE IRRITATION

No data available.

**RTV133
SILICONE SEALANT**

MUTAGENICITY

Unknown

12. ECOLOGICAL INFORMATION**ECOTOXICITY**

No data available.

DISTRIBUTION

No data available.

CHEMICAL FATE

No data available.

13. DISPOSAL CONSIDERATIONS**DISPOSAL METHOD**

Disposal should be made in accordance with federal, state and local regulations.

14. TRANSPORT INFORMATION**Further Information:**

This product is not regarded as dangerous goods according to the national and international regulations on the transport of dangerous goods.

15. REGULATORY INFORMATION**Inventories**

Australia Inventory of Chemical Substances (AICS)	y (positive listing)
EU list of existing chemical substances	y (positive listing)
Japan Inventory of Existing & New Chemical Substances (ENCS)	y (positive listing)
China Inventory of Existing Chemical Substances	y (positive listing)
Korea Existing Chemicals Inventory (KECI)	y (positive listing)
Canada DSL Inventory	y (positive listing)
Canada NDSL Inventory	n (Negative listing)

**RTV133
SILICONE SEALANT**

Philippines Inventory of Chemicals y (positive listing)
and Chemical Substances
(PICCS)

TSCA list y (positive listing) On TSCA Inventory
For inventories that are marked as quantity restricted or special cases, please contact Momentive.

US Regulatory Information

SARA (311,312) HAZARD CLASS
Acute Health Hazard

SARA (313) CHEMICALS

CALIFORNIA PROPOSITION 65

Warning! This product contains a chemical known to the State of California to cause cancer, birth defects or other reproductive harm.

Canadian Regulatory Information**WHMIS HAZARD CLASS**

D2B - Toxic Material Causing Other Toxic Effects

16. OTHER INFORMATION**OTHER**

These data are offered in good faith as typical values and not as product specifications. No warranty, either expressed or implied, is made. The recommended industrial hygiene and safe handling procedures are believed to be generally applicable. However, each user should review these recommendations in the specific context of the intended use and determine whether they are appropriate., C = ceiling limit NEGL = negligible EST = estimated NF = none found NA = not applicable UNKN = unknown NE = none established REC = recommended ND = none determined V = recommended by vendor SKN = skin TS = trade secret R = recommended MST = mist NT = not tested STEL = short term exposure limit ppm = parts per million ppb = parts per billion By-product= reaction by-product, TSCA inventory status not required under 40 CFR part 720.30(h-2).