

Revision Date: 03/27/2008

Issue date: 03/27/2008

1. CHEMICAL PRODUCT AND COMPANY IDENTIFICATION

Product name: C5-A® Copper Anti-Seize Stick
Product type: Lubricant
Company address:
 Henkel Corporation
 1001 Trout Brook Crossing
 Rocky Hill, Connecticut 06067

Item No. : 37229 / IDH No. 466863
Region: United States
Contact Information:
 Telephone: 860.571.5100
 Emergency telephone: 860.571.5100
 Internet: www.loctite.com

2. COMPOSITION/INFORMATION ON INGREDIENTS

<u>Hazardous components</u>	<u>%</u>	<u>ACGIH TLV</u>	<u>OSHA PEL</u>	<u>OTHER</u>
Distillates (petroleum), hydrotreated heavy naphthenic 64742-52-5	30-60	5 mg/m ³ TWA (mist) 10mg/m ³ STEL (mist)	5 mg/m ³ TWA (mist)	None
Copper 7440-50-8	10-30	0.2 mg/m ³ TWA 1 mg/m ³ TWA	0.1 mg/m ³ TWA fume 1 mg/m ³ TWA dusts and mists	None
Graphite 7782-42-5	10-30	2 mg/m ³ TWA all forms except graphite fibers	15 mg/m ³ (total), 5 mg/m ³ (respirable)	None
Distillates (petroleum), hydrotreated light naphthenic 64742-53-6	10-30	5 mg/m ³ TWA (mist) 10mg/m ³ STEL (mist)	5 mg/m ³ TWA (mist)	None
Silica, quartz 14808-60-7	1-5	0.025 mg/m ³ TWA respirable fraction	0.1mg/m ³ TWA (respirable)	None

3. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW

Physical state: Solid
Color: Copper
Odor: Mild petroleum

HMIS:

HEALTH: 1
FLAMMABILITY: 1
PHYSICAL HAZARD: 0
Personal Protection: See Section 8

CAUTION: MAY CAUSE EYE AND SKIN IRRITATION.

Relevant routes of exposure: Skin, Eyes

Potential Health Effects

Inhalation: This product has low volatility and is not expected to cause respiratory tract irritation during normal conditions of use. May cause respiratory tract irritation. Inhalation of copper fumes may result in metal fume fever. Symptoms include metallic taste, discoloration of skin or hair.

Skin contact: Prolonged or repeated contact may cause irritation.

Eye contact: Contact with eyes will cause irritation.

Ingestion: Ingestion may cause gastrointestinal irritation, nausea, vomiting and diarrhea. Principal hazard of ingestion is aspiration into the lungs and subsequent pneumonitis.

Existing conditions aggravated by exposure: Eye, skin, and respiratory disorders.

See Section 11 for additional toxicological information.

4. FIRST AID MEASURES

Inhalation:	Remove to fresh air. If discomfort persists seek medical attention.
Skin contact:	Wash with soap and water. Get medical attention if symptoms develop and persist.
Eye contact:	Immediately flush eyes with plenty of water for at least 15 minutes. Get medical attention.
Ingestion:	Do not induce vomiting. Aspiration may cause pulmonary edema and pneumonitis. Obtain medical attention.

5. FIRE-FIGHTING MEASURES

Flash point:	Not applicable Product is a solid. Burn Rate: Approx 14mm/2 minutes
Autoignition temperature:	Not determined
Flammable/Explosive limits-lower %:	Not determined
Flammable/Explosive limits-upper %:	Not determined
Extinguishing media:	Carbon dioxide (CO2). Dry chemical. Foam.
Special fire fighting procedures:	None
Unusual fire or explosion hazards:	None
Hazardous combustion products:	Oxides of carbon.

6. ACCIDENTAL RELEASE MEASURES

Environmental precautions:	No special environmental precautions required.
Clean-up methods:	Scrape up as much material as possible. Clean residue with soap and water. Dispose of in accordance with local and national regulations.

7. HANDLING AND STORAGE

Handling:	Keep container closed. Avoid contact with eyes, skin and clothing. Wash thoroughly after handling.
Storage:	Keep in a cool, well ventilated area.
Incompatible products:	Oxidizing agents.

For information on product shelf life contact Henkel Customer Service at (800) 243-4874.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Engineering controls:	Ensure adequate ventilation. Local exhaust ventilation is recommended when general ventilation is not sufficient to control airborne contamination below occupational exposure limits.
Respiratory protection:	Use NIOSH approved respirator if there is potential to exceed exposure limit(s). Observe OSHA regulations for respiratory use (29 CFR 1910.134).
Skin protection:	Cover as much of the exposed skin area as possible with appropriate clothing.
Eye/face protection:	Safety glasses with side-shields. Goggles.

See Section 2 for exposure limits.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state:	Solid
Color:	Copper

Item No. : 37229 / IDH No. 466863

Odor:	Mild petroleum
Vapor pressure:	Not determined
pH:	Not applicable
Boiling point/range:	Not available
Melting point/range:	Not available
Specific gravity:	1.18
Vapor density:	Not determined
Evaporation rate:	Not determined
Solubility in water:	Insoluble.
Partition coefficient (n-octanol/water):	Not determined
VOC content:	13.0%; 153 grams/liter

10. STABILITY AND REACTIVITY

Stability:	Stable at normal conditions
Hazardous polymerization:	Will not occur.
Hazardous decomposition products:	Oxides of carbon.
Incompatibility:	Oxidizing agents.
Conditions to avoid:	None known.

11. TOXICOLOGICAL INFORMATION

Carcinogen Status

Hazardous components	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen
Distillates (petroleum), hydrotreated heavy naphthenic 64742-52-5	No	No	No
Copper 7440-50-8	No	No	No
Graphite 7782-42-5	No	No	No
Distillates (petroleum), hydrotreated light naphthenic 64742-53-6	No	Group 1	Yes
Silica, quartz 14808-60-7	Known Carcinogen	Group 1	Yes

Literature Referenced Target Organ & Other Health Effects

Hazardous components	Health Effects/Target Organs
Distillates (petroleum), hydrotreated heavy naphthenic 64742-52-5	Irritant
Copper 7440-50-8	Skin, Sensory, Mutagen, Liver, Kidney, Irritant, Immune system, Gastrointestinal, Central nervous system, Blood, Allergen, Developmental
Graphite 7782-42-5	Lung
Distillates (petroleum), hydrotreated light naphthenic 64742-53-6	Irritant
Silica, quartz 14808-60-7	Some evidence of carcinogenicity, Lung, Immune system

12. ECOLOGICAL INFORMATION

Ecological information:	Not available
--------------------------------	---------------

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Dispose of according to Federal, State and local governmental regulations.

EPA hazardous waste number: Not a RCRA hazardous waste.

14. TRANSPORT INFORMATION

The shipping classifications in this section are for non-bulk packaging only (unless otherwise specified). Shipping classification may be different for bulk packaging.

U.S. Department of Transportation Ground (49 CFR):

Proper shipping name:	Unrestricted
Hazard class or division:	None
Identification number:	None
Packing group:	None
DOT reportable quantity (lbs):	Copper (CAS# 7440-50-8) is reportable at 5000 pounds (2700kg)
Marine pollutant:	Copper

International Air Transportation (ICAO/IATA):

Proper shipping name:	Unrestricted
Hazard class or division:	None
Identification number:	None
Packing group:	None

WaterTransportation (IMO/IMDG):

Proper shipping name:	Environmentally hazardous substances, solid, n.o.s. (Copper)
Hazard class or division:	9
Identification number:	UN3077
Packing group:	III
Marine pollutant:	Copper

15. REGULATORY INFORMATION

United States Regulatory Information

TSCA 8 (b) Inventory Status: All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.
TSCA 12 (b) Export Notification: None.

CERCLA/SARA Section 302 EHS: None.
CERCLA/SARA Section 311/312: Immediate Health Hazard
CERCLA/SARA 313: This product contains the following toxic chemicals subject to the reporting requirements of section 313 of the Emergency Planning and Community Right-To-Know Act of 1986 (40 CFR 372). Copper (CAS# 7440-50-8).

California Proposition 65: No California Proposition 65 listed chemicals are known to be present.

Canada Regulatory Information

CEPA DSL/NDSL Status: All components are listed on or are exempt from listing on the Domestic Substances List.
WHMIS hazard class: D.2.A, D.2.B

16. OTHER INFORMATION

This material safety data sheet contains changes from the previous version in sections: New Material Safety Data Sheet format.

Prepared by: C.J. Michaels, Manager, Regulatory Affairs

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation does not assume responsibility for any results obtained by persons over whose methods Henkel Corporation has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any of Henkel Corporation's products. In light of the foregoing, Henkel Corporation specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation further disclaims any liability for consequential or incidental damages of any kind, including lost profits.