



## Material Safety Data Sheet

Copyright, 2011, 3M Company All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

### SECTION 1: PRODUCT AND COMPANY IDENTIFICATION

**PRODUCT NAME:** 3M FireBarrier(TM) Sealant IC 15 WB+  
**MANUFACTURER:** 3M  
**DIVISION:** Building & Commercial Services Division  
**ADDRESS:** 3M Center, St. Paul, MN 55144-1000

**EMERGENCY PHONE: 1-800-364-3577 or (651) 737-6501 (24 hours)**

**Issue Date:** 09/16/11  
**Supersedes Date:** 12/02/10

**Document Group:** 19-9776-6

**Product Use:**

Specific Use: Fire Barrier Sealant  
 Intended Use: Sealant

### SECTION 2: INGREDIENTS

<u>Ingredient</u>	<u>C.A.S. No.</u>	<u>% by Wt</u>
Calcium Carbonate	1317-65-3	30 - 60
Polymer	Trade Secret	10 - 30
Water	7732-18-5	10 - 30
Sodium Silicate	1344-09-8	3 - 7
ZINC BORATE 2335	138265-88-0	3 - 7
Fiberglass	65997-17-3	0.5 - 1.5
Sodium Nonylphenyl Polyethoxy Ether Sulfate	9014-90-8	0.1 - 1.0
Polyoxyethylene Monoctylphenyl Ether	9036-19-5	0.1 - 1.0
Quartz Silica	14808-60-7	< 0.5

### SECTION 3: HAZARDS IDENTIFICATION

#### 3.1 EMERGENCY OVERVIEW

**Specific Physical Form:** Paste  
**Odor, Color, Grade:** Light yellow viscous paste with a mild odor  
**General Physical Form:** Solid

**Immediate health, physical, and environmental hazards:** Contains a chemical or chemicals which can cause cancer.

### 3.2 POTENTIAL HEALTH EFFECTS

**Eye Contact:**

Moderate Eye Irritation: Signs/symptoms may include redness, swelling, pain, tearing, and blurred or hazy vision.

**Skin Contact:**

Moderate Skin Irritation: Signs/symptoms may include localized redness, swelling, itching, and dryness.

**Inhalation:**

Respiratory Tract Irritation: Signs/symptoms may include cough, sneezing, nasal discharge, headache, hoarseness, and nose and throat pain.

**Ingestion:**

Gastrointestinal Irritation: Signs/symptoms may include abdominal pain, stomach upset, nausea, vomiting and diarrhea.

**Carcinogenicity:**

Contains a chemical or chemicals which can cause cancer.

This product contains quartz silica. Lung cancer and silicosis have been associated with exposure to quartz silica. No user exposure to quartz silica from this product is anticipated during normal intended use. Warnings are provided to comply with US federal and state regulations.

<u>Ingredient</u>	<u>C.A.S. No.</u>	<u>Class Description</u>	<u>Regulation</u>
Quartz Silica	14808-60-7	Grp. 1: Carcinogenic to humans	International Agency for Research on Cancer

## SECTION 4: FIRST AID MEASURES

### 4.1 FIRST AID PROCEDURES

The following first aid recommendations are based on an assumption that appropriate personal and industrial hygiene practices are followed.

**Eye Contact:** Immediately flush eyes with large amounts of water for at least 15 minutes. Get immediate medical attention.

**Skin Contact:** Remove contaminated clothing and shoes. Immediately flush skin with large amounts of water. Get medical attention. Wash contaminated clothing and clean shoes before reuse.

**Inhalation:** Remove person to fresh air. If signs/symptoms develop, get medical attention.

**If Swallowed:** Do not induce vomiting unless instructed to do so by medical personnel. Give victim two glasses of water. Never give anything by mouth to an unconscious person. Get medical attention.

## SECTION 5: FIRE FIGHTING MEASURES

### 5.1 FLAMMABLE PROPERTIES

<b>Autoignition temperature</b>	<i>No Data Available</i>
<b>Flash Point</b>	<i>Not Applicable</i>
<b>Flammable Limits(LEL)</b>	<i>Not Applicable</i>
<b>Flammable Limits(UEL)</b>	<i>Not Applicable</i>
<b>OSHA Flammability Classification:</b>	<i>Not Applicable</i>

## 5.2 EXTINGUISHING MEDIA

Non-combustible. Choose material suitable for surrounding fire.

## 5.3 PROTECTION OF FIRE FIGHTERS

**Special Fire Fighting Procedures:** Wear full protective equipment (Bunker Gear) and a self-contained breathing apparatus (SCBA).

**Unusual Fire and Explosion Hazards:** No unusual fire or explosion hazards are anticipated.

**Note:** See STABILITY AND REACTIVITY (SECTION 10) for hazardous combustion and thermal decomposition information.

## SECTION 6: ACCIDENTAL RELEASE MEASURES

### 6.1. Personal precautions, protective equipment and emergency procedures

Evacuate unprotected and untrained personnel from hazard area. The spill should be cleaned up by qualified personnel. Ventilate the area with fresh air.

### 6.2. Environmental precautions

Place in a closed container approved for transportation by appropriate authorities. Dispose of collected material as soon as possible.

### Clean-up methods

Observe precautions from other sections. Call 3M- HELPS line (1-800-364-3577) for more information on handling and managing the spill. Collect as much of the spilled material as possible. Clean up residue.

**In the event of a release of this material, the user should determine if the release qualifies as reportable according to local, state, and federal regulations.**

## SECTION 7: HANDLING AND STORAGE

### 7.1 HANDLING

Do not eat, drink or smoke when using this product. Wash exposed areas thoroughly with soap and water. For industrial or professional use only. Avoid eye contact with dust or airborne particles. Avoid skin contact.

### 7.2 STORAGE

Store under normal warehouse conditions.

## SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

### 8.1 ENGINEERING CONTROLS

Use in a well-ventilated area.

### 8.2 PERSONAL PROTECTIVE EQUIPMENT (PPE)

#### 8.2.1 Eye/Face Protection

Avoid eye contact.

The following eye protection(s) are recommended: Safety Glasses with side shields  
Indirect Vented Goggles

**8.2.2 Skin Protection**

Avoid skin contact.

Select and use gloves and/or protective clothing to prevent skin contact based on the results of an exposure assessment. Consult with your glove and/or protective clothing manufacturer for selection of appropriate compatible materials.

Gloves made from the following material(s) are recommended: Butyl Rubber  
Nitrile Rubber

**8.2.3 Respiratory Protection**

Under normal use conditions, airborne exposures are not expected to be significant enough to require respiratory protection.

**8.2.4 Prevention of Swallowing**

Do not eat, drink or smoke when using this product. Wash exposed areas thoroughly with soap and water.

**8.3 EXPOSURE GUIDELINES**

<u>Ingredient</u>	<u>Authority</u>	<u>Type</u>	<u>Limit</u>	<u>Additional Information</u>
Calcium Carbonate	OSHA	TWA, respirable fraction	5 mg/m3	
Calcium Carbonate	OSHA	TWA, as total dust	15 mg/m3	
Fiberglass	Manufacturer determined	TWA, as dust	10 mg/m3	
POLYETHYLENE GLYCOLS	AIHA	TWA, as particulate	10 mg/m3	
Quartz Silica	ACGIH	TWA, respirable fraction	0.025 mg/m3	
Quartz Silica	OSHA	TWA concentration, respirable	0.1 mg/m3	
Quartz Silica	OSHA	TWA concentration, as total dust	0.3 mg/m3	

SOURCE OF EXPOSURE LIMIT DATA:

ACGIH: American Conference of Governmental Industrial Hygienists

CMRG: Chemical Manufacturer Recommended Guideline

OSHA: Occupational Safety and Health Administration

AIHA: American Industrial Hygiene Association Workplace Environmental Exposure Level (WEEL)

**SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES**

<b>Specific Physical Form:</b>	Paste
<b>Odor, Color, Grade:</b>	Light yellow viscous paste with a mild odor
<b>General Physical Form:</b>	Solid
<b>Autoignition temperature</b>	<i>No Data Available</i>
<b>Flash Point</b>	<i>Not Applicable</i>
<b>Flammable Limits(LEL)</b>	<i>Not Applicable</i>
<b>Flammable Limits(UEL)</b>	<i>Not Applicable</i>
<b>Boiling Point</b>	<i>Not Applicable</i>

Specific Gravity	1.4 [Ref Std: WATER=1]
Melting point	No Data Available
Solubility in Water	Moderate
Volatile Organic Compounds	< 2 g/l
VOC Less H2O & Exempt Solvents	< 2 g/l

## SECTION 10: STABILITY AND REACTIVITY

**Stability:** Stable.

**Materials and Conditions to Avoid:**

### 10.1 Conditions to avoid

None known

### 10.2 Materials to avoid

None known

**Hazardous Polymerization:** Hazardous polymerization will not occur.

## Hazardous Decomposition or By-Products

<u>Substance</u>	<u>Condition</u>
Carbon monoxide	Not Specified
Carbon dioxide	Not Specified

## SECTION 11: TOXICOLOGICAL INFORMATION

Please contact the address listed on the first page of the MSDS for Toxicological Information on this material and/or its components.

## SECTION 12: ECOLOGICAL INFORMATION

### ECOTOXICOLOGICAL INFORMATION

Not determined.

### CHEMICAL FATE INFORMATION

Not determined.

## SECTION 13: DISPOSAL CONSIDERATIONS

**Waste Disposal Method:** For quantities <100 lbs. (50kg): dispose of waste product in a sanitary landfill. For larger quantities: Dispose of waste product in a facility permitted to accept chemical waste.

**EPA Hazardous Waste Number (RCRA):** Not regulated

Since regulations vary, consult applicable regulations or authorities before disposal.

## SECTION 14: TRANSPORT INFORMATION

### ID Number(s):

42-0016-4768-6, 42-0016-4769-4, 42-0016-4770-2, 98-0400-5509-1, 98-0400-5510-9, 98-0400-5511-7, 98-0400-5512-5

For Transport Information, please visit <http://3M.com/Transportinfo> or call 1-800-364-3577 or 651-737-6501.

## SECTION 15: REGULATORY INFORMATION

### US FEDERAL REGULATIONS

Contact 3M for more information.

Section 313 Toxic Chemicals subject to the reporting requirements of that section and 40 CFR part 372 (EPCRA):

<u>Ingredient</u>	<u>C.A.S. No</u>	<u>% by Wt</u>
ZINC BORATE 2335 (ZINC COMPOUNDS)	138265-88-0	3 - 7

### STATE REGULATIONS

Contact 3M for more information.

### CHEMICAL INVENTORIES

The components of this product are in compliance with the chemical notification requirements of TSCA.

All applicable chemical ingredients in this material are listed on the European Inventory of Existing Chemical Substances (EINECS), or are exempt polymers whose monomers are listed on EINECS. Contact 3M for more information.

### INTERNATIONAL REGULATIONS

Contact 3M for more information.

This MSDS has been prepared to meet the U.S. OSHA Hazard Communication Standard, 29 CFR 1910.1200.

## SECTION 16: OTHER INFORMATION

### NFPA Hazard Classification

Health: 2 Flammability: 0 Reactivity: 0 Special Hazards: None

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

### Revision Changes:

Section 1: Product use information was modified.  
Section 16: Disclaimer (second paragraph) was modified.  
Section 10: Hazardous decomposition or by-products table was modified.  
Section 15: Inventories information was modified.  
Section 9: Boiling point information was modified.  
Section 5: Flammable limits (UE) information was modified.  
Section 5: Flammable limits (LEL) information was modified.

Section 5: Autoignition temperature information was modified.  
Section 5: Flash point information was modified.  
Section 9: Property description for optional properties was modified.  
Section 9: Specific gravity information was modified.  
Section 9: Melting point information was modified.  
Section 9: Solubility in water text was modified.  
Section 9: Flash point information was modified.  
Section 9: Flammable limits (LEL) information was modified.  
Section 9: Flammable limits (UEL) information was modified.  
Section 9: Autoignition temperature information was modified.  
Section 2: Ingredient table was modified.  
Section 15: EPCRA 313 information was modified.  
Section 8: Exposure guidelines ingredient information was modified.  
Section 3: Carcinogenicity table was modified.  
Section 6: 6.2. Environmental precautions heading was modified.  
Section 6: 6.1. Personal precautions, protective equipment and emergency procedures heading was modified.  
Section 16: Web address was added.  
Section 1: Address was added.  
Copyright was added.  
Company logo was added.  
Telephone header was added.  
Company Telephone was added.  
Section 1: Emergency phone information was added.  
Section 1: Emergency phone information was deleted.  
Company Logo was deleted.  
Copyright was deleted.  
Section 16: Web address heading was deleted.  
Section 1: Address line 1 was deleted.  
Section 1: Address line 2 was deleted.

DISCLAIMER: The information in this Material Safety Data Sheet (MSDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the MSDS available directly from 3M

**3M USA MSDSs are available at [www.3M.com](http://www.3M.com)**



## Transport Information Document

**Date:** January 30, 2012

**3M ID Number:** 98-0400-5509-1

**Product Description:** 3M(TM) Fire Barrier Sealant IC 15WB+, 10.1 fl. oz., Cartridge, 12/case

**Transport Protective Service:** PROTECTIVE SERVICE NOT REQUIRED

**NMFC Item:** 050155

**NMFC Sub:** 03

**NMFC Class:** 070.0

**Flash Point (Closed-cup):** No Flash Point

### UNITED STATES DEPARTMENT OF TRANSPORTATION - GROUND (U.S. DOT, 49 CFR)

NOT REGULATED

### UNITED STATES DEPARTMENT OF TRANSPORTATION - VESSEL (U.S. DOT, 49 CFR)

NOT REGULATED

### INTERNATIONAL AIR TRANSPORT ASSOCIATION (IATA)

NOT REGULATED

### INTERNATIONAL MARITIME ORGANIZATION (IMO)

NOT REGULATED

The classification is authorized by the Competent Authority of the United States of America and may not meet the requirements of other competent authorities.

These transportation classifications are provided as a customer service. AS THE SHIPPER YOU REMAIN RESPONSIBLE FOR COMPLYING WITH ALL THE APPLICABLE LAWS AND REGULATIONS, INCLUDING PROPER TRANSPORTATION CLASSIFICATION AND PACKAGING. 3M's transportation classifications are based on product formulations, packaging, 3M policies and 3M's understanding of applicable current regulations and is valid for the original 3M package only. 3M does not guarantee the accuracy of this classification information. This information applies only to transportation classification and NOT THE PACKAGING, LABELING, OR MARKING REQUIREMENTS. The original 3M package is certified for U.S. ground shipment only. If you are shipping by air or ocean, the package may not meet applicable regulatory requirements.

For Transport Information, please visit [3M.com/Transportinfo](http://3M.com/Transportinfo)

or call 1-800-364-3577 or 651-737-6501 for assistance.