

SECTION 1: CHEMICAL PRODUCT AND COMPANY IDENTIFICATION

Company Address:

8125 Cobb Center Drive
Kennesaw, GA 30152

Product Information: 800-TECH-401
Customer Service: 800-645-5244

Emergency: (Chemtrec) 800-424-9300
Revision Date: February 10, 2010

Product Identification

FLUX-OFF® HEAVY DUTY

Product Code: ES1631, ES831B, ES1631C, ES831BC

SECTION 2: COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS#	Wt. % Range
Fluorinated Hydrocarbon (HFE)	163702-07-6/163702-08-7	30.0-50.0
trans-1,2-Dichloroethylene	156-60-5	30.0-50.0
Ethanol	64-17-5	1.0-5.0
1,1,1,2-Tetrafluoroethane	811-97-2	10.0-40.0
Carbon Dioxide	124-38-9	1.0-5.0

SECTION 3: HAZARD IDENTIFICATION

Emergency Overview: Clear, colorless liquid with faint ethereal odor. This product is nonflammable. Liquid may irritate eyes and skin under repeated or prolonged exposure. Breathing high concentrations of product vapor may produce dizziness and nausea.

Potential Health Effects:

Eyes: Liquid, aerosols and vapors of this product may be irritating and can cause pain, tearing, reddening and swelling accompanied by a stinging sensation.

Skin: Prolonged contact can cause skin irritation, including redness, burning, drying and/or cracking of skin..

Ingestion: May be harmful if swallowed. Swallowing this material may result in nausea, vomiting and weakness followed by central nervous system depression.

Inhalation: Can be harmful if inhaled. High concentrations of vapors in immediate area can cause dizziness, nausea, vomiting, unconsciousness and death.

SECTION 4: FIRST AID MEASURES

Eyes: Immediately flush with plenty of water. After initial flushing, remove any contact lenses and continue flushing for at least 15 minutes. Have eyes examined and tested by medical personnel if irritation develops or persists.

Skin: Wash skin with soap and water. Remove contaminated clothing. Get medical attention if irritation develops or persist. Wash clothing before reuse.

Ingestion: If swallowed, do not induce vomiting. If conscious, give 2 glasses of water. Never give anything by mouth to an unconscious person. Keep head below knees to minimize chance of aspirating material into the lungs. Get medical attention immediately.

Inhalation: Remove to fresh air. If breathing is difficult, give oxygen. Get medical attention.

SECTION 5: FIRE FIGHTING MEASURES

Flash Point: None to boiling(TCC)

Extinguishing Media: Use water spray or fog, CO2, dry chemical or water stream when fighting fires involving this material.

Fire Fighting Instructions: As in any fire, wear self-contained breathing apparatus (pressure-demand, MSHA/NIOSH approved or equivalent) and full protective gear.

SECTION 6: ACCIDENTAL RELEASE MEASURES

Spills: Shut off leak if possible and safe to do so. Absorb spill with inert material (e.g. dry sand or earth), then place in a chemical waste container for proper disposal. Do not flush to sewer. Avoid runoff into storm sewers and ditches which lead to waterways.

SECTION 7: HANDLING AND STORAGE

Avoid prolonged or repeated contact with eyes, skin, and clothing. Wash hands before eating. Use with adequate ventilation. Avoid breathing product vapor or mist. Do not reuse this container. Store in a cool dry place away from heat, sparks and flame. Keep container closed when not in use. Do not store in direct sunlight.

KEEP OUT OF REACH OF CHILDREN.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

Exposure Guidelines:

CHEMICAL NAME	ACGIH TLV	OSHA PEL	OTHER
Fluorinated Hydrocarbon(HFE)	NE	NE	750 ppm (3M)
trans-1,2-Dichloroethylene	200 ppm	200 ppm	
1,1,1,2-Tetrafluoroethane	NE	NE	1000 ppm (Dupont)
Ethanol	1,000ppm	1000ppm	

NE = Not Established

NFPA and HMIS Codes:

	NFPA	HMIS
Health	1	1
Flammability	1	1
Reactivity	1	1
Personal Protection	-	B

Work/Hygienic Practices: Good general ventilation should be sufficient to control airborne levels. If vapor concentration exceeds TLV, use NIOSH approved organic vapor cartridge respirator. Wear safety glasses with side shields (or goggles) and rubber or other chemically resistant gloves.

