



MATERIAL SAFETY DATA SHEET

GENERAL INFORMATION

PRODUCT NAME OR NUMBER (as it appears on label) ClearGlide™ Wire Pulling Lubricant		CATALOG NUMBER All "31" Series
MANUFACTURER'S NAME IDEAL INDUSTRIES, INC.		EMERGENCY TELEPHONE NO. (815) 895-5181
ADDRESS (Number, Street, City, State, Zip Code) Becker Place, Sycamore, IL 60178		
HAZARDOUS MATERIAL DESCRIPTION, PROPER SHIPPING NAME, HAZARD CLASS, HAZARD CLASS, HAZARD ID NO. (49 CFR 172.101) None		
CHEMICAL DESCRIPTION Polymer-based Mixture	FORMULA Proprietary	

SECTION I - INGREDIENTS

CAS REGISTRY NO.	%W	CHEMICAL NAME(S)*	Listed as a carcinogen in NTP, IARC or OSHA 1910(z) (specify)
7732-18-5	<98	Water	No
6440-58-0	<1	DMDM Hydantoin	No
9038-95-3	<5	Oxirane, Methyl-, Polymer With Oxirane, Monobutyl Ether	No
9003-11-6	<1	Amino-Methyl-Propanol	No
25322-68-3	<1	Polyethylene Glycol	No
9003-01-4	<1	Carbomer Thickener	No
68037-64-9	<1	Silicone Glycol Blend	No

SECTION II - PHYSICAL DATA

BOILING POINT 212 °F °C	SPECIFIC GRAVITY (H ₂ O=1) 1.09	PERCENT VOLATILE BY VOLUME (%) <98
SOLUBILITY IN WATER Infinite	pH = 7.0 - 8.0	PERCENT SOLID BY WEIGHT (%) ~5
APPEARANCE AND ODOR Clear, colorless gel, slight odor	IS MATERIAL: LIQUID SOLID GEL GAS PASTE	

SECTION III - FIRE AND EXPLOSION HAZARD DATA

FLASH POINT None	method used C.O.C	FLAMMABLE LIMITS	LEL None	UEL None
EXTINGUISHING MEDIA Use extinguishing media suitable for surrounding materials.				
SPECIAL FIRE FIGHTING PROCEDURES None				
UNUSUAL FIRE AND EXPLOSION HAZARDS None				

* None of the chemical raw materials contained in this formulation are considered hazardous under the Federal Hazards Communication Standard 29 C. F. R 1910.1200

SECTION IV - HEALTH HAZARD INFORMATION

EFFECTS OF OVEREXPOSURE - Conditions to Avoid	
	None normally expected. Upon prolonged contact, may cause temporary eye discomfort.
THRESHOLD LIMIT VALUE	
N F	
PRIMARY ROUTES OF ENTRY Inhalation <input type="checkbox"/> Skin Contact <input checked="" type="checkbox"/> Other (specify)	
EMERGENCY FIRST AID PROCEDURES	
SKIN CONTACT:	Wash with soap and water for 15 minutes
EYE CONTACT:	Flush with water for 15 minutes Inhalation - Move to fresh air
INGESTION:	
Administer water or milk. Consult physician or local poison control center	

SECTION V - REACTIVITY DATA

STABILITY	UNSTABLE		CONDITIONS TO AVOID Avoid prolonged storage at temperatures exceeding 190 F.
	STABLE	X	
INCOMPATIBILITY (materials to avoid)			
Avoid strong oxidizers and nitrites			
HAZARDOUS DECOMPOSITION PRODUCTS:			
Oxides of carbon, nitrogen and silicone			
HAZARDOUS POLYMERIZATION	MAY OCCUR		CONDITIONS TO AVOID None
	WILL NOT OCCUR	X	

SECTION VI - SPILL AND LEAK PROCEDURES

STEPS TO BE TAKEN IF MATERIAL IS RELEASED OR SPILLED	
	Wipe up, shovel or vacuum spilled material. Clean up spills immediately as they can be dangerously slippery.
WASTE DISPOSAL METHOD	
Comply with Federal, state or local regulations for solid landfill	
CERCLA (Superfund) REPORTABLE QUANTITY (in lbs)	
N/A	
RCRA HAZARDOUS WASTE NO. (40CFR 261.33)	
N/A	
VOLATILE ORGANIC COMPOUND (VOC) (as packaged, minus water)	
N/A	
^a Theoretical _____ lb/gal	N/A
^b Analytical _____ lb/gal	N/A

SECTION VII - PERSONAL PROTECTION INFORMATION

RESPIRATORY PROTECTION (specify type)			
None normally required			
VENTILATION	LOCAL EXHAUST (Specify Rate)	None	SPECIAL
	MECHANICAL (General) (Specify Rate)	Recommended in closed areas.	OTHER
		None	
PROTECTIVE GLOVES (specify type)		EYE PROTECTION (specify type)	
None normally		Safety glasses or splash goggles.	
OTHER PROTECTIVE EQUIPMENT			
Eye fountain in work area is recommended			

SECTION VIII - SPECIAL PRECAUTIONS

PRECAUTIONS TO BE TAKEN IN HANDLING AND STORING	
	Store at temperatures between 40 - 180 F. Avoid freezing.
OTHER PRECAUTIONS	
Keep away from children, infants and pets.	

SECTION IX - ADDITIONAL INFORMATION

N/A = Not Applicable, N.E. = None Established	
THIS MATERIAL SAFETY DATA SHEET PREPARED BY:	
NAME	James R. MacMurdo
TITLE	Director, Corporate Quality Assurance
DATE	03/10/2006
SIGNATURE 	