



Revision Number: 002.2

Issue date: 03/26/2012

**1. PRODUCT AND COMPANY IDENTIFICATION**

<b>Product name:</b>	<b>Super Lube(R) Synthetic-Based Lubricant with PTFE</b>	<b>IDH number:</b>	209807
<b>Product type:</b>	Lubricant Lubricant	<b>Item number:</b>	82328
<b>Company address:</b>	Henkel Corporation One Henkel Way Rocky Hill, Connecticut 06067	<b>Region:</b>	United States
		<b>Contact information:</b>	Telephone: 860.571.5100 MEDICAL EMERGENCY Phone: Poison Control Center 1-877-671-4608 (toll free) or 1-303-592-1711 TRANSPORT EMERGENCY Phone: CHEMTREC 1-800-424-9300 (toll free) or 1-703-527-3887 Internet: www.henkelna.com

**2. HAZARDS IDENTIFICATION**

**EMERGENCY OVERVIEW**

<b>Physical state:</b>	paste	<b>HEALTH:</b>	1
<b>Color:</b>	white	<b>FLAMMABILITY:</b>	1
<b>Odor:</b>	None	<b>PHYSICAL HAZARD:</b>	0
		<b>Personal Protection:</b>	See MSDS Section 8

**CAUTION:** MAY CAUSE EYE, SKIN AND RESPIRATORY TRACT IRRITATION.

**Relevant routes of exposure:** Skin, Inhalation, Eyes

**Potential Health Effects**

**Inhalation:** May cause respiratory tract irritation. Excessive inhalation of this material causes headache, dizziness, nausea and incoordination.

**Skin contact:** May cause skin irritation. Solvent action can dry and defat the skin, causing the skin to crack, leading to dermatitis.

**Eye contact:** Vapors may irritate eyes. Contact with eyes will cause irritation.

**Ingestion:** Not a likely route of entry. May be harmful if swallowed.

**Existing conditions aggravated by exposure:** Eye, skin, and respiratory disorders.

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

See Section 11 for additional toxicological information.

**3. COMPOSITION / INFORMATION ON INGREDIENTS**

Hazardous components	CAS NUMBER	%
1-Decene, homopolymer, hydrogenated	68037-01-4	60 - 100
White mineral oil (petroleum), highly refined	8042-47-5	10 - 30
Amorphous fumed silica	68611-44-9	1 - 5
Ethene, tetrafluoro-, homopolymer	9002-84-0	1 - 5
2,2'-Thiodiethylene bis(3-(3,5-di-tert-butyl-4-hydroxyphenyl)propionate)	41484-35-9	1 - 5
Polypropyleneglycol	25322-69-4	0.1 - 1
1-Propene,-2-Methyl-, homopolymer	9003-27-4	0.1 - 1

#### 4. FIRST AID MEASURES

<b>Inhalation:</b>	Move to fresh air. If symptoms persist, seek medical advice.
<b>Skin contact:</b>	Wipe off with paper towel or cloth. Wash with soap and water. If adverse health effects develop seek medical attention.
<b>Eye contact:</b>	Immediately flush eyes with plenty of water for at least 15 minutes. Get medical attention.
<b>Ingestion:</b>	Do not induce vomiting. Keep individual calm. Never give anything by mouth to an unconscious person. Get medical attention.

#### 5. FIRE FIGHTING MEASURES

<b>Flash point:</b>	> 93 °C (> 199.4 °F) Tagliabue closed cup
<b>Autoignition temperature:</b>	Not available.
<b>Flammable/Explosive limits - lower:</b>	Not available.
<b>Flammable/Explosive limits - upper:</b>	Not available.
<b>Extinguishing media:</b>	Water spray (fog), foam, dry chemical or carbon dioxide.
<b>Special firefighting procedures:</b>	Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.
<b>Unusual fire or explosion hazards:</b>	None
<b>Hazardous combustion products:</b>	Oxides of carbon. Irritating organic fragments.

#### 6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

<b>Environmental precautions:</b>	Do not allow product to enter sewer or waterways.
<b>Clean-up methods:</b>	Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Keep in suitable and closed containers for disposal.

#### 7. HANDLING AND STORAGE

<b>Handling:</b>	Avoid contact with eyes, skin and clothing. Avoid breathing vapors or mists of this product. Do not taste or swallow.
<b>Storage:</b>	Keep in a cool, well ventilated area away from heat, sparks and open flame. Keep container tightly closed until ready for use. Do not puncture, incinerate, or expose to temperatures above 48.9 °C (120 °F).

For information on product shelf life contact Henkel Customer Service at (800) 243-4874.

#### 8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous components	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
1-Decene, homopolymer, hydrogenated	5 mg/m3 TWA mist 10 mg/m3 STEL mist	5 mg/m3 TWA mist	None	None
White mineral oil (petroleum), highly refined	5 mg/m3 TWA Inhalable fraction.	5 mg/m3 TWA mist 5 mg/m3 TWA Mist.	None	None
Amorphous fumed silica	None	None	None	None
Ethene, tetrafluoro-, homopolymer	None	None	None	10 mg/m3 TWA Total dust. 5 mg/m3 TWA Respirable fraction.
2,2'-Thiodiethylene bis(3-(3,5-di-tert-butyl-4-hydroxyphenyl)propionate)	None	None	None	None
Polypropyleneglycol	None	None	10 mg/m3 TWA Aerosol.	None
1-Propene,-2-Methyl-, homopolymer	None	None	None	None

**Engineering controls:**

Handle in accordance with good industrial hygiene and safety practice In case of insufficient ventilation, wear suitable respiratory equipment.

**Respiratory protection:**

Use NIOSH approved respirator if there is potential to exceed exposure limit(s).

**Eye/face protection:**

Safety goggles or safety glasses with side shields.

**Skin protection:**

Use impermeable gloves and protective clothing as necessary to prevent skin contact.

## 9. PHYSICAL AND CHEMICAL PROPERTIES

<b>Physical state:</b>	paste
<b>Color:</b>	white
<b>Odor:</b>	None
<b>Odor threshold:</b>	Not available.
<b>pH:</b>	Not available.
<b>Vapor pressure:</b>	Not available.
<b>Boiling point/range:</b>	Not available.
<b>Melting point/ range:</b>	Not available.
<b>Vapor density:</b>	Not available.
<b>Flash point:</b>	> 93 °C (> 199.4 °F) Tagliabue closed cup
<b>Flammable/Explosive limits - lower:</b>	Not available.
<b>Flammable/Explosive limits - upper:</b>	Not available.
<b>Autoignition temperature:</b>	Not available.
<b>Evaporation rate:</b>	Not available.
<b>Solubility in water:</b>	Not available.
<b>Partition coefficient (n-octanol/water):</b>	Not available.
<b>VOC content:</b>	66.56 % EPA Method 24

## 10. STABILITY AND REACTIVITY

<b>Stability:</b>	Stable
<b>Hazardous reactions:</b>	Will not occur.
<b>Hazardous decomposition products:</b>	Oxides of carbon. Irritating organic fragments.
<b>Incompatible materials:</b>	Strong oxidizing agents. Acids and bases. Avoid contact with flammable materials.
<b>Conditions to avoid:</b>	Keep away from heat, ignition sources and incompatible materials.

## 11. TOXICOLOGICAL INFORMATION

Hazardous components	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
1-Decene, homopolymer, hydrogenated	No	No	No
White mineral oil (petroleum), highly refined	No	No	No
Amorphous fumed silica	No	No	No
Ethene, tetrafluoro-, homopolymer	No	No	No
2,2'-Thiodiethylene bis(3-(3,5-di-tert-butyl-4-hydroxyphenyl)propionate)	No	No	No
Polypropyleneglycol	No	No	No
1-Propene,-2-Methyl-, homopolymer	No	No	No

Hazardous components	Health Effects/Target Organs
1-Decene, homopolymer, hydrogenated	No Target Organs
White mineral oil (petroleum), highly refined	Irritant
Amorphous fumed silica	No Target Organs
Ethene, tetrafluoro-, homopolymer	No Target Organs
2,2'-Thiodiethylene bis(3-(3,5-di-tert-butyl-4-hydroxyphenyl)propionate)	No Target Organs
Polypropyleneglycol	Allergen, Cardiac, Central nervous system, Irritant
1-Propene,-2-Methyl-, homopolymer	No Target Organs

## 12. ECOLOGICAL INFORMATION

**Ecological information:** Do not empty into drains / surface water / ground water.

## 13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

**Recommended method of disposal:** Follow all local, state, federal and provincial regulations for disposal.

**Hazardous waste number:** Not a RCRA hazardous waste.

## 14. TRANSPORT INFORMATION

### U.S. Department of Transportation Ground (49 CFR)

**Proper shipping name:** Not regulated  
**Hazard class or division:** None  
**Identification number:** None  
**Packing group:** None

### International Air Transportation (ICAO/IATA)

**Proper shipping name:** Not regulated  
**Hazard class or division:** None  
**Identification number:** None  
**Packing group:** None

### Water Transportation (IMO/IMDG)

**Proper shipping name:** Not regulated  
**Hazard class or division:** None  
**Identification number:** None  
**Packing group:** None

## 15. REGULATORY INFORMATION

### United States Regulatory Information

**TSCA 8 (b) Inventory Status:** All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.

**TSCA 12(b) Export Notification:** None above reporting de minimus

**CERCLA/SARA Section 302 EHS:** None above reporting de minimus  
**CERCLA/SARA Section 311/312:** Immediate Health  
**CERCLA/SARA 313:** This product contains the following toxic chemicals subject to the reporting requirements of section 313 of the Emergency Planning and Community Right-To-Know Act of 1986 (40 CFR 372). Barium sulfonate (CAS# 61790-48-5).

**California Proposition 65:** No California Proposition 65 listed chemicals are known to be present.

**Canada Regulatory Information**

**CEPA DSL/NDSL Status:** All components are listed on or are exempt from listing on the Canadian Domestic Substances List.  
**WHMIS hazard class:** D.2.B

**16. OTHER INFORMATION**

**This material safety data sheet contains changes from the previous version in sections:** New Material Safety Data Sheet format.

**Prepared by:** Lou Fabrizio, Regulatory Affairs Specialist

**DISCLAIMER:** The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.