# 200 V, 4 A Schottky Fast Soft-Recovery Power Rectifier

# **SMC Power Surface Mount Package**

## Features

- Lower Forward Voltage than any Ultrafast Rectifier: V<sub>F</sub> < 0.61 V at 150°C</li>
- Fast Switching Speed: Reverse Recovery Time  $(t_{RR}) < 35$  ns
- Soft Recovery Characteristics: Softness Factor  $(t_b/t_a) \ge 1$
- Highly Stable Over Temperature
- AEC-Q101 Qualified and PPAP Capable
- NRVB Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements
- These are Pb-Free Packages\*

#### Benefits

- Significantly Reduced EMI
- Eliminates the Need of Snubber Circuits
- Low Switching and Heat Losses
- Improved Thermal Management

#### Applications

- Engine and Convenience Control Systems
- Motor Controls
- Battery Chargers and Switching Power Supplies

#### **Mechanical Characteristics**

- Small Compact Surface Mount Package with J-Bend Leads
- Rectangular Package for Automated Handling
- Weight: 217 mg (Approximately)
- Finish: All External Surfaces Corrosion Resistant and Terminal Leads are Readily Solderable
- Lead and Mounting Surface Temperature for Soldering Purposes: 260°C Maximum for 10 Seconds
- ESD Ratings:
  - ♦ Machine Model = A
  - Human Body Model = 1C
- Polarity: Notch in Plastic Body Indicates Cathode Lead



## **ON Semiconductor®**

http://onsemi.com

## SCHOTTKY RECTIFIER 4 AMPS, 200 VOLTS



CASE 403 PLASTIC



## MARKING DIAGRAM



B421	= Specific Device Code
А	= Assembly Location
Y	= Year
WW	= Work Week
_	Dh. Free Deelvere

= Pb-Free Package

(Note: Microdot may be in either location)

#### **ORDERING INFORMATION**

Device	Package	Shipping <sup>†</sup>		
MBRS4201T3G	SMC (Pb-Free)	2,500 / Tape & Reel		
NRVBS4201T3G	SMC (Pb-Free)	2,500 / Tape & Reel		

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

#### MAXIMUM RATINGS

Characteristic	Symbol	Value	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	V <sub>RRM</sub> V <sub>RWM</sub> V <sub>R</sub>	200	V
Average Rectified Forward Current (Rated $V_R$ , $T_L = 70^{\circ}$ C)	I <sub>F(AV)</sub>	4	A
Nonrepetitive Peak Surge Current (Surge Applied at Rated Load Conditions Halfwave, Single Phase, 60 Hz)	I <sub>FSM</sub>	100	A
Operating Junction Temperature	TJ	-55 to +150	°C


Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.


#### THERMAL CHARACTERISTICS

Characteristic	Symbol	Value	Unit
Thermal Resistance, Junction-to-Lead	$R_{ hetaJL}$	11	°C/W

### **ELECTRICAL CHARACTERISTICS**

Characteristic	Symbol	Value	Unit
Maximum Instantaneous Forward Voltage $(I_F = 4 \text{ A}, T_J = 25^{\circ}\text{C})$ $(I_F = 4 \text{ A}, T_J = 150^{\circ}\text{C})$	V <sub>F</sub>	0.86 0.61	V
Maximum Instantaneous Reverse Current (Rated $V_R$ ) (Rated DC Voltage, $T_J = 25^{\circ}$ C) (Rated DC Voltage, $T_J = 150^{\circ}$ C)	Ι <sub>R</sub>	1.0 5.0	mA mA
Maximum Reverse Recovery Time (I <sub>F</sub> = 1.0 A, di/dt = 100 A/μs, V <sub>R</sub> = 30 V)	t <sub>rr</sub>	35	ns










Figure 8. Reverse Recovery Time\* (t<sub>RR</sub>) at 125°C

#### PACKAGE DIMENSIONS

SMC CASE 403-03 **ISSUE E** 







NOTES:

DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982. CONTROLLING DIMENSION: INCH. 1. 2.


D DIMENSION SHALL BE MEASURED WITHIN DIMENSION P.
4. 403-01 THRU -02 OBSOLETE, NEW STANDARD 403-03.

	MILLIMETERS			INCHES		
DIM	MIN	NOM	MAX	MIN	NOM	MAX
Α	1.90	2.13	2.41	0.075	0.084	0.095
A1	0.05	0.10	0.15	0.002	0.004	0.006
b	2.92	3.00	3.07	0.115	0.118	0.121
С	0.15	0.23	0.30	0.006	0.009	0.012
D	5.59	5.84	6.10	0.220	0.230	0.240
Е	6.60	6.86	7.11	0.260	0.270	0.280
HE	7.75	7.94	8.13	0.305	0.313	0.320
Г	0.76	1.02	1.27	0.030	0.040	0.050
L1	0.51 REF			0.020 REF		





#### SOLDERING FOOTPRINT\*



\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and 💷 are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILC does not convey any license under its patent rights or the rights of others. SCILC products are not designed, intended, or authorized for use a components in systems intended for surgical implant into the body, or other applications. intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

#### PUBLICATION ORDERING INFORMATION

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support:

Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative