

**SECTION 1: CHEMICAL PRODUCT AND COMPANY IDENTIFICATION****Company Address:**8125 Cobb Center Drive  
Kennesaw, GA 30152Product Information: 800-TECH-401  
Customer Service: 800-645-5244Emergency: (Chemtrec) 800-424-9300  
Revision Date: February 17, 2010**Product Identification****ELECTRO-WASH ® CZ (Liquid)****Product Code: ES7101, ES7105, ES7155, ES7108L, ES7101C, ES7105C, ES7108LC****SECTION 2: COMPOSITION/INFORMATION ON INGREDIENTS**

Chemical Name	CAS#	Wt. % Range
Cirozane™	Mixture	45-80.0
trans-1,2-dichloroethylene	156-60-5	10-50.0
Methylcyclohexane	108-87-2	1.0-10.0
Methanol	67-56-1	1.0-3.0

**SECTION 3: HAZARD IDENTIFICATION****Emergency Overview:** Clear, colorless liquid with faint ethereal odor. This product is nonflammable. Liquid may irritate eyes and skin under repeated or prolonged exposure. Breathing high concentrations of product vapor may produce dizziness and nausea.**Potential Health Effects:****Eyes:** Liquid, aerosols and vapors of this product may be irritating and can cause pain, tearing, reddening and swelling accompanied by a stinging sensation.**Skin:** Prolonged contact can cause skin irritation.**Ingestion:** May be harmful if swallowed. Swallowing this material may result in nausea, vomiting and weakness followed by central nervous system depression.**Inhalation:** Can be harmful if inhaled. High concentrations of vapors in immediate area can cause dizziness, nausea and vomiting.**SECTION 4: FIRST AID MEASURES****Eyes:** Immediately flush with plenty of water. After initial flushing, remove any contact lenses and continue flushing for at least 15 minutes. Have eyes examined and tested by medical personnel if irritation develops or persists.**Skin:** Wash skin with soap and water. Remove contaminated clothing. Get medical attention if irritation develops or persist. Wash clothing before reuse.**Ingestion:** If swallowed, do not induce vomiting. If conscious, give 2 glasses of water. Never give anything by mouth to an unconscious person. Keep head below knees to minimize chance of aspirating material into the lungs. Get medical attention immediately.**Inhalation:** Remove to fresh air. If breathing is difficult, give oxygen. Get medical attention.**SECTION 5: FIRE FIGHTING MEASURES****Flash Point:** None to boiling (TCC)**Extinguishing Media:** Use water spray or fog, CO<sub>2</sub>, dry chemical or water stream when fighting fires involving this material.**Fire Fighting Instructions:** As in any fire, wear self-contained breathing apparatus (pressure-demand, MSHA/NIOSH approved or equivalent) and full protective gear.**SECTION 6: ACCIDENTAL RELEASE MEASURES****Spills:** Shut off leak if possible and safe to do so. Absorb spill with inert material (e.g. dry sand or earth), then place in a chemical waste container for proper disposal. Do not flush to sewer. Avoid runoff into storm sewers and ditches which lead to waterways.**SECTION 7: HANDLING AND STORAGE**

Avoid prolonged or repeated contact with eyes, skin, and clothing. Wash hands before eating. Use with adequate ventilation. Avoid breathing product vapor or mist. Do not reuse this container. Store in a cool dry place away from heat, sparks and flame. Keep container closed when not in use. Do not store in direct sunlight.

**KEEP OUT OF REACH OF CHILDREN.****SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION****Exposure Guidelines:**

CHEMICAL NAME	ACGIH TLV	OSHA PEL	OTHER
Cirozane™	NE	NE	750 ppm*
trans-1,2-dichloroethylene	200 ppm	200 ppm	
Methylcyclohexane	400 ppm	500 ppm	
Methanol	200 ppm	200 ppm	

NE = None Established

\* = Chemtronics Recommended Threshold Limit Value

**Work/Hygienic Practices:** Good general ventilation should be sufficient to control airborne levels. If vapor concentration exceeds TLV, use NIOSH approved organic vapor cartridge respirator. Wear safety glasses with side shields (or goggles) and rubber or other chemically resistant gloves when handling this material.**NFPA and HMIS Codes:**

	NFPA	HMIS
Health	1	1
Flammability	0	0
Reactivity	1	1
Personal Protection	-	B

**SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES****Physical State:** Clear, colorless liquid**Odor:** Ethereal Odor**pH:** NA**Vapor Pressure:** 220 mmHg@ 70 F**Percent Volatile:** 100%**Boiling Point:** 90°F (32C) initial**Solubility in Water:** Negligible**Specific Gravity:** 1.33  
(Water =1)**Evaporation Rate:** >1  
(Butyl acetate=1)**Viscosity:** NA

**SECTION 10: STABILITY AND REACTIVITY**

Stability - This product is stable.

Conditions to Avoid: Steam, oxidizers, elevated temperatures. Keep away from elevated temperatures. Do not spray near open flames, red hot surfaces or other sources of ignition.

Incompatibility: Do not mix with chemically active metals such as potassium, magnesium, zinc and powdered aluminum, strong base, caustic soda, caustic potash or oxidizing.

Products of Decomposition: Thermal decomposition may release carbon monoxide, carbon dioxide, hydrogen chloride and hydrogen fluoride.

Hazardous Polymerization: Will not occur

Conditions to Avoid: Finely divided active metals, alkali and alkaline earth metals

**SECTION 11: TOXICOLOGICAL INFORMATION**Inhalation:

Methylcyclohexane	LC50/mouse	41,500 mg/m <sup>3</sup> /2 hrs
Methanol	LC50 rats	64,000ppm/4hrs
trans-1,2-dichloroethylene	LC50 rats	24,100 ppm/4hrs

Ingestion:

Methanol	LD50 rats	5,628 mg/kg
Methylcyclohexane	LD50 Mouse	2,250 mg/kg
trans-1,2-dichloroethylene	LD50 rats	>5,000 mg/kg

Skin

Methanol	20mg/24H	MLD
Methylcyclohexane	LD50 rabbit	86,700 mg/kg
trans-1,2-dichloroethylene	LD50 rabbit	>5,000 mg/kg

Eye:

Methanol	40 mg	MOD
trans-1,2-dichloroethylene		MOD-SEV

Cancer Information: No ingredients listed as human carcinogens by NTP or IARC

Reproductive effects: none    Teratogenic effects: none    Mutagenic effects: none

**SECTION 12: ECOLOGICAL INFORMATION**

Avoid runoff into storm sewers and ditches which lead to waterways. Water runoff can cause environmental damage.

**REPORTING**

US regulations require reporting spills of this material that could reach any surface waters. The toll free number for the US Coast Guard National Response Center is: **1-800-424-8802**

**SECTION 13: DISPOSAL CONSIDERATIONS**

Dispose of in accordance with all federal, state and local regulations. Water runoff can cause environmental damage.

**SECTION 14: TRANSPORTATION INFORMATION**

<u>Air and Ground:</u>	Proper
	Shipping Name
	Cleaning Compound
	Not Regulated

**SECTION 15: REGULATORY INFORMATION****SECTION 313 SUPPLIER NOTIFICATION**

This product contains the following toxic chemicals subject to the reporting requirements of Section 313 of the Emergency Planning and Community Right-To-Know Act of 1986 (40 CFR 372).

Methanol	CAS #67-56-1	1.0-3.0%
----------	--------------	----------

This information should be included on all MSDSs copied and distributed for this material.

**TOXIC SUBSTANCES CONTROL ACT (TSCA)**

All ingredients of this product are listed on the TSCA Inventory.

WHMIS: Class D2B

This product has been classified according to the hazard criteria of the CPR and the MSDS contains all of the information required by the CPR.

**SECTION 16: OTHER INFORMATION**

Normal ventilation for standard manufacturing practices is usually adequate. Local exhaust should be used when large amounts are released.

To the best of our knowledge, the information contained herein is accurate. However, all materials may present unknown hazards and should be used with caution. In particular, improper use of our products and their inappropriate combination with other products and substances may produce harmful results which cannot be anticipated. Final determination of the suitability of any material is the sole responsibility of the user. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that may exist.