



Revision Number: 003.1

Issue date: 02/27/2013

1. PRODUCT AND COMPANY IDENTIFICATION

Product name: Silver Grade Anti-Seize Lubricant
Product type: Lubricant
Company address: Henkel Corporation, One Henkel Way, Rocky Hill, Connecticut 06067
IDH number: 235005
Item number: 76764
Region: United States
Contact information: Telephone: 860.571.5100
 MEDICAL EMERGENCY Phone: Poison Control Center 1-877-671-4608 (toll free) or 1-303-592-1711
 TRANSPORT EMERGENCY Phone: CHEMTREC 1-800-424-9300 (toll free) or 1-703-527-3887
 Internet: www.henkelna.com

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW

Physical state: paste
Color: silver
Odor: Hydrocarbon-like
HEALTH: *1
FLAMMABILITY: 1
PHYSICAL HAZARD: 0
Personal Protection: See MSDS Section 8
WARNING: CAUSES EYE, SKIN AND RESPIRATORY TRACT IRRITATION.

Relevant routes of exposure: Skin, Inhalation, Eyes

Potential Health Effects

Inhalation: Moderate respiratory tract irritation.
Skin contact: Moderate skin irritation.
Eye contact: Moderate eye irritation.
Ingestion: Principal hazard of ingestion is aspiration into the lungs and subsequent pneumonitis. Ingestion may cause gastrointestinal irritation, nausea, vomiting and diarrhea.

Existing conditions aggravated by exposure: Eye, skin, and respiratory disorders.

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

See Section 11 for additional toxicological information.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous components	CAS NUMBER	%
Distillates (petroleum), hydrotreated heavy naphthenic	64742-52-5	10 - 30
Graphite	7782-42-5	10 - 30
Calcium oxide	1305-78-8	10 - 30
Mineral oil light naphthenic hydrotreat. <3% DMSO	64742-53-6	10 - 30
Aluminum not powder, dust or fume	7429-90-5	5 - 10
Distillates (petroleum), straight-run middle	64741-44-2	1 - 5
Quartz (SiO2)	14808-60-7	0.1 - 1

4. FIRST AID MEASURES

Inhalation: Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:	If symptoms develop and persist, get medical attention. Wash with soap and water.
Eye contact:	Immediately flush eyes with plenty of water for at least 15 minutes. Get medical attention.
Ingestion:	Do not induce vomiting. Get immediate medical attention.

5. FIRE FIGHTING MEASURES

Flash point:	> 93 °C (> 199.4 °F)
Autoignition temperature:	Not determined
Flammable/Explosive limits - lower:	Not available.
Flammable/Explosive limits - upper:	Not available.
Extinguishing media:	Dry chemical. Carbon dioxide. foam
Special firefighting procedures:	None
Unusual fire or explosion hazards:	None
Hazardous combustion products:	Oxides of carbon. Oxides of nitrogen.

6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

Environmental precautions:	Prevent further leakage or spillage if safe to do so.
Clean-up methods:	Store in a partly filled, closed container until disposal. Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Remove all sources of ignition.

7. HANDLING AND STORAGE

Handling:	Keep away from heat, spark and flame. Avoid skin and eye contact.
Storage:	Keep in a cool, well ventilated area.

For information on product shelf life contact Henkel Customer Service at (800) 243-4874.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous components	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Distillates (petroleum), hydrotreated heavy naphthenic	5 mg/m3 TWA mist 10 mg/m3 STEL mist	5 mg/m3 TWA mist 500 ppm (2,000 mg/m3) TWA 5 mg/m3 TWA Mist.	None	None
Graphite	2 mg/m3 TWA Respirable fraction.	15 mg/m3 TWA Total dust. 5 mg/m3 TWA Respirable fraction. 15 MPPCF TWA	None	None
Calcium oxide	2 mg/m3 TWA	5 mg/m3 TWA	None	None
Mineral oil light naphthenic hydrotreat. <3% DMSO	5 mg/m3 TWA Inhalable fraction.	500 ppm (2,000 mg/m3) TWA 5 mg/m3 TWA Mist.	None	None
Aluminum not powder, dust or fume	1 mg/m3 TWA Respirable fraction.	5 mg/m3 TWA (as Al) Respirable dust. 15 mg/m3 TWA (as Al) Total dust.	None	None
Distillates (petroleum), straight-run middle	5 mg/m3 TWA mist 10 mg/m3 STEL mist	5 mg/m3 TWA mist	None	None
Quartz (SiO2)	0.025 mg/m3 TWA Respirable fraction.	2.4 MPPCF TWA Respirable. 0.1 mg/m3 TWA Respirable. 0.3 mg/m3 TWA Total dust.	None	None

Engineering controls:

Use local ventilation if general ventilation is insufficient to maintain vapor concentration below established exposure limits.

Respiratory protection:

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

Eye/face protection:

Safety goggles or safety glasses with side shields.

Skin protection:

Neoprene or oil resistant gloves.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state:	paste
Color:	silver
Odor:	Hydrocarbon-like
Odor threshold:	Not available.
pH:	Not applicable
Vapor pressure:	< 5 mm hg
Boiling point/range:	Not available.
Melting point/ range:	Not available.
Specific gravity:	1.25
Vapor density:	Not available.
Flash point:	> 93 °C (> 199.4 °F)
Flammable/Explosive limits - lower:	Not available.
Flammable/Explosive limits - upper:	Not available.
Autoignition temperature:	Not determined
Evaporation rate:	Not available.
Solubility in water:	Insoluble
Partition coefficient (n-octanol/water):	Not available.
VOC content:	12.96 %; 162 g/l

10. STABILITY AND REACTIVITY

Stability:	Stable
Hazardous reactions:	Will not occur.
Hazardous decomposition products:	None reasonably foreseeable.
Incompatible materials:	Strong oxidizing agents.
Conditions to avoid:	None known

11. TOXICOLOGICAL INFORMATION

Hazardous components	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Distillates (petroleum), hydrotreated heavy naphthenic	Known To Be Human Carcinogen.	Group 1	No
Graphite	No	No	No
Calcium oxide	No	No	No
Mineral oil light naphthenic hydrotreat. <3% DMSO	No	No	No
Aluminum not powder, dust or fume	No	No	No
Distillates (petroleum), straight-run middle	No	No	No
Quartz (SiO ₂)	Known To Be Human Carcinogen.	Group 1	No

Hazardous components	Health Effects/Target Organs
Distillates (petroleum), hydrotreated heavy naphthenic	Irritant
Graphite	Lung
Calcium oxide	Irritant, Corrosive, Eyes
Mineral oil light naphthenic hydrotreat. <3% DMSO	Irritant
Aluminum not powder, dust or fume	Central nervous system, Irritant, Lung
Distillates (petroleum), straight-run middle	Irritant
Quartz (SiO ₂)	Immune system, Lung, Some evidence of carcinogenicity

12. ECOLOGICAL INFORMATION

Ecological information: Not available.

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Follow all local, state, federal and provincial regulations for disposal.

Hazardous waste number: Not a RCRA hazardous waste.

14. TRANSPORT INFORMATION

U.S. Department of Transportation Ground (49 CFR)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

International Air Transportation (ICAO/IATA)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

Water Transportation (IMO/IMDG)

Proper shipping name:	Not regulated
Hazard class or division:	None
Identification number:	None
Packing group:	None

15. REGULATORY INFORMATION

United States Regulatory Information

TSCA 8 (b) Inventory Status:	All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.
TSCA 12(b) Export Notification:	None above reporting de minimus
CERCLA/SARA Section 302 EHS:	None above reporting de minimis
CERCLA/SARA Section 311/312:	Immediate Health
CERCLA/SARA 313:	This product contains the following toxic chemicals subject to the reporting requirements of section 313 of the Emergency Planning and Community Right-To-Know Act of 1986 (40 CFR 372). Aluminum not powder, dust or fume (CAS# 7429-90-5).
California Proposition 65:	This product contains a chemical known in the State of California to cause cancer.

Canada Regulatory Information

CEPA DSL/NDL Status:	All components are listed on or are exempt from listing on the Canadian Domestic Substances List.
WHMIS hazard class:	D.2.A, D.2.B

16. OTHER INFORMATION

This material safety data sheet contains changes from the previous version in sections: Updated Contact Information in Section 1., Updated HMIS rating in Section 2.

Prepared by: Lou Fabrizio, Regulatory Affairs Specialist

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.