



Material Safety Data Sheet

Copyright, 2011, 3M Company All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

SECTION 1: PRODUCT AND COMPANY IDENTIFICATION

PRODUCT NAME: Connectors w/EG5 Sealant (UR, UR2, UY, UY2, UYF, UDW2, UB2A, UG, UCC, UAL, 2A, 211, 557)
MANUFACTURER: 3M
DIVISION: Communication Markets Division
ADDRESS: 3M Center, St. Paul, MN 55144-1000

EMERGENCY PHONE: 1-800-364-3577 or (651) 737-6501 (24 hours)

Issue Date: 07/07/11
Supersedes Date: 06/02/11

Document Group: 20-2665-6

Product Use:

Intended Use: Sealant

SECTION 2: INGREDIENTS

<u>Ingredient</u>	<u>C.A.S. No.</u>	<u>% by Wt</u>
WHITE MINERAL OIL	8042-47-5	35 - 45
POLYBUTYLENE	9003-29-6	35 - 45
DIMETHYL SILOXANE, REACTION PRODUCT WITH SILICA	67762-90-7	10 - 20
HYDROCINNAMIC ACID, 3,5-DI-TERT-BUTYL-4-HYDROXY-, OCTADECYL ESTER	2082-79-3	0 - 1

SECTION 3: HAZARDS IDENTIFICATION

3.1 EMERGENCY OVERVIEW

Specific Physical Form: Viscous

Odor, Color, Grade: Light colored grease, slight aromatic odor

General Physical Form: Solid

Immediate health, physical, and environmental hazards: May cause allergic skin reaction.

3.2 POTENTIAL HEALTH EFFECTS

Eye Contact:

Mild Eye Irritation: Signs/symptoms may include redness, pain, and tearing.

Skin Contact:

Allergic Skin Reaction (non-photo induced): Signs/symptoms may include redness, swelling, blistering, and itching.

Mild Skin Irritation: Signs/symptoms may include localized redness, swelling, and itching.

Inhalation:

No health effects are expected.

Ingestion:

Gastrointestinal Irritation: Signs/symptoms may include abdominal pain, stomach upset, nausea, vomiting and diarrhea.

SECTION 4: FIRST AID MEASURES

4.1 FIRST AID PROCEDURES

The following first aid recommendations are based on an assumption that appropriate personal and industrial hygiene practices are followed.

Eye Contact: Flush eyes with large amounts of water. If signs/symptoms persist, get medical attention.

Skin Contact: Remove contaminated clothing and shoes. Immediately flush skin with large amounts of water. Get medical attention. Wash contaminated clothing and clean shoes before reuse.

Inhalation: No need for first aid is anticipated.

If Swallowed: Do not induce vomiting unless instructed to do so by medical personnel. Give victim two glasses of water. Never give anything by mouth to an unconscious person. Get medical attention.

SECTION 5: FIRE FIGHTING MEASURES

5.1 FLAMMABLE PROPERTIES

Autoignition temperature	No Data Available
Flash Point	No flash point
Flammable Limits(LEL)	No Data Available
Flammable Limits(UEL)	No Data Available

5.2 EXTINGUISHING MEDIA

Use fire extinguishers with class B extinguishing agents (e.g., dry chemical, carbon dioxide).

5.3 PROTECTION OF FIRE FIGHTERS

Special Fire Fighting Procedures: Wear full protective equipment (Bunker Gear) and a self-contained breathing apparatus (SCBA).

Unusual Fire and Explosion Hazards: Not applicable. No unusual fire or explosion hazards are anticipated.

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Evacuate unprotected and untrained personnel from hazard area. The spill should be cleaned up by qualified personnel.

6.2. Environmental precautions

Place in a closed container approved for transportation by appropriate authorities. Dispose of collected material as soon as possible.

Clean-up methods

Observe precautions from other sections. Call 3M- HELPS line (1-800-364-3577) for more information on handling and managing the spill. Contain spill. Collect as much of the spilled material as possible. Clean up residue with an appropriate solvent selected by a qualified and authorized person. Ventilate the area with fresh air. Read and follow safety precautions on the solvent label and MSDS.

In the event of a release of this material, the user should determine if the release qualifies as reportable according to local, state, and federal regulations.

SECTION 7: HANDLING AND STORAGE

7.1 HANDLING

For industrial or professional use only. Do not eat, drink or smoke when using this product. Wash exposed areas thoroughly with soap and water. Avoid prolonged or repeated skin contact. Decontaminate work surfaces frequently to avoid exposure by contact.

7.2 STORAGE

Store under normal warehouse conditions.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1 ENGINEERING CONTROLS

Use general dilution ventilation and/or local exhaust ventilation to control airborne exposures to below Occupational Exposure Limits and/or control dust, fume, or airborne particles. If ventilation is not adequate, use respiratory protection equipment.

8.2 PERSONAL PROTECTIVE EQUIPMENT (PPE)

8.2.1 Eye/Face Protection

Avoid eye contact.

The following eye protection(s) are recommended: Safety Glasses with side shields

.

8.2.2 Skin Protection

Avoid prolonged or repeated skin contact.

Select and use gloves and/or protective clothing to prevent skin contact based on the results of an exposure assessment. Consult with your glove and/or protective clothing manufacturer for selection of appropriate compatible materials.

Gloves made from the following material(s) are recommended: Neoprene

Nitrile Rubber

.

8.2.3 Respiratory Protection

Under normal use conditions, airborne exposures are not expected to be significant enough to require respiratory protection.

8.2.4 Prevention of Swallowing

Do not eat, drink or smoke when using this product. Wash exposed areas thoroughly with soap and water.

8.3 EXPOSURE GUIDELINES

<u>Ingredient</u>	<u>Authority</u>	<u>Type</u>	<u>Limit</u>	<u>Additional Information</u>
DIMETHYL SILOXANE, REACTION PRODUCT WITH SILICA	CMRG	CEIL	5 mg/m3	
HYDROCINNAMIC ACID, 3,5-DI-TERT-BUTYL-4-HYDROXY-, OCTADECYL ESTER	CMRG	TWA	10 mg/m3	
WHITE MINERAL OIL	CMRG	TWA	5 mg/m3	
WHITE MINERAL OIL	CMRG	STEL	10 mg/m3	

SOURCE OF EXPOSURE LIMIT DATA:

ACGIH: American Conference of Governmental Industrial Hygienists
 CMRG: Chemical Manufacturer Recommended Guideline
 OSHA: Occupational Safety and Health Administration
 AIHA: American Industrial Hygiene Association Workplace Environmental Exposure Level (WEEL)

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

Specific Physical Form:	Viscous
Odor, Color, Grade:	Light colored grease, slight aromatic odor
General Physical Form:	Solid
Autoignition temperature	<i>No Data Available</i>
Flash Point	No flash point
Flammable Limits(LEL)	<i>No Data Available</i>
Flammable Limits(UEL)	<i>No Data Available</i>
Boiling Point	<i>No Data Available</i>
Density	0.91 g/ml
Vapor Density	<i>No Data Available</i>
Vapor Density	<i>No Data Available</i>
Vapor Pressure	<i>No Data Available</i>
Vapor Pressure	<i>No Data Available</i>
Specific Gravity	0.91 [Ref Std: WATER=1]
pH	<i>Not Applicable</i>
Melting point	<i>No Data Available</i>
Solubility in Water	Nil
Evaporation rate	<i>No Data Available</i>
Volatile Organic Compounds	<i>No Data Available</i>
Kow - Oct/Water partition coef	<i>No Data Available</i>
Percent volatile	<i>No Data Available</i>
VOC Less H2O & Exempt Solvents	<i>No Data Available</i>
Viscosity	<i>No Data Available</i>
Conditions to avoid	None known
Materials to avoid	None known

SECTION 10: STABILITY AND REACTIVITY

Stability: Stable.

Materials and Conditions to Avoid:

10.1 Conditions to avoid

None known

10.2 Materials to avoid

None known

Hazardous Polymerization: Hazardous polymerization will not occur.

Hazardous Decomposition: Carbon dioxide and carbon monoxide and unidentified hydrocarbons.

SECTION 11: TOXICOLOGICAL INFORMATION

Please contact the address listed on the first page of the MSDS for Toxicological Information on this material and/or its components.

SECTION 12: ECOLOGICAL INFORMATION

ECOTOXICOLOGICAL INFORMATION

Not determined.

CHEMICAL FATE INFORMATION

Not determined.

SECTION 13: DISPOSAL CONSIDERATIONS

Waste Disposal Method: As a disposal alternative, dispose of waste product in a facility permitted to accept chemical waste.

EPA Hazardous Waste Number (RCRA): Not regulated

Since regulations vary, consult applicable regulations or authorities before disposal.

SECTION 14: TRANSPORT INFORMATION

ID Number(s):

80-6113-1647-4, 80-6113-1648-2, 80-6113-1649-0, 80-6113-1650-8, 80-6113-1709-2, 80-6113-2011-2, 80-6113-2121-9, 80-6113-2207-6, 80-6113-2209-2, 80-6113-2493-2, 80-6113-2656-4, 80-6113-2673-9, 80-6113-2674-7, 80-6113-2675-4, 80-6113-2676-2, 80-6113-2677-0, 80-6113-2678-8, 80-6113-2679-6, 80-6113-2703-4, 80-6113-2704-2, 80-6113-2705-9, 80-6113-2742-2, 80-6113-2743-0, 80-6113-2744-8, 80-6113-2745-5, 80-6113-2746-3, 80-6113-2747-1, 80-6113-2748-9, 80-6113-2749-7, 80-6113-2750-5, 80-6113-2751-3, 80-6113-2752-1, 80-6113-2753-9, 80-6113-2754-7, 80-6113-2755-4, 80-6113-2757-0, 80-6113-2758-8, 80-6113-2759-6, 80-6113-2760-4, 80-6113-2762-0, 80-6113-2763-8, 80-6113-2764-6, 80-6113-2765-3, 80-6113-2769-5, 80-6113-2770-3, 80-6113-2771-1, 80-6113-2772-9, 80-6113-2779-4, 80-6113-2781-0, 80-6113-2782-8, 80-6113-2783-6, 80-6113-2784-4, 80-6113-2785-1, 80-6113-2786-9, 80-6113-2787-7, 80-6113-2788-5, 80-6113-2789-3, 80-6113-2790-1, 80-6113-2791-9, 80-6113-2792-7, 80-6113-2793-5, 80-6113-2795-0, 80-6113-2796-8, 80-6113-3448-5, 80-6113-8832-5, 80-6113-8833-3, FQ-1000-5752-7, FQ-1000-5753-5

For Transport Information, please visit <http://3M.com/Transportinfo> or call 1-800-364-3577 or 651-737-6501.

SECTION 15: REGULATORY INFORMATION

US FEDERAL REGULATIONS

Contact 3M for more information.

311/312 Hazard Categories:

Fire Hazard - No Pressure Hazard - No Reactivity Hazard - No Immediate Hazard - Yes Delayed Hazard - No

STATE REGULATIONS

Contact 3M for more information.

CHEMICAL INVENTORIES

The components of this product are in compliance with the chemical notification requirements of TSCA.

All applicable chemical ingredients in this material are listed on the European Inventory of Existing Chemical Substances (EINECS), or are exempt polymers whose monomers are listed on EINECS. Contact 3M for more information.

INTERNATIONAL REGULATIONS

Contact 3M for more information.

This MSDS has been prepared to meet the U.S. OSHA Hazard Communication Standard, 29 CFR 1910.1200.

SECTION 16: OTHER INFORMATION

NFPA Hazard Classification

Health: 2 Flammability: 1 Reactivity: 0 Special Hazards: None

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

Reason for Reissue: Add new stock number 80-6113-2674-780-6113-8832-5, 80-6113-8833-3.

Revision Changes:

Section 1: Product name was modified.

Section 16: Reason for reissue comment was modified.

Page Heading: Product name was modified.

Section 14: ID Number(s) Template 1 was modified.

DISCLAIMER: The information in this Material Safety Data Sheet (MSDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the MSDS available directly from 3M

3M USA MSDSs are available at www.3M.com



Transport Information Document

Date: May 29, 2012

3M ID Number: 80-6113-2759-6

Product Description: 3M(TM) Scotchlok(TM) IDC Butt Connector UR2 Box

Transport Protective Service: PROTECTIVE SERVICE NOT REQUIRED

NMFC Item: 061205

NMFC Sub: 00

NMFC Class: 110.0

Flash Point (Closed-cup): No Flash Point

UNITED STATES DEPARTMENT OF TRANSPORTATION - GROUND (U.S. DOT, 49 CFR)

NOT REGULATED

UNITED STATES DEPARTMENT OF TRANSPORTATION - VESSEL (U.S. DOT, 49 CFR)

NOT REGULATED

INTERNATIONAL AIR TRANSPORT ASSOCIATION (IATA)

NOT REGULATED

INTERNATIONAL MARITIME ORGANIZATION (IMO)

NOT REGULATED

The classification is authorized by the Competent Authority of the United States of America and may not meet the requirements of other competent authorities.

These transportation classifications are provided as a customer service. AS THE SHIPPER YOU REMAIN RESPONSIBLE FOR COMPLYING WITH ALL THE APPLICABLE LAWS AND REGULATIONS, INCLUDING PROPER TRANSPORTATION CLASSIFICATION AND PACKAGING. 3M's transportation classifications are based on product formulations, packaging, 3M policies and 3M's understanding of applicable current regulations and is valid for the original 3M package only. 3M does not guarantee the accuracy of this classification information. This information applies only to transportation classification and NOT THE PACKAGING, LABELING, OR MARKING REQUIREMENTS. The original 3M package is certified for U.S. ground shipment only. If you are shipping by air or ocean, the package may not meet applicable regulatory requirements.

For Transport Information, please visit 3M.com/Transportinfo
or call 1-800-364-3577 or 651-737-6501 for assistance.