



4801 North Ravenswood Avenue
Chicago, IL 60640-4496
Phone: (773) 907-5181
Fax: (773) 907-5180
E-mail (techsupport@spctechnology.com)

Doc. No.: MSDS-024-NM
DCP No.: 1423
Effective Date: 11/13/03

Material Safety Data Sheet

(Non-Mandatory)

Identity: Hand Lotion, Static Dissipative

SECTION I – Manufacturer’s p/n’s

1447, 1448, 1449, 1450, 1451

SECTION II - Hazardous Ingredients/Identity Information

Hazardous Components Other Limits

(Specific Chemical Identity) OSHA PEL ACHIH TIV Recommended %Optional

NONE

WHMIS REGULATIONS (CANADIAN)

THE CANADIAN WORKPLACE HAZARDOUS MATERIALS INFORMATION SYSTEM

CLASSIFICATION FOR THIS PRODUCT IS, “THIS PRODUCT IS NOT A CONTROLLED PRODUCT UNDER THE WHMIS REGULATIONS.”

SARA HAZARDOUS CATEGORY

THIS PRODUCT HAS BEEN REVIEWED ACCORDING TO THE EPA HAZARD CATAGORIES UNDER SECTION 311 & 312 OF THE SUPERFUND AMENDMENT AND REORGANIZATION ACT OF 1986 AND IS CONSIDERED UNDER APPLICABLE DEFINITIONS TO MEET THE FOLLOWING CATEGORY: NOT TO HAVE MET ANY HAZARDOUS CATEGORY.

TOXIC SUBSTANCES CONTROL ACT (TSCA)

ALL INGREDIENTS ARE ON THE TSCA INVENTORY OR ARE NOT REQUIRED TO BE LISTED ON THE TSCA INVENTORY.

SECTION III -Physical/Chemical Characteristics

Boiling Point: 100°C

Specific Gravity (H₂O= 1): 1.02

Vapor Pressure (mm Hg): N/A

Melting Point: N/A

Vapor Density (AIR =1): N/A

Evaporation Rate (Butyl Acetate = 1): N/A

Solubility in Water: Infinitely

Appearance and Odor: BLUE LOTION AND PLEASANT ODOR

SECTION IV - Fire and Explosion Hazard Data

Flash Point (Method Used) Flammable Limits

N/A

N/A

LEL

N/A

UEL

N/A

Extinguishing Media: N/A

Special Fire Fighting Procedures: N/A.

Unusual Fire and Explosion Hazards: N/A



4801 North Ravenswood Avenue
Chicago, IL 60640-4496
Phone: (773) 907-5181
Fax: (773) 907-5180
E-mail (techsupport@spctechnology.com)

Doc. No.: MSDS-024-NM
DCP No.: 1423
Effective Date: 11/13/03

Material Safety Data Sheet

(Non-Mandatory)

SECTION V - Reactivity Data

Stability Unstable.

Stable: X

Conditions to Avoid: N/A

Incompatibility (Materials to Avoid): N/A

Hazardous Decomposition or Byproducts: N/A

Hazardous Polymerization May Occur: Will not Occur: X Conditions to Avoid: X

SECTION VI - Health Hazard Data

Routes of Entry: Inhalation: N/A Skin: X Ingestion: N/A

Health Hazards (Acute and Chronic): None

Carcinogenicity: NTP IARC Monographs OSHA Regulated: N/A

Signs and Symptoms of Exposure: N/A

Medical Conditions Generally Aggravated by Exposure: None

Emergency and First Aid Procedures: N/A

SECTION VII - Precautions for Safe Handling and Use:

Steps to Be Taken in Case Material is Released or Spilled:

MOP UP WITH SOAP AND WATER

Waste Disposal Method

FLUSH DOWN SEWER WITH COPIOUS AMOUNTS OF WATER

Precautions to Be Taken in Handling and Storing: N/A

Other Precautions: NONE

SECTION VIII - Control Measures

Respiratory Protection (Specify Type): N/A

Ventilation: N/A Local Exhaust: N/A Special: N/A

Mechanical (General) Other

Protective Gloves: N/A Eye: N/A Protection: N/A

Other Protective Clothing or Equipment: N/A

Work/Hygienic Practices: N/A