



Material Safety Data Sheet

Copyright, 2012, 3M Company All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

SECTION 1: PRODUCT AND COMPANY IDENTIFICATION

PRODUCT NAME: 3M™ Hi-Strength Spray Adhesive 90 (aerosol)
MANUFACTURER: 3M
DIVISION: Industrial Adhesives and Tapes Division
ADDRESS: 3M Center, St. Paul, MN 55144-1000

EMERGENCY PHONE: 1-800-364-3577 or (651) 737-6501 (24 hours)

Issue Date: 04/04/12
Supersedes Date: 03/30/12

Document Group: 16-4935-9

Product Use:

Intended Use: aerosol adhesive
 Specific Use: hi-strength aerosol adhesive

SECTION 2: INGREDIENTS

<u>Ingredient</u>	<u>C.A.S. No.</u>	<u>% by Wt</u>
Dimethyl ether	115-10-6	35 - 45
Methyl acetate	79-20-9	25 - 35
N.J.T.S. Reg No. 0449960-6448P	Trade Secret	10 - 20
Cyclohexane	110-82-7	7 - 13
Propellant R-152a	75-37-6	1 - 5
Pentane	109-66-0	1 - 5

SECTION 3: HAZARDS IDENTIFICATION

3.1 EMERGENCY OVERVIEW

Specific Physical Form: Aerosol

Odor, Color, Grade: clear, sweet fruity odor

General Physical Form: Gas

Immediate health, physical, and environmental hazards: Closed containers exposed to heat from fire may build pressure and explode. Extremely flammable liquid and vapor. Vapors may travel long distances along the ground or floor to an ignition source and flash back. Aerosol container contains flammable material under pressure. May cause target organ effects.

3.2 POTENTIAL HEALTH EFFECTS

Eye Contact:

Moderate Eye Irritation: Signs/symptoms may include redness, swelling, pain, tearing, and blurred or hazy vision.

Skin Contact:

Mild Skin Irritation: Signs/symptoms may include localized redness, swelling, and itching.

Inhalation:

Respiratory Tract Irritation: Signs/symptoms may include cough, sneezing, nasal discharge, headache, hoarseness, and nose and throat pain.

Intentional concentration and inhalation may be harmful or fatal.

Cardiac Sensitization: Signs/symptoms may include irregular heartbeat (arrhythmia), faintness, chest pain, and may be fatal.

Prolonged or repeated exposure may cause:

Respiratory Effects: Signs/symptoms may include cough, shortness of breath, chest tightness, wheezing, increased heart rate, bluish colored skin (cyanosis), sputum production, changes in lung function tests, and/or respiratory failure.

May be absorbed following inhalation and cause target organ effects.

Ingestion:

Gastrointestinal Irritation: Signs/symptoms may include abdominal pain, stomach upset, nausea, vomiting and diarrhea.

May be absorbed following ingestion and cause target organ effects.

Target Organ Effects:

Central Nervous System (CNS) Depression: Signs/symptoms may include headache, dizziness, drowsiness, incoordination, nausea, slowed reaction time, slurred speech, giddiness, and unconsciousness.

SECTION 4: FIRST AID MEASURES

4.1 FIRST AID PROCEDURES

The following first aid recommendations are based on an assumption that appropriate personal and industrial hygiene practices are followed.

Eye Contact: Flush eyes with large amounts of water. If signs/symptoms persist, get medical attention.

Skin Contact: Wash affected area with soap and water. If signs/symptoms develop, get medical attention.

Inhalation: Remove person to fresh air. Get immediate medical attention.

If Swallowed: Do not induce vomiting unless instructed to do so by medical personnel. Give victim two glasses of water. Never give anything by mouth to an unconscious person. Get medical attention.

4.2 NOTE TO PHYSICIANS

Exposure may increase myocardial irritability. Do not administer sympathomimetic drugs unless absolutely necessary.

SECTION 5: FIRE FIGHTING MEASURES

5.1 FLAMMABLE PROPERTIES

Autoignition temperature

No Data Available

Flash Point	-42.00 °F [<i>Test Method:</i> Tagliabue Closed Cup]
Flammable Limits(LEL)	<i>No Data Available</i>
Flammable Limits(UEL)	<i>No Data Available</i>
OSHA Flammability Classification:	Class IA Flammable Liquid

5.2 EXTINGUISHING MEDIA

Use fire extinguishers with class B extinguishing agents (e.g., dry chemical, carbon dioxide).

5.3 PROTECTION OF FIRE FIGHTERS

Special Fire Fighting Procedures: Wear full protective equipment (Bunker Gear) and a self-contained breathing apparatus (SCBA).

Unusual Fire and Explosion Hazards: Closed containers exposed to heat from fire may build pressure and explode. Extremely flammable liquid and vapor. Vapors may travel long distances along the ground or floor to an ignition source and flash back. Aerosol container contains flammable material under pressure.

Note: See STABILITY AND REACTIVITY (SECTION 10) for hazardous combustion and thermal decomposition information.

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

If possible, seal leaking container. Place leaking containers in a well-ventilated area, preferably an operating exhaust hood, or if necessary outdoors on an impermeable surface until appropriate packaging for the leaking container or its contents is available.

Evacuate unprotected and untrained personnel from hazard area. The spill should be cleaned up by qualified personnel.

6.2. Environmental precautions

Collect the resulting residue containing solution. Place in a metal container approved for transportation by appropriate authorities. Dispose of collected material as soon as possible.

Clean-up methods

Refer to other sections of this MSDS for information regarding physical and health hazards, respiratory protection, ventilation, and personal protective equipment. Call 3M-HELPS line (1-800-364-3577) for more information on handling and managing the spill. Contain spill. Clean up residue.

In the event of a release of this material, the user should determine if the release qualifies as reportable according to local, state, and federal regulations.

SECTION 7: HANDLING AND STORAGE

7.1 HANDLING

Do not eat, drink or smoke when using this product. Wash exposed areas thoroughly with soap and water. Keep away from heat, sparks, open flame, pilot lights and other sources of ignition. Avoid prolonged or repeated skin contact. Avoid eye contact with vapors, mists, or spray. Keep out of the reach of children. Vapors may ignite explosively. May cause flash fire. Prevent build-up of vapors - open all windows and doors. Maintain vapor concentrations below recommended exposure limits. Use only with cross-ventilation. Without adequate ventilation, vapors may settle in low-lying areas. Keep away from heat, sparks, and open flame. Do not smoke or ignite matches, lighters, etc.

7.2 STORAGE

Store away from acids. Store away from heat. Store out of direct sunlight.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1 ENGINEERING CONTROLS

Use with appropriate local exhaust ventilation. Do not use in a confined area or areas with little or no air movement. Use general dilution ventilation and/or local exhaust ventilation to control airborne exposures to below Occupational Exposure Limits and/or control mist, vapor, or spray. If ventilation is not adequate, use respiratory protection equipment.

8.2 PERSONAL PROTECTIVE EQUIPMENT (PPE)

8.2.1 Eye/Face Protection

Avoid eye contact. Avoid eye contact with vapors, mists, or spray.

The following eye protection(s) are recommended: Safety Glasses with side shields

8.2.2 Skin Protection

Avoid skin contact. Avoid prolonged or repeated skin contact.

Select and use gloves and/or protective clothing to prevent skin contact based on the results of an exposure assessment. Consult with your glove and/or protective clothing manufacturer for selection of appropriate compatible materials.

Gloves made from the following material(s) are recommended: Nitrile Rubber

8.2.3 Respiratory Protection

Avoid breathing of vapors, mists or spray.

Select one of the following NIOSH approved respirators based on airborne concentration of contaminants and in accordance with OSHA regulations: Half facepiece or fullface air-purifying respirator with organic vapor cartridges

Select and use respiratory protection to prevent an inhalation exposure based on the results of an exposure assessment. Consult with your respirator manufacturer for selection of appropriate types of respirators. Organic vapor cartridges may have short service life.

8.2.4 Prevention of Swallowing

Do not eat, drink or smoke when using this product. Wash exposed areas thoroughly with soap and water.

8.3 EXPOSURE GUIDELINES

<u>Ingredient</u>	<u>Authority</u>	<u>Type</u>	<u>Limit</u>	<u>Additional Information</u>
Propellant R-152a	AIHA	TWA	2700 mg/m ³	
Propellant R-152a	CMRG	TWA	1000 ppm	
Cyclohexane	ACGIH	TWA	100 ppm	
Cyclohexane	OSHA	TWA	1050 mg/m ³	
Dimethyl ether	AIHA	TWA	1880 mg/m ³	
Dimethyl ether	CMRG	TWA	1000 ppm	
Methyl acetate	ACGIH	TWA	200 ppm	
Methyl acetate	ACGIH	STEL	250 ppm	
Methyl acetate	OSHA	TWA	610 mg/m ³	
Pentane	ACGIH	TWA	600 ppm	
Pentane	OSHA	TWA	2950 mg/m ³	

SOURCE OF EXPOSURE LIMIT DATA:

ACGIH: American Conference of Governmental Industrial Hygienists

CMRG: Chemical Manufacturer Recommended Guideline

OSHA: Occupational Safety and Health Administration

AIHA: American Industrial Hygiene Association Workplace Environmental Exposure Level (WEEL)

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

Specific Physical Form:	Aerosol
Odor, Color, Grade:	clear, sweet fruity odor
General Physical Form:	Gas
Autoignition temperature	<i>No Data Available</i>
Flash Point	-42.00 °F [<i>Test Method:</i> Tagliabue Closed Cup]
Flammable Limits(LEL)	<i>No Data Available</i>
Flammable Limits(UEL)	<i>No Data Available</i>
Boiling Point	<i>Not Applicable</i>
Density	0.726 g/ml
Vapor Density	2.97 [<i>Ref Std:</i> AIR=1]
Specific Gravity	0.726 [<i>Ref Std:</i> WATER=1]
pH	<i>No Data Available</i>
Melting point	<i>Not Applicable</i>
Solubility in Water	Nil
Evaporation rate	1.90 [<i>Ref Std:</i> ETHER=1]
Hazardous Air Pollutants	<=0 % weight [<i>Test Method:</i> Calculated]
Volatile Organic Compounds	<=631 g/l [<i>Details:</i> EU VOC content]
Kow - Oct/Water partition coef	<i>No Data Available</i>
Percent volatile	<=75 % weight
VOC Less H2O & Exempt Solvents	<= 55 % [<i>Test Method:</i> calculated SCAQMD rule 443.1]
VOC Less H2O & Exempt Solvents	<=3.32 lb/gal [<i>Test Method:</i> calculated SCAQMD rule 443.1]
VOC Less H2O & Exempt Solvents	<=55 % [<i>Test Method:</i> calculated per CARB title 2]
Viscosity	<i>Not Applicable</i>

SECTION 10: STABILITY AND REACTIVITY

Stability: Stable.

Materials and Conditions to Avoid:

10.1 Conditions to avoid

Heat

10.2 Materials to avoid

Strong oxidizing agents

Hazardous Polymerization: Hazardous polymerization will not occur.

Hazardous Decomposition or By-Products

<u>Substance</u>	<u>Condition</u>
Carbon monoxide	During Combustion
Carbon dioxide	During Combustion
Irritant Vapors or Gases	During Combustion

SECTION 11: TOXICOLOGICAL INFORMATION

Please contact the address listed on the first page of the MSDS for Toxicological Information on this material and/or its components.

SECTION 12: ECOLOGICAL INFORMATION

ECOTOXICOLOGICAL INFORMATION

Not determined.

CHEMICAL FATE INFORMATION

Not determined.

SECTION 13: DISPOSAL CONSIDERATIONS

Waste Disposal Method: Incinerate in a permitted hazardous waste incinerator. Facility must be capable of handling aerosol cans. Dispose of empty product containers in a sanitary landfill.

EPA Hazardous Waste Number (RCRA): D001 (Ignitable)

Since regulations vary, consult applicable regulations or authorities before disposal.

SECTION 14: TRANSPORT INFORMATION

ID Number(s):

62-4942-4730-7, 62-4942-4920-4, 62-4942-4921-2, 62-4942-4925-3, 62-4942-4930-3, 62-4942-4935-2, 62-4942-4950-1, 62-4942-4955-0, 62-4942-4970-9, 62-4942-4975-8, CS-0406-7111-0

For Transport Information, please visit <http://3M.com/Transportinfo> or call 1-800-364-3577 or 651-737-6501.

SECTION 15: REGULATORY INFORMATION

US FEDERAL REGULATIONS

Contact 3M for more information.

311/312 Hazard Categories:

Fire Hazard - Yes Pressure Hazard - Yes Reactivity Hazard - No Immediate Hazard - Yes Delayed Hazard - Yes

Section 313 Toxic Chemicals subject to the reporting requirements of that section and 40 CFR part 372 (EPCRA):

<u>Ingredient</u>	<u>C.A.S. No</u>	<u>% by Wt</u>
Cyclohexane	110-82-7	7 - 13

STATE REGULATIONS

Contact 3M for more information.

CHEMICAL INVENTORIES

The components of this product are in compliance with the chemical notification requirements of TSCA.

All applicable chemical ingredients in this material are listed on the European Inventory of Existing Chemical Substances (EINECS), or are exempt polymers whose monomers are listed on EINECS. Contact 3M for more information.

INTERNATIONAL REGULATIONS

Contact 3M for more information.

This MSDS has been prepared to meet the U.S. OSHA Hazard Communication Standard, 29 CFR 1910.1200.

SECTION 16: OTHER INFORMATION

NFPA Hazard Classification

Health: 2 Flammability: 4 Reactivity: 0 Special Hazards: None
Aerosol Storage Code: 3

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

Revision Changes:

Section 9: Property description for optional properties was modified.

Section 2: Ingredient table was modified.

Section 8: Exposure guidelines ingredient information was modified.

DISCLAIMER: The information in this Material Safety Data Sheet (MSDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the MSDS available directly from 3M

3M USA MSDSs are available at www.3M.com



Transport Information Document

Date: January 28, 2013

3M ID Number: 62-4942-4970-9

Product Description: 3M(TM) Hi-Strength 90 Spray Adhesive, INVERTED 24 fl oz aerosol, 12 cans per case

Transport Protective Service: PROTECTIVE SERVICE NOT REQUIRED

NMFC Item: 004620

NMFC Sub: 06

NMFC Class: 060.0

Flash Point (Closed-cup): No Flash Point

UNITED STATES DEPARTMENT OF TRANSPORTATION - GROUND (U.S. DOT, 49 CFR)

CONSUMER COMMODITY, ORM-D OR LIMITED QUANTITY

UNITED STATES DEPARTMENT OF TRANSPORTATION - VESSEL (U.S. DOT, 49 CFR)

UN1950, AEROSOLS, 2.1, LIMITED QUANTITY

INTERNATIONAL AIR TRANSPORT ASSOCIATION (IATA)

UN1950, AEROSOLS, FLAMMABLE, 2.1

INTERNATIONAL MARITIME ORGANIZATION (IMO)

UN1950, AEROSOLS, 2.1, LIMITED QUANTITY

The classification is authorized by the Competent Authority of the United States of America and may not meet the requirements of other competent authorities.

These transportation classifications are provided as a customer service. AS THE SHIPPER YOU REMAIN RESPONSIBLE FOR COMPLYING WITH ALL THE APPLICABLE LAWS AND REGULATIONS, INCLUDING PROPER TRANSPORTATION CLASSIFICATION AND PACKAGING. 3M's transportation classifications are based on product formulations, packaging, 3M policies and 3M's understanding of applicable current regulations and is valid for the original 3M package only. 3M does not guarantee the accuracy of this classification information. This information applies only to transportation classification and NOT THE PACKAGING, LABELING, OR MARKING REQUIREMENTS. The original 3M package is certified for U.S. ground shipment only. If you are shipping by air or ocean, the package may not meet applicable regulatory requirements.

For Transport Information, please visit 3M.com/Transportinfo
or call 1-800-364-3577 or 651-737-6501 for assistance.