



Material Safety Data Sheet

Copyright, 2010, 3M Company. All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

SECTION 1: PRODUCT AND COMPANY IDENTIFICATION

PRODUCT NAME: 3M(TM) Scotch-Weld(TM) Instant Adhesive Accelerator AC452 (formerly sold as Rite-Lok™ Rapid Flash CA Accelerator AC452, AC452-2, AC452-8, AC452-12A, & AC452-1G)

MANUFACTURER: 3M

DIVISION: Industrial Adhesives and Tapes Division

ADDRESS: 3M Center
St. Paul, MN 55144-1000

EMERGENCY PHONE: 1-800-364-3577 or (651) 737-6501 (24 hours)

Issue Date: 02/11/10

Supersedes Date: 01/08/10

Document Group: 22-6150-1

Product Use:

Intended Use: Adhesive activator
Specific Use: Cure activator

SECTION 2: INGREDIENTS

<u>Ingredient</u>	<u>C.A.S. No.</u>	<u>% by Wt</u>
ACETONE	67-64-1	95 - 99
N,N-DIMETHYL-P-TOLUIDINE	99-97-8	1 - 5

SECTION 3: HAZARDS IDENTIFICATION

3.1 EMERGENCY OVERVIEW

Odor, Color, Grade: Pale yellow solution with solvent odor.

General Physical Form: Liquid

Immediate health, physical, and environmental hazards: Closed containers exposed to heat from fire may build pressure and explode. Extremely flammable liquid and vapor. Vapors may travel long distances along the ground or floor to an ignition source and flash back. May cause severe eye irritation. May cause target organ effects.

3.2 POTENTIAL HEALTH EFFECTS

Eye Contact:

Severe Eye Irritation: Signs/symptoms may include significant redness, swelling, pain, tearing, cloudy appearance of the cornea, and impaired vision.

Skin Contact:

Mild Skin Irritation: Signs/symptoms may include localized redness, swelling, and itching.

May be absorbed through skin and cause target organ effects.

Inhalation:

Respiratory Tract Irritation: Signs/symptoms may include cough, sneezing, nasal discharge, headache, hoarseness, and nose and throat pain.

May be absorbed following inhalation and cause target organ effects.

Ingestion:

Gastrointestinal Irritation: Signs/symptoms may include abdominal pain, stomach upset, nausea, vomiting and diarrhea.

May be absorbed following ingestion and cause target organ effects.

Target Organ Effects:

Methemoglobinemia: Signs/symptoms may include headache, dizziness, nausea, difficulty breathing, and generalized weakness.

Central Nervous System (CNS) Depression: Signs/symptoms may include headache, dizziness, drowsiness, incoordination, nausea, slowed reaction time, slurred speech, giddiness, and unconsciousness.

SECTION 4: FIRST AID MEASURES

4.1 FIRST AID PROCEDURES

The following first aid recommendations are based on an assumption that appropriate personal and industrial hygiene practices are followed.

Eye Contact: Immediately flush eyes with large amounts of water for at least 15 minutes. Get immediate medical attention.

Skin Contact: Wash affected area with soap and water. If signs/symptoms develop, get medical attention.

Inhalation: Remove person to fresh air. If signs/symptoms develop, get medical attention.

If Swallowed: Do not induce vomiting unless instructed to do so by medical personnel. Give victim two glasses of water. Never give anything by mouth to an unconscious person. Get medical attention.

SECTION 5: FIRE FIGHTING MEASURES

5.1 FLAMMABLE PROPERTIES

Autoignition temperature	465 °C
Flash Point	-4 °F [<i>Test Method:</i> Closed Cup]
Flammable Limits - LEL	2.6 % volume
Flammable Limits - UEL	12.8 % volume
OSHA Flammability Classification:	Class IB Flammable Liquid

5.2 EXTINGUISHING MEDIA

Use fire extinguishers with class B extinguishing agents (e.g., dry chemical, carbon dioxide).

5.3 PROTECTION OF FIRE FIGHTERS

Special Fire Fighting Procedures: Water may not effectively extinguish fire; however, it should be used to keep fire-exposed containers and surfaces cool and prevent explosive rupture. Wear full protective equipment (Bunker Gear) and a self-contained breathing apparatus (SCBA).

Unusual Fire and Explosion Hazards: Closed containers exposed to heat from fire may build pressure and explode. Extremely flammable liquid and vapor. Vapors may travel long distances along the ground or floor to an ignition source and flash back.

Note: See STABILITY AND REACTIVITY (SECTION 10) for hazardous combustion and thermal decomposition information.

SECTION 6: ACCIDENTAL RELEASE MEASURES

Accidental Release Measures:

Evacuate unprotected and untrained personnel from hazard area. The spill should be cleaned up by qualified personnel. Remove all ignition sources such as flames, smoking materials, and electrical spark sources. Use only non-sparking tools. Ventilate the area with fresh air. For large spill, or spills in confined spaces, provide mechanical ventilation to disperse or exhaust vapors, in accordance with good industrial hygiene practice. Warning! A motor could be an ignition source and could cause flammable gases or vapors in the spill area to burn or explode. Remember, adding an absorbent material does not remove a toxic, corrosivity or flammability hazard. For larger spills, cover drains and build dikes to prevent entry into sewer systems or bodies of water. Collect the resulting residue containing solution. Place in a metal container approved for transportation by appropriate authorities. Dispose of collected material as soon as possible.

Refer to other sections of this MSDS for information regarding physical and health hazards, respiratory protection, ventilation, and personal protective equipment. Call 3M-HELPS line (1-800-364-3577) for more information on handling and managing the spill. Contain spill. Cover spill area with a fire-extinguishing foam designed for use on solvents, such as alcohols and acetone, that can dissolve in water. An AR - AFFF type foam is recommended. Working from around the edges of the spill inward, cover with bentonite, vermiculite, or commercially available inorganic absorbent material. Mix in sufficient absorbent until it appears dry. Collect as much of the spilled material as possible using non-sparking tools. Clean up residue with water. Seal the container.

In the event of a release of this material, the user should determine if the release qualifies as reportable according to local, state, and federal regulations.

SECTION 7: HANDLING AND STORAGE

7.1 HANDLING

Vapors may ignite explosively. May cause flash fire. Prevent build-up of vapors - open all windows and doors. Maintain vapor concentrations below recommended exposure limits. Use only with cross-ventilation. Without adequate ventilation, vapors may settle in low-lying areas. Keep away from heat, sparks, and open flame. Do not smoke or ignite matches, lighters, etc. Contents may be under pressure, open carefully. Ground containers securely when transferring contents. Wear low static or properly grounded shoes. Avoid static discharge. Avoid breathing of vapors, mists or spray. Avoid eye contact with vapors, mists, or spray. Keep out of the reach of children. For industrial or professional use only. Avoid contact with oxidizing agents.

7.2 STORAGE

Store away from acids. Store away from heat. Store out of direct sunlight. Keep container in well-ventilated area. Keep container tightly closed. Store away from oxidizing agents.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1 ENGINEERING CONTROLS

Provide local exhaust ventilation at transfer points. Provide appropriate local exhaust ventilation on open containers. Use general dilution ventilation and/or local exhaust ventilation to control airborne exposures to below Occupational Exposure Limits and/or control mist, vapor, or spray. If ventilation is not adequate, use respiratory protection equipment.

8.2 PERSONAL PROTECTIVE EQUIPMENT (PPE)

8.2.1 Eye/Face Protection

Avoid eye contact with vapors, mists, or spray.

The following eye protection(s) are recommended: Indirect Vented Goggles.

8.2.2 Skin Protection

Avoid skin contact.

Select and use gloves and/or protective clothing to prevent skin contact based on the results of an exposure assessment. Consult with your glove and/or protective clothing manufacturer for selection of appropriate compatible materials.

Gloves made from the following material(s) are recommended: Butyl Rubber, Polyethylene/Ethylene Vinyl Alcohol.

8.2.3 Respiratory Protection

Avoid breathing of vapors, mists or spray.

Select one of the following NIOSH approved respirators based on airborne concentration of contaminants and in accordance with OSHA regulations: Half facepiece or fullface air-purifying respirator with organic vapor cartridges. Consult the current 3M Respiratory Selection Guide for additional information or call 1-800-243-4630 for 3M technical assistance.

8.2.4 Prevention of Swallowing

Do not eat, drink or smoke when using this product. Wash exposed areas thoroughly with soap and water.

8.3 EXPOSURE GUIDELINES

<u>Ingredient</u>	<u>Authority</u>	<u>Type</u>	<u>Limit</u>	<u>Additional Information</u>
ACETONE	ACGIH	TWA	500 ppm	
ACETONE	ACGIH	STEL	750 ppm	
ACETONE	OSHA	TWA	2400 mg/m3	

SOURCE OF EXPOSURE LIMIT DATA:

ACGIH: American Conference of Governmental Industrial Hygienists

CMRG: Chemical Manufacturer Recommended Guideline

OSHA: Occupational Safety and Health Administration

AIHA: American Industrial Hygiene Association Workplace Environmental Exposure Level (WEEL)

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

Odor, Color, Grade:	Pale yellow solution with solvent odor.
General Physical Form:	Liquid
Autoignition temperature	465 °C
Flash Point	-4 °F [<i>Test Method:</i> Closed Cup]
Flammable Limits - LEL	2.6 % volume
Flammable Limits - UEL	12.8 % volume
Boiling point	>=56 °C
Density	0.79 g/ml
Vapor Density	2.0 [<i>Ref Std:</i> AIR=1]
Vapor Pressure	185 mmHg [<i>@ 20 °C</i>]
Specific Gravity	0.79 [<i>Ref Std:</i> WATER=1]
pH	<i>Not Applicable</i>
Melting point	<i>Not Applicable</i>
Solubility in Water	Complete
Evaporation rate	<i>No Data Available</i>
Evaporation rate	Negligible
Hazardous Air Pollutants	0 % weight
Kow - Oct/Water partition coef	<i>No Data Available</i>
Percent volatile	100 % weight
VOC Less H2O & Exempt Solvents	< 40 g/l [<i>Details:</i> Calculated as a low solid adhesive primer per SCAQMD Rule 1168]
Viscosity	1 - 10 centipoise [<i>@ 73.4 °F</i>]

SECTION 10: STABILITY AND REACTIVITY

Stability: Stable.

Materials and Conditions to Avoid:

10.1 Conditions to avoid

Sparks and/or flames, Heat

10.2 Materials to avoid

Strong oxidizing agents

Hazardous Polymerization: Hazardous polymerization will not occur.

Hazardous Decomposition or By-Products

Substance

Carbon monoxide
Carbon dioxide
Irritant Vapors or Gases

Condition

During Combustion
During Combustion
During Combustion

SECTION 11: TOXICOLOGICAL INFORMATION

Please contact the address listed on the first page of the MSDS for Toxicological Information on this material and/or its components.

SECTION 12: ECOLOGICAL INFORMATION

ECOTOXICOLOGICAL INFORMATION

Not determined.

CHEMICAL FATE INFORMATION

Not determined.

SECTION 13: DISPOSAL CONSIDERATIONS

Waste Disposal Method: Incinerate in a permitted hazardous waste incinerator. As a disposal alternative, dispose of waste product in a permitted hazardous waste facility.

EPA Hazardous Waste Number (RCRA): D001 (Ignitable)

Since regulations vary, consult applicable regulations or authorities before disposal.

SECTION 14: TRANSPORT INFORMATION

ID Number(s):

62-6195-0850-0, 62-6195-0855-9, 62-6195-3750-9, 62-6195-7550-9

Please contact the emergency numbers listed on the first page of the MSDS for Transportation Information for this material.

SECTION 15: REGULATORY INFORMATION

US FEDERAL REGULATIONS

Contact 3M for more information.

311/312 Hazard Categories:

Fire Hazard - Yes Pressure Hazard - No Reactivity Hazard - No Immediate Hazard - Yes Delayed Hazard - No

STATE REGULATIONS

Contact 3M for more information.

CHEMICAL INVENTORIES

The components of this product are in compliance with the chemical notification requirements of TSCA.

Contact 3M for more information.

INTERNATIONAL REGULATIONS

Contact 3M for more information.

This MSDS has been prepared to meet the U.S. OSHA Hazard Communication Standard, 29 CFR 1910.1200.

SECTION 16: OTHER INFORMATION

NFPA Hazard Classification

Health: 2 Flammability: 4 Reactivity: 0 Special Hazards: None

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

Revision Changes:

Section 1: Product name was modified.

Page Heading: Product name was modified.

Section 8: Exposure guidelines ingredient information was modified.

Section 6: Release measures information was modified.

Section 6: Release measures information was modified.

Section 6: Release measures information was modified.

Section 8: Exposure guidelines legend was deleted.

DISCLAIMER: The information in this Material Safety Data Sheet (MSDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the MSDS available directly from 3M.

3M MSDSs are available at www.3M.com



Transport Information Document

Date: April 07, 2010

3M ID Number: 62-6195-0850-0

Product Description: 3M(TM) Scotch-Weld Instant Adhesive Accelerator AC452, 2 fl oz Bottle, 10 per case

Transport Protective Service: PROTECTIVE SERVICE NOT REQUIRED

NMFC Item: 043940

NMFC Sub: 00

NMFC Class: 070.0

Flash Point (Closed-cup): -4°F/-20°C

UNITED STATES DEPARTMENT OF TRANSPORTATION - GROUND (U.S. DOT, 49 CFR)

CONSUMER COMMODITY, ORM-D

UNITED STATES DEPARTMENT OF TRANSPORTATION - VESSEL (U.S. DOT, 49 CFR)

CONSUMER COMMODITY, ORM-D

INTERNATIONAL AIR TRANSPORT ASSOCIATION (IATA)

UN1090, ACETONE SOLUTION, 3, II

INTERNATIONAL MARITIME ORGANIZATION (IMO)

UN1090, ACETONE SOLUTION, 3, II, LIMITED QUANTITY, -020C

The classification is authorized by the Competent Authority of the United States of America and may not meet the requirements of other competent authorities.

These transportation classifications are provided as a customer service. AS THE SHIPPER YOU REMAIN RESPONSIBLE FOR COMPLYING WITH ALL THE APPLICABLE LAWS AND REGULATIONS, INCLUDING PROPER TRANSPORTATION CLASSIFICATION AND PACKAGING. 3M's transportation classifications are based on product formulations, packaging, 3M policies and 3M's understanding of applicable current regulations and is valid for the original 3M package only. 3M does not guarantee the accuracy of this classification information. This information applies only to transportation classification and NOT THE PACKAGING, LABELING, OR MARKING REQUIREMENTS. The original 3M package is certified for U.S. ground shipment only. If you are shipping by air or ocean, the package may not meet applicable regulatory requirements.

For Transport Information, please visit 3M.com/Transportinfo
or call 1-800-364-3577 or 651-737-6501 for assistance.