

DOW CORNING CORPORATION

Material Safety Data Sheet

Page: 1 of 8

Version: 1.4

Revision Date: 2005/02/23

DOW CORNING(R) SE 9187 L BLACK

1. PRODUCT AND COMPANY IDENTIFICATION

Dow Corning Corporation
South Saginaw Road
Midland, Michigan 48686

24 Hour Emergency Telephone: (989) 496-5900
Customer Service: (989) 496-6000
Product Disposal Information: (989) 496-6315
CHEMTREC: (800) 424-9300

MSDS No.: 02697751

Revision Date: 2005/02/23

Generic Description: Silicone Sealant
Physical Form: Liquid
Color: Black
Odor: Alcoholic odor

NFPA Profile: Health 1 Flammability 2 Instability/Reactivity 0

Note: NFPA = National Fire Protection Association

2. OSHA HAZARDOUS COMPONENTS

<u>CAS Number</u>	<u>Wt %</u>	<u>Component Name</u>
27858-32-8	1.0 - 5.0	Diisopropoxy di(ethoxyacetoacetyl) titanate
1185-55-3	1.0 - 5.0	Methyltrimethoxysilane
67-63-0	<=0.1	Isopropyl alcohol

The above components are hazardous as defined in 29 CFR 1910.1200.

3. HAZARDS IDENTIFICATION

Potential Health Effects

Acute Effects

Eye: Direct contact may cause mild irritation.

Skin: No significant irritation expected from a single short-term exposure.

Inhalation: Irritates respiratory passages very slightly. Vapor overexposure may cause drowsiness.

Oral: Low ingestion hazard in normal use.

Prolonged/Repeated Exposure Effects

Skin: Repeated or prolonged exposure may cause irritation.

Inhalation: No known applicable information.

DOW CORNING(R) SE 9187 L BLACK

Oral: Repeated ingestion or swallowing large amounts may injure internally.

Signs and Symptoms of Overexposure

No known applicable information.

Medical Conditions Aggravated by Exposure

No known applicable information.

The above listed potential effects of overexposure are based on actual data, results of studies performed upon similar compositions, component data and/or expert review of the product. Please refer to Section 11 for the detailed toxicology information.

4. FIRST AID MEASURES

Eye: Immediately flush with water for 15 minutes.

Skin: No first aid should be needed.

Inhalation: Remove to fresh air. Get medical attention if ill effects persist.

Oral: Get medical attention.

Comments: Treat according to person's condition and specifics of exposure.

5. FIRE FIGHTING MEASURES

Flash Point: 145.4 °F / 63 °C (Seta Closed Cup)

Autoignition Temperature: Not determined.

Flammability Limits in Air: Not determined.

Extinguishing Media: On large fires use dry chemical, foam or water spray. On small fires use carbon dioxide (CO₂), dry chemical or water spray. Water can be used to cool fire exposed containers.

Fire Fighting Measures: Self-contained breathing apparatus and protective clothing should be worn in fighting large fires involving chemicals. Determine the need to evacuate or isolate the area according to your local emergency plan. Use water spray to keep fire exposed containers cool.

Unusual Fire Hazards: None.

Hazardous Decomposition Products

Thermal breakdown of this product during fire or very high heat conditions may evolve the following hazardous decomposition products: Carbon oxides and traces of incompletely burned carbon compounds. Silicon dioxide. Nitrogen oxides. Formaldehyde. Metal oxides.

6. ACCIDENTAL RELEASE MEASURES

DOW CORNING CORPORATION

Material Safety Data Sheet

Page: 3 of 8

Version: 1.4

Revision Date: 2005/02/23

DOW CORNING(R) SE 9187 L BLACK

Containment/Clean up: Determine whether to evacuate or isolate the area according to your local emergency plan. Observe all personal protection equipment recommendations described in Sections 5 and 8. For large spills, provide diking or other appropriate containment to keep material from spreading. If diked material can be pumped, store recovered material in appropriate container. Clean up remaining materials from spill with suitable absorbant. Clean area as appropriate since spilled materials, even in small quantities, may present a slip hazard. Final cleaning may require use of steam, solvents or detergents. Dispose of saturated absorbant or cleaning materials appropriately, since spontaneous heating may occur. Local, state and federal laws and regulations may apply to releases and disposal of this material, as well as those materials and items employed in the cleanup of releases. You will need to determine which federal, state and local laws and regulations are applicable. Sections 13 and 15 of this MSDS provide information regarding certain federal and state requirements.

Note: See section 8 for Personal Protective Equipment for Spills. Call (989) 496-5900, if additional information is required.

7. HANDLING AND STORAGE

Use with adequate ventilation. Product evolves flammable methyl alcohol when exposed to water or humid air. Provide ventilation during use to control exposure within Section 8 guidelines or use air-supplied or self-contained breathing apparatus. Product evolves isopropyl alcohol when exposed to water or humid air. Provide ventilation during use to control exposure within guidelines or use respiratory protection. Avoid eye contact. Avoid breathing vapor. Keep container closed. Do not take internally.

Static electricity will accumulate and may ignite vapors. Prevent a possible fire hazard by bonding and grounding or inert gas purge. Keep container closed and away from heat, sparks, and flame. Keep container closed and store away from water or moisture.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Component Exposure Limits

<u>CAS Number</u>	<u>Component Name</u>	<u>Exposure Limits</u>
1185-55-3	Methyltrimethoxysilane	Dow Corning guide: TWA 50 ppm. Also see methyl alcohol comments.
27858-32-8	Diisopropoxy di(ethoxyacetoacetyl) titanate	See isopropyl alcohol comments.

Methyl alcohol forms on contact with water or humid air. Provide adequate ventilation to control exposures within guidelines of OSHA PEL: TWA 200 ppm and ACGIH TLV-skin: TWA 200 ppm, STEL 250 ppm. Isopropyl alcohol is formed on contact with water or humid air. Provide adequate ventilation to control exposures to within exposure guidelines of OSHA PEL (final rule): TWA 400 ppm, 980 mg/m³ and ACGIH TLV: TWA 200 ppm, STEL 400 ppm.

Engineering Controls

Local Ventilation: Recommended.

DOW CORNING(R) SE 9187 L BLACK

General Ventilation: Recommended.

Personal Protective Equipment for Routine Handling

Eyes: Use proper protection - safety glasses as a minimum.

Skin: Washing at mealtime and end of shift is adequate.

Suitable Gloves: No special protection needed.

Inhalation: Use respiratory protection unless adequate local exhaust ventilation is provided or exposure assessment demonstrates that exposures are within recommended exposure guidelines. IH personnel can assist in judging the adequacy of existing engineering controls.

Suitable Respirator: General and local exhaust ventilation is recommended to maintain vapor exposures below recommended limits. Where concentrations are above recommended limits or are unknown, appropriate respiratory protection should be worn. Follow OSHA respirator regulations (29 CFR 1910.134) and use NIOSH/MSHA approved respirators.

Personal Protective Equipment for Spills

Eyes: Use full face respirator.

Skin: Washing at mealtime and end of shift is adequate.

Inhalation/Suitable Respirator: Respiratory protection recommended. Follow OSHA Respirator Regulations (29 CFR 1910.134) and use NIOSH/MHSA approved respirators. Protection provided by air purifying respirators against exposure to any hazardous chemical is limited. Use a positive pressure air supplied respirator if there is any potential for uncontrolled release, exposure levels are unknown, or any other circumstance where air purifying respirators may not provide adequate protection.

Precautionary Measures: Avoid eye contact. Avoid breathing vapor. Keep container closed. Do not take internally. Use reasonable care.

Comments: Product evolves flammable methyl alcohol when exposed to water or humid air. Provide ventilation during use to control exposure within Section 8 guidelines or use air-supplied or self-contained breathing apparatus. Product evolves isopropyl alcohol when exposed to water or humid air. Provide ventilation during use to control exposure within guidelines or use respiratory protection.

Note: These precautions are for room temperature handling. Use at elevated temperature or aerosol/spray applications may require added precautions.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical Form: Liquid

Color: Black

Odor: Alcoholic odor

Specific Gravity @ 25°C: 1.00

DOW CORNING(R) SE 9187 L BLACK

Viscosity: 10 Poise

Freezing/Melting Point: Not determined.

Boiling Point: > 100 °C

Vapor Pressure @ 25°C: Not determined.

Vapor Density: Not determined.

Solubility in Water: Not determined.

pH: Not determined.

Volatile Content: Not determined.

Note: The above information is not intended for use in preparing product specifications. Contact Dow Corning before writing specifications.

10. STABILITY AND REACTIVITY

Chemical Stability: Stable.

Hazardous Polymerization: Hazardous polymerization will not occur.

Conditions to Avoid: None.

Materials to Avoid: Oxidizing material can cause a reaction. Water, moisture, or humid air can cause hazardous vapors to form as described in Section 8.

11. TOXICOLOGICAL INFORMATION**Component Toxicology Information**

This material contains methyltrimethoxysilane (MTMS). MTMS was evaluated in a combined repeated-dose toxicity study that included screening tests for reproductive and developmental toxicity (OECD 422). Sprague-Dawley rats were treated (oral route, corn oil as carrier) daily at dose levels of 0, 50, 250, and 1000 mg MTMS/kg body weight. Test article effects on organ weight were limited to increased liver weight for both males and females in the top two dose levels.

Histomorphological findings included increased hepatocellular hypertrophy (both sexes) and increased periportal vacuolation (females only) in the top two dose levels. Thymus weight was decreased in males in the top two dose groups. The thymus appeared normal histomorphologically. Other test article related histomorphological changes included increased incidence of thyroid follicular cell hyperplasia/hypertrophy and severity in males and females in the top two dose levels. There was also an increased incidence of hyperplasia/hypertrophy, apoptosis, and lymphocytic infiltration in the zona reticularis of the adrenal glands in high-dose females and acanthocytosis in high-dose males and females. Clinical pathology evaluations demonstrated a marked prolongation in prothrombin time for males in the top two dose levels. Marked elevation in blood platelet count was observed in both males and females at the high dose. Serum total protein was elevated in high-dose males and in females from the top two dose levels. Serum total cholesterol was elevated in females from the top two dose levels. There were no test article related effects on any of the reproductive and developmental endpoints. Because this study is considered to be a screening of repeated-dose and reproductive/developmental toxicity, the results do not provide sufficient information needed to interpret potential relevance to human health and are not indicative of a specific toxicity. This type of study is commonly used as a screening study to determine whether further testing should be conducted. Also, this study was conducted via the oral route of exposure, which is not a typical route of exposure for either manufacturing or end use applications of MTMS. A longer-term study by a more relevant route of exposure (inhalation) is being conducted to understand these preliminary findings.

DOW CORNING(R) SE 9187 L BLACK

Special Hazard Information on Components

No known applicable information.

12. ECOLOGICAL INFORMATION**Environmental Fate and Distribution**

Complete information is not yet available.

Environmental Effects

Complete information is not yet available.

Fate and Effects in Waste Water Treatment Plants

Complete information is not yet available.

Ecotoxicity Classification Criteria

Hazard Parameters (LC50 or EC50)	High	Medium	Low
Acute Aquatic Toxicity (mg/L)	<=1	>1 and <=100	>100
Acute Terrestrial Toxicity	<=100	>100 and <= 2000	>2000

This table is adapted from "Environmental Toxicology and Risk Assessment", ASTM STP 1179, p.34, 1993.

This table can be used to classify the ecotoxicity of this product when ecotoxicity data is listed above. Please read the other information presented in the section concerning the overall ecological safety of this material.

13. DISPOSAL CONSIDERATIONS**RCRA Hazard Class (40 CFR 261)**

When a decision is made to discard this material, as received, is it classified as a hazardous waste?

State or local laws may impose additional regulatory requirements regarding disposal.

Call (989) 496-6315, if additional information is required.

14. TRANSPORT INFORMATION**DOT Road Shipment Information (49 CFR 172.101)**

Proper Shipping Name: COMBUSTIBLE LIQUID, N.O.S.

Hazard Technical Name: METHOXYSILANE/ORGANOTITANATE

Hazard Class: COMBUSTIBLE LIQUID

UN/NA Number: NA1993

DOW CORNING(R) SE 9187 L BLACK

Packing Group: III

Remarks: Above applies only to containers over 119 gallons or 450 liters.

Ocean Shipment (IMDG)

Not subject to IMDG code.

Air Shipment (IATA)

Not subject to IATA regulations.

15. REGULATORY INFORMATION

Contents of this MSDS comply with the OSHA Hazard Communication Standard 29 CFR 1910.1200.

TSCA Status: All chemical substances in this material are included on or exempted from listing on the TSCA Inventory of Chemical Substances.

EPA SARA Title III Chemical Listings**Section 302 Extremely Hazardous Substances (40 CFR 355):**

None.

Section 304 CERCLA Hazardous Substances (40 CFR 302):

None.

Section 311/312 Hazard Class (40 CFR 370):Acute: Yes
Chronic: No
Fire: Yes
Pressure: No
Reactive: No**Section 313 Toxic Chemicals (40 CFR 372):**

None present or none present in regulated quantities.

Supplemental State Compliance Information**California**

Warning: This product contains the following chemical(s) listed by the State of California under the Safe Drinking Water and Toxic Enforcement Act of 1986 (Proposition 65) as being known to cause cancer, birth defects or other reproductive harm.

None known.

Massachusetts

DOW CORNING(R) SE 9187 L BLACK

No ingredient regulated by MA Right-to-Know Law present.

New Jersey

<u>CAS Number</u>	<u>Wt %</u>	<u>Component Name</u>
142982-20-5	40.0 - 70.0	Dimethyl siloxane, trimethoxysilyloxy-terminated
472976-92-4	30.0 - 60.0	Dimethyl siloxane mono-trimethoxysiloxy-terminated
63148-62-9	10.0 - 30.0	Polydimethylsiloxane
68909-20-6	3.0 - 7.0	Trimethylated silica
27858-32-8	1.0 - 5.0	Diisopropoxy di(ethoxyacetoacetyl) titanate
1185-55-3	1.0 - 5.0	Methyltrimethoxysilane
1333-86-4	<1.0	Carbon black

Pennsylvania

<u>CAS Number</u>	<u>Wt %</u>	<u>Component Name</u>
142982-20-5	40.0 - 70.0	Dimethyl siloxane, trimethoxysilyloxy-terminated
472976-92-4	30.0 - 60.0	Dimethyl siloxane mono-trimethoxysiloxy-terminated
63148-62-9	10.0 - 30.0	Polydimethylsiloxane
68909-20-6	3.0 - 7.0	Trimethylated silica

16. OTHER INFORMATION

Prepared by: Dow Corning Corporation

These data are offered in good faith as typical values and not as product specifications. No warranty, either expressed or implied, is hereby made. The recommended industrial hygiene and safe handling procedures are believed to be generally applicable. However, each user should review these recommendations in the specific context of the intended use and determine whether they are appropriate.

(R) indicates Registered Trademark