



## Material Safety Data Sheet

Copyright, 2010, 3M Company. All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

### SECTION 1: PRODUCT AND COMPANY IDENTIFICATION

**PRODUCT NAME:** 3M™ Nexcare™ Moisturizing Hand Sanitizer

**MANUFACTURER:** 3M

**DIVISION:** Skin & Wound Care Division

**ADDRESS:** 3M Center  
St. Paul, MN 55144-1000

EMERGENCY PHONE: 1-800-364-3577 or (651) 737-6501 (24 hours)

**Issue Date:** 04/30/10

**Supersedes Date:** 03/27/09

**Document Group:** 20-9656-8

**Product Use:**

Intended Use: Hand sanitizer.

### SECTION 2: INGREDIENTS

<u>Ingredient</u>	<u>C.A.S. No.</u>	<u>% by Wt</u>
Ethyl alcohol w/w	64-17-5	50 - 70
Water	7732-18-5	25 - 35
Polyethylene glycol	25322-68-3	< 3
Docosyl alcohol	661-19-8	< 2
Fatty acids	103213-20-3	< 2
Squalane	111-01-3	< 2
Alcohols	26636-40-8	< 2

### SECTION 3: HAZARDS IDENTIFICATION

#### 3.1 EMERGENCY OVERVIEW

**Odor, Color, Grade:** White viscous liquid with slight alcohol odor.

**General Physical Form:** Liquid

**Immediate health, physical, and environmental hazards:** Flammable liquid and vapor. Vapors may travel long distances along the ground or floor to an ignition source and flash back. Closed containers exposed to heat from fire may build pressure and explode.

May cause target organ effects. Contains a chemical or chemicals which can cause birth defects or other reproductive harm.

### 3.2 POTENTIAL HEALTH EFFECTS

#### Eye Contact:

Moderate Eye Irritation: Signs/symptoms may include redness, swelling, pain, tearing, and blurred or hazy vision.

#### Skin Contact:

No health effects are expected.

#### Inhalation:

Respiratory Tract Irritation: Signs/symptoms may include cough, sneezing, nasal discharge, headache, hoarseness, and nose and throat pain.

May be absorbed following inhalation and cause target organ effects.

#### Ingestion:

Gastrointestinal Irritation: Signs/symptoms may include abdominal pain, stomach upset, nausea, vomiting and diarrhea.

May be absorbed following ingestion and cause target organ effects.

#### Target Organ Effects:

Central Nervous System (CNS) Depression: Signs/symptoms may include headache, dizziness, drowsiness, incoordination, nausea, slowed reaction time, slurred speech, giddiness, and unconsciousness.

Prolonged or repeated exposure may cause:

Liver Effects: Signs/symptoms may include loss of appetite, weight loss, fatigue, weakness, abdominal tenderness and jaundice.

Contains a chemical or chemicals which can cause birth defects or other reproductive harm.

NOTE: This product contains ethanol. There are data associating human consumption of alcoholic beverages (ethanol) with developmental toxicity. This is not an expected effect during the foreseeable use of this product.

#### Carcinogenicity:

Contains a chemical or chemicals which can cause cancer.

NOTE: This product contains ethanol. In IARC published Monograph No. 44, entitled, "Alcohol Drinking", the carcinogenicity of ethanol was determined based on chronic exposure to ethanol through human consumption of alcoholic beverages. This is not an expected effect during the foreseeable use of this product.

#### Ingredient

Ethyl alcohol w/w

#### C.A.S. No.

64-17-5

#### Class Description

Grp. 1: Carcinogenic to humans

#### Regulation

International Agency for Research on Cancer

## SECTION 4: FIRST AID MEASURES

### 4.1 FIRST AID PROCEDURES

The following first aid recommendations are based on an assumption that appropriate personal and industrial hygiene practices are followed.

**Eye Contact:** Flush eyes with large amounts of water. If signs/symptoms persist, get medical attention.

**Skin Contact:** No need for first aid is anticipated.

**Inhalation:** Remove person to fresh air. If signs/symptoms develop, get medical attention.

**If Swallowed:** Do not induce vomiting unless instructed to do so by medical personnel. Give victim two glasses of water. Never give anything by mouth to an unconscious person. Get medical attention.

## SECTION 5: FIRE FIGHTING MEASURES

### 5.1 FLAMMABLE PROPERTIES

<b>Autoignition temperature</b>	1,470 °F
<b>Flash Point</b>	69.8 °F
<b>Flammable Limits - LEL</b>	3.28 % volume
<b>Flammable Limits - UEL</b>	19 % volume
<b>OSHA Flammability Classification:</b>	Class IB Flammable Liquid

### 5.2 EXTINGUISHING MEDIA

Use fire extinguishers with class B extinguishing agents (e.g., dry chemical, carbon dioxide).

### 5.3 PROTECTION OF FIRE FIGHTERS

**Special Fire Fighting Procedures:** Wear full protective equipment (Bunker Gear) and a self-contained breathing apparatus (SCBA). Water may not effectively extinguish fire; however, it should be used to keep fire-exposed containers and surfaces cool and prevent explosive rupture.

**Unusual Fire and Explosion Hazards:** Extremely flammable liquid and vapor. Vapors may travel long distances along the ground or floor to an ignition source and flash back. Closed containers exposed to heat from fire may build pressure and explode.

**Note:** See STABILITY AND REACTIVITY (SECTION 10) for hazardous combustion and thermal decomposition information.

## SECTION 6: ACCIDENTAL RELEASE MEASURES

### Accidental Release Measures:

Evacuate unprotected and untrained personnel from hazard area. The spill should be cleaned up by qualified personnel. For larger spills, cover drains and build dikes to prevent entry into sewer systems or bodies of water. Collect the resulting residue containing solution. Place in a metal container approved for transportation by appropriate authorities. Dispose of collected material as soon as possible.

Refer to other sections of this MSDS for information regarding physical and health hazards, respiratory protection, ventilation, and personal protective equipment. Call 3M-HELPS line (1-800-364-3577) for more information on handling and managing the spill. Contain spill. Working from around the edges of the spill inward, cover with bentonite, vermiculite, or commercially available

inorganic absorbent material. Mix in sufficient absorbent until it appears dry. Collect as much of the spilled material as possible using non-sparking tools. Clean up residue with an appropriate solvent selected by a qualified and authorized person. Ventilate the area with fresh air. Read and follow safety precautions on the solvent label and MSDS.

**In the event of a release of this material, the user should determine if the release qualifies as reportable according to local, state, and federal regulations.**

**SECTION 7: HANDLING AND STORAGE**

**7.1 HANDLING**

Avoid eye contact. Do not ingest. Keep away from heat, sparks, open flame, pilot lights and other sources of ignition. No smoking while handling this material. Keep out of the reach of children.

**7.2 STORAGE**

Store away from heat. Keep container tightly closed.

**SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION**

**8.1 ENGINEERING CONTROLS**

Use in a well-ventilated area.

**8.2 PERSONAL PROTECTIVE EQUIPMENT (PPE)**

**8.2.1 Eye/Face Protection**

Avoid eye contact.

**8.2.2 Skin Protection**

Not applicable.

**8.2.3 Respiratory Protection**

Under normal use conditions, airborne exposures are not expected to be significant enough to require respiratory protection.

**8.2.4 Prevention of Swallowing**

Do not ingest.

**8.3 EXPOSURE GUIDELINES**

<u>Ingredient</u>	<u>Authority</u>	<u>Type</u>	<u>Limit</u>	<u>Additional Information</u>
Ethyl alcohol w/w	ACGIH	STEL	1000 ppm	Table A3
Ethyl alcohol w/w	OSHA	TWA	1900 mg/m3	
Polyethylene glycol	AIHA	TWA, as particulate	10 mg/m3	
POLYETHYLENE GLYCOLS	AIHA	TWA, as particulate	10 mg/m3	

SOURCE OF EXPOSURE LIMIT DATA:

ACGIH: American Conference of Governmental Industrial Hygienists

CMRG: Chemical Manufacturer Recommended Guideline  
 OSHA: Occupational Safety and Health Administration  
 AIHA: American Industrial Hygiene Association Workplace Environmental Exposure Level (WEEL)

## SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

<b>Odor, Color, Grade:</b>	White viscous liquid with slight alcohol odor.
<b>General Physical Form:</b>	Liquid
<b>Autoignition temperature</b>	1,470 °F
<b>Flash Point</b>	69.8 °F
<b>Flammable Limits - LEL</b>	3.28 % volume
<b>Flammable Limits - UEL</b>	19 % volume
<b>Boiling point</b>	172 °F
<b>Vapor Density</b>	1.6 [ <i>Ref Std: AIR=1</i> ]
<b>Specific Gravity</b>	0.83 [ <i>Ref Std: WATER=1</i> ]
<b>pH</b>	6
<b>Melting point</b>	<i>Not Applicable</i>
<b>Solubility in Water</b>	Moderate
<b>Evaporation rate</b>	1.4 [ <i>Ref Std: BUOAC=1</i> ]
<b>Volatile Organic Compounds</b>	496 g/l
<b>Kow - Oct/Water partition coef</b>	<i>No Data Available</i>
<b>Percent volatile</b>	90 % weight
<b>VOC Less H2O &amp; Exempt Solvents</b>	630 g/l
<b>Viscosity</b>	50000 - 250000 centipoise

## SECTION 10: STABILITY AND REACTIVITY

**Stability:** Stable.

**Materials and Conditions to Avoid:**

**10.1 Conditions to avoid**

Heat

**10.2 Materials to avoid**

None known

**Hazardous Polymerization:** Hazardous polymerization will not occur.

### Hazardous Decomposition or By-Products

<u>Substance</u>	<u>Condition</u>
Carbon monoxide	During Combustion

Carbon dioxide

During Combustion

## SECTION 11: TOXICOLOGICAL INFORMATION

Please contact the address listed on the first page of the MSDS for Toxicological Information on this material and/or its components.

## SECTION 12: ECOLOGICAL INFORMATION

### ECOTOXICOLOGICAL INFORMATION

Not determined.

### CHEMICAL FATE INFORMATION

Not determined.

## SECTION 13: DISPOSAL CONSIDERATIONS

**Waste Disposal Method:** Incinerate in a permitted hazardous waste incinerator. As a disposal alternative, dispose of waste product in a permitted hazardous waste facility.

**EPA Hazardous Waste Number (RCRA):** D001 (Ignitable)

Since regulations vary, consult applicable regulations or authorities before disposal.

## SECTION 14: TRANSPORT INFORMATION

### ID Number(s):

70-0711-7620-3, 70-0711-7621-1, 70-0711-7750-8, 70-0712-0550-7, 70-0712-2082-9, 70-0713-2013-2, 70-0713-5127-7

Please contact the emergency numbers listed on the first page of the MSDS for Transportation Information for this material.

## SECTION 15: REGULATORY INFORMATION

### US FEDERAL REGULATIONS

Contact 3M for more information.

### 311/312 Hazard Categories:

Fire Hazard - Yes    Pressure Hazard - No    Reactivity Hazard - No    Immediate Hazard - Yes    Delayed Hazard - Yes

## STATE REGULATIONS

Contact 3M for more information.

## CHEMICAL INVENTORIES

This material contains one or more substances not listed on the TSCA Inventory. Commercial use of this material is regulated by the FDA.

Contact 3M for more information.

## INTERNATIONAL REGULATIONS

Contact 3M for more information.

**This MSDS has been prepared to meet the U.S. OSHA Hazard Communication Standard, 29 CFR 1910.1200.**

## SECTION 16: OTHER INFORMATION

### NFPA Hazard Classification

**Health:** 1 **Flammability:** 3 **Reactivity:** 0 **Special Hazards:** None

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

### Revision Changes:

Copyright was modified.

Section 9: Property description for optional properties was modified.

Section 14: ID Number(s) Template 1 was modified.

Section 2: Ingredient table was modified.

Section 8: Exposure guidelines ingredient information was modified.

Section 3: Carcinogenicity table was modified.

Section 10.1 Conditions to avoid heading was added.

Section 10.2 Materials to avoid heading was added.

Section 6: Personal precautions information was added.

Section 6: Environmental procedures information was added.

Section 6: Methods for cleaning up information was added.

Section 10: Materials to avoid physical property was added.

Section 10: Conditions to avoid physical property was added.

Section 6: Release measures information was deleted.

Section 10: Materials and conditions to avoid physical property was deleted.

DISCLAIMER: The information in this Material Safety Data Sheet (MSDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the MSDS available directly from 3M.

**3M MSDSs are available at [www.3M.com](http://www.3M.com)**





# Transport Information Document

**Date:** August 20, 2010

**3M ID Number:** 70-0711-7621-1

**Product Description:** Nexcare(TM) Moisturizing Hand Sanitizer H9222, 16 oz. pump

**Transport Protective Service:** MAINTAIN TEMP BELOW 80F (27C)

**NMFC Item:** 059220      **NMFC Sub:** 00      **NMFC Class:** 065.0

**Flash Point (Closed-cup):** 70°F/21°C

## UNITED STATES DEPARTMENT OF TRANSPORTATION - GROUND (U.S. DOT, 49 CFR)

CONSUMER COMMODITY, ORM-D

## UNITED STATES DEPARTMENT OF TRANSPORTATION - VESSEL (U.S. DOT, 49 CFR)

CONSUMER COMMODITY, ORM-D

## INTERNATIONAL AIR TRANSPORT ASSOCIATION (IATA)

UN1170, ETHANOL SOLUTION, 3, II

## INTERNATIONAL MARITIME ORGANIZATION (IMO)

UN1170, ETHANOL SOLUTION, 3, II, LIMITED QUANTITY, +021C

The classification is authorized by the Competent Authority of the United States of America and may not meet the requirements of other competent authorities.

These transportation classifications are provided as a customer service. AS THE SHIPPER YOU REMAIN RESPONSIBLE FOR COMPLYING WITH ALL THE APPLICABLE LAWS AND REGULATIONS, INCLUDING PROPER TRANSPORTATION CLASSIFICATION AND PACKAGING. 3M's transportation classifications are based on product formulations, packaging, 3M policies and 3M's understanding of applicable current regulations and is valid for the original 3M package only. 3M does not guarantee the accuracy of this classification information. This information applies only to transportation classification and NOT THE PACKAGING, LABELING, OR MARKING REQUIREMENTS. The original 3M package is certified for U.S. ground shipment only. If you are shipping by air or ocean, the package may not meet applicable regulatory requirements.

For Transport Information, please visit [3M.com/Transportinfo](http://3M.com/Transportinfo)  
or call 1-800-364-3577 or 651-737-6501 for assistance.