

Material Safety Data Sheet



Revision Number: 003.2

Issue date: 01/20/2012

1. PRODUCT AND COMPANY IDENTIFICATION

Product name: Color Guard® Black Tough Rubber Coating
Product type: Coating
Company address: Henkel Corporation
One Henkel Way
Rocky Hill, Connecticut 06067

IDH number: 338124
Item number: 34979
Region: United States
Contact information:
Telephone: 860.571.5100
Emergency telephone: 860.571.5100
Internet: www.henkeln.com

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW

Physical state: liquid
Color: Black
Odor: Solvent

HMIS:
HEALTH: *2
FLAMMABILITY: 3
PHYSICAL HAZARD: 1
Personal Protection: See MSDS Section 8

DANGER: EXTREMELY FLAMMABLE LIQUID AND VAPOR.
MAY BE HARMFUL IF SWALLOWED OR INHALED.
MAY CAUSE EYE AND RESPIRATORY TRACT IRRITATION.

Relevant routes of exposure: Skin, Inhalation, Eyes, Ingestion

Potential Health Effects

Inhalation: Vapors may cause headaches, nausea, dizziness and respiratory tract irritation. Reports have associated repeated and prolonged overexposure to solvents with permanent brain and nervous system damage. Prolonged exposure to solvents may cause adverse effects to the liver, urinary, and reproductive systems.

Skin contact: Contact may dry the skin; prolonged contact may cause moderate irritation.

Eye contact: Vapors may irritate eyes. Contact with eyes will cause irritation. Contact with eyes will cause irritation.

Ingestion: May be harmful if swallowed.

Existing conditions aggravated by exposure: Eye, skin, and respiratory disorders. Heart disease. Pulmonary diseases. Kidney disease.

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

See Section 11 for additional toxicological information.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous components	CAS NUMBER	%
Solvent naphtha, petroleum, light aliph.	64742-89-8	30 - 60
n-Hexane	110-54-3	10 - 30
Xylenes	1330-20-7	10 - 30
Acetone	67-64-1	5 - 10
Ethylbenzene	100-41-4	1 - 5
Silica, amorphous, fumed, crystal-free	112945-52-5	1 - 5
Carbon black	1333-86-4	0.1 - 1

IDH number: 338124

Product name: Color Guard® Black Tough Rubber Coating

4. FIRST AID MEASURES

Inhalation:	Move to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. If symptoms develop and persist, get medical attention.
Skin contact:	Remove contaminated clothing and footwear. Immediately flush skin with plenty of water (using soap, if available). Wash clothing before reuse. If symptoms develop and persist, get medical attention.
Eye contact:	Immediately flush eyes with plenty of water for at least 15 minutes. Get medical attention.
Ingestion:	Do not induce vomiting. Keep individual calm. Never give anything by mouth to an unconscious person. If symptoms develop and persist, get medical attention.

5. FIRE FIGHTING MEASURES

Flash point:	-23 °C (-9.4 °F)
Autoignition temperature:	Not available.
Flammable/Explosive limits - lower:	Not available.
Flammable/Explosive limits - upper:	Not available.
Extinguishing media:	Foam, extinguishing powder, carbon dioxide.
Special firefighting procedures:	Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.
Unusual fire or explosion hazards:	In the event of a fire, carbon monoxide (CO) and carbon dioxide (CO ₂) can be released. In case of fire, keep containers cool with water spray.
Hazardous combustion products:	Oxides of carbon, oxides of nitrogen, irritating organic vapors.

6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

Environmental precautions:	Do not allow product to enter sewer or waterways.
Clean-up methods:	Remove all sources of ignition. Ensure adequate ventilation. Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Store in a closed container until ready for disposal.

7. HANDLING AND STORAGE

Handling:	Avoid contact with skin and clothing. Avoid breathing vapors or mists of this product. Keep away from heat, spark and flame.
Storage:	For safe storage, store at or below 48 °C (118.4 °F) Keep in a cool, well ventilated area away from heat, sparks and open flame. Keep container tightly closed until ready for use.

For information on product shelf life contact Henkel Customer Service at (800) 243-4874.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous components	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Solvent naphtha, petroleum, light aliph.	None	None	None	None
n-Hexane	(SKIN) 50 ppm TWA	500 ppm (1,800 mg/m3) TWA	None	None
Xylenes	100 ppm TWA 150 ppm STEL	100 ppm (435 mg/m3) TWA	None	None
Acetone	500 ppm TWA 750 ppm STEL	1,000 ppm (2,400 mg/m3) TWA	None	None
Ethylbenzene	20 ppm TWA	100 ppm (435 mg/m3) TWA	None	None
Silica, amorphous, fumed, crystal-free	10 mg/m3 TWA Inhalable dust. 3 mg/m3 TWA Respirable fraction.	20 MPPCF TWA 0.8 mg/m3 TWA	None	None
Carbon black	3.5 mg/m3 TWA 3 mg/m3 TWA Inhalable fraction.	3.5 mg/m3 TWA	None	None

Engineering controls:	Use local ventilation if general ventilation is insufficient to maintain vapor concentration below established exposure limits.
Respiratory protection:	Use NIOSH approved respirator if there is potential to exceed exposure limit(s).
Eye/face protection:	Safety goggles or safety glasses with side shields.
Skin protection:	Chemical resistant, impermeable gloves.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state:	liquid
Color:	Black
Odor:	Solvent
Odor threshold:	Not available.
pH:	Not available.
Vapor pressure:	185 mm hg (20 °C (68°F))
Boiling point/range:	56.1 - 141.1 °C (133°F - 286°F)
Melting point/ range:	Not available.
Specific gravity:	0.83
Vapor density:	> 1
Flash point:	-23 °C (-9.4 °F)
Flammable/Explosive limits - lower:	Not available.
Flammable/Explosive limits - upper:	Not available.
Autoignition temperature:	Not available.
Evaporation rate:	Greater than butyl acetate.
Solubility in water:	Insoluble
Partition coefficient (n-octanol/water):	Not available.
VOC content:	67.0 %; 556 g/l

10. STABILITY AND REACTIVITY

Stability:	Stable
Hazardous reactions:	Will not occur.
Hazardous decomposition products:	None
Incompatible materials:	Strong acids and strong bases. Strong oxidizing agents. Amines. Alkali metals. Halogenated compounds.
Conditions to avoid:	Store away from incompatible materials. Heat, flames, sparks and other sources of ignition.

11. TOXICOLOGICAL INFORMATION

Hazardous components	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Solvent naphtha, petroleum, light aliph.	No	No	No
n-Hexane	No	No	No
Xylenes	No	No	No
Acetone	No	No	No
Ethylbenzene	No	Group 2B	No
Silica, amorphous, fumed, crystal-free	No	No	No
Carbon black	No	Group 2B	No

Hazardous components	Health Effects/Target Organs
Solvent naphtha, petroleum, light aliph.	Irritant
n-Hexane	Developmental, Irritant, Lung, Nervous System, Reproductive
Xylenes	Cardiac, Central nervous system, Irritant, Kidney, Liver
Acetone	Blood, Central nervous system, Irritant, Reproductive
Ethylbenzene	Irritant, Central nervous system
Silica, amorphous, fumed, crystal-free	Nuisance dust
Carbon black	Respiratory, Some evidence of carcinogenicity

12. ECOLOGICAL INFORMATION

Ecological information: Not available.

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Follow all local, state, federal and provincial regulations for disposal.

Hazardous waste number: D001: Ignitable.

14. TRANSPORT INFORMATION

The shipping classifications in this sections are for non-bulk packaging only (unless otherwise specified). Shipping classification may be different for bulk packaging.

U.S. Department of Transportation Ground (49 CFR)

Proper shipping name: Coating solution
Hazard class or division: 3
Identification number: UN 1139
Packing group: II
DOT Reportable quantity: Xylene (mixed), Benzene

International Air Transportation (ICAO/IATA)

Proper shipping name: Coating solution
Hazard class or division: 3
Identification number: UN 1139
Packing group: II

Water Transportation (IMO/IMDG)

Proper shipping name: COATING SOLUTION
Hazard class or division: 3
Identification number: UN 1139
Packing group: II

15. REGULATORY INFORMATION

United States Regulatory Information

TSCA 8 (b) Inventory Status:	All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.
TSCA 12(b) Export Notification:	Xylenes (CAS# 1330-20-7).
CERCLA/SARA Section 302 EHS:	None above reporting de minimus
CERCLA/SARA Section 311/312:	Immediate Health, Delayed Health, Fire
CERCLA/SARA 313:	This product contains the following toxic chemicals subject to the reporting requirements of section 313 of the Emergency Planning and Community Right-To-Know Act of 1986 (40 CFR 372). Ethylbenzene (CAS# 100-41-4). n-Hexane (CAS# 110-54-3). Xylenes (CAS# 1330-20-7).
CERCLA Reportable quantity:	n-Hexane (CAS# 110-54-3) 5,000 lbs. (2,270 kg) Xylenes (CAS# 1330-20-7) 100 lbs. (45.4 kg) Ethylbenzene (CAS# 100-41-4) 1,000 lbs. (454 kg)
California Proposition 65:	This product contains a chemical known in the State of California to cause cancer. This product contains a chemical known to the State of California to cause birth defects or other reproductive harm.

Canada Regulatory Information

CEPA DSL/NDSL Status:	All components are listed on or are exempt from listing on the Canadian Domestic Substances List.
WHMIS hazard class:	B.2, D.2.A, D.2.B

16. OTHER INFORMATION

This material safety data sheet contains changes from the previous version in sections: New Material Safety Data Sheet format.

Prepared by: Lou Fabrizio, Regulatory Affairs Specialist

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.