

## Safety data sheet

### SECTION 1. Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

Product name **AS1703**

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use **Adhesive sealant.**

#### 1.3. Details of the supplier of the safety data sheet

Name **ACC Silicones LTD**  
Full address **Amber House Showground Road**  
District and Country **TA6 6AJ Bridgwater (Somerset)**  
**England**  
Tel. **+44(0)1278411400**  
Fax **+44(0)1278411444**

e-mail address of the competent person responsible for the Safety Data Sheet **sean.stoodley@acc-silicones.com**

#### 1.4. Emergency telephone number

For urgent inquiries refer to **+44(0)1278411400**

### SECTION 2. Hazards identification.

#### 2.1. Classification of the substance or mixture.

The product is classified as hazardous pursuant to the provisions set forth in EC Regulation 1272/2008 (CLP) (and subsequent amendments and supplements). The product thus requires a safety datasheet that complies with the provisions of EC Regulation 1907/2006 and subsequent amendments.

Any additional information concerning the risks for health and/or the environment are given in sections 11 and 12 of this sheet.

##### 2.1.1. Regulation 1272/2008 (CLP) and following amendments and adjustments.

Hazard classification and indication:  
Skin Sens. 1 H317

##### 2.1.2. 67/548/EEC and 1999/45/EC Directives and following amendments and adjustments.

Danger Symbols: Xi

R phrases: 43

The full wording of the Risk (R) and hazard (H) phrases is given in section 16 of the sheet.

#### 2.2. Label elements.

Hazard labelling pursuant to EC Regulation 1272/2008 (CLP) and subsequent amendments and supplements.

Hazard pictograms:



Signal words: Warning

Hazard statements:  
**H317** May cause an allergic skin reaction.

Precautionary statements:



# ACC Silicones LTD

## AS1703

Revision nr.3  
Dated 24/1/2014  
Printed on 24/1/2014  
Page n. 2 / 7

EN

### SECTION 2. Hazards identification. ... / >>

**P280** Wear protective gloves / protective clothing / eye protection / face protection.  
**P302+P352** IF ON SKIN: Wash with plenty of soap and water.  
**P333+P313** If skin irritation or rash occurs: Get medical advice / attention.

**Contains:** TRIMETHOXY (METHYL) SILANE

#### 2.3. Other hazards.

Information not available.

### SECTION 3. Composition/information on ingredients.

#### 3.1. Substances.

Information not relevant.

#### 3.2. Mixtures.

**Contains:**

Identification.	Conc. %.	Classification 67/548/EEC.	Classification 1272/2008 (CLP).
<b>TRIMETHOXY (METHYL) SILANE</b>			
CAS. 1185-55-3	1 - 5	F R11, Xi R43	Flam. Liq. 2 H225, Skin Sens. 1 H317
EC. 214-685-0			
INDEX. -			
<b>METHANOL</b>			
CAS. 67-56-1	0 - 0.1	F R11, T R23/24/25, T R39/23/24/25	Flam. Liq. 2 H225, Acute Tox. 3 H301, Acute Tox. 3 H311, Acute Tox. 3 H331, STOT SE 1 H370
EC. 200-659-6			
INDEX. 603-001-00-X			

Note: Upper limit is not included into the range.

The full wording of the Risk (R) and hazard (H) phrases is given in section 16 of the sheet.

T+ = Very Toxic(T+), T = Toxic(T), Xn = Harmful(Xn), C = Corrosive(C), Xi = Irritant(Xi), O = Oxidizing(O), E = Explosive(E), F+ = Extremely Flammable(F+), F = Highly Flammable(F), N = Dangerous for the Environment(N)

### SECTION 4. First aid measures.

#### 4.1. Description of first aid measures.

Not specifically necessary. Observance of good industrial hygiene is recommended.

#### 4.2. Most important symptoms and effects, both acute and delayed.

No episodes of damage to health ascribable to the product have been reported.

#### 4.3. Indication of any immediate medical attention and special treatment needed.

Information not available.

### SECTION 5. Firefighting measures.

#### 5.1. Extinguishing media.

SUITABLE EXTINGUISHING EQUIPMENT

Extinguishing substances are: carbon dioxide, foam, chemical powder. For product loss or leakage that has not caught fire, water spray can be used to disperse flammable vapours and protect those trying to stem the leak.

UNSUITABLE EXTINGUISHING EQUIPMENT

Do not use jets of water. Water is not effective for putting out fires but can be used to cool containers exposed to flames to prevent explosions.

#### 5.2. Special hazards arising from the substance or mixture.

HAZARDS CAUSED BY EXPOSURE IN THE EVENT OF FIRE

Excess pressure may form in containers exposed to fire at a risk of explosion. Do not breathe combustion products.

#### 5.3. Advice for firefighters.

GENERAL INFORMATION

Use jets of water to cool the containers to prevent product decomposition and the development of substances potentially hazardous for health. Always wear full fire prevention gear. Collect extinguishing water to prevent it from draining into the sewer system. Dispose of contaminated water used for extinction and the remains of the fire according to applicable regulations.

SPECIAL PROTECTIVE EQUIPMENT FOR FIRE-FIGHTERS



# ACC Silicones LTD

## AS1703

Revision nr.3  
Dated 24/1/2014  
Printed on 24/1/2014  
Page n. 3 / 7

EN

Normal fire fighting clothing i.e. fire kit (BS EN 469), gloves (BS EN 659) and boots (HO specification A29 and A30) in combination with self-contained open circuit positive pressure compressed air breathing apparatus (BS EN 137).

### SECTION 6. Accidental release measures.

#### 6.1. Personal precautions, protective equipment and emergency procedures.

Block the leakage if there is no hazard.

Wear suitable protective equipment (including personal protective equipment referred to under Section 8 of the safety data sheet) to prevent any contamination of skin, eyes and personal clothing. These indications apply for both processing staff and those involved in emergency procedures.

#### 6.2. Environmental precautions.

The product must not penetrate into the sewer system or come into contact with surface water or ground water.

#### 6.3. Methods and material for containment and cleaning up.

Collect the leaked product into a suitable container. Evaluate the compatibility of the container to be used, by checking section 10.

Absorb the remainder with inert absorbent material.

Make sure the leakage site is well aired. Check incompatibility for container material in section 7. Contaminated material should be disposed of in compliance with the provisions set forth in point 13.

#### 6.4. Reference to other sections.

Any information on personal protection and disposal is given in sections 8 and 13.

### SECTION 7. Handling and storage.

#### 7.1. Precautions for safe handling.

Keep away from heat, sparks and naked flames; do not smoke or use matches or lighters. Vapours may catch fire and an explosion may occur; vapour accumulation is therefore to be avoided by leaving windows and doors open and ensuring good cross ventilation. Without adequate ventilation, vapours may accumulate at ground level and, if ignited, catch fire even at a distance, with the danger of backfire.

Avoid bunching of electrostatic charges. When performing transfer operations involving large containers, connect to an earthing system and wear antistatic footwear. Vigorous stirring and flow through the tubes and equipment may cause the formation and accumulation of electrostatic charges. In order to avoid the risk of fires and explosions, never use compressed air when handling. Open containers with caution as they may be pressurised. Do not eat, drink or smoke during use. Avoid leakage of the product into the environment.

#### 7.2. Conditions for safe storage, including any incompatibilities.

Store only in the original container. Store the containers sealed, in a well ventilated place, away from direct sunlight. Store in a well ventilated place, keep far away from sources of heat, naked flames and sparks and other sources of ignition. Keep containers away from any incompatible materials, see section 10 for details.

#### 7.3. Specific end use(s).

Information not available.

### SECTION 8. Exposure controls/personal protection.

#### 8.1. Control parameters.

Information not available.

#### 8.2. Exposure controls.

As the use of adequate technical equipment must always take priority over personal protection equipment, make sure that the workplace is well aired through effective local aspiration. Personal protection equipment must comply with the rules in force indicated below.

##### HAND PROTECTION

Protect hands with category II (ref. Directive 89/686/EEC and standard EN 374) work gloves, such as those in PVC, neoprene, nitril or equivalent. The following should be considered when choosing work glove material: degradation, breakage times and permeation. Work glove resistance to preparations should be checked before use, as it can be unpredictable. Gloves' limit depends on the duration of exposure.

##### EYE PROTECTION

Wear protective airtight goggles (ref. standard EN 166).

##### SKIN PROTECTION

Wear category II professional long-sleeved overalls and safety footwear (ref. Directive 89/686/CEE and standard EN 344). Wash body with soap and water after removing overalls.

##### RESPIRATORY PROTECTION

If the threshold value (if available) for one or more of the substances present in the preparation for daily exposure in the workplace or to a fraction established by the company's prevention and protection service is exceeded, wear a mask with an A or universal filter, the class (1, 2 or 3) of which must be chosen according to the limit concentration of use (ref. standard EN 141).

The use of respiratory tract protection equipment, such as masks like that indicated above, is necessary to reduce worker exposure in the absence of technical measures. The protection provided by masks is in any case limited.

**AS1703****SECTION 8. Exposure controls/personal protection. ... / >>**

If the substance in question is odourless or its olfactory threshold is higher than the relative exposure limit and in the event of an emergency, or when exposure levels are unknown or the concentration of oxygen in the workplace is less than 17% volume, wear self-contained, open-circuit compressed air breathing apparatus (ref. standard EN 137) or fresh air hose breathing apparatus for use with full face mask, half mask or mouthpiece (ref. standard EN 138).

An emergency eye washing and shower system must be provided.

**ENVIRONMENTAL EXPOSURE CONTROLS.**

The emissions generated by manufacturing processes, including those generated by ventilation equipment, should be checked to ensure compliance with environmental standards.

**SECTION 9. Physical and chemical properties.****9.1. Information on basic physical and chemical properties.**

Appearance		paste
Colour		colourless
Odour		characteristic
Odour threshold.		Not available.
pH.		Not available.
Melting point / freezing point.		Not available.
Initial boiling point.		Not available.
Boiling range.		Not available.
Flash point.	>	150 °C.
Evaporation Rate		Not available.
Flammability of solids and gases		Not available.
Lower inflammability limit.		Not available.
Upper inflammability limit.		Not available.
Lower explosive limit.		Not available.
Upper explosive limit.		Not available.
Vapour pressure.		Not available.
Vapour density		Not available.
Relative density.		Not available.
Solubility		immiscible with water
Partition coefficient: n-octanol/water		Not available.
Auto-ignition temperature.	>	400 °C.
Decomposition temperature.		Not available.
Viscosity		Not available.
Explosive properties		Not available.
Oxidising properties		Not available.

**9.2. Other information.**

Information not available.

**SECTION 10. Stability and reactivity.****10.1. Reactivity.**

There are no particular risks of reaction with other substances in normal conditions of use.

**10.2. Chemical stability.**

The product is stable in normal conditions of use and storage.

**10.3. Possibility of hazardous reactions.**

No hazardous reactions are foreseeable in normal conditions of use and storage.

**10.4. Conditions to avoid.**

None in particular. However the usual precautions used for chemical products should be respected.

**10.5. Incompatible materials.**

Information not available.

**10.6. Hazardous decomposition products.**

Information not available.

**SECTION 11. Toxicological information.****11.1. Information on toxicological effects.**

In the absence of experimental data for the product itself, health hazards are evaluated according to the properties of the substances it contains, using the criteria specified in the applicable regulation for classification.

It is therefore necessary to take into account the concentration of the individual hazardous substances indicated in section 3, to evaluate the toxicological effects of exposure to the product.

**SECTION 11. Toxicological information.** ... / >>

Upon contact with skin, this product causes sensitization (dermatitis). Dermatitis derives from skin irritation on the areas which repeatedly come into contact with the sensitizing agent. Cutaneous lesions may include: erythemas, edemas, papules, vesicles, pustules, scurvies, ulcerations and exudative phenomena, whose intensity varies according to illness seriousness and affected areas. Erythemas, edemas and exudative phenomena prevail during the acute phase. Scuffy skin, dryness, ulcerations and skin thickening prevail during the chronic phase.

TRIMETHOXY (METHYL) SILANE  
LD50 (Oral).

7000 mg/kg

**SECTION 12. Ecological information.**

Use this product according to good working practices. Avoid littering. Inform the competent authorities, should the product reach waterways or sewers or contaminate soil or vegetation.

**12.1. Toxicity.**

TRIMETHOXY (METHYL) SILANE  
LC50 (96h) - for Fish.

42.1 mg/l

**12.2. Persistence and degradability.**

Information not available.

**12.3. Bioaccumulative potential.**

Information not available.

**12.4. Mobility in soil.**

Information not available.

**12.5. Results of PBT and vPvB assessment.**

On the basis of available data, the product does not contain any PBT or vPvB in percentage greater than 0,1%.

**12.6. Other adverse effects.**

Information not available.

**SECTION 13. Disposal considerations.****13.1. Waste treatment methods.**

Reuse, when possible. Product residues should be considered special hazardous waste. The hazard level of waste containing this product should be evaluated according to applicable regulations.

Disposal must be performed through an authorised waste management firm, in compliance with national and local regulations.

Avoid littering. Do not contaminate soil, sewers and waterways.

CONTAMINATED PACKAGING

Contaminated packaging must be recovered or disposed of in compliance with national waste management regulations.

**SECTION 14. Transport information.**

The product is not dangerous under current provisions of the Code of International Carriage of Dangerous Goods by Road (ADR) and by Rail (RID), of the International Maritime Dangerous Goods Code (IMDG), and of the International Air Transport Association (IATA) regulations.

**SECTION 15. Regulatory information.****15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture.**

Seveso category. None.

Restrictions relating to the product or contained substances pursuant to Annex XVII to EC Regulation 1907/2006.

Product.

Point. 3

### SECTION 15. Regulatory information. ... / >>

Substances in Candidate List (Art. 59 REACH).  
None.

Substances subject to authorisation (Annex XIV REACH).  
None.

Substances subject to exportation reporting pursuant to (EC) Reg. 689/2008:  
None.

Substances subject to the Rotterdam Convention:  
None.

Substances subject to the Stockholm Convention:  
None.

Healthcare controls.

Workers exposed to this chemical agent must not undergo health checks, provided that available risk-assessment data prove that the risks related to the workers' health and safety are modest and that the 98/24/EC directive is respected.

### 15.2. Chemical safety assessment.

No chemical safety assessment has been processed for the mixture and the substances it contains.

### SECTION 16. Other information.

Text of hazard (H) indications mentioned in section 2-3 of the sheet:

<b>Flam. Liq. 2</b>	Flammable liquid, category 2
<b>Acute Tox. 3</b>	Acute toxicity, category 3
<b>STOT SE 1</b>	Specific target organ toxicity - single exposure, category 1
<b>Skin Sens. 1</b>	Skin sensitization, category 1
<b>H225</b>	Highly flammable liquid and vapour.
<b>H301</b>	Toxic if swallowed.
<b>H311</b>	Toxic in contact with skin.
<b>H331</b>	Toxic if inhaled.
<b>H370</b>	Causes damage to organs.
<b>H317</b>	May cause an allergic skin reaction.

Text of risk (R) phrases mentioned in section 2-3 of the sheet:

<b>R11</b>	HIGHLY FLAMMABLE.
<b>R23/24/25</b>	TOXIC BY INHALATION, IN CONTACT WITH SKIN AND IF SWALLOWED.
<b>R39/23/24/25</b>	TOXIC: DANGER OF VERY SERIOUS IRREVERSIBLE EFFECTS THROUGH INHALATION, IN CONTACT WITH SKIN AND IF SWALLOWED.
<b>R43</b>	MAY CAUSE SENSITISATION BY SKIN CONTACT.

#### LEGEND:

- ADR: European Agreement concerning the carriage of Dangerous goods by Road
- CAS NUMBER: Chemical Abstract Service Number
- CE50: Effective concentration (required to induce a 50% effect)
- CE NUMBER: Identifier in ESIS (European archive of existing substances)
- CLP: EC Regulation 1272/2008
- DNEL: Derived No Effect Level
- EmS: Emergency Schedule
- GHS: Globally Harmonized System of classification and labeling of chemicals
- IATA DGR: International Air Transport Association Dangerous Goods Regulation
- IC50: Immobilization Concentration 50%
- IMDG: International Maritime Code for dangerous goods
- IMO: International Maritime Organization
- INDEX NUMBER: Identifier in Annex VI of CLP
- LC50: Lethal Concentration 50%
- LD50: Lethal dose 50%
- OEL: Occupational Exposure Level
- PBT: Persistent bioaccumulative and toxic as REACH Regulation
- PEC: Predicted environmental Concentration
- PEL: Predicted exposure level

### SECTION 16. Other information. ... / >>

- PNEC: Predicted no effect concentration
- REACH: EC Regulation 1907/2006
- RID: Regulation concerning the international transport of dangerous goods by train
- TLV: Threshold Limit Value
- TLV CEILING: Concentration that should not be exceeded during any time of occupational exposure.
- TWA STEL: Short-term exposure limit
- TWA: Time-weighted average exposure limit
- VOC: Volatile organic Compounds
- vPvB: Very Persistent and very Bioaccumulative as for REACH Regulation.

#### GENERAL BIBLIOGRAPHY

1. Directive 1999/45/EC and following amendments
2. Directive 67/548/EEC and following amendments and adjustments
3. Regulation (EC) 1907/2006 (REACH) of the European Parliament
4. Regulation (EC) 1272/2008 (CLP) of the European Parliament
5. Regulation (EC) 790/2009 (I Atp. CLP) of the European Parliament
6. Regulation (EC) 453/2010 of the European Parliament
7. Regulation (EC) 286/2011 (II Atp. CLP) of the European Parliament
8. The Merck Index. - 10th Edition
9. Handling Chemical Safety
10. Niosh - Registry of Toxic Effects of Chemical Substances
11. INRS - Fiche Toxicologique (toxicological sheet)
12. Patty - Industrial Hygiene and Toxicology
13. N.I. Sax - Dangerous properties of Industrial Materials-7, 1989 Edition
14. ECHA website

#### Note for users:

The information contained in the present sheet are based on our own knowledge on the date of the last version. Users must verify the suitability and thoroughness of provided information according to each specific use of the product.

This document must not be regarded as a guarantee on any specific product property.

The use of this product is not subject to our direct control; therefore, users must, under their own responsibility, comply with the current health and safety laws and regulations. The producer is relieved from any liability arising from improper uses.

Provide appointed staff with adequate training on how to use chemical products.

#### Changes to previous review:

The following sections were modified:

01 / 02 / 03 / 05 / 06 / 07 / 08 / 09 / 11 / 12 / 15 / 16.