



Material Safety Data Sheet

Copyright, 2011, 3M Company All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

SECTION 1: PRODUCT AND COMPANY IDENTIFICATION

PRODUCT NAME: 3M Desiccant, Plastic Pouch
MANUFACTURER: 3M
DIVISION: Electronic Solutions Division

ADDRESS: 3M Center, St. Paul, MN 55144-1000

EMERGENCY PHONE: 1-800-364-3577 or (651) 737-6501 (24 hours)

Issue Date: 12/12/11
Supersedes Date: 05/03/11

Document Group: 22-3548-9

Product Use:

Intended Use: Humidity absorption

SECTION 2: INGREDIENTS

<u>Ingredient</u>	<u>C.A.S. No.</u>	<u>% by Wt</u>
Clay Mineral	1302-78-9	≥ 99
Silicon Dioxide	14808-60-7	≤ 1

SECTION 3: HAZARDS IDENTIFICATION

3.1 EMERGENCY OVERVIEW

Specific Physical Form: Granules

Odor, Color, Grade: No odor. Gray granules.

General Physical Form: Solid

Immediate health, physical, and environmental hazards: Contains a chemical or chemicals which can cause cancer.

3.2 POTENTIAL HEALTH EFFECTS

Eye Contact:

Mechanical eye irritation: Signs/symptoms may include pain, redness, tearing and corneal abrasion.

Skin Contact:

Mechanical Skin irritation: Signs/symptoms may include abrasion, redness, pain, and itching.

Inhalation:

Respiratory Tract Irritation: Signs/symptoms may include cough, sneezing, nasal discharge, headache, hoarseness, and nose and throat pain.

Prolonged or repeated exposure may cause:

Silicosis: Signs/symptoms may include breathlessness, weakness, chest pain, persistent cough, increased amounts of sputum, and heart disease.

Ingestion:

No health effects are expected.

Carcinogenicity:

Contains a chemical or chemicals which can cause cancer.

<u>Ingredient</u>	<u>C.A.S. No.</u>	<u>Class Description</u>	<u>Regulation</u>
Silicon Dioxide	14808-60-7	Grp. 1: Carcinogenic to humans	International Agency for Research on Cancer
Silicon Dioxide	14808-60-7	Known human carcinogen	National Toxicology Program Carcinogens

SECTION 4: FIRST AID MEASURES

4.1 FIRST AID PROCEDURES

The following first aid recommendations are based on an assumption that appropriate personal and industrial hygiene practices are followed.

Eye Contact: Flush eyes with large amounts of water. If signs/symptoms persist, get medical attention.

Skin Contact: Wash affected area with soap and water. If signs/symptoms develop, get medical attention.

Inhalation: Remove person to fresh air. If signs/symptoms develop, get medical attention.

If Swallowed: No need for first aid is anticipated.

SECTION 5: FIRE FIGHTING MEASURES

5.1 FLAMMABLE PROPERTIES

Autoignition temperature	<i>No Data Available</i>
Flash Point	<i>Not Applicable</i>
Flammable Limits(LEL)	<i>No Data Available</i>
Flammable Limits(UEL)	<i>No Data Available</i>

5.2 EXTINGUISHING MEDIA

Ordinary combustible material. Use fire extinguishers with class A extinguishing agents (e.g., water, foam).

5.3 PROTECTION OF FIRE FIGHTERS

Special Fire Fighting Procedures: Wear full protective equipment (Bunker Gear) and a self-contained breathing apparatus (SCBA).

Unusual Fire and Explosion Hazards: No unusual fire or explosion hazards are anticipated.

Note: See STABILITY AND REACTIVITY (SECTION 10) for hazardous combustion and thermal decomposition information.

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Evacuate unprotected and untrained personnel from hazard area. The spill should be cleaned up by qualified personnel. Ventilate the area with fresh air.

6.2. Environmental precautions

Place in a closed container approved for transportation by appropriate authorities. Dispose of collected material as soon as possible.

Clean-up methods

Observe precautions from other sections. Call 3M- HELPS line (1-800-364-3577) for more information on handling and managing the spill. Contain spill. Collect as much of the spilled material as possible. Use wet sweeping compound or water to avoid dusting. Sweep up. Clean up residue.

In the event of a release of this material, the user should determine if the release qualifies as reportable according to local, state, and federal regulations.

SECTION 7: HANDLING AND STORAGE

7.1 HANDLING

For industrial or professional use only.

7.2 STORAGE

Store under normal warehouse conditions.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1 ENGINEERING CONTROLS

Use in an enclosed process area is recommended. Not applicable.

8.2 PERSONAL PROTECTIVE EQUIPMENT (PPE)

8.2.1 Eye/Face Protection

Avoid eye contact.

8.2.2 Skin Protection

Avoid skin contact. Gloves are not required.

8.2.3 Respiratory Protection

Under normal use conditions, airborne exposures are not expected to be significant enough to require respiratory protection.

Select one of the following NIOSH approved respirators based on airborne concentration of contaminants and in accordance with OSHA regulations: Half facepiece air-purifying respirator with N95 particulate filters

. Select and use respiratory protection to prevent an inhalation exposure based on the results of an exposure assessment. Consult with your respirator manufacturer for selection of appropriate types of respirators.

8.2.4 Prevention of Swallowing

Not applicable.

8.3 EXPOSURE GUIDELINES

<u>Ingredient</u>	<u>Authority</u>	<u>Type</u>	<u>Limit</u>	<u>Additional Information</u>
Silicon Dioxide	ACGIH	TWA, respirable fraction	0.025 mg/m3	
Silicon Dioxide	OSHA	TWA concentration, respirable	0.1 mg/m3	
Silicon Dioxide	OSHA	TWA concentration, as total dust	0.3 mg/m3	

SOURCE OF EXPOSURE LIMIT DATA:

ACGIH: American Conference of Governmental Industrial Hygienists

CMRG: Chemical Manufacturer Recommended Guideline

OSHA: Occupational Safety and Health Administration

AIHA: American Industrial Hygiene Association Workplace Environmental Exposure Level (WEEL)

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

Specific Physical Form:	Granules
Odor, Color, Grade:	No odor. Gray granules.
General Physical Form:	Solid
Autoignition temperature	<i>No Data Available</i>
Flash Point	<i>Not Applicable</i>
Flammable Limits(LEL)	<i>No Data Available</i>
Flammable Limits(UEL)	<i>No Data Available</i>
Boiling Point	<i>Not Applicable</i>
Density	57 - 64 lb/ft3
Vapor Density	<i>No Data Available</i>
Vapor Pressure	<i>No Data Available</i>
Specific Gravity	<i>No Data Available</i>
pH	<i>Not Applicable</i>
Melting point	<i>No Data Available</i>
Solubility in Water	Nil
Evaporation rate	<i>Not Applicable</i>
Kow - Oct/Water partition coef	<i>Not Applicable</i>
Viscosity	<i>Not Applicable</i>

SECTION 10: STABILITY AND REACTIVITY

Stability: Stable.

Materials and Conditions to Avoid:

10.1 Conditions to avoid

None known

10.2 Materials to avoid

None known

Hazardous Polymerization: Hazardous polymerization will not occur.

Hazardous Decomposition or By-Products

Substance
Carbon monoxide
Carbon dioxide

Condition
Not Specified
Not Specified

SECTION 11: TOXICOLOGICAL INFORMATION

Please contact the address listed on the first page of the MSDS for Toxicological Information on this material and/or its components.

SECTION 12: ECOLOGICAL INFORMATION

ECOTOXICOLOGICAL INFORMATION

Not determined.

CHEMICAL FATE INFORMATION

Not determined.

SECTION 13: DISPOSAL CONSIDERATIONS

Waste Disposal Method: For quantities <100 lbs. (50kg): dispose of waste product in a sanitary landfill. For larger quantities: incinerate in an industrial or commercial facility in the presence of a combustible material. As a disposal alternative, dispose of waste product in a facility permitted to accept chemical waste.

EPA Hazardous Waste Number (RCRA): Not regulated

Since regulations vary, consult applicable regulations or authorities before disposal.

SECTION 14: TRANSPORT INFORMATION

ID Number(s):

80-0009-5544-5, 80-0009-5545-2, 80-0009-5546-0, 80-0009-5547-8, 80-0009-5548-6, 80-0009-5549-4, 80-0009-5550-2, 80-0009-5551-0, 80-0009-5552-8, 80-0009-5563-5, 80-0009-5564-3, 80-0012-5852-6, 80-0013-8459-5, 80-0013-8460-3, 80-0013-8461-1, 80-0013-8462-9, 80-0013-8463-7, 80-0013-8464-5, 80-0013-8465-2, 80-0013-8466-0, 80-0013-8467-8, 80-0013-8468-6, 80-0013-8469-4, GE-7000-4047-2

For Transport Information, please visit <http://3M.com/Transportinfo> or call 1-800-364-3577 or 651-737-6501.

SECTION 15: REGULATORY INFORMATION

US FEDERAL REGULATIONS

Contact 3M for more information.

311/312 Hazard Categories:

Fire Hazard - No Pressure Hazard - No Reactivity Hazard - No Immediate Hazard - Yes Delayed Hazard - Yes

STATE REGULATIONS

Contact 3M for more information.

CHEMICAL INVENTORIES

Contact 3M for more information.

INTERNATIONAL REGULATIONS

Contact 3M for more information.

WHMIS: Hazardous

This MSDS has been prepared to meet the U.S. OSHA Hazard Communication Standard, 29 CFR 1910.1200.

SECTION 16: OTHER INFORMATION

NFPA Hazard Classification

Health: 1 **Flammability:** 0 **Reactivity:** 0 **Special Hazards:** None

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

HMIS Hazard Classification

Health: 1 **Flammability:** 0 **Reactivity:** 0 **Protection:** X - See PPE section.

Hazardous Material Identification System (HMIS®) hazard ratings are designed to inform employees of chemical hazards in the workplace. These ratings are based on the inherent properties of the material under expected conditions of normal use and are not intended for use in emergency situations. HMIS® ratings are to be used with a fully implemented HMIS® program. HMIS® is a registered mark of the National Paint and Coatings Association (NPCA).

Revision Changes:

- Section 1: Product use information was modified.
- Section 5: Extinguishing media information was modified.
- Section 8: Engineering controls information was modified.
- Section 10: Hazardous decomposition or by-products table was modified.
- Section 16: HMIS explanation was modified.
- Section 9: Density information was modified.
- Section 9: Boiling point information was modified.
- Section 5: Flammable limits (UE) information was modified.
- Section 5: Flammable limits (LEL) information was modified.
- Section 5: Autoignition temperature information was modified.
- Section 9: Vapor density text was modified.
- Section 9: Vapor pressure text was modified.
- Section 5: Flash point information was modified.
- Section 9: Property description for optional properties was modified.
- Section 9: Specific gravity information was modified.
- Section 9: pH information was modified.
- Section 9: Melting point information was modified.

Section 9: Solubility in water text was modified.
Section 9: Flash point information was modified.
Section 9: Flammable limits (LEL) information was modified.
Section 9: Flammable limits (UEL) information was modified.
Section 9: Autoignition temperature information was modified.
Section 14: ID Number(s) Template 1 was modified.
Section 2: Ingredient table was modified.
Section 8: Exposure guidelines ingredient information was modified.
Section 3: Carcinogenicity table was modified.
Section 6: Environmental procedures information was modified.
Section 6: Methods for cleaning up information was modified.
Section 8: Hand protection information was added.

DISCLAIMER: The information in this Material Safety Data Sheet (MSDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the MSDS available directly from 3M

3M USA MSDSs are available at www.3M.com



Transport Information Document

Date: May 07, 2013

3M ID Number: 80-0013-8463-7

Product Description: 3M(TM) Dessicant, 1 Unit Plastic Pouch, 300/Pail

Transport Protective Service: PROTECTIVE SERVICE NOT REQUIRED

NMFC Item: 048170

NMFC Sub: 00

NMFC Class: 050.0

Flash Point (Closed-cup): No Flash Point

UNITED STATES DEPARTMENT OF TRANSPORTATION - GROUND (U.S. DOT, 49 CFR)

NOT REGULATED

UNITED STATES DEPARTMENT OF TRANSPORTATION - VESSEL (U.S. DOT, 49 CFR)

NOT REGULATED

INTERNATIONAL AIR TRANSPORT ASSOCIATION (IATA)

NOT REGULATED

INTERNATIONAL MARITIME ORGANIZATION (IMO)

NOT REGULATED

The classification is authorized by the Competent Authority of the United States of America and may not meet the requirements of other competent authorities.

These transportation classifications are provided as a customer service. AS THE SHIPPER YOU REMAIN RESPONSIBLE FOR COMPLYING WITH ALL THE APPLICABLE LAWS AND REGULATIONS, INCLUDING PROPER TRANSPORTATION CLASSIFICATION AND PACKAGING. 3M's transportation classifications are based on product formulations, packaging, 3M policies and 3M's understanding of applicable current regulations and is valid for the original 3M package only. 3M does not guarantee the accuracy of this classification information. This information applies only to transportation classification and NOT THE PACKAGING, LABELING, OR MARKING REQUIREMENTS. The original 3M package is certified for U.S. ground shipment only. If you are shipping by air or ocean, the package may not meet applicable regulatory requirements.

For Transport Information, please visit 3M.com/Transportinfo
or call 1-800-364-3577 or 651-737-6501 for assistance.