

## SAFETY DATA SHEET

### SATIN BLACK(16OZ)UK0271

#### 1 IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

PRODUCT NAME SATIN BLACK(16OZ)UK0271  
 PRODUCT NO. XUK0271  
 SUPPLIER James Briggs Ltd.  
 Salmon Fields  
 Royton, Oldham, Lancashire,  
 England OL2 6HZ  
 0161 627 0101  
 0161 627 0971  
 sds@jamesbriggs.co.uk

#### 2 HAZARDS IDENTIFICATION

Extremely flammable Repeated exposure may cause skin dryness or cracking. Vapours may cause drowsiness and dizziness. Irritating to eyes.

CLASSIFICATION (1999/45) Xi;R36. F+;R12. R66, R67.

#### 3 COMPOSITION/INFORMATION ON INGREDIENTS

Name	EC No.	CAS-No.	Content %	Classification (67/548/EEC)
1,2,4-TRIMETHYLBENZENE	202-436-9	95-63-6	< 1%	R10 Xn;R20 Xi;R36/37/38 N;R51/53
1-METHOXY-2-PROPANOL	203-539-1	107-98-2	1-5%	R10
2-BUTOXYETHANOL	203-905-0	111-76-2	1-5%	Xn;R20/21/22 Xi;R36/38
2-METHOXY-1-METHYLETHYL ACETATE	203-603-9	108-65-6	< 1%	R10 Xi;R36
ACETONE	200-662-2	67-64-1	30-60%	F;R11 Xi;R36 R66 R67
BUTANE	203-448-7	106-97-8	10-30%	F+;R12
ISOBUTANE	200-857-2	75-28-5	5-10%	F+;R12
MESITYLENE	203-604-4	108-67-8	< 1%	R10 Xi;R37 N;R51/53
METHYL METHACRYLATE	201-297-1	80-62-6	< 1%	F;R11 R43 Xi;R37/38
PROPANE	200-827-9	74-98-6	10-30%	F+;R12
XYLENE	215-535-7	1330-20-7	5-10%	R10 Xn;R20/21 Xi;R38

The Full Text for all R-Phrases is Displayed in Section 16

#### 4 FIRST-AID MEASURES

##### GENERAL INFORMATION

Move the exposed person to fresh air at once. Get medical attention if any discomfort continues.

##### INHALATION

Move the exposed person to fresh air at once. When breathing is difficult, properly trained personnel may assist affected person by administering oxygen. Keep the affected person warm and at rest. Get prompt medical attention.

##### INGESTION

DO NOT INDUCE VOMITING! Rinse mouth thoroughly with water and give large amounts of milk or water to people not unconscious. Get medical attention if any discomfort continues.

##### SKIN CONTACT

Wash the skin immediately with soap and water. Get medical attention if any discomfort continues.

##### EYE CONTACT

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

#### 5 FIRE-FIGHTING MEASURES

##### EXTINGUISHING MEDIA

Use: Powder. Dry chemicals, sand, dolomite etc. Water spray, fog or mist.

## SATIN BLACK(16OZ)UK0271

### SPECIAL FIRE FIGHTING PROCEDURES

Containers close to fire should be removed or cooled with water. Use water to keep fire exposed containers cool and disperse vapours.

### UNUSUAL FIRE & EXPLOSION HAZARDS

Aerosol cans may explode in a fire.

## 6 ACCIDENTAL RELEASE MEASURES

### SPILL CLEAN UP METHODS

Wear necessary protective equipment. Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. Let evaporate. Keep out of confined spaces because of explosion risk. If leakage cannot be stopped, evacuate area.

## 7 HANDLING AND STORAGE

### USAGE PRECAUTIONS

Keep away from heat, sparks and open flame. Avoid spilling, skin and eye contact. Ventilate well, avoid breathing vapours. Use approved respirator if air contamination is above accepted level.

### STORAGE PRECAUTIONS

Aerosol cans: Must not be exposed to direct sunlight or temperatures above 50°C.

## 8 EXPOSURE CONTROLS/PERSONAL PROTECTION

Name	STD	TWA - 8 Hrs		STEL - 15 Min		Notes
1-METHOXY-2-PROPANOL	WEL	100 ppm(Sk)	375 mg/m3(Sk)	150 ppm(Sk)	560 mg/m3(Sk)	
2-BUTOXYETHANOL	WEL	25 ppm(Sk)		50 ppm(Sk)		
2-METHOXY-1-METHYLETHYL ACETATE	WEL	50 ppm(Sk)	274 mg/m3(Sk)	100 ppm(Sk)	548 mg/m3(Sk)	
ACETONE				500 ppm	1210 mg/m3	
BUTANE	WEL	600 ppm	1450 mg/m3	750 ppm	1810 mg/m3	
ISOBUTANE	WEL	800 ppm		800 ppm		
METHYL METHACRYLATE	WEL	50 ppm	208 mg/m3	100 ppm	416 mg/m3	
PROPANE		Asphyxiating	Asphyxiating	Asphyxiating	Asphyxiating	
XYLENE	WEL	50 ppm(Sk)	220 mg/m3(Sk)	100 ppm(Sk)	441 mg/m3(Sk)	

WEL = Workplace Exposure Limit.

### INGREDIENT COMMENTS

WEL = Workplace Exposure Limits

### PROTECTIVE EQUIPMENT



### ENGINEERING MEASURES

Provide adequate general and local exhaust ventilation.

### RESPIRATORY EQUIPMENT

No specific recommendation made, but respiratory protection must be used if the general level exceeds the recommended occupational exposure limit. Use chemical cartridge protection with appropriate cartridge.

### HAND PROTECTION

Use protective gloves.

### EYE PROTECTION

Use approved safety goggles or face shield.

### OTHER PROTECTION

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

### HYGIENE MEASURES

DO NOT SMOKE IN WORK AREA! Wash at the end of each work shift and before eating, smoking and using the toilet. Promptly remove any clothing that becomes contaminated. When using do not eat, drink or smoke.

**SATIN BLACK(16OZ)UK0271****9 PHYSICAL AND CHEMICAL PROPERTIES**

APPEARANCE	Aerosol
COLOUR	Black
ODOUR	Characteristic
SOLUBILITY	Insoluble in water
FLAMMABILITY LIMIT - LOWER(%)	0.8
FLAMMABILITY LIMIT - UPPER(%)	13.0
VOLATILE ORGANIC COMPOUND (VOC)	656 g/litre

**10 STABILITY AND REACTIVITY****STABILITY**

Stable under normal temperature conditions.

**CONDITIONS TO AVOID**

Avoid heat, flames and other sources of ignition. Avoid contact with: Strong oxidising agents. Strong alkalis. Strong mineral acids.

**HAZARDOUS DECOMPOSITION PRODUCTS**

Fire creates: Vapours/gases/fumes of: Carbon monoxide (CO). Carbon dioxide (CO<sub>2</sub>).

**11 TOXICOLOGICAL INFORMATION****INHALATION**

May cause irritation to the respiratory system. Vapours may cause headache, fatigue, dizziness and nausea. Prolonged inhalation of high concentrations may damage respiratory system. Irritating to respiratory system.

**INGESTION**

May cause discomfort if swallowed. May cause stomach pain or vomiting. Gastrointestinal symptoms, including upset stomach.

**SKIN CONTACT**

Prolonged or repeated exposure may cause severe irritation. Acts as a defatting agent on skin. May cause cracking of skin, and eczema. May cause allergic contact eczema. May cause sensitisation by skin contact. Irritating to skin.

**EYE CONTACT**

Irritating to eyes. May cause chemical eye burns.

**ROUTE OF ENTRY**

Inhalation. Skin and/or eye contact.

**12 ECOLOGICAL INFORMATION****ECOTOXICITY**

Dangerous for the environment if discharged into watercourses.

**13 DISPOSAL CONSIDERATIONS****DISPOSAL METHODS**

Empty containers must not be burned because of explosion hazard. Dispose of waste and residues in accordance with local authority requirements.

**14 TRANSPORT INFORMATION**

PROPER SHIPPING NAME	AEROSOLS
ENVIRONMENTALLY HAZARDOUS SUBSTANCE/MARINE POLLUTANT	No.
UN NO. ROAD	1950
ADR CLASS NO.	2
ADR CLASS	Class 2: Gases

**SATIN BLACK(16OZ)UK0271**

ADR PACK GROUP	N/A
TUNNEL RESTRICTION CODE	(D)
ADR LABEL NO.	2.1
UN NO. SEA	1950
IMDG CLASS	2.1
IMDG PACK GR.	N/A
EMS	F-D, S-U
UN NO. AIR	1950
AIR CLASS	2.1
AIR PACK GR.	N/A

**15 REGULATORY INFORMATION**

**LABELLING**



Irritant



Extremely Flammable

**RISK PHRASES**

R12	Extremely flammable.
R36	Irritating to eyes.
R66	Repeated exposure may cause skin dryness or cracking.
R67	Vapours may cause drowsiness and dizziness.

**SAFETY PHRASES**

S2	Keep out of the reach of children.
S16	Keep away from sources of ignition - No smoking.
S23	Do not breathe vapour/spray.
S26	In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
S37	Wear suitable gloves.
S51	Use only in well-ventilated areas.

**UK REGULATORY REFERENCES**

The Chemicals (Hazard Information and Packaging for Supply) Regulations 2002.

The Control of Substances Hazardous to Health Regulations 2002.

**STATUTORY INSTRUMENTS**

The Control of Substances Hazardous to Health Regulations 2002.

The Chemicals (Hazard Information and Packaging for Supply) Regulations 2002.

**APPROVED CODE OF PRACTICE**

Classification and Labelling of Substances and Preparations Dangerous for Supply.

**GUIDANCE NOTES**

Workplace Exposure Limits EH40.

Introduction to Local Exhaust Ventilation HS(G)37.

CHIP for everyone HSG(108).

**16 OTHER INFORMATION**

REVISION DATE 03/08/2010

REV. NO./REPL. SDS GENERATED 11

## SATIN BLACK(16OZ)UK0271

### RISK PHRASES IN FULL

R12	Extremely flammable.
R10	Flammable.
R20/21	Harmful by inhalation and in contact with skin.
R20/21/22	Harmful by inhalation, in contact with skin and if swallowed.
R20	Harmful by inhalation.
R11	Highly flammable.
R36/38	Irritating to eyes and skin.
R36/37/38	Irritating to eyes, respiratory system and skin.
R36	Irritating to eyes.
R37/38	Irritating to respiratory system and skin.
R37	Irritating to respiratory system.
R38	Irritating to skin.
R43	May cause sensitisation by skin contact.
R66	Repeated exposure may cause skin dryness or cracking.
R51/53	Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R67	Vapours may cause drowsiness and dizziness.

### DISCLAIMER

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.