



Revision Number: 003.3

Issue date: 03/22/2010

1. PRODUCT AND COMPANY IDENTIFICATION

Product name:	LOCTITE® 7452™ ACCELERATOR TAK PAK®	IDH number:	229769
Product type:	Accelerator	Item number:	18580
Company address:	Henkel Corporation One Henkel Way Rocky Hill, Connecticut 06067	Region:	United States
		Contact information:	Telephone: 860.571.5100 Emergency telephone: 860.571.5100 Internet: www.henkelna.com

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW

Physical state:	Liquid	HMIS:	
Color:	Clear, to, Amber	HEALTH:	*2
Odor:	Acetone	FLAMMABILITY:	3
		PHYSICAL HAZARD:	0
		Personal Protection:	See MSDS Section 8

DANGER: EXTREMELY FLAMMABLE.
CAUSES EYE IRRITATION.
VAPOR MAY CAUSE FLASH FIRE.
ASPIRATION HAZARD IF SWALLOWED.
MAY CAUSE SKIN IRRITATION.
MAY CAUSE RESPIRATORY TRACT IRRITATION.

Relevant routes of exposure: Skin, Inhalation, Eyes

Potential Health Effects

Inhalation:	May cause respiratory tract irritation. Central nervous system depression, including dizziness, drowsiness, fatigue, nausea, headache, unconsciousness.
Skin contact:	May cause irritation due to defatting of the skin. Redness. Burns. Skin absorption is possible, but harmful effects are not expected from this route of exposure under normal conditions of handling and use.
Eye contact:	Causes eye irritation. Exposure to vapor may cause tearing of the eyes, irritation and burning sensation.
Ingestion:	Ingestion may cause gastrointestinal irritation, nausea, vomiting and diarrhea. Central nervous system depression, including dizziness, drowsiness, fatigue, nausea, headache, unconsciousness.

Existing conditions aggravated by exposure: Liver disorders. Kidney disorders. Lung disorders.

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

See Section 11 for additional toxicological information.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous components	CAS NUMBER	%
Acetone	67-64-1	60 - 100
Benzenamine, N,N,4-trimethyl-	99-97-8	0.1 - 1

4. FIRST AID MEASURES

Inhalation:	Move to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get immediate medical attention.
Skin contact:	Remove contaminated clothing and footwear. Wash with soap and water. Wash clothing before reuse. If symptoms develop and persist, get medical attention.
Eye contact:	Immediately flush eyes with plenty of water for at least 15 minutes. Get medical attention.
Ingestion:	Do not induce vomiting. Never give anything by mouth to an unconscious person. Keep individual calm. Get immediate medical attention.

5. FIRE FIGHTING MEASURES

Flash point:	-17 °C (1.4 °F) Tagliabue closed cup
Autoignition temperature:	Not available
Flammable/Explosive limits - lower:	2.8 %
Flammable/Explosive limits - upper:	12.8 %
Extinguishing media:	Foam, dry chemical or carbon dioxide.
Special firefighting procedures:	Use water spray to keep fire exposed containers cool and disperse vapors.
Unusual fire or explosion hazards:	Vapors may accumulate in low or confined areas, travel considerable distance to source of ignition, and flash back. Closed containers may rupture (due to build up of pressure) when exposed to extreme heat.
Hazardous combustion products:	Oxides of carbon. Oxides of nitrogen.

6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

Environmental precautions:	Do not allow product to enter sewer or waterways.
Clean-up methods:	Remove all sources of ignition. Vapors are heavier than air and may travel along the ground or be moved by ventilation and subsequently ignited by heat, pilot lights or other ignition sources at locations distant from the material handling point. Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Store in a closed metal container until ready for disposal.

7. HANDLING AND STORAGE

Handling:	Prevent contact with eyes, skin and clothing. Do not breathe vapor and mist. Wash thoroughly after handling.
Storage:	Keep in a cool, well ventilated area away from heat, sparks and open flame. Keep container tightly closed until ready for use.

For information on product shelf life contact Henkel Customer Service at (800) 243-4874.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous components	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Acetone	500 ppm TWA 750 ppm STEL	1,000 ppm (2,400 mg/m3) TWA	None	None
Benzenamine, N,N,4-trimethyl-	None	None	0.5 ppm TWA	None

Engineering controls: Use local ventilation if general ventilation is insufficient to maintain vapor concentration below established exposure limits.

Respiratory protection: Use NIOSH approved respirator if there is potential to exceed exposure limit(s). Observe OSHA regulations for respiratory use (29 CFR 1910.134).

Eye/face protection: Goggles. Safety glasses with side-shields.

Skin protection: Chemical resistant, impermeable gloves.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state: Liquid
Color: Clear, to, Amber
Odor: Acetone
Odor threshold: Not available
pH: not applicable
Vapor pressure: 185 mm hg (20 °C (68°F)) Approximately
Boiling point/range: 57 °C (134.6 °F)
Melting point/ range: Not available
Specific gravity: 0.7926
Vapor density: 2 Approximately
Flash point: -17 °C (1.4 °F) Tagliabue closed cup
Flammable/Explosive limits - lower: 2.8 %
Flammable/Explosive limits - upper: 12.8 %
Autoignition temperature: Not available
Evaporation rate: 1.9 (Ether = 1)
Solubility in water: Soluble
Partition coefficient (n-octanol/water): Not available
VOC content: 1.02 %; 80 g/l

10. STABILITY AND REACTIVITY

Stability: Stable

Hazardous reactions: Will not occur.

Hazardous decomposition products: Not available

Incompatible materials: Strong oxidizing agents.

Conditions to avoid: See "Handling and Storage" (Section 7) and "Incompatibility" (Section 10).

11. TOXICOLOGICAL INFORMATION

Hazardous components	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Acetone	No	No	No
Benzenamine, N,N,4-trimethyl-	No	No	No

Hazardous components	Health Effects/Target Organs
Acetone	Blood, Central nervous system, Irritant, Reproductive
Benzenamine, N,N,4-trimethyl-	Mutagen, Allergen

12. ECOLOGICAL INFORMATION

Ecological information: Not available

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Follow all local, state, federal and provincial regulations for disposal.

Hazardous waste number: D001: Ignitable.

14. TRANSPORT INFORMATION

U.S. Department of Transportation Ground (49 CFR)

Proper shipping name: Acetone solution
Hazard class or division: 3
Identification number: UN 1090
Packing group: II
DOT Reportable quantity: Acetone
Exceptions: Consumer Commodity, ORM-D, (Not more than 1 L)

International Air Transportation (ICAO/IATA)

Proper shipping name: Acetone solution
Hazard class or division: 3
Identification number: UN 1090
Packing group: II
Exceptions: (Not more than 500 ml), May Qualify as Consumer Commodity, ID8000

Water Transportation (IMO/IMDG)

Proper shipping name: ACETONE solution
Hazard class or division: 3
Identification number: UN 1090
Packing group: II
Exceptions: Limited quantity (Not more than 1 L).

15. REGULATORY INFORMATION

United States Regulatory Information

TSCA 8 (b) Inventory Status: All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.
TSCA 12(b) Export Notification: None above reporting de minimus
CERCLA/SARA Section 302 EHS: None above reporting de minimus
CERCLA/SARA Section 311/312: Fire, Immediate Health, Delayed Health
CERCLA/SARA 313: None above reporting de minimus
CERCLA Reportable quantity: Acetone (CAS# 67-64-1) 5,000 lbs. (2,270 kg)
California Proposition 65: This product contains a chemical known in the State of California to cause cancer. This product contains a chemical known to the State of California to cause birth defects or other reproductive harm.

Canada Regulatory Information

CEPA DSL/NDL Status: All components are listed on or are exempt from listing on the Canadian Domestic Substances List.
WHMIS hazard class: B.2, D.2.A, D.2.B

16. OTHER INFORMATION

This material safety data sheet contains changes from the previous version in sections: 2

Prepared by: Kyra Kozak Woods, Manager, Regulatory Affairs

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation does not assume responsibility for any results obtained by persons over whose methods Henkel Corporation has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any of Henkel Corporation's products. In light of the foregoing, Henkel Corporation specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation further disclaims any liability for consequential or incidental damages of any kind, including lost profits.