

## TECHNICAL DATA SHEET


CABLE REFERENCE : 1Pair(PVC)

ISSUE NO. : 1

ISSUE DATE : 30 March, 2011.

### CABLE CONSTRUCTION

<b>Category</b>	1Pair(PVC)			
<b>Test Standard</b>	UL1581,UL758			
<b>1.Conductor</b>	Material	STRANDED-Tinned Copper		
	Nom.O.D.(mm)	7x0.20	Up	+0.001
			Down	-0.008
<b>2.Insulation</b>	Material	<b>FR-PVC</b>		
	Diameter	1.25(+/-0.13)mmx2		
<b>Color</b>	red,black			
<b>3.Drain</b>	Material	STRANDED-Tinned Copper		
	Nom.O.D.(mm)	7x <b>0.20</b>	Up	+0.001
			Down	-0.008
<b>4.Shield</b>	Material	AL-foil		
	Color	Blue		
<b>5.Jacket</b>	External O.D.	3.90(+/-0.18)mm		
	Surface	Clean,Smooth		
	Material	FR-PVC(complies RoHS)		
	Color	Black		
<b>6. CHARACTERISTICS</b>	Item	Description	Standard	
	1.Cond. Resistance	20°C, Conductor DC Resistance	< 9.41 Ω/100M	
	2.Min.Insulation DC Resistance	20°C,Insulation DC Resistance	200 MΩ*M	
	3. Rated Voltage	-----	300 V	
	4.Rated Temperature(°C)	-----	80°C	



Information in this data sheet supplied to users is based on general experience and is given in good faith, but because of the many particular factors which are outside our knowledge which affect the use of the products, no warranty is given nor is to be implied with respect to such information. Users should make their own enquiries to determine the stability of products for any particular use.