

Material Safety Data Sheet



Revision Number: 003.1

Issue date: 02/10/2009

1. PRODUCT AND COMPANY IDENTIFICATION

Product name:	Loctite(R) 648 Retaining Compound Press Fit	IDH number:	231105
Product type:	Anaerobic Adhesive	Item number:	21444
		Region:	United States
Company address:	Contact information:		
Henkel Corporation	Telephone: 860.571.5100		
1001 Trout Brook Crossing	Emergency telephone: 860.571.5100		
Rocky Hill, Connecticut 06067	Internet: www.henkelna.com		

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW

Physical state:	Liquid	HMIS:	
Color:	Green	HEALTH:	*2
Odor:	Sharp	FLAMMABILITY:	1
		PHYSICAL HAZARD:	1
		Personal Protection:	See MSDS Section 8

WARNING: CAUSES EYE AND SKIN IRRITATION.
MAY CAUSE ALLERGIC SKIN REACTION.
MAY BE HARMFUL IF SWALLOWED.
MAY CAUSE RESPIRATORY TRACT IRRITATION.

Relevant routes of exposure: Skin, Inhalation, Eyes

Potential Health Effects

Inhalation:	May cause irritation to nose and throat.
Skin contact:	Causes skin irritation. May cause allergic skin reaction.
Eye contact:	Vapors may irritate eyes. Contact with eyes will cause irritation.
Ingestion:	May cause gastrointestinal tract irritation if swallowed.

Existing conditions aggravated by exposure: Eye, skin, and respiratory disorders.

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

See Section 11 for additional toxicological information.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous components	CAS NUMBER	%
Polyurethane Methacrylate Resin	Proprietary	30 - 60
Polyglycol dimethacrylate	109-16-0	10 - 30
Acrylic acid	79-10-7	5 - 10
Hydroxyalkyl methacrylate	27813-02-1	5 - 10
Polyglycol dimethacrylate	25852-47-5	1 - 5
Cumene hydroperoxide	80-15-9	1 - 5
Acetic acid, 2-phenylhydrazide	114-83-0	0.1 - 1

IDH number: 231105

Product name: Loctite(R) 648 Retaining Compound Press Fit
Page 1 of 5

4. FIRST AID MEASURES

Inhalation:	Move to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get medical attention.
Skin contact:	Wash with soap and water. Remove contaminated clothing and footwear. Wash clothing before reuse. If symptoms develop and persist, get medical attention.
Eye contact:	Flush with copious amounts of water, preferably, lukewarm water for at least 15 minutes, holding eyelids open all the time. Get medical attention.
Ingestion:	Do not induce vomiting. Never give anything by mouth to an unconscious person. Keep individual calm. Get medical attention.

5. FIRE FIGHTING MEASURES

Flash point:	> 93.3 °C (> 199.94 °F) Tagliabue closed cup
Autoignition temperature:	Not available
Flammable/Explosive limits - lower:	Not available
Flammable/Explosive limits - upper:	Not available
Extinguishing media:	Foam, dry chemical or carbon dioxide.
Special firefighting procedures:	Not available
Unusual fire or explosion hazards:	Not available
Hazardous combustion products:	Oxides of carbon. Oxides of sulfur. Oxides of nitrogen. Irritating organic vapours.

6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

Environmental precautions:	Do not allow product to enter sewer or waterways.
Clean-up methods:	Ensure adequate ventilation. Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Store in a partly filled, closed container until disposal.

7. HANDLING AND STORAGE

Handling:	Use only with adequate ventilation. Avoid contact with eyes, skin and clothing. Do not breathe gas/fumes/vapor/spray.
Storage:	For safe storage, store at or below 38 °C (100.4 °F)

For information on product shelf life contact Henkel Customer Service at (800) 243-4874.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous components	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Polyurethane Methacrylate Resin	None	None	None	None
Polyglycol dimethacrylate	None	None	None	None
Acrylic acid	2 ppm TWA (SKIN)	None	None	1 ppm TWA 3 ppm STEL (SKIN)
Hydroxyalkyl methacrylate	None	None	None	1 ppm TWA 3 ppm STEL
Polyglycol dimethacrylate	None	None	None	None
Cumene hydroperoxide	None	None	1 ppm (6 mg/m3) TWA (SKIN)	None
Acetic acid, 2-phenylhydrazide	None	None	None	None

Engineering controls:	Provide adequate local exhaust ventilation to maintain worker exposure below exposure limits.
Respiratory protection:	Use NIOSH approved respirator if there is potential to exceed exposure limit(s).
Eye/face protection:	Safety goggles or safety glasses with side shields.
Skin protection:	Use impermeable gloves and protective clothing as necessary to prevent skin contact. Neoprene gloves.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state:	Liquid
Color:	Green
Odor:	Sharp
Odor threshold:	Not available
pH:	Not applicable
Vapor pressure:	< 10 mm Hg (27 °C (80.6 °F))
Boiling point/range:	> 149 °C (> 300.2 °F)
Melting point/ range:	Not available
Specific gravity:	1.1
Vapor density:	Not available
Flash point:	> 93.3 °C (> 199.94 °F) Tagliabue closed cup
Flammable/Explosive limits - lower:	Not available
Flammable/Explosive limits - upper:	Not available
Autoignition temperature:	Not available
Evaporation rate:	Not available
Solubility in water:	Slight
Partition coefficient (n-octanol/water):	Not available
VOC content:	5.34 %; 50.98 g/l

10. STABILITY AND REACTIVITY

Stability:	Stable
Hazardous reactions:	Will not occur.
Hazardous decomposition products:	Oxides of carbon. Oxides of sulfur. Oxides of nitrogen. Irritating organic vapours.
Incompatible materials:	Strong oxidizing agents.
Conditions to avoid:	Store away from incompatible materials. See "Handling and Storage" (Section 7) and "Incompatibility" (Section 10).

11. TOXICOLOGICAL INFORMATION

Acute oral product toxicity:	LD50 (rat) > 5,000 mg/kg (Estimated)
Acute dermal product toxicity:	LD50 (rabbit) > 5,000 mg/kg (Estimated)

Hazardous components	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Polyurethane Methacrylate Resin	No	No	No
Polyglycol dimethacrylate	No	No	No
Acrylic acid	No	No	No
Hydroxyalkyl methacrylate	No	No	No
Polyglycol dimethacrylate	No	No	No
Cumene hydroperoxide	No	No	No
Acetic acid, 2-phenylhydrazide	No	No	No

Hazardous components	Health Effects/Target Organs
Polyurethane Methacrylate Resin	Irritant, Allergen
Polyglycol dimethacrylate	Irritant, Allergen
Acrylic acid	Allergen, Corrosive, Irritant, Kidney, Liver
Hydroxyalkyl methacrylate	Irritant, Allergen
Polyglycol dimethacrylate	Irritant, Allergen
Cumene hydroperoxide	Allergen, Central nervous system, Corrosive, Irritant, Mutagen
Acetic acid, 2-phenylhydrazide	Allergen, Blood, Kidney, Mutagen, Some evidence of carcinogenicity

12. ECOLOGICAL INFORMATION

Ecological information: Not available

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Follow all local, state, federal and provincial regulations for disposal.

Hazardous waste number: Not a RCRA hazardous waste.

14. TRANSPORT INFORMATION

The shipping classifications in this sections are for non-bulk packaging only (unless otherwise specified). Shipping classification may be different for bulk packaging.

U.S. Department of Transportation Ground (49 CFR)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

International Air Transportation (ICAO/IATA)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

Water Transportation (IMO/IMDG)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

15. REGULATORY INFORMATION

United States Regulatory Information

TSCA 8 (b) Inventory Status: All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.
TSCA 12(b) Export Notification: None above reporting de minimus

CERCLA/SARA Section 302 EHS: None above reporting de minimus
CERCLA/SARA Section 311/312: Immediate Health, Delayed Health
CERCLA/SARA 313: This product contains the following toxic chemicals subject to the reporting requirements of section 313 of the Emergency Planning and Community Right-To-Know Act of 1986 (40 CFR 372). Acrylic acid (CAS# 79-10-7). Cumene hydroperoxide (CAS# 80-15-9). Cumene hydroperoxide (CAS# 80-15-9) 10 lbs. (4.54 kg)
CERCLA Reportable quantity:
California Proposition 65: This product contains a chemical known in the State of California to cause cancer.

Canada Regulatory Information

CEPA DSL/NDSL Status: All components are listed on or are exempt from listing on the Canadian Domestic Substances List.
WHMIS hazard class: D.2.B

16. OTHER INFORMATION

This material safety data sheet contains changes from the previous version in sections: New Material Safety Data Sheet format.

Prepared by: Kyra Kozak Woods, Manager, Regulatory Affairs

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation does not assume responsibility for any results obtained by persons over whose methods Henkel Corporation has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any of Henkel Corporation's products. In light of the foregoing, Henkel Corporation specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation further disclaims any liability for consequential or incidental damages of any kind, including lost profits.