

GC Electronics
1801 Morgan Street
Rockford, IL 61102
Phone: (815) 968-9661
Fax: (815) 968-9731
www.gcelectronics.com

Product Name: GLASS & PLASTIC CLEANER

MSDS Number: 167
Revision Date: 3/22/12
Supersedes Date: 3/24/09

MATERIAL SAFETY DATA SHEET

Complies with OSHA Hazard Communication Standard 29 CFR 1910.1200

Product Type: **Specialty**
Product Name: **GC Glass & Plastic Cleaner**
Part Number(s): **10-9082**

Emergency Contact: **Chemtrec**
Phone (24 hours): **(800) 424-9300**

Section 1 - Identification of Product

COMMON NAME (used on label) (Trade Name & Synonyms): **GC Glass & Plastic Cleaner**

CAS. NUMBER: See Section 2

CHEMICAL NAME: Alcohol & Water

CHEMICAL FAMILY: N/A

FORMULA: N/A

HMIS RATINGS

	Minimal Hazard	0
	Slight Hazard	1
Health: 1	Moderate Hazard	2
Flammability: 0	Serious Hazard	3
Reactivity: 0	Severe Hazard	4
Personal Protection: B	Gloves, Safety Glasses	B

Section 2 - Hazardous Ingredients

Principal Hazardous Component(s)

CHEMICAL AND COMMON NAME(S)	CAS. #	OSHA PEL	ACGIH TLV	VAPOR	LEL	UEL	FLASH POINT DEG. F	% BY WT
				PRESSURE @ 25 DEG. C.				
Ethyl Alcohol	64-17-5	1000ppm	1000ppm	44 mmHg	3.3	19.0	54(TCC)	5 - 10
Ethylene Glycol								
Monobutyl Ether	111-76-2	50ppm	50ppm	0.6mmHg	1.1	10.6	154 (TCC)	2 - 5
Liquefied Petroleum Gas (Propellant)	68476-85-7	1000ppm	1000ppm	3691 mmHg	2.0	10.0	-156 Est.	5 - 10
Aqua Ammonia	1336-21-6	NE	5 mg/m ³	N/A	N/A	N/A	None	<1

NOTE: Not subject to Section 313 of SARA Title III.

N/A is not available or not applicable

NE is not established

Section 3 - Physical Data

BOILING POINT (Deg. F): Concentrate Range: 212
SPECIFIC GRAVITY (Water = 1): Concentrate: 1.0
VAPOR PRESSURE (mmHg): See Section 2
PERCENT VOLATILE ORGANIC COMPOUNDS: 8%
VAPOR DENSITY (Air = 1): >1
EVAPORATION RATE (BA = 1): >1
SOLUBILITY IN WATER: Yes
REACTIVITY IN WATER: None
APPEARANCE AND ODOR: CONCENTRATE: Clear liquid, slight ammonia odor; PROPELLANT: Colorless, odorless gas; FINISHED PACKAGE: Pressurized containers.

Section 4 - Fire & Explosion Hazard Data

FLASH POINT: See Section 2
FLAMMABLE LIMITS IN AIR - % BY VOLUME: See Section 2
EXTINGUISHER MEDIA: Water fog, dry chemical, carbon dioxide
AUTO-IGNITION TEMPERATURE: Unknown
SPECIAL FIRE FIGHTING PROCEDURES: Water may be used to cool closed containers to prevent pressure build-up and possible bursting when exposed to high temperatures. Firemen should wear self-contained, positive pressure, respiratory equipment.
UNUSUAL FIRE AND EXPLOSION HAZARDS: Contents under pressure. Self-pressurized aerosol containers. Keep temperature of containers below 120 deg. F. to prevent bursting.

Section 5 - Health Hazard Data

THRESHOLD LIMIT VALUE: See Section 2

SIGNS AND SYMPTOMS OF EXPOSURE:

EYE CONTACT: Contact with liquid or mist may cause irritation. Vapors may irritate eyes;
SKIN CONTACT: Prolonged contact may cause irritation, defatting of skin;
INHALATION: Overexposure to vapor may cause dizziness, loss of concentration and irritation. INTENTIONAL MISUSE BY DELIBERATELY CONCENTRATING AND INHALING THE CONTENTS OF THE CAN MAY BE HARMFUL OR FATAL;
INGESTION: Single dose oral toxicity low. Aspiration may cause rapid absorption through the lungs, which may result in systemic effects.

EMERGENCY AND FIRST AID PROCEDURES

INHALATION: Remove to fresh air. If not breathing, give mouth-to-mouth. If breathing is difficult, give oxygen. Call a physician.

GC Electronics
1801 Morgan Street
Rockford, IL 61102
Phone: (815) 968-9661
Fax: (815) 968-9731
www.gcelectronics.com

Product Name: GLASS & PLASTIC CLEANER

MSDS Number: 167
Revision Date: 3/22/12
Supersedes Date: 3/24/09

EYES: Flush with water for at least 15 minutes. Get medical assistance if irritation persists.

SKIN: Wash off in flowing water or shower. Remove contaminated clothing and wash before reuse.

INGESTION: Do not induce vomiting. Call a physician immediately.

Section 6 - Reactivity Data

STABILITY: Stable

CONDITIONS TO AVOID: Avoid any excessive heat, ignition sources, open flames, or other high temperatures which induce thermal decomposition.

INCOMPATIBILITY (Materials to Avoid): None

HAZARDOUS DECOMPOSITION PRODUCTS: Carbon Dioxide. Carbon Monoxide

HAZARDOUS POLYMERIZATION: Will not occur.

CONDITIONS TO AVOID: Not Applicable

Section 7 - Spill or Leak Procedures

STEPS TO BE TAKEN IN CASE MATERIAL IS RELEASED OR SPILLED:

SMALL SPILLS: Remove ignition sources. Mop up, wipe up, or soak up immediately. Use proper protective equipment.

LARGE SPILLS: Evacuate area. Remove ignition sources. Contain liquid; transfer to closed containers; keep out of water supplies.

WASTE DISPOSAL METHODS: Dispose in accordance with Federal, State, and Local regulations. Do not incinerate closed or empty containers.

Section 8 - Special Protection Information

RESPIRATORY PROTECTION: NIOSH or Bureau of Mines approved organic vapor-type respirator is required in absence of proper environmental control.

VENTILATION:

LOCAL EXHAUST: To keep below TLV
MECHANICAL (General): To keep below TLV
SPECIAL: None
OTHER: None

PROTECTIVE GLOVES: Solvent resistant gloves - impervious gloves

EYE PROTECTION: Safety glasses or goggles

OTHER PROTECTIVE CLOTHING OR EQUIPMENT: None reasonably foreseeable.

GC Electronics
1801 Morgan Street
Rockford, IL 61102
Phone: (815) 968-9661
Fax: (815) 968-9731
www.gcelectronics.com

Product Name: GLASS & PLASTIC CLEANER

MSDS Number: 167
Revision Date: 3/22/12
Supersedes Date: 3/24/09

Section 9 – Special Precautions

PRECAUTIONS TO BE TAKEN

IN HANDLING AND STORAGE: Do not store above 110 Deg. F. Do not use or store near any open flames or ignition sources.

OTHER PRECAUTIONS: Contents under pressure. Do not puncture or incinerate. Exposure to temperatures above 120 Deg. F may cause can to burst with violence and cause injury. Vapors are heavier than air and will collect in low areas.

Section 10 - Regulatory Information

SUBJECT TO SECTION 313 OF SARA TITLE III: No.

ALL CHEMICAL COMPONENTS ARE LISTED IN THE TSCA INVENTORY.

CHEMICAL LISTED AS CARCINOGEN OR POTENTIAL CARCINOGEN: NATIONAL TOXICOLOGY PROGRAM: No

I.A.R.C. MONOGRAPHS: No

OSHA: No

OSHA PERMISSIBLE EXPOSURE LIMIT: See Section 2

ACGIH THRESHOLD LIMIT VALUE: See Section 2

OTHER EXPOSURE LIMITED USED: None

Section 11 - Other Information

TRANSPORTATION INFORMATION – DOMESTIC GROUND

Shipping Name: Consumer Commodity
Hazard Class: ORM-D
UN Number: N/A
Packing Group: N/A
Hazard Label: None
Carton Marking: Consumer Commodity ORM-D

Disclaimer

GC Electronics believes that the information contained herein is accurate and reliable as of the date of this material safety data sheet, but no representation guarantee or warranty, express or implied, is made as to the accuracy, reliability, or completeness of the information. Persons receiving this information are encouraged to make their own determination as to the information's suitability and completeness for their particular application. NO INFORMATION CONTAINED HEREIN CONSTITUTES A PRODUCT WARRANTY OF ANY KIND, WHETHER EXPRESS OR IMPLIED; AND ALL IMPLIED WARRANTIES OF MERCHANTABILITY AND OF FITNESS FOR A PARTICULAR PURPOSE ARE HEREBY DISCLAIMED BY GC ELECTRONICS.