


Part Number: G501

Type	Size	Rating	Description
Incandescent	G11	6.5V 300mA	G-3½ Edison screw lamp



All dimensions in mm.

TEST VOLTS	CURRENT (mA)			LIGHT OUTPUT (Lm)			LIFE Hours
	Min.	Nom.	Max.	Min.	Nom.	Max.	
6.5	270	300	330	10	12	14	4,000

Notes:

- 1 **Base Type** E10/13 Nickel plated brass
- 2 **Filament Shape** C-2R
- 3 **Bead Colour** White or clear
- 4 **Marking** CML 6.5V 300mA
- 5 **Environmental** RoHS & REACH SVHC compliant
- 6 **General** Equivalent to part N9951183