



Material Safety Data Sheet

Copyright, 2012, 3M Company All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

SECTION 1: PRODUCT AND COMPANY IDENTIFICATION

PRODUCT NAME: 3M™ Scotch-Weld™ Neoprene High Performance Contact Adhesive 1357
MANUFACTURER: 3M
DIVISION: Industrial Adhesives and Tapes Division
ADDRESS: 3M Center, St. Paul, MN 55144-1000

EMERGENCY PHONE: 1-800-364-3577 or (651) 737-6501 (24 hours)

Issue Date: 11/28/12
Supersedes Date: 03/09/11

Document Group: 10-2789-5

Product Use:

Intended Use: Adhesive
 Specific Use: Contact Adhesive

SECTION 2: INGREDIENTS

<u>Ingredient</u>	<u>C.A.S. No.</u>	<u>% by Wt</u>
Petroleum distillate	64741-84-0	30 - 60
Acetone	67-64-1	10 - 30
n-Hexane	110-54-3	5 - 20
Magnesium resinate	68037-42-3	7 - 13
Polychloroprene	9010-98-4	7 - 13
Methyl ethyl ketone	78-93-3	7 - 13
Toluene	108-88-3	3 - 7
Rosin	8050-09-7	0.1 - 1
Zinc oxide	1314-13-2	0.1 - 1

SECTION 3: HAZARDS IDENTIFICATION

3.1 EMERGENCY OVERVIEW

Odor, Color, Grade: Grey/green, strong petroleum odor.

General Physical Form: Liquid

Immediate health, physical, and environmental hazards: Closed containers exposed to heat from fire may build pressure and

explode. Extremely flammable liquid and vapor. Vapors may travel long distances along the ground or floor to an ignition source and flash back. May cause allergic skin reaction. May cause target organ effects. Contains a chemical or chemicals which can cause birth defects or other reproductive harm.

3.2 POTENTIAL HEALTH EFFECTS

Eye Contact:

Moderate Eye Irritation: Signs/symptoms may include redness, swelling, pain, tearing, and blurred or hazy vision.

Skin Contact:

Moderate Skin Irritation: Signs/symptoms may include localized redness, swelling, itching, and dryness.

Allergic Skin Reaction (non-photo induced): Signs/symptoms may include redness, swelling, blistering, and itching.

Inhalation:

Respiratory Tract Irritation: Signs/symptoms may include cough, sneezing, nasal discharge, headache, hoarseness, and nose and throat pain.

Prolonged or repeated exposure may cause:

Respiratory Effects: Signs/symptoms may include cough, shortness of breath, chest tightness, wheezing, increased heart rate, bluish colored skin (cyanosis), sputum production, changes in lung function tests, and/or respiratory failure.

May be absorbed following inhalation and cause target organ effects.

Ingestion:

Gastrointestinal Irritation: Signs/symptoms may include abdominal pain, stomach upset, nausea, vomiting and diarrhea.

May be absorbed following ingestion and cause target organ effects.

Target Organ Effects:

Central Nervous System (CNS) Depression: Signs/symptoms may include headache, dizziness, drowsiness, incoordination, nausea, slowed reaction time, slurred speech, giddiness, and unconsciousness.

Prolonged or repeated exposure may cause:

Auditory Effects: Signs/symptoms may include hearing impairment, balance dysfunction and ringing in the ears.

Neurological Effects: Signs/symptoms may include personality changes, lack of coordination, sensory loss, tingling or numbness of the extremities, weakness, tremors, and/or changes in blood pressure and heart rate.

Ocular Effects: Signs/symptoms may include blurred or significantly impaired vision.

Olfactory Effects: Signs/symptoms may include decreased ability to detect odors and/or complete loss of smell.

Peripheral Neuropathy: Signs/symptoms may include tingling or numbness of the extremities, incoordination, weakness of the hands and feet, tremors and muscle atrophy.

Contains a chemical or chemicals which can cause birth defects or other reproductive harm.

SECTION 4: FIRST AID MEASURES

4.1 FIRST AID PROCEDURES

The following first aid recommendations are based on an assumption that appropriate personal and industrial hygiene practices are

followed.

Eye Contact: Flush eyes with large amounts of water. If signs/symptoms persist, get medical attention.

Skin Contact: Remove contaminated clothing and shoes. Immediately flush skin with large amounts of water. Get medical attention. Wash contaminated clothing and clean shoes before reuse.

Inhalation: Remove person to fresh air. If signs/symptoms develop, get medical attention.

If Swallowed: Do not induce vomiting unless instructed to do so by medical personnel. Give victim two glasses of water. Never give anything by mouth to an unconscious person. Get medical attention.

SECTION 5: FIRE FIGHTING MEASURES

5.1 FLAMMABLE PROPERTIES

Autoignition temperature	404 °C
Flash Point	-14 °F [<i>Test Method:</i> Closed Cup] [<i>Details:</i> Acetone]
Flammable Limits(LEL)	1.0 % volume
Flammable Limits(UEL)	12.8 % volume
OSHA Flammability Classification:	Class IB Flammable Liquid

5.2 EXTINGUISHING MEDIA

Use fire extinguishers with class B extinguishing agents (e.g., dry chemical, carbon dioxide).

5.3 PROTECTION OF FIRE FIGHTERS

Special Fire Fighting Procedures: Water may not effectively extinguish fire; however, it should be used to keep fire-exposed containers and surfaces cool and prevent explosive rupture. Wear full protective equipment (Bunker Gear) and a self-contained breathing apparatus (SCBA).

Unusual Fire and Explosion Hazards: Closed containers exposed to heat from fire may build pressure and explode. Extremely flammable liquid and vapor. Vapors may travel long distances along the ground or floor to an ignition source and flash back.

Note: See STABILITY AND REACTIVITY (SECTION 10) for hazardous combustion and thermal decomposition information.

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Evacuate unprotected and untrained personnel from hazard area. The spill should be cleaned up by qualified personnel. Remove all ignition sources such as flames, smoking materials, and electrical spark sources. Use only non-sparking tools. Ventilate the area with fresh air. For large spill, or spills in confined spaces, provide mechanical ventilation to disperse or exhaust vapors, in accordance with good industrial hygiene practice. Warning! A motor could be an ignition source and could cause flammable gases or vapors in the spill area to burn or explode. Remember, adding an absorbent material does not remove a toxic, corrosivity or flammability hazard.

6.2. Environmental precautions

For larger spills, cover drains and build dikes to prevent entry into sewer systems or bodies of water. Collect the resulting residue containing solution. Place in a metal container approved for transportation by appropriate authorities. Dispose of collected material as soon as possible.

Clean-up methods

Refer to other sections of this MSDS for information regarding physical and health hazards, respiratory protection, ventilation, and personal protective equipment. Call 3M-HELPS line (1-800-364-3577) for more information on handling and managing the spill. Contain spill. Cover spill area with a fire-extinguishing foam. An aqueous film forming foam (AFFF) is recommended. Working from around the edges of the spill inward, cover with bentonite, vermiculite, or commercially available inorganic absorbent material.

Mix in sufficient absorbent until it appears dry. Collect as much of the spilled material as possible using non-sparking tools. Clean up residue with an appropriate solvent selected by a qualified and authorized person. Ventilate the area with fresh air. Read and follow safety precautions on the solvent label and MSDS. Seal the container.

In the event of a release of this material, the user should determine if the release qualifies as reportable according to local, state, and federal regulations.

SECTION 7: HANDLING AND STORAGE

7.1 HANDLING

Do not eat, drink or smoke when using this product. Wash exposed areas thoroughly with soap and water. Contents may be under pressure, open carefully. Ground containers securely when transferring contents. Wear low static or properly grounded shoes. Vapors may ignite explosively. May cause flash fire. Prevent build-up of vapors - open all windows and doors. Maintain vapor concentrations below recommended exposure limits. Use only with cross-ventilation. Without adequate ventilation, vapors may settle in low-lying areas. Keep away from heat, sparks, and open flame. Do not smoke or ignite matches, lighters, etc. Extinguish pilot lights and turn off stoves, ovens and other gas and electric appliances (space and water heaters, furnaces, etc.), electric motors, and other sources of ignition during adhesive use and until all vapors are gone; i.e., until the odor of vapors at the floor level has disappeared. Do not use electric light switches. Do not generate static sparks (such as by walking on carpet, etc.). Use the same precautions in the work area and all connected areas. Be sure that any people in the area follow the precautions. Attach a copy of the precautions to any other container to which this product may be transferred. Avoid prolonged breathing of vapors. Avoid eye and skin contact. Keep container closed when not in use. If work area conditions prevent compliance with any of the above precautions, do not use the product. Keep out of the reach of children. For industrial or professional use only. Not intended for consumer sale or use. Do not breathe vapors.

7.2 STORAGE

Store away from acids. Store away from heat. Store out of direct sunlight. Keep container in well-ventilated area. Keep container tightly closed. Store away from oxidizing agents.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1 ENGINEERING CONTROLS

Use with appropriate local exhaust ventilation. Provide local exhaust ventilation at transfer points. Provide appropriate local exhaust ventilation on open containers. Use in an enclosed process area is recommended. If exhaust ventilation is not available, use appropriate respiratory protection. Do not use in a confined area or areas with little or no air movement. Use general dilution ventilation and/or local exhaust ventilation to control airborne exposures to below Occupational Exposure Limits and/or control mist, vapor, or spray. If ventilation is not adequate, use respiratory protection equipment.

8.2 PERSONAL PROTECTIVE EQUIPMENT (PPE)

8.2.1 Eye/Face Protection

Avoid eye contact with vapors, mists, or spray.

The following eye protection(s) are recommended: Indirect Vented Goggles

.

8.2.2 Skin Protection

Avoid skin contact.

Select and use gloves and/or protective clothing to prevent skin contact based on the results of an exposure assessment. Consult with your glove and/or protective clothing manufacturer for selection of appropriate compatible materials.

Gloves made from the following material(s) are recommended: Butyl Rubber

Polymer laminate

.

8.2.3 Respiratory Protection

Avoid breathing of vapors, mists or spray. Do not breathe vapors.

An exposure assessment may be needed to decide if a respirator is required. If a respirator is needed, use respirators as part of a full respiratory protection program. Based on the results of the exposure assessment, select from the following respirator type(s) to reduce inhalation exposure:

Half facepiece or full facepiece air-purifying respirator suitable for organic vapors

For questions about suitability for a specific application, consult with your respirator manufacturer.

8.2.4 Prevention of Swallowing

Do not eat, drink or smoke when using this product. Wash exposed areas thoroughly with soap and water.

8.3 EXPOSURE GUIDELINES

<u>Ingredient</u>	<u>Authority</u>	<u>Type</u>	<u>Limit</u>	<u>Additional Information</u>
Acetone	ACGIH	TWA	500 ppm	
Acetone	ACGIH	STEL	750 ppm	
Acetone	OSHA	TWA	2400 mg/m3	
n-Hexane	ACGIH	TWA	50 ppm	Skin Notation*
n-Hexane	OSHA	TWA	1800 mg/m3	
Methyl ethyl ketone	ACGIH	TWA	200 ppm	
Methyl ethyl ketone	ACGIH	STEL	300 ppm	
Methyl ethyl ketone	OSHA	TWA	590 mg/m3	
Toluene	ACGIH	TWA	20 ppm	
Toluene	CMRG	STEL	75 ppm	Skin Notation*
Toluene	OSHA	TWA	200 ppm	
Toluene	OSHA	CEIL	300 ppm	
Zinc oxide	ACGIH	TWA, respirable fraction	2 mg/m3	
Zinc oxide	ACGIH	STEL, respirable fraction	10 mg/m3	
Zinc oxide	OSHA	TWA, as fume	5 mg/m3	
Zinc oxide	OSHA	TWA, respirable fraction	5 mg/m3	
Zinc oxide	OSHA	TWA, as total dust	15 mg/m3	

* Substance(s) refer to the potential contribution to the overall exposure by the cutaneous route including mucous membrane and eye, either by airborne or, more particularly, by direct contact with the substance. Vehicles can alter skin absorption.

SOURCE OF EXPOSURE LIMIT DATA:

ACGIH: American Conference of Governmental Industrial Hygienists

CMRG: Chemical Manufacturer Recommended Guideline

OSHA: Occupational Safety and Health Administration

AIHA: American Industrial Hygiene Association Workplace Environmental Exposure Level (WEEL)

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

Odor, Color, Grade:	Grey/green, strong petroleum odor.
General Physical Form:	Liquid
Autoignition temperature	404 °C
Flash Point	-14 °F [Test Method: Closed Cup] [Details: Acetone]
Flammable Limits(LEL)	1.0 % volume
Flammable Limits(UEL)	12.8 % volume
Boiling Point	>=80 °C [Details: Acetone]

Density	0.815 g/ml
Vapor Density	2.0 [<i>Ref Std:</i> AIR=1]
Vapor Pressure	<=185 mmHg [<i>@</i> 68 °F]
Specific Gravity	.815 [<i>Ref Std:</i> WATER=1]
pH	<i>Not Applicable</i>
Melting point	<i>Not Applicable</i>
Solubility in Water	Slight (less than 10%)
Evaporation rate	>=2.0 [<i>Ref Std:</i> WATER=1]
Hazardous Air Pollutants	<=13.2 % weight [<i>Test Method:</i> Calculated]
Volatile Organic Compounds	<=674 g/l [<i>Details:</i> EU VOC content]
Kow - Oct/Water partition coef	<i>No Data Available</i>
Percent volatile	70 - 80 %
VOC Less H2O & Exempt Solvents	<=582 g/l [<i>Test Method:</i> tested per EPA method 24A]
VOC Less H2O & Exempt Solvents	<=5.44 lb/gal [<i>Test Method:</i> calculated SCAQMD rule 443.1]
VOC Less H2O & Exempt Solvents	<=66.2 % [<i>Test Method:</i> calculated per CARB title 2]
Viscosity	200 - 450 centipoise [<i>@</i> 73.4 °F]
Solids Content	>=16.8 %

SECTION 10: STABILITY AND REACTIVITY

Stability: Stable.

Materials and Conditions to Avoid:

10.1 Conditions to avoid

Heat
Sparks and/or flames

10.2 Materials to avoid

Strong oxidizing agents

Hazardous Polymerization: Hazardous polymerization will not occur.

Hazardous Decomposition or By-Products

<u>Substance</u>	<u>Condition</u>
Hydrocarbons	During Combustion
Carbon monoxide	During Combustion
Carbon dioxide	During Combustion

SECTION 11: TOXICOLOGICAL INFORMATION

Please contact the address listed on the first page of the MSDS for Toxicological Information on this material and/or its components.

SECTION 12: ECOLOGICAL INFORMATION

ECOTOXICOLOGICAL INFORMATION

Not determined.

CHEMICAL FATE INFORMATION

Not determined.

SECTION 13: DISPOSAL CONSIDERATIONS

Waste Disposal Method: Dispose of completely cured (or polymerized) wastes in a sanitary landfill. Incinerate uncured product in a permitted hazardous waste incinerator.

EPA Hazardous Waste Number (RCRA): D001 (Ignitable), D035 (Methyl ethyl ketone)

Since regulations vary, consult applicable regulations or authorities before disposal.

SECTION 14: TRANSPORT INFORMATION

ID Number(s):

62-1357-2630-5, 62-1357-2631-3, 62-1357-5530-4, 62-1357-5535-3, 62-1357-6530-3, 62-1357-7530-2, 62-1357-8530-1, 62-1357-8540-0, 62-1357-9530-0, 62-1357-9531-8, 62-1357-9532-6, 78-8990-0393-9

For Transport Information, please visit <http://3M.com/Transportinfo> or call 1-800-364-3577 or 651-737-6501.

SECTION 15: REGULATORY INFORMATION

US FEDERAL REGULATIONS

Contact 3M for more information.

311/312 Hazard Categories:

Fire Hazard - Yes Pressure Hazard - No Reactivity Hazard - No Immediate Hazard - Yes Delayed Hazard - Yes

Section 313 Toxic Chemicals subject to the reporting requirements of that section and 40 CFR part 372 (EPCRA):

<u>Ingredient</u>	<u>C.A.S. No</u>	<u>% by Wt</u>
Toluene	108-88-3	3 - 7
n-Hexane	110-54-3	5 - 20

STATE REGULATIONS

Contact 3M for more information.

CALIFORNIA PROPOSITION 65

<u>Ingredient</u>	<u>C.A.S. No.</u>	<u>Classification</u>
Toluene	108-88-3	*Female reproductive toxin
Toluene	108-88-3	*Developmental Toxin

* WARNING: contains a chemical or chemicals which can cause birth defects or other reproductive harm.

CHEMICAL INVENTORIES

The components of this product are in compliance with the chemical notification requirements of TSCA.

All applicable chemical ingredients in this material are listed on the European Inventory of Existing Chemical Substances (EINECS),

or are exempt polymers whose monomers are listed on EINECS. Contact 3M for more information.

INTERNATIONAL REGULATIONS

Contact 3M for more information.

WHMIS: Hazardous

This MSDS has been prepared to meet the U.S. OSHA Hazard Communication Standard, 29 CFR 1910.1200.

SECTION 16: OTHER INFORMATION

NFPA Hazard Classification

Health: 2 **Flammability:** 3 **Reactivity:** 0 **Special Hazards:** None

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

Revision Changes:

Section 1: Product use information was modified.
Section 16: Disclaimer (second paragraph) was modified.
Section 10: Hazardous decomposition or by-products table was modified.
Section 8: Respiratory protection - recommended respirators information was modified.
Section 8: Respiratory protection - recommended respirators was modified.
Section 9: Density information was modified.
Section 9: Vapor density value was modified.
Section 9: Vapor pressure value was modified.
Section 9: Boiling point information was modified.
Section 5: Flammable limits (UE) information was modified.
Section 5: Flammable limits (LEL) information was modified.
Section 5: Autoignition temperature information was modified.
Section 5: Flash point information was modified.
Section 9: Property description for required properties was modified.
Section 9: Property description for optional properties was modified.
Section 9: Specific gravity information was modified.
Section 9: pH information was modified.
Section 9: Melting point information was modified.
Section 9: Solubility in water text was modified.
Section 8: Respiratory protection - recommended respirators guide was modified.
Section 9: Flash point information was modified.
Section 9: Flammable limits (LEL) information was modified.
Section 9: Flammable limits (UEL) information was modified.
Section 9: Autoignition temperature information was modified.
Section 2: Ingredient table was modified.
Section 15: EPCRA 313 information was modified.
Section 8: Exposure guidelines ingredient information was modified.
Section 15: California proposition 65 ingredient information was modified.
Section 16: Web address was added.
Section 1: Address was added.
Copyright was added.
Company logo was added.

Telephone header was added.
Company Telephone was added.
Section 1: Emergency phone information was added.
Section 1: Emergency phone information was deleted.
Company Logo was deleted.
Copyright was deleted.
Section 16: Web address heading was deleted.
Section 1: Address line 1 was deleted.
Section 1: Address line 2 was deleted.
Section 8: Respiratory protection - recommended respirators punctuation was deleted.

DISCLAIMER: The information in this Material Safety Data Sheet (MSDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the MSDS available directly from 3M

3M USA MSDSs are available at www.3M.com



Transport Information Document

Date: April 04, 2013

3M ID Number: 62-1357-2631-3

Product Description: 3M(TM) Scotch-Weld(TM) Neoprene High Performance Contact Adhesive 1357 Gray-Green, 5 Ounce Tube, 36 per case

Transport Protective Service: MAINTAIN TEMP ABOVE 32F (0C)

NMFC Item: 004620

NMFC Sub: 06

NMFC Class: 060.0

Flash Point (Closed-cup): -4°F/-20°C

UNITED STATES DEPARTMENT OF TRANSPORTATION - GROUND (U.S. DOT, 49 CFR)

CONSUMER COMMODITY, ORM-D OR LIMITED QUANTITY

UNITED STATES DEPARTMENT OF TRANSPORTATION - VESSEL (U.S. DOT, 49 CFR)

UN1133, ADHESIVES, 3, II, LIMITED QUANTITY, MARINE POLLUTANT, (NAPTHA(PETROLEUM), SOLVENT-REFINED LIGHT AND ZINC OXIDE), -020C

INTERNATIONAL AIR TRANSPORT ASSOCIATION (IATA)

UN1133, ADHESIVES, 3, II

INTERNATIONAL MARITIME ORGANIZATION (IMO)

UN1133, ADHESIVES, 3, II, LIMITED QUANTITY, MARINE POLLUTANT, (NAPTHA(PETROLEUM), SOLVENT-REFINED LIGHT AND ZINC OXIDE), -020C

The classification is authorized by the Competent Authority of the United States of America and may not meet the requirements of other competent authorities.

These transportation classifications are provided as a customer service. AS THE SHIPPER YOU REMAIN RESPONSIBLE FOR COMPLYING WITH ALL THE APPLICABLE LAWS AND REGULATIONS, INCLUDING PROPER TRANSPORTATION CLASSIFICATION AND PACKAGING. 3M's transportation classifications are based on product formulations, packaging, 3M policies and 3M's understanding of applicable current regulations and is valid for the original 3M package only. 3M does not guarantee the accuracy of this classification information. This information applies only to transportation classification and NOT THE PACKAGING, LABELING, OR MARKING REQUIREMENTS. The original 3M package is certified for U.S. ground shipment only. If you are shipping by air or ocean, the package may not meet applicable regulatory requirements.

For Transport Information, please visit 3M.com/Transportinfo

or call 1-800-364-3577 or 651-737-6501 for assistance.