


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [74441-0010](#)  
**Status:** **Active**  
**Description:** 0.80mm Pitch SFP, SFP Plus (SFP+) Host Connector, Z-Axis Pluggable, Right Angle, SMT, 20 Circuits, 0.76µm Gold (Au)

**Documents:**

<a href="#">3D Model</a>	<a href="#">Test Summary TS-74441-0003 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Test Summary TS-74441-002 (PDF)</a>
<a href="#">Product Specification PS-74441-001 (PDF)</a>	<a href="#">Test Summary TS-74441-010 (PDF)</a>
<a href="#">Application Specification AS-74441-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>



**Agency Certification**

CSA	LR19980
UL	E29179

**General**

Product Family	I/O Connectors
Series	<a href="#">74441</a>
Application	Module-to-Board
Component Type	Receptacle
Electrical Model	Yes
Product Name	SFP, SFP Plus
Type	N/A
UPC	800756382647

**Physical**

Boot Color	N/A
Circuits (Loaded)	20
Circuits (maximum)	20
Circuits Detail	20
Color - Resin	Black
Durability (mating cycles max)	200
Flammability	94V-0
Gender	Receptacle
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	0.700/g
Number of Rows	2
Orientation	Right Angle
PCB Locator	Yes
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Panel Mount	No
Pitch - Mating Interface	0.80mm
Pitch - Termination Interface	0.80mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Ports	1
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40°C to +85°C

**EU RoHS** **China RoHS**

**ELV and RoHS Compliant**  
**REACH SVHC Contains SVHC: No**  
**Low-Halogen Status Low-Halogen**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[74441Series](#)

**Mates With**

SFP Modules

**Use With**

EMI Shield, [73927 SFP Cage](#), [86025 LC Duplex Cable Assembly](#), Guide Frame, [73939 HSSDC2 Cable Assembly](#)

Termination Interface: Style	Surface Mount
Waterproof / Dustproof	No
Wire Size AWG	N/A

### **Electrical**

Current - Maximum per Contact	0.5A
Grounding to Panel	Yes
Shielded	No
Voltage - Maximum	30V AC (RMS)/DC

### **Solder Process Data**

Duration at Max. Process Temperature (seconds)	40
Lead-free Process Capability	Reflow Capable (SMT only)
Max. Cycles at Max. Process Temperature	3
Process Temperature max. C	260

### **Material Info**

#### **Reference - Drawing Numbers**

Application Specification	AS-74441-001
Electrical Model Document	EE-74441-001
Product Specification	PS-74441-001
S-Parameter Model	SP-74441-001
Sales Drawing	SD-74441-001
Test Summary	TS-74441-0003, TS-74441-002, TS-74441-010

This document was generated on 02/07/2014

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**