

SECTION 1: CHEMICAL PRODUCT AND COMPANY IDENTIFICATION**Company Address:**

8125 Cobb Center Drive
Kennesaw, GA 30152

Product Information: 800-TECH-401
Customer Service: 800-645-5244

Emergency: (Chemtrec) 800-424-9300
Revision Date: October 31, 2012

Product Identification**CHEMSWAB™ PRESATURATED SWAB****Product Code:** CS25**SECTION 2: COMPOSITION/INFORMATION ON INGREDIENTS**

Chemical Name	CAS#	Wt. % Range
Isopropanol	67-63-0	85.0-95.0
Deionized water	7732-18-5	5.0-15.0

SECTION 3: HAZARD IDENTIFICATION

Emergency Overview: Plastic handled foam swab, pre-saturated with isopropanol. Liquid is flammable. Liquid will irritate eyes and skin under repeated or prolonged exposure. Breathing high concentrations of product vapor may produce drowsiness and a headache.

Potential Health Effects:

Eyes: Liquid contents of this product are irritating and can cause pain, tearing, reddening and swelling accompanied by a stinging sensation.

Skin: Prolonged contact with liquid contents may cause skin irritation.

Ingestion: Harmful if swallowed. Irritating to mouth, throat and stomach. May cause vomiting.

Inhalation: Harmful if inhaled. High concentrations of liquid vapors in immediate area can displace oxygen and can cause dizziness, unconsciousness, and even death with longer exposure. Keep people away from such vapors without self-contained breathing apparatus.

Pre-Existing Medical Conditions Aggravated by Exposure Skin.

SECTION 4: FIRST AID MEASURES

Eyes: Immediately flush with plenty of water. After initial flushing, remove any contact lenses and continue flushing for at least 15 minutes. Have eyes examined and tested by medical personnel if irritation develops or persists.

Skin: Wash skin with soap and water. Remove contaminated clothing. Get medical attention if irritation develops or persist. Wash clothing separately before reuse.

Ingestion: Swallowing less than an ounce will not cause significant harm. For larger amounts, do not induce vomiting, but give one or two glasses of water to drink and get immediate medical attention.

Inhalation: Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get medical attention.

SECTION 5: FIRE FIGHTING MEASURES

Flash Point: 61°F (16C) (Liquid) **LEL/UEL:** 2.0/12.7 (% by volume in air for product liquid)

Extinguishing Media: Use alcohol foam, carbon dioxide, or water spray when fighting fires involving this material.

Fire Fighting Instructions: As in any fire, wear self-contained breathing apparatus (pressure-demand, MSHA/NIOSH approved or equivalent) and full protective gear.

SECTION 6: ACCIDENTAL RELEASE MEASURES

Large Spills: Shut off leak if possible and safe to do so. Wear a self-contained breathing apparatus and appropriate personal protective equipment. Absorb spilled liquid with inert material (e.g. dry sand or earth), then place in a chemical waste container for proper disposal. Do not flush to sewer. Avoid runoff into storm sewers and ditches which lead to waterways.

Small Spills: Absorb spilled liquid with inert material (e.g. dry sand or earth), then place in a chemical waste container for proper disposal.

SECTION 7: HANDLING AND STORAGE

Avoid prolonged or repeated contact with eyes, skin, and clothing. Wash hands before eating. Use with adequate ventilation. Avoid breathing product vapor or mist. Do not reuse this container. Store in a cool dry place away from heat, sparks and flame. Keep container closed when not in use. Do not store in direct sunlight.

KEEP OUT OF REACH OF CHILDREN.**SECTION 8: EXPOSURE CONTROLS/ PERSONAL PROTECTION****Exposure Guidelines:**

CHEMICAL NAME	ACGIH TLV	OSHA PEL	ACGIH STEL
Isopropanol	200 ppm	400 ppm	400ppm

Work/Hygienic Practices: Good general ventilation should be sufficient to control airborne levels. Local exhaust ventilation may be necessary to control any air contaminants to within their TLVs during the use of this product. If vapor concentration exceeds TLV, use NIOSH approved organic vapor cartridge respirator. Wear safety glasses with side shields (or goggles) and rubber or other chemically resistant gloves when handling this material.

NFPA and HMIS Codes:

	NFPA	HMIS
Health	1	1
Flammability	3	3
Reactivity	1	1
Personal Protection	-	B

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

Physical State: Premoistened swab

Solubility in Water: Soluble (liquid only)

Odor: Ethereal solvent

Specific Gravity: (Water =1) 0.78 (liquid only)

Color: Colorless liquid

Evaporation Rate: >1

pH: NA

(Butyl acetate=1)

Vapor Pressure: 33 mm Hg @75F (liquid)

Viscosity: NA

Vapor Density: 2.07 @ 75 F (liquid)

Percent Volatile: 100%

(Air 1)

Boiling Point: 180 F (82C) (liquid only)

SECTION 10: STABILITY AND REACTIVITY

Stability: This product is stable. Conditions to Avoid: Do not allow swab to come in contact with open flames, red hot surfaces or other sources of ignition.

Incompatibility: Do not mix with strong acids, bases or oxidizing agents.

Products of Decomposition: Thermal decomposition may release carbon monoxide, carbon dioxide.

Hazardous Polymerization: Will not occur.

Conditions to Avoid: NA

SECTION 11: TOXICOLOGICAL INFORMATION**Inhalation:**

Isopropanol Rats LC50 12,000 ppm/8hrs.

Ingestion:

Isopropanol Rats LD50 5,800 mg/kg

Skin:

Isopropanol Rabbit MLD

Eye:

Isopropanol Rabbit 100mg MLD-MOD

Cancer Information: No ingredients listed as human carcinogens by NTP or IARC

Reproductive effects: none

Teratogenic effects: none

Mutagenic effects: none

SECTION 12: ECOLOGICAL INFORMATION

Avoid runoff into storm sewers and ditches, which lead to waterways. Water runoff can cause environmental damage.

REPORTING

US regulations require reporting spills of this material that could reach any surface waters. The toll free number for the US Coast Guard National Response Center is: 1-800-424-8802

SECTION 13: DISPOSAL CONSIDERATIONS

Dispose of in accordance with all federal, state and local regulations.

SECTION 14: TRANSPORTATION INFORMATION

Proper Shipping Name

Air and Ground: Not regulated

SECTION 15: REGULATORY INFORMATION**SECTION 313 SUPPLIER NOTIFICATION**

This product contains no toxic chemicals subject to the reporting requirements of Section 313 of the Emergency Planning and Community Right-To-Know Act of 1986 (40 CFR 372).

This information should be included on all MSDSs copied and distributed for this material.

TOXIC SUBSTANCES CONTROL ACT (TSCA): All ingredients of this product are listed on the TSCA Inventory.

WHMIS: Class: B2 Flammable Liquid

Class: D2B Material causing other toxic effects

This product has been classified according to the hazard criteria of the CPR and the MSDS contains all of the information required by the CPR.

SECTION 16: OTHER INFORMATION

Normal ventilation for standard manufacturing procedures is generally adequate. Local exhaust should be used when large amounts are released.

To the best of our knowledge, the information contained herein is accurate. However, all materials may present unknown hazards and should be used with caution. In particular, improper use of our products and their inappropriate combination with other products and substances may produce harmful results which cannot be anticipated. Final determination of the suitability of any material is the sole responsibility of the user. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that may exist.