



Revision Number: 003.1

Issue date: 04/08/2009

1. PRODUCT AND COMPANY IDENTIFICATION

Product name: PST® 592 Pipe Sealant With PTFE **IDH number:** 88567
Product type: Anaerobic Sealant **Item number:** 59214
Region: United States
Company address:
 Henkel Corporation
 1001 Trout Brook Crossing
 Rocky Hill, Connecticut 06067
Contact information:
 Telephone: 860.571.5100
 Emergency telephone: 860.571.5100
 Internet: www.henkelna.com

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW

Physical state: Paste **HMIS:** *2
Color: White **HEALTH:** 2
Odor: Mild **FLAMMABILITY:** 1
Personal Protection: See MSDS Section 8
WARNING: CAUSES EYE IRRITATION.
 MAY CAUSE ALLERGIC SKIN REACTION.
 MAY CAUSE RESPIRATORY TRACT IRRITATION.

Relevant routes of exposure: Skin, Inhalation, Eyes

Potential Health Effects

Inhalation: May cause respiratory tract irritation. Vapors may cause headaches, nausea, dizziness and respiratory tract irritation.
Skin contact: May cause allergic skin reaction. May cause skin irritation with discomfort or rash.
Eye contact: Contact with eyes will cause irritation.
Ingestion: Not expected to be harmful by ingestion.

Existing conditions aggravated by exposure: Eye, skin, and respiratory disorders.

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

See Section 11 for additional toxicological information.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous components	CAS NUMBER	%
Bisphenol A fumarate resin	39382-25-7	10 - 30
Mica	12001-26-2	10 - 30
Polyglycol dimethacrylate	25852-47-5	10 - 30
Octan-1-ol	111-87-5	10 - 30
Polyglycol dioctanoate	18268-70-7	10 - 30
Silica, amorphous, treated	68909-20-6	1 - 5
Titanium dioxide	13463-67-7	1 - 5
Propanediol-1,2	57-55-6	1 - 5
Fragrance	Unknown	1 - 5
Quartz (SiO ₂)	14808-60-7	0.1 - 1

4. FIRST AID MEASURES

Inhalation:	Move to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get medical attention.
Skin contact:	Wash with soap and water. Remove contaminated clothing and footwear. Wash clothing before reuse. If symptoms develop and persist, get medical attention.
Eye contact:	Flush with copious amounts of water, preferably, lukewarm water for at least 15 minutes, holding eyelids open all the time. Get medical attention.
Ingestion:	Do not induce vomiting. Never give anything by mouth to an unconscious person. Keep individual calm. Get medical attention.

5. FIRE FIGHTING MEASURES

Flash point:	> 93.3 °C (> 199.94 °F) Tagliabue closed cup
Autoignition temperature:	Not available
Flammable/Explosive limits - lower:	Not available
Flammable/Explosive limits - upper:	Not available
Extinguishing media:	Foam, dry chemical or carbon dioxide.
Special firefighting procedures:	Not available
Unusual fire or explosion hazards:	Not available
Hazardous combustion products:	Oxides of carbon. Toxic fluorine compounds. Irritating organic vapours.

6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

Environmental precautions:	Do not allow product to enter sewer or waterways.
Clean-up methods:	Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Store in a partly filled, closed container until disposal.

7. HANDLING AND STORAGE

Handling:	Avoid contact with eyes, skin and clothing. Use only with adequate ventilation.
Storage:	For safe storage, store at or below 38 °C (100.4 °F)

For information on product shelf life contact Henkel Customer Service at (800) 243-4874.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous components	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Bisphenol A fumarate resin	None	None	None	None
Mica	3 mg/m ³ TWA Respirable fraction.	20 MPPCF TWA	None	None
Polyglycol dimethacrylate	None	None	None	None
Octan-1-ol	None	None	50 ppm (265 mg/m ³) TWA	None
Polyglycol dioctanoate	None	None	None	None
Silica, amorphous, treated	10 mg/m ³ TWA Inhalable dust.	6 mg/m ³ TWA	None	None
Titanium dioxide	10 mg/m ³ TWA	15 mg/m ³ TWA Total dust.	None	None
Propanediol-1,2	None	None	10 mg/m ³ TWA Aerosol.	None
Fragrance	None	None	None	None
Quartz (SiO ₂)	0.025 mg/m ³ TWA Respirable fraction.	2.4 MPPCF TWA Respirable. 0.1 mg/m ³ TWA Respirable. 0.3 mg/m ³ TWA Total dust.	None	None

Engineering controls:

No specific ventilation requirements noted, but forced ventilation may still be required if concentrations exceed occupational exposure limits.

Respiratory protection:

Use a NIOSH approved supplied air respirator with an organic cartridge if the potential to exceed established exposure limits exists.

Eye/face protection:

Safety goggles or safety glasses with side shields.

Skin protection:

Use impermeable gloves and protective clothing as necessary to prevent skin contact. Neoprene, Butyl-rubber, or nitrile-rubber gloves.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state:	Paste
Color:	White
Odor:	Mild
Odor threshold:	Not available
pH:	Not applicable
Vapor pressure:	< 10 mm hg (27 °C (80.6 °F))
Boiling point/range:	> 149 °C (> 300.2 °F)
Melting point/ range:	Not available
Specific gravity:	1.21
Vapor density:	Not available
Flash point:	> 93.3 °C (> 199.94 °F) Tagliabue closed cup
Flammable/Explosive limits - lower:	Not available
Flammable/Explosive limits - upper:	Not available
Autoignition temperature:	Not available
Evaporation rate:	Not available
Solubility in water:	Slight
Partition coefficient (n-octanol/water):	Not available
VOC content:	0.72 %; 6.86 g/l

10. STABILITY AND REACTIVITY

Stability:	Stable
Hazardous reactions:	Will not occur.
Hazardous decomposition products:	Oxides of carbon. Toxic fluorine compounds. Irritating organic vapours.
Incompatible materials:	Strong oxidizing agents.
Conditions to avoid:	See "Handling and Storage" (Section 7) and "Incompatibility" (Section 10).

11. TOXICOLOGICAL INFORMATION

Acute oral product toxicity:	LD50 (rat) > 10,000 mg/kg
Acute dermal product toxicity:	LD50 (rabbit) > 5,000 mg/kg

Hazardous components	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Bisphenol A fumarate resin	No	No	No
Mica	No	No	No
Polyglycol dimethacrylate	No	No	No
Octan-1-ol	No	No	No
Polyglycol dioctanoate	No	No	No
Silica, amorphous, treated	No	No	No
Titanium dioxide	No	Group 2B	No
Propanediol-1,2	No	No	No
Fragrance	No	No	No
Quartz (SiO ₂)	Known carcinogen	Group 1	No

Hazardous components	Health Effects/Target Organs
Bisphenol A fumarate resin	Irritant, Allergen
Mica	Lung
Polyglycol dimethacrylate	Irritant, Allergen
Octan-1-ol	Central nervous system, Irritant
Polyglycol dioctanoate	Irritant
Silica, amorphous, treated	No Target Organs
Titanium dioxide	Irritant, Respiratory
Propanediol-1,2	Irritant
Fragrance	No Data
Quartz (SiO ₂)	Immune system, Lung, Some evidence of carcinogenicity

12. ECOLOGICAL INFORMATION

Ecological information:	Not available
--------------------------------	---------------

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Follow all local, state, federal and provincial regulations for disposal.

Hazardous waste number: Not a RCRA hazardous waste.

14. TRANSPORT INFORMATION

The shipping classifications in this sections are for non-bulk packaging only (unless otherwise specified). Shipping classification may be different for bulk packaging.

U.S. Department of Transportation Ground (49 CFR)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

International Air Transportation (ICAO/IATA)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

Water Transportation (IMO/IMDG)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

15. REGULATORY INFORMATION

United States Regulatory Information

TSCA 8 (b) Inventory Status: All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.

TSCA 12(b) Export Notification: None above reporting de minimus

CERCLA/SARA Section 302 EHS: None above reporting de minimus
CERCLA/SARA Section 311/312: Immediate Health, Delayed Health
CERCLA/SARA 313: None above reporting de minimus

California Proposition 65: This product contains a chemical known in the State of California to cause cancer. This product contains a chemical known to the State of California to cause birth defects or other reproductive harm.

Canada Regulatory Information

CEPA DSL/NDSL Status: All components are listed on or are exempt from listing on the Canadian Domestic Substances List.

WHMIS hazard class: D.2.A, D.2.B

16. OTHER INFORMATION

This material safety data sheet contains changes from the previous version in sections: New Material Safety Data Sheet format.

Prepared by: Kyra Kozak Woods, Manager, Regulatory Affairs

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation does not assume responsibility for any results obtained by persons over whose methods Henkel Corporation has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any of Henkel Corporation's products. In light of the foregoing, Henkel Corporation specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation further disclaims any liability for consequential or incidental damages of any kind, including lost profits.