



## Material Safety Data Sheet

Copyright, 2012, 3M Company All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

### SECTION 1: PRODUCT AND COMPANY IDENTIFICATION

**PRODUCT NAME:** 3M(TM) Super 77(TM) Multipurpose Adhesive (Aerosol)  
**MANUFACTURER:** 3M  
**DIVISION:** Industrial Adhesives and Tapes Division  
**ADDRESS:** 3M Center, St. Paul, MN 55144-1000

**EMERGENCY PHONE: 1-800-364-3577 or (651) 737-6501 (24 hours)**

**Issue Date:** 04/19/12  
**Supersedes Date:** 03/30/12

**Document Group:** 16-3472-4

**Product Use:**

Intended Use: general purpose aerosol adhesive  
 Specific Use: General Purpose Aerosol adhesive

### SECTION 2: INGREDIENTS

<u>Ingredient</u>	<u>C.A.S. No.</u>	<u>% by Wt</u>
Non-volatile components - N.J.T.S. Registry No. 04499600-6433P	Trade Secret	20 - 30
Acetone	67-64-1	20 - 30
Propane	74-98-6	15 - 25
Cyclohexane	110-82-7	10 - 20
Petroleum distillates	64742-49-0	10 - 20
Hexane	110-54-3	< 1

### SECTION 3: HAZARDS IDENTIFICATION

#### 3.1 EMERGENCY OVERVIEW

**Specific Physical Form:** Aerosol

**Odor, Color, Grade:** Clear, sweet, fruity odor

**General Physical Form:** Gas aerosol

**Immediate health, physical, and environmental hazards:** Closed containers exposed to heat from fire may build pressure and explode. Extremely flammable liquid and vapor. Vapors may travel long distances along the ground or floor to an ignition source and flash back. Aerosol container contains flammable material under pressure. May cause target organ effects. Contains a

chemical or chemicals which can cause birth defects or other reproductive harm.

### 3.2 POTENTIAL HEALTH EFFECTS

**Eye Contact:**

Moderate Eye Irritation: Signs/symptoms may include redness, swelling, pain, tearing, and blurred or hazy vision.

**Skin Contact:**

Mild Skin Irritation: Signs/symptoms may include localized redness, swelling, and itching.

**Inhalation:**

Respiratory Tract Irritation: Signs/symptoms may include cough, sneezing, nasal discharge, headache, hoarseness, and nose and throat pain.

Single exposure, above recommended guidelines, may cause:

Cardiac Sensitization: Signs/symptoms may include irregular heartbeat (arrhythmia), faintness, chest pain, and may be fatal.

Intentional concentration and inhalation may be harmful or fatal.

May be absorbed following inhalation and cause target organ effects.

**Ingestion:**

Gastrointestinal Irritation: Signs/symptoms may include abdominal pain, stomach upset, nausea, vomiting and diarrhea.

May be absorbed following ingestion and cause target organ effects.

**Target Organ Effects:**

Central Nervous System (CNS) Depression: Signs/symptoms may include headache, dizziness, drowsiness, incoordination, nausea, slowed reaction time, slurred speech, giddiness, and unconsciousness.

Prolonged or repeated exposure may cause:

Peripheral Neuropathy: Signs/symptoms may include tingling or numbness of the extremities, incoordination, weakness of the hands and feet, tremors and muscle atrophy.

Contains a chemical or chemicals which can cause birth defects or other reproductive harm.

## SECTION 4: FIRST AID MEASURES

### 4.1 FIRST AID PROCEDURES

The following first aid recommendations are based on an assumption that appropriate personal and industrial hygiene practices are followed.

**Eye Contact:** Flush eyes with large amounts of water. If signs/symptoms persist, get medical attention.

**Skin Contact:** Wash affected area with soap and water. If signs/symptoms develop, get medical attention.

**Inhalation:** Remove person to fresh air. Get immediate medical attention.

**If Swallowed:** Do not induce vomiting unless instructed to do so by medical personnel. Give victim two glasses of water. Never give anything by mouth to an unconscious person. Get medical attention.

### 4.2 NOTE TO PHYSICIANS

Exposure may increase myocardial irritability. Do not administer sympathomimetic drugs unless absolutely necessary.

## SECTION 5: FIRE FIGHTING MEASURES

### 5.1 FLAMMABLE PROPERTIES

<b>Autoignition temperature</b>	<i>No Data Available</i>
<b>Flash Point</b>	-42.00 °F [ <i>Test Method: Tagliabue Closed Cup</i> ]
<b>Flammable Limits(LEL)</b>	<i>No Data Available</i>
<b>Flammable Limits(UEL)</b>	<i>No Data Available</i>
<b>OSHA Flammability Classification:</b>	Class IA Flammable Liquid

### 5.2 EXTINGUISHING MEDIA

Use fire extinguishers with class B extinguishing agents (e.g., dry chemical, carbon dioxide).

### 5.3 PROTECTION OF FIRE FIGHTERS

**Special Fire Fighting Procedures:** Wear full protective equipment (Bunker Gear) and a self-contained breathing apparatus (SCBA).

**Unusual Fire and Explosion Hazards:** Closed containers exposed to heat from fire may build pressure and explode. Extremely flammable liquid and vapor. Vapors may travel long distances along the ground or floor to an ignition source and flash back. Aerosol container contains flammable material under pressure.

**Note: See STABILITY AND REACTIVITY (SECTION 10) for hazardous combustion and thermal decomposition information.**

## SECTION 6: ACCIDENTAL RELEASE MEASURES

### 6.1. Personal precautions, protective equipment and emergency procedures

Refer to other sections of this MSDS for information regarding physical and health hazards, respiratory protection, ventilation and personal protective equipment. Evacuate unprotected and untrained personnel from the hazard area. The spill should be cleaned up by qualified personnel. Ventilate the area. **WARNING !** A motor could be an ignition source and could cause flammable gases or vapors in the spill area to burn or explode. If it can be done safely, place the leaking containers in an exhaust hood or well-ventilated area. **WARNING !** To avoid problems with pressure buildup, slowly leaking pressurized aerosol cans should not be placed in sealed containers. Evacuate unprotected and untrained personnel from hazard area. The spill should be cleaned up by qualified personnel. Remove all ignition sources such as flames, smoking materials, and electrical spark sources. Use only non-sparking tools. Ventilate the area with fresh air. Read and follow safety precautions on the solvent label and MSDS.

### 6.2. Environmental precautions

Place in a metal container approved for transportation by appropriate authorities. Dispose of collected material as soon as possible.

#### Clean-up methods

Contain spill, using absorbent if necessary. Collect spilled material with non-sparking tools. Clean up residue. Place depressurized cans and clean up wastes in a metal container approved for transportation. Seal the container. Refer to other sections of this MSDS for information regarding physical and health hazards, respiratory protection, ventilation, and personal protective equipment. Call 3M-HELPS line (1-800-364-3577) for more information on handling and managing the spill. Working from around the edges of the spill inward, cover with bentonite, vermiculite, or commercially available inorganic absorbent material. Mix in sufficient absorbent until it appears dry. Collect as much of the spilled material as possible using non-sparking tools. Clean up residue with an appropriate organic solvent. Seal the container.

**In the event of a release of this material, the user should determine if the release qualifies as reportable according to local, state, and federal regulations.**

## SECTION 7: HANDLING AND STORAGE

### 7.1 HANDLING

Do not eat, drink or smoke when using this product. Wash exposed areas thoroughly with soap and water. Keep away from heat, sparks, open flame, pilot lights and other sources of ignition. Do not pierce or burn container, even after use. No smoking while handling this material. Do not spray near flames or sources of ignition. Avoid breathing of vapors, mists or spray. Avoid eye contact with vapors, mists, or spray. Keep out of the reach of children. Vapors may ignite explosively. May cause flash fire. Prevent build-up of vapors - open all windows and doors. Maintain vapor concentrations below recommended exposure limits. Use only with cross-ventilation. Without adequate ventilation, vapors may settle in low-lying areas. Keep away from heat, sparks, and open flame. Do not smoke or ignite matches, lighters, etc. Avoid contact with oxidizing agents.

### 7.2 STORAGE

Store away from acids. Store away from heat. Store out of direct sunlight. Store away from oxidizing agents.

## SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

### 8.1 ENGINEERING CONTROLS

Use with appropriate local exhaust ventilation. Use in an enclosed process area is recommended. Use with functioning spray booth or local exhaust. Use in a well-ventilated area. If exhaust ventilation is not available, use appropriate respiratory protection. Do not use in a confined area or areas with little or no air movement. Do not remain in area where available oxygen may be reduced. Use general dilution ventilation and/or local exhaust ventilation to control airborne exposures to below Occupational Exposure Limits and/or control mist, vapor, or spray. If ventilation is not adequate, use respiratory protection equipment. Do not use in a confined area or areas with little or no air movement. If exhaust ventilation is not adequate, use appropriate respiratory protection. Provide ventilation adequate to control vapor concentrations below recommended exposure limits and/or control spray or mist.

### 8.2 PERSONAL PROTECTIVE EQUIPMENT (PPE)

#### 8.2.1 Eye/Face Protection

Avoid eye contact with vapors, mists, or spray.

The following eye protection(s) are recommended: Safety Glasses with side shields

.

#### 8.2.2 Skin Protection

Not applicable. Avoid skin contact.

Select and use gloves and/or protective clothing to prevent skin contact based on the results of an exposure assessment. Consult with your glove and/or protective clothing manufacturer for selection of appropriate compatible materials.

Gloves made from the following material(s) are recommended: Polymer laminate

.

#### 8.2.3 Respiratory Protection

Avoid breathing of vapors, mists or spray.

Select one of the following NIOSH approved respirators based on airborne concentration of contaminants and in accordance with OSHA regulations: Half facepiece or full facepiece air-purifying respirator suitable for organic vapors

. Select and use respiratory protection to prevent an inhalation exposure based on the results of an exposure assessment. Consult with your respirator manufacturer for selection of appropriate types of respirators.

#### 8.2.4 Prevention of Swallowing

Do not eat, drink or smoke when using this product. Wash exposed areas thoroughly with soap and water.

### 8.3 EXPOSURE GUIDELINES

<u>Ingredient</u>	<u>Authority</u>	<u>Type</u>	<u>Limit</u>	<u>Additional Information</u>
Acetone	ACGIH	TWA	500 ppm	
Acetone	ACGIH	STEL	750 ppm	
Acetone	OSHA	TWA	2400 mg/m3	
Hexane	ACGIH	TWA	50 ppm	Skin Notation*
Hexane	OSHA	TWA	1800 mg/m3	
Petroleum distillates	CMRG	TWA	50 ppm	
Propane	OSHA	TWA	1800 mg/m3	

\* Substance(s) refer to the potential contribution to the overall exposure by the cutaneous route including mucous membrane and eye, either by airborne or, more particularly, by direct contact with the substance. Vehicles can alter skin absorption.

#### SOURCE OF EXPOSURE LIMIT DATA:

ACGIH: American Conference of Governmental Industrial Hygienists

CMRG: Chemical Manufacturer Recommended Guideline

OSHA: Occupational Safety and Health Administration

AIHA: American Industrial Hygiene Association Workplace Environmental Exposure Level (WEEL)

## SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

<b>Specific Physical Form:</b>	Aerosol
<b>Odor, Color, Grade:</b>	Clear, sweet, fruity odor
<b>General Physical Form:</b>	Gas aerosol
<b>Autoignition temperature</b>	<i>No Data Available</i>
<b>Flash Point</b>	-42.00 °F [ <i>Test Method:</i> Tagliabue Closed Cup]
<b>Flammable Limits(LEL)</b>	<i>No Data Available</i>
<b>Flammable Limits(UEL)</b>	<i>No Data Available</i>
<b>Boiling Point</b>	<i>Not Applicable</i>
<b>Density</b>	0.726 g/ml
<b>Vapor Density</b>	2.97 [ <i>Ref Std:</i> AIR=1]
<b>Specific Gravity</b>	0.726 [ <i>Ref Std:</i> WATER=1]
<b>pH</b>	<i>No Data Available</i>
<b>Melting point</b>	<i>No Data Available</i>
<b>Solubility in Water</b>	Nil
<b>Evaporation rate</b>	1.90 [ <i>Ref Std:</i> ETHER=1]
<b>Hazardous Air Pollutants</b>	<=0.4 % weight [ <i>Test Method:</i> Calculated]
<b>Volatile Organic Compounds</b>	<=537 g/l [ <i>Details:</i> EU VOC content]
<b>Kow - Oct/Water partition coef</b>	<i>No Data Available</i>
<b>Percent volatile</b>	<=75 % weight [ <i>Details:</i> all volatiles]
<b>VOC Less H2O &amp; Exempt Solvents</b>	<=51 % weight [ <i>Test Method:</i> calculated SCAQMD rule 443.1]
<b>VOC Less H2O &amp; Exempt Solvents</b>	<=3.82 lb/gal [ <i>Test Method:</i> calculated SCAQMD rule 443.1]
<b>VOC Less H2O &amp; Exempt Solvents</b>	<=458 g/l [ <i>Test Method:</i> calculated SCAQMD rule 443.1]
<b>Viscosity</b>	<i>Not Applicable</i>
<b>Solids Content</b>	>=22.4 %

## SECTION 10: STABILITY AND REACTIVITY

**Stability:** Stable.

**Materials and Conditions to Avoid:**

**10.1 Conditions to avoid**

Heat

**10.2 Materials to avoid**

Strong oxidizing agents

**Hazardous Polymerization:** Hazardous polymerization will not occur.

**Hazardous Decomposition or By-Products**

**Substance**

Aldehydes  
Carbon monoxide  
Carbon dioxide

**Condition**

During Combustion  
During Combustion  
During Combustion

**SECTION 11: TOXICOLOGICAL INFORMATION**

Please contact the address listed on the first page of the MSDS for Toxicological Information on this material and/or its components.

**SECTION 12: ECOLOGICAL INFORMATION**

**ECOTOXICOLOGICAL INFORMATION**

Not determined.

**CHEMICAL FATE INFORMATION**

Not determined.

**SECTION 13: DISPOSAL CONSIDERATIONS**

**Waste Disposal Method:** Vent cylinder or pressurized container in an operating exhaust hood or remote area.

A qualified person should adjust the release rate so gas concentration in ducts is less than 20% of the lower explosive limit (LEL). The LEL is the lowest concentration that can propagate (spread) a flame. Incinerate uncured product in a permitted hazardous waste incinerator.

Incinerate in a permitted hazardous waste incinerator. For quantities <10 lbs. (5 kg):

As a disposal alternative, dispose of waste product in a permitted hazardous waste facility.

The facility should be equipped to handle gaseous waste.

Facility must be capable of handling aerosol cans. Dispose of empty product containers in a sanitary landfill.

RECYCLE EMPTY AEROSOL CONTAINERS WHERE AVAILABLE.

**EPA Hazardous Waste Number (RCRA):** D001 (Ignitable)

Since regulations vary, consult applicable regulations or authorities before disposal.

**SECTION 14: TRANSPORT INFORMATION**

**ID Number(s):**

62-4977-4730-3, 62-4977-4925-9, 62-4977-4929-1, 62-4977-4930-9, 62-4977-4935-8

For Transport Information, please visit <http://3M.com/Transportinfo> or call 1-800-364-3577 or 651-737-6501.

## SECTION 15: REGULATORY INFORMATION

### US FEDERAL REGULATIONS

Contact 3M for more information.

**311/312 Hazard Categories:**

Fire Hazard - Yes Pressure Hazard - Yes Reactivity Hazard - No Immediate Hazard - Yes Delayed Hazard - Yes

### STATE REGULATIONS

Contact 3M for more information.

### CHEMICAL INVENTORIES

The components of this product are in compliance with the chemical notification requirements of TSCA.

All applicable chemical ingredients in this material are listed on the European Inventory of Existing Chemical Substances (EINECS), or are exempt polymers whose monomers are listed on EINECS. Contact 3M for more information.

### INTERNATIONAL REGULATIONS

Contact 3M for more information.

This MSDS has been prepared to meet the U.S. OSHA Hazard Communication Standard, 29 CFR 1910.1200.

## SECTION 16: OTHER INFORMATION

### NFPA Hazard Classification

Health: 2 Flammability: 4 Reactivity: 0 Special Hazards: None  
Aerosol Storage Code: 3

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

### HMIS Hazard Classification

Health: 2 Flammability: 4 Reactivity: 0 Protection: X - See PPE section.

Hazardous Material Identification System (HMIS®) hazard ratings are designed to inform employees of chemical hazards in the workplace. These ratings are based on the inherent properties of the material under expected conditions of normal use and are not intended for use in emergency situations. HMIS® ratings are to be used with a fully implemented HMIS® program. HMIS® is a registered mark of the National Paint and Coatings Association (NPCA).

**Reason for Reissue:** Removed stock numbers.

**Revision Changes:**

Section 8: Respiratory protection - recommended respirators information was modified.

DISCLAIMER: The information in this Material Safety Data Sheet (MSDS) is believed to be correct as of the date issued. 3M

MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the MSDS available directly from 3M

**3M USA MSDSs are available at [www.3M.com](http://www.3M.com)**





## Transport Information Document

**Date:** June 13, 2012

**3M ID Number:** 62-4977-4930-9

**Product Description:** 3M(TM) Super 77(TM) Multipurpose Spray Adhesive, 24 fl oz Net Wt 16 3/4 oz, 12 per case

**Transport Protective Service:** PROTECTIVE SERVICE NOT REQUIRED

**NMFC Item:** 004620

**NMFC Sub:** 06

**NMFC Class:** 060.0

**Flash Point (Closed-cup):** No Flash Point

### UNITED STATES DEPARTMENT OF TRANSPORTATION - GROUND (U.S. DOT, 49 CFR)

CONSUMER COMMODITY, ORM-D OR LIMITED QUANTITY

### UNITED STATES DEPARTMENT OF TRANSPORTATION - VESSEL (U.S. DOT, 49 CFR)

UN1950, AEROSOLS, 2.1, LIMITED QUANTITY

### INTERNATIONAL AIR TRANSPORT ASSOCIATION (IATA)

UN1950, AEROSOLS, FLAMMABLE, 2.1

### INTERNATIONAL MARITIME ORGANIZATION (IMO)

UN1950, AEROSOLS, 2.1, LIMITED QUANTITY

The classification is authorized by the Competent Authority of the United States of America and may not meet the requirements of other competent authorities.

These transportation classifications are provided as a customer service. AS THE SHIPPER YOU REMAIN RESPONSIBLE FOR COMPLYING WITH ALL THE APPLICABLE LAWS AND REGULATIONS, INCLUDING PROPER TRANSPORTATION CLASSIFICATION AND PACKAGING. 3M's transportation classifications are based on product formulations, packaging, 3M policies and 3M's understanding of applicable current regulations and is valid for the original 3M package only. 3M does not guarantee the accuracy of this classification information. This information applies only to transportation classification and NOT THE PACKAGING, LABELING, OR MARKING REQUIREMENTS. The original 3M package is certified for U.S. ground shipment only. If you are shipping by air or ocean, the package may not meet applicable regulatory requirements.

For Transport Information, please visit [3M.com/Transportinfo](http://3M.com/Transportinfo)  
or call 1-800-364-3577 or 651-737-6501 for assistance.