





P.C.B. MOUNTING PLAN



CIRCUIT DIAGRAM



LED SCHEMATIC



TECHNICAL CHARACTERISTICS

SPECIFICATION

- >Rating: 50mA, 12VDC
- >Contact Resistance:
 - Initial: 100mOHM max.
 - After Life Test: 20HM max.
- >Insulation Resistance: min. 100MOHM at 500VDC
- >Dielectric Strength: 500VAC for 1 minute
- >Stroke: 0.3 ± 0.1 mm

MATERIAL

- >Diffuser plate: PC UL HB
- >Actuator: PA66 UL HB
- >Frame: PA66 UL HB, color Black
- >Contact: Stainless Steel with Ag
- >Terminal: Brass with Ag
- >Rubber: Silicone

SOLDERING INFORMATION

- >Terminal in THT version
- >Wave soldering 260°C 10 sec. max.
- >Hand soldering under 350°C for 3 sec. max

ENVIRONMENTAL

- >Storage condition: -40°C ~ +85°C, 60% RH max.
- >Operation condition: -40°C ~ +85°C
- >Compliance: ROHS, Reach

HANDLING ADVISE

- >ESD prevention methods need to be applicated for manual handling and processing by machinery
- >Resistors for protection are obligator

PACKAGING INFORMATION

- >ESD Tray

PN	Force	Color of LED	Life cycle
440 RS670 82622	220g ± 50gf	Red	100.000
440 GS670 82622	220g ± 50gf	Green	100.000
440 BS670 82622	220g ± 50gf	Blue	100.000
440 YS670 82622	220g ± 50gf	Yellow	100.000

Scale - 2:1

This electronic component is designed and developed with the intention for use in general electronics equipments.

Before incorporating the components into any equipments in the field such as aerospace, aviation, nuclear control, submarine, transportation, (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc. where higher safety and reliability are especially required or if there is possibility of direct damage or injury to human body, Würth Elektronik must be asked for a written approval.

In addition, even electronic component in general electronic equipments, when used in electrical circuits that require high safety, reliability functions or performance, the sufficient reliability evaluation-check for the safety must be performed before by the user before usage.

		GENERAL TOLERANCE		Basic material	
		.x = +/- 0,2 .xx = +/- 0,15			
		Date	Name	DESCRIPTION	
		Drawn	12-09-21	Jelisarow	SwTLT
		Checked			WS-TLT 12x12mm Tact Switch with integrated LED, THT version
				Scale	2:1
				Position	
				Drawing.- No.	440xx67082622
					SIZE
					A4
REV	FILE	DATE	BY	EDV NO	440xx67082622.dft
					System Solid Edge V20

item	Emitting color		Yellow	Red	bright green	green	Blue
	Order code	unit	YS	RS	VS	GS	BS
1	Peak wavelength typ.	nm	590	650	574	520	468
2	Dominant Wave length @IF=20mA	typ.nm	590	630	567	525	470
	spectral Line Half-width @IF=20mA						
3	Capacitance	typ.pF	20	35	15	100	100
4	VF=0V;f=1MHZ	typ. V	2	1,95	2,1	3,2	3,2
	Forward voltage @IF=20mA						
6	Reverse current @VR=5V	uA	10	10	10	10	10
	ESD						
8	Viewing Angle	°	145	145	145	145	145
	@20mA 2θ 50% typ						
9	Luminous intensity	min. mcd	80	120	20	80	20
	@IF=20mA	typ. mcd	180	220	50	150	50
10	Material		AlGaN	AlGaN	AlGaN	InGaN	InGaN
11	lens type		water clear	water clear	water clear	water clear	water clear

HANDLING ADVISE

- 1) The solder profile has to be complied with according to the technical reflow /or wave soldering specification, otherwise no warranty will be sustained
- 2) All products are supposed to be used before the end of the period of 12 months based on the product date-code, if not 100% solderability can't be warranted
- 3) Violation of the technical product specifications such as exceeding the absolute maximum ratings will be result in the loss of warranty
- 4) It's also recommended to return the products into the original packaging
- 5) ESD prevention methods need to be applied for manual handling and processing by machinery
- 6) Resistors for protection are obligatory




Absolute Maximun Ratings (Ambient Temperature 25C)

Properties	Blue & green	Red	yellow	bright green	Unit
Power Dissipation	120	75	75	75	mW
Peak Forward current	100	185	175	150	mA
continuous Forward current	30	30	30	30	mA
Reverse voltage	5	5	5	5	V
ESD Threshold / HBM	1000	2000	2000	2000	V

This electronic component is designed and developed with the intention for use in general electronics equipments.

Before incorporating the components into any equipments in the field such as aerospace, aviation, nuclear control, submarine, transportation, (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc. where higher safety and reliability are especially required or if there is possibility of direct damage or injury to human body, Wurth Elektronik must be asked for a written approval.

In addition, even electronic component in general electronic equipments, when used in electrical circuits that require high safety, reliability functions or performance, the sufficient reliability evaluation-check for the safety must be performed before by the user before usage.

		Projection 		GENERAL TOLERANCE .x = +/- 0,2 .xx = +/- 0,15		Basic material	
				Date	Name	DESCRIPTION	
				Drawn	12-09-21	Jelisarow	
				Checked		WS-TLT 12x12mm Tact Switch with integrated LED, THT version	
				 Würth Elektronik eiCan		Scale	2:1
						Position	
						Drawing- No. 440xx67082622	
REV	FILE	DATE	BY	EDV NO	440xx67082622.dft	System Solid Edge V20	
						SIZE A4	