



4801 North Ravenswood Avenue
Chicago, IL 60640-4496
Phone: (773) 907-5181
Fax: (773) 907-5180
E-mail (techsupport@spctechnology.com)

Doc. No.: MSDS-025-NM
DCP No.: 1682
Effective Date: 1/29/04

Material Safety Data Sheet

(Non-Mandatory)

Identity: IC Work Station Cleaners

SECTION I – Manufacturer’s P/N’s

1458, 1459, 1461& SPC9986

SECTION II - Hazardous Ingredients/Identity Information

Hazardous Components

(Specific Chemical Identity: OSHA PEL / ACGIH TIV / Other Limits Recommended / %Optional / Common Names):
None

SARA TITLE 3= To the best of our knowledge, this product contains no chemicals subject to SARA TITLE 3, Section 313, supplier notification requirements. SARA HAZARDOUS CATERGORY: This product has been reviewed according to the EPA hazard categories under Section 311 &312 of the Superfund Amendment and Reorganization Act of 1986 and is considered under applicable definitions to meet the following category. Not to have met a hazardous category.

TOXIC CONTROL ACT: (TSA) All ingredients are on the TSCA inventory or are not required to be listed on the TCSA inventory.

WHMIS REGULATIONS: (Canadian)= the Canadian Workplace Hazardous Materials Information System classification for this product is “This product is not a controlled product under WHMIS regulations.

SECTION III -Physical/Chemical Characteristics

Boiling Point: 101°C

Vapor Pressure (mm Hg): N/A

Vapor Density (AIR =1): Not established

Solubility in Water: 100%

Appearance and Odor: Clear Blue Liquid with Mild Odor

Specific Gravity (H 2 O= 1): 1

Melting Point: N/A

Evaporation Rate (Butyl Acetate = 1): 0.71

SECTION IV - Fire and Explosion Hazard Data

Flash Point (Method Used): None

Flammable Limits: N/A

LEL: N/A

UEL: N/A

Extinguishing Media: CO²

Special Fire Fighting Procedures: Precaution-Use Breathing Apparatus

Unusual Fire and Explosion Hazards: None

Material Safety Data Sheet

(Non-Mandatory)

SECTION V - Reactivity Data

Stability: Stable: Unstable: X
Conditions to Avoid: Evaporation - Open containers may change concentrations.
Incompatibility (Materials to Avoid): N/A
Hazardous Polymerization: May Occur: Conditions to Avoid: X Will not Occur: X

SECTION VI - Health Hazard Data

Routes of Entry: Inhalation: Skin: X Ingestion:
Health Hazards (Acute and Chronic): Prolonged contact will remove body oils.
Carcinogenicity: NTP: N/A IARC Monographs: N/A OSHA Regulated: N/A
Signs and Symptoms of Exposure: Dry flaking skin
Medical Conditions Generally Aggravated by Exposure: N/A

Emergency and First Aid Procedures: Replenish Body Oils with Body Lotion

SECTION VII - Precautions for Safe Handling and Use:

Steps to Be Taken in Case Material is Released or Spilled: Mop up spills or rinse down sewer
Waste Disposal Method: Sewer
Precautions to Be Taken in Handling and Storing: Avoid temperatures > 110°F
Other Precautions: None

SECTION VIII - Control Measures

Respiratory Protection (Specify Type): None Required
Ventilation: Local Exhaust: None Special: None Required
Mechanical (General): N/A Other: N/A

Protective Gloves: For Long Periods of Exposure
Eye Protection: Goggles when splashing may occur
Other Protective Clothing or Equipment: N/A
Work/Hygienic Practices: Normal

NFPA Rating

Health	Flammability	Reactivity	Personal Protection
1	0	0	1