



Material Safety Data Sheet

Copyright, 2011, 3M Company All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

SECTION 1: PRODUCT AND COMPANY IDENTIFICATION

PRODUCT NAME: 3M™ Scotch-Brite™ Products, 7447, 7467, General Purpose Pad
MANUFACTURER: 3M
DIVISION: Abrasives Systems Division
ADDRESS: 3M Center, St. Paul, MN 55144-1000

EMERGENCY PHONE: 1-800-364-3577 or (651) 737-6501 (24 hours)

Issue Date: 10/03/11
Supersedes Date: 03/11/11

Document Group: 18-8534-2

Product Use:

Intended Use: Abrasive Product

SECTION 2: INGREDIENTS

<u>Ingredient</u>	<u>C.A.S. No.</u>	<u>% by Wt</u>
Aluminum Oxide Mineral	1344-28-1	30 - 40
Filler	1317-65-3	5 - 15
Titanium Dioxide	13463-67-7	0 - 1.5
Quartz Silica	14808-60-7	0.10 - 0.12
Cured Resin	Mixture	20 - 30
Nylon Fiber	Mixture	15 - 25

SECTION 3: HAZARDS IDENTIFICATION

3.1 EMERGENCY OVERVIEW

Odor, Color, Grade: Solid Abrasive Product

General Physical Form: Solid

Immediate health, physical, and environmental hazards: This document covers only the 3M product. For complete assessment, when determining the degree of hazard, the material being abraded must also be considered.

3.2 POTENTIAL HEALTH EFFECTS

Eye Contact:

Mechanical eye irritation: Signs/symptoms may include pain, redness, tearing and corneal abrasion.

Dust created by grinding, sanding, or machining may cause eye irritation. Signs/symptoms may include redness, swelling, pain, tearing, and blurred or hazy vision.

Skin Contact:

Mechanical Skin irritation: Signs/symptoms may include abrasion, redness, pain, and itching.

Inhalation:

Dust from grinding, sanding or machining may cause irritation of the respiratory system. Signs/symptoms may include cough, sneezing, nasal discharge, headache, hoarseness, and nose and throat pain.

Prolonged or repeated exposure may cause:

Pneumoconiosis: Sign/symptoms may include persistent cough, breathlessness, chest pain, increased amounts of sputum, and changes in lung function tests.

Ingestion:

No health effects are expected.

This product contains titanium dioxide and quartz silica. Cancer of the lungs has been associated with titanium dioxide, and cancer of the lungs and silicosis have been associated with quartz (crystalline) silica. No exposure to titanium dioxide or quartz (crystalline) silica is anticipated during normal intended use of 3M Coated Abrasives and Surface Conditioning Products. No detectable levels of these materials were found when simulated grinding air sampling studies were conducted on analogous coated abrasive and surface conditioning constructions that contained similar to or greater concentrations of titanium dioxide and crystalline silica. Therefore, the health effects associated with titanium dioxide and quartz (crystalline) silica are not expected during the intended use of this product.

<u>Ingredient</u>	<u>C.A.S. No.</u>	<u>Class Description</u>	<u>Regulation</u>
Quartz Silica	14808-60-7	Grp. 1: Carcinogenic to humans	International Agency for Research on Cancer
SILICA, CRYSTALLINE (AIRBORNE PARTICLES OF RESPIRABLE SIZE)	SEQ677	Grp. 1: Carcinogenic to humans	International Agency for Research on Cancer
SILICA, CRYSTALLINE (AIRBORNE PARTICLES OF RESPIRABLE SIZE)	SEQ677	Known human carcinogen	National Toxicology Program Carcinogens
Titanium Dioxide	13463-67-7	Grp. 2B: Possible human carc.	International Agency for Research on Cancer

SECTION 4: FIRST AID MEASURES

4.1 FIRST AID PROCEDURES

The following first aid recommendations are based on an assumption that appropriate personal and industrial hygiene practices are followed.

Eye Contact: Flush eyes with large amounts of water. If signs/symptoms persist, get medical attention.

Skin Contact: Wash affected area with soap and water. If signs/symptoms develop, get medical attention.

Inhalation: Remove person to fresh air. If signs/symptoms develop, get medical attention.

If Swallowed: No need for first aid is anticipated.

SECTION 5: FIRE FIGHTING MEASURES

5.1 FLAMMABLE PROPERTIES

Autoignition temperature	<i>Not Applicable</i>
Flash Point	<i>Not Applicable</i>
Flammable Limits(LEL)	<i>Not Applicable</i>
Flammable Limits(UEL)	<i>Not Applicable</i>

5.2 EXTINGUISHING MEDIA

Ordinary combustible material. Use fire extinguishers with class A extinguishing agents (e.g., water, foam).

5.3 PROTECTION OF FIRE FIGHTERS

Special Fire Fighting Procedures: Wear full protective equipment (Bunker Gear) and a self-contained breathing apparatus (SCBA).

Unusual Fire and Explosion Hazards: Not applicable. None inherent in this product.

Note: See STABILITY AND REACTIVITY (SECTION 10) for hazardous combustion and thermal decomposition information.

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Not applicable.

6.2. Environmental precautions

Not applicable.

Clean-up methods

Not applicable.

In the event of a release of this material, the user should determine if the release qualifies as reportable according to local, state, and federal regulations.

SECTION 7: HANDLING AND STORAGE

7.1 HANDLING

For industrial or professional use only. Avoid breathing of dust created by sanding, grinding or machining. Avoid eye contact with dust or airborne particles. Damaged product can break apart during use and cause serious injury to face or eyes. Check product for damage such as cracks or nicks prior to use. Replace if damaged. Always wear eye and face protection when working at sanding or grinding operations or when near such operations. Sparks and particles flying from the product during sanding or grinding can cause injury and fire.

7.2 STORAGE

Store in a cool, dry place.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1 ENGINEERING CONTROLS

Provide ventilation adequate to control dust concentrations below recommended exposure limits and/or control dust. Provide appropriate local exhaust ventilation for sanding, grinding or machining. Use general dilution ventilation and/or local exhaust

ventilation to control airborne exposures to below Occupational Exposure Limits and/or control dust, fume, or airborne particles. If ventilation is not adequate, use respiratory protection equipment.

8.2 PERSONAL PROTECTIVE EQUIPMENT (PPE)

8.2.1 Eye/Face Protection

Avoid eye contact. To minimize the risk of injury to face and eyes, always wear eye and face protection when working at sanding or grinding operations or when near such operations. The following eye protection(s) are recommended: Safety Glasses with side shields.

8.2.2 Skin Protection

Avoid skin contact. Wear appropriate gloves to minimize risk of injury to skin from contact with dust or physical abrasion from grinding or sanding.

8.2.3 Respiratory Protection

Avoid breathing of dust created by sanding, grinding or machining. Assess exposure concentrations of all materials involved in the work process. Consider material being abraded when determining the appropriate respiratory protection. Select and use appropriate respirators to prevent inhalation overexposure. Select one of the following NIOSH approved respirators based on airborne concentration of contaminants and in accordance with OSHA regulations: Half facepiece or fullface air-purifying respirator with N95 particulate filters. Select and use respiratory protection to prevent an inhalation exposure based on the results of an exposure assessment. Consult with your respirator manufacturer for selection of appropriate types of respirators.

8.2.4 Prevention of Swallowing

Not an expected route of exposure. Wash hands after handling and before eating.

8.3 EXPOSURE GUIDELINES

<u>Ingredient</u>	<u>Authority</u>	<u>Type</u>	<u>Limit</u>	<u>Additional Information</u>
Aluminum Oxide Mineral	CMRG	TWA	1 fiber/cc	
Aluminum Oxide Mineral	OSHA	TWA, respirable fraction	5 mg/m3	
Aluminum Oxide Mineral	OSHA	TWA, as total dust	15 mg/m3	
Filler	OSHA	TWA, respirable fraction	5 mg/m3	
Filler	OSHA	TWA, as total dust	15 mg/m3	
Quartz Silica	ACGIH	TWA, respirable fraction	0.025 mg/m3	
Quartz Silica	OSHA	TWA concentration, respirable	0.1 mg/m3	
Quartz Silica	OSHA	TWA concentration, as total dust	0.3 mg/m3	
Titanium Dioxide	ACGIH	TWA	10 mg/m3	
Titanium Dioxide	CMRG	TWA, as respirable dust	5 mg/m3	
Titanium Dioxide	OSHA	TWA, as total dust	15 mg/m3	

SOURCE OF EXPOSURE LIMIT DATA:

- ACGIH: American Conference of Governmental Industrial Hygienists
- CMRG: Chemical Manufacturer Recommended Guideline
- OSHA: Occupational Safety and Health Administration
- AIHA: American Industrial Hygiene Association Workplace Environmental Exposure Level (WEEL)

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

Odor, Color, Grade:	Solid Abrasive Product
General Physical Form:	Solid
Autoignition temperature	<i>Not Applicable</i>
Flash Point	<i>Not Applicable</i>
Flammable Limits(LEL)	<i>Not Applicable</i>
Flammable Limits(UEL)	<i>Not Applicable</i>
Boiling Point	<i>Not Applicable</i>
Vapor Density	<i>Not Applicable</i>
Vapor Pressure	<i>Not Applicable</i>
Specific Gravity	<i>Not Applicable</i>
pH	<i>Not Applicable</i>
Melting point	<i>Not Applicable</i>
Solubility in Water	<i>Not Applicable</i>
Evaporation rate	<i>Not Applicable</i>
Kow - Oct/Water partition coef	<i>Not Applicable</i>
Viscosity	<i>Not Applicable</i>

SECTION 10: STABILITY AND REACTIVITY

Stability: Stable.

Materials and Conditions to Avoid:

10.1 Conditions to avoid

None known

10.2 Materials to avoid

None known

Hazardous Polymerization: Hazardous polymerization will not occur.

Hazardous Decomposition or By-Products

<u>Substance</u>	<u>Condition</u>
Amine Compounds	During Combustion
Carbon monoxide	During Combustion
Carbon dioxide	During Combustion
Hydrogen Cyanide	During Combustion
Ammonia	During Combustion
Oxides of Nitrogen	During Combustion

Hazardous Decomposition: Under recommended usage conditions, hazardous decomposition products are not expected. Hazardous decomposition products may occur as a result of oxidation, heating, or reaction with another material.

SECTION 11: TOXICOLOGICAL INFORMATION

Please contact the address listed on the first page of the MSDS for Toxicological Information on this material and/or its components.

SECTION 12: ECOLOGICAL INFORMATION

ECOTOXICOLOGICAL INFORMATION

Not determined.

CHEMICAL FATE INFORMATION

Not determined.

SECTION 13: DISPOSAL CONSIDERATIONS

Waste Disposal Method: The substrate that was abraded must be considered as a factor in the disposal method for this product. Dispose of waste product in a sanitary landfill. As a disposal alternative, incinerate in an industrial or commercial facility in the presence of a combustible material.

EPA Hazardous Waste Number (RCRA): Not regulated

Since regulations vary, consult applicable regulations or authorities before disposal.

SECTION 14: TRANSPORT INFORMATION

Not regulated per U.S. DOT, IATA or IMO.

*These transportation classifications are provided as a customer service. As the shipper YOU remain responsible for complying with all applicable laws and regulations, including proper transportation classification and packaging. 3M transportation classifications are based on product formulation, packaging, 3M policies and 3M understanding of applicable current regulations. 3M does not guarantee the accuracy of this classification information. This information applies only to transportation classification and **not the packaging, labeling, or marking requirements**. The original 3M package is certified for U.S. ground shipment only. If you are shipping by air or ocean, the package may not meet applicable regulatory requirements.*

SECTION 15: REGULATORY INFORMATION

US FEDERAL REGULATIONS

Contact 3M for more information.

311/312 Hazard Categories:

Fire Hazard - No Pressure Hazard - No Reactivity Hazard - No Immediate Hazard - Yes Delayed Hazard - Yes

Section 313 Toxic Chemicals subject to the reporting requirements of that section and 40 CFR part 372 (EPCRA):

<u>Ingredient</u>	<u>C.A.S. No</u>	<u>% by Wt</u>
Aluminum Oxide Mineral	1344-28-1	30 - 40

STATE REGULATIONS

Contact 3M for more information.

CALIFORNIA PROPOSITION 65

<u>Ingredient</u>	<u>C.A.S. No.</u>	<u>Classification</u>
SILICA, CRYSTALLINE (AIRBORNE PARTICLES OF RESPIRABLE SIZE)	SEQ677	**Carcinogen

** WARNING: contains a chemical which can cause cancer.

CHEMICAL INVENTORIES

This product is an article as defined by TSCA regulations, and is exempt from TSCA Inventory listing requirements.

Contact 3M for more information.

INTERNATIONAL REGULATIONS

Contact 3M for more information.

This MSDS has been prepared to meet the U.S. OSHA Hazard Communication Standard, 29 CFR 1910.1200.

SECTION 16: OTHER INFORMATION

NFPA Hazard Classification

Health: 1 Flammability: 1 Reactivity: 0 Special Hazards: None

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

Revision Changes: Updated.

DISCLAIMER: The information in this Material Safety Data Sheet (MSDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the MSDS available directly from 3M

3M USA MSDSs are available at www.3M.com



Transport Information Document

Date: September 17, 2013

3M ID Number: 61-5001-2323-9

Product Description: Scotch-Brite(TM) General Purpose Hand Pad 7447, 6 in x 9 in, 20 pads per box 3 boxes per case

Transport Protective Service: PROTECTIVE SERVICE NOT REQUIRED

NMFC Item: 149240

NMFC Sub: 04

NMFC Class: 150.0

Flash Point (Closed-cup): No Flash Point

UNITED STATES DEPARTMENT OF TRANSPORTATION - GROUND (U.S. DOT, 49 CFR)

NOT REGULATED

UNITED STATES DEPARTMENT OF TRANSPORTATION - VESSEL (U.S. DOT, 49 CFR)

NOT REGULATED

INTERNATIONAL AIR TRANSPORT ASSOCIATION (IATA)

NOT REGULATED

INTERNATIONAL MARITIME ORGANIZATION (IMO)

NOT REGULATED

The classification is authorized by the Competent Authority of the United States of America and may not meet the requirements of other competent authorities.

These transportation classifications are provided as a customer service. AS THE SHIPPER YOU REMAIN RESPONSIBLE FOR COMPLYING WITH ALL THE APPLICABLE LAWS AND REGULATIONS, INCLUDING PROPER TRANSPORTATION CLASSIFICATION AND PACKAGING. 3M's transportation classifications are based on product formulations, packaging, 3M policies and 3M's understanding of applicable current regulations and is valid for the original 3M package only. 3M does not guarantee the accuracy of this classification information. This information applies only to transportation classification and NOT THE PACKAGING, LABELING, OR MARKING REQUIREMENTS. The original 3M package is certified for U.S. ground shipment only. If you are shipping by air or ocean, the package may not meet applicable regulatory requirements.

For Transport Information, please visit 3M.com/Transportinfo
or call 1-800-364-3577 or 651-737-6501 for assistance.