



Revision Number: 009.2

Issue date: 09/14/2010

1. PRODUCT AND COMPANY IDENTIFICATION

Product name: Instant Gasket 90ml AE	IDH number: 743912
Product type: Silicone Sealant	Item number: 40478
	Region: United States
Company address: Henkel Corporation One Henkel Way Rocky Hill, Connecticut 06067	Contact information: Telephone: 860.571.5100 MEDICAL EMERGENCY Phone: Poison Control Center 1-877-671-4608 (toll free) or 1-303-592-1711 TRANSPORT EMERGENCY Phone: CHEMTREC 1-800-424-9300 (toll free) or 1-703-527-3887 Internet: www.henkelna.com

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW

Physical state: Aerosol, Paste	HEALTH: *2
Color: Black	FLAMMABILITY: 1
Odor: Mild, Petroleum	PHYSICAL HAZARD: 0
	Personal Protection: See MSDS Section 8

WARNING: CONTENTS UNDER PRESSURE.
 PROLONGED OR REPEATED CONTACT WITH UNCURED ADHESIVE MAY CAUSE EYE, SKIN AND RESPIRATORY TRACT IRRITATION.
 REPEATED OR PROLONGED CONTACT MAY CAUSE ALLERGIC SKIN REACTION.

Relevant routes of exposure: Skin, Inhalation, Eyes

Potential Health Effects

Inhalation: Inhalation of mist or spray may cause irritation of the respiratory tract and nasal passages. When heated to temperatures exceeding 300° F (150° C) in the presence of air, silicones may form formaldehyde vapors. Formaldehyde is a potential cancer hazard and a known skin and respiratory sensitizer. Vapors irritate the eyes, nose and throat. Safe handling conditions may be maintained by keeping formaldehyde vapor concentrations below the OSHA permissible limit.

Skin contact: Prolonged and/or repeated skin contact with this product may cause irritation. Prolonged contact with this product may cause allergic skin sensitization reactions. The silane is a skin and eye irritant and prolonged contact may cause eye and skin burns. The low concentration makes such overexposure unlikely and minimizes its affect on health and safety.

Eye contact: Contact with uncured product may irritate the eyes. The silane is a skin and eye irritant and prolonged contact may cause eye and skin burns. The low concentration makes such overexposure unlikely and minimizes its affect on health and safety.

Ingestion: Not expected under normal conditions of use. May be harmful if swallowed.

Existing conditions aggravated by exposure: Not available

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

See Section 11 for additional toxicological information.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous components	CAS NUMBER	%
Calcium carbonate	471-34-1	30 - 60
Norflurane	811-97-2	5 - 10
Oximino silane	Proprietary	1 - 5
Butanone oxime	96-29-7	1 - 5
Organic Acid	Proprietary	1 - 5
Carbon black	1333-86-4	0.1 - 1

4. FIRST AID MEASURES

Inhalation:	Move to fresh air. If symptoms persist, seek medical advice.
Skin contact:	Wipe off paste with paper towel or cloth. Wash with soap and water. If symptoms develop and persist, get medical attention.
Eye contact:	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. If eye irritation persists, consult a specialist.
Ingestion:	Do not induce vomiting. Seek medical advice.

5. FIRE FIGHTING MEASURES

Flash point:	> 93.00 °C (> 199.4 °F)
Autoignition temperature:	Not available
Flammable/Explosive limits - lower:	Not available
Flammable/Explosive limits - upper:	Not available
Extinguishing media:	Carbon dioxide. Dry Chemical Foam.
Special firefighting procedures:	Use water spray to keep fire exposed containers cool and disperse vapors.
Unusual fire or explosion hazards:	Contents under pressure. Closed containers may rupture (due to build up of pressure) when exposed to extreme heat.
Hazardous combustion products:	Oxides of Silicon Oxides of carbon. Formaldehyde

6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

Environmental precautions:	Do not allow spill to enter sewage systems or open bodies of water.
Clean-up methods:	Scrape up as much material as possible. Maintain good ventilation for large spills. Place scrap material in a well ventilated area and allow to cure to rubber.

7. HANDLING AND STORAGE

Handling:	Avoid contact with eyes, skin and clothing. Avoid breathing vapors or mists of this product. Wash thoroughly after handling. Do not handle contact lenses until all sealant has been removed from hands. Residual sealant may transfer to lenses and cause eye irritation.
Storage:	Store in a cool, dry, well-ventilated area.

For information on product shelf life contact Henkel Customer Service at (800) 243-4874.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous components	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Calcium carbonate	10 mg/m3 TWA Total dust.	5 mg/m3 TWA Respirable fraction. 15 mg/m3 TWA Total dust.	None	None
Norflurane	None	None	1,000 ppm (4,240 mg/m3) TWA	None
Oximino silane	None	None	None	None
Butanone oxime	None	None	10 ppm (36 mg/m3) TWA (Skin sensitizer.)	None
Organic Acid	10 mg/m3 TWA	None	None	None
Carbon black	3.5 mg/m3 TWA	3.5 mg/m3 TWA	None	None

Engineering controls:	Provide adequate local exhaust ventilation to maintain worker exposure below exposure limits.
Respiratory protection:	Use a NIOSH approved air-purifying respirator if the potential to exceed established exposure limits exists.
Eye/face protection:	Safety goggles or safety glasses with side shields.
Skin protection:	Chemical resistant, impermeable gloves.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state:	Aerosol, Paste
Color:	Black
Odor:	Mild, Petroleum
Odor threshold:	Not available
pH:	Not available
Vapor pressure:	Not available
Boiling point/range:	Not available
Melting point/ range:	Not available
Vapor density:	Not available
Flash point:	> 93.00 °C (> 199.4 °F)
Flammable/Explosive limits - lower:	Not available
Flammable/Explosive limits - upper:	Not available
Autoignition temperature:	Not available
Evaporation rate:	Not available
Solubility in water:	Polymerizes on contact with water.
Partition coefficient (n-octanol/water):	Not available
VOC content:	3.90 %; 50.70 g/l

10. STABILITY AND REACTIVITY

Stability:	Stable
Hazardous reactions:	Will not occur
Hazardous decomposition products:	Oxides of carbon. Oxides of silicon. Methyl ethyl ketoxime formed during cure. Formaldehyde.
Incompatible materials:	Polymerizes on contact with water.
Conditions to avoid:	Moisture.

11. TOXICOLOGICAL INFORMATION

Hazardous components	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Calcium carbonate	No	No	No
Norflurane	No	No	No
Oximino silane	No	No	No
Butanone oxime	No	No	No
Organic Acid	No	No	No
Carbon black	No	Group 2B	No

Hazardous components	Health Effects/Target Organs
Calcium carbonate	Nuisance dust
Norflurane	Cardiac, Central nervous system, Irritant, Respiratory, Skin
Oximino silane	Irritant, Allergen
Butanone oxime	Allergen, Blood, Central nervous system, Eyes, Irritant, Some evidence of carcinogenicity
Organic Acid	Irritant
Carbon black	Respiratory, Some evidence of carcinogenicity

12. ECOLOGICAL INFORMATION

Ecological information:

No specific studies have been conducted by Henkel on the ecotoxicity or environmental fate of this material; however, commonly available data on the material indicate that uncontrolled releases to soil, ground water, or surface waters could entail acute and/or chronic ecological effects, depending on the quantity and concentration of such releases. Releases of volatile components to the atmosphere are not believed to entail significant ecological consequences provided such releases are within the exposure levels set forth in this document. Accordingly, all appropriate measures should be taken to avoid uncontrolled releases to the environment, and any spills or other uncontrolled releases which may occur should be contained and cleaned up immediately in accordance with Section 6.

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Dispose of in accordance with local and national regulations.

Hazardous waste number: Not a RCRA hazardous waste.

14. TRANSPORT INFORMATION

U.S. Department of Transportation Ground (49 CFR)

Proper shipping name: Aerosols
Hazard class or division: 2.2
Identification number: UN 1950
Packing group: None

International Air Transportation (ICAO/IATA)

Proper shipping name: Aerosols, non-flammable
Hazard class or division: 2.2
Identification number: UN 1950
Packing group: None

Water Transportation (IMO/IMDG)

Proper shipping name: AEROSOLS
Hazard class or division: 2.2
Identification number: UN 1950
Packing group: None

15. REGULATORY INFORMATION

United States Regulatory Information

TSCA 8 (b) Inventory Status:	All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.
TSCA 12(b) Export Notification:	None above reporting de minimus
CERCLA/SARA Section 302 EHS:	None above reporting de minimus
CERCLA/SARA Section 311/312:	Immediate Health, Delayed Health
CERCLA/SARA 313:	None above reporting de minimus
California Proposition 65:	This product contains a chemical known in the State of California to cause cancer. This product contains a chemical known to the State of California to cause birth defects or other reproductive harm.

Canada Regulatory Information

CEPA DSL/NDSL Status:	All components are listed on or are exempt from listing on the Canadian Domestic Substances List.
WHMIS hazard class:	D.2.A, D.2.B

16. OTHER INFORMATION

This material safety data sheet contains changes from the previous version in sections: New Material Safety Data Sheet format.

Prepared by: Lou Fabrizio, Regulatory Affairs Specialist

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation does not assume responsibility for any results obtained by persons over whose methods Henkel Corporation has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any of Henkel Corporation's products. In light of the foregoing, Henkel Corporation specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation further disclaims any liability for consequential or incidental damages of any kind, including lost profits.