



Revision Date: 10/23/2007

Issue date: 10/23/2007

1. CHEMICAL PRODUCT AND COMPANY IDENTIFICATION

Product name: 30 CC 3875 EFD PART A	Item No. : TC3875A-V19 / IDH No. 891434
Product type: Anaerobic	Region: United States
Company address: Henkel Corporation 15051 East Don Julian Road Industry, California 91746	Contact Information: Telephone: 626.968.6511 Emergency Telephone: 860.571.5100 Internet: www.electronics.henkel.us

2. COMPOSITION/INFORMATION ON INGREDIENTS

<u>Hazardous components</u>	<u>%</u>	<u>ACGIH TLV</u>	<u>OSHA PEL</u>	<u>OTHER</u>
Aluminum oxide 1344-28-1	30-60	10 mg/m ³ TWA particulate matter containing no asbestos and <1% crystalline silica	15 mg/m ³ TWA total dust 5 mg/m ³ TWA respirable fraction	None
Hydroxyalkyl methacrylate 27813-02-1	30-60	None	None	1 ppm TWA; 3 ppm STEL
Boron Nitride Proprietary	10-30	None	None	None
Acrylonitrile Proprietary	5-10	None	None	None
1-Acetyl-2-phenylhydrazine 114-83-0	0.1-1	None	None	None

3. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW

Physical state: Liquid/paste	HMIS:	
Color: Light yellow	HEALTH:	3*
Odor: Mild, Characteristic	FLAMMABILITY:	1
	PHYSICAL HAZARD:	0
	Personal Protection:	See Section 8

WARNING: CAUSES EYE, SKIN AND RESPIRATORY TRACT IRRITATION
MAY CAUSE ALLERGIC SKIN REACTION.
MAY BE HARMFUL IF SWALLOWED.

Relevant routes of exposure: Skin, Inhalation, Eyes, Ingestion

Potential Health Effects

Inhalation:	Causes respiratory tract irritation. High vapor concentrations may cause central nervous system depression (headache, nausea, dizziness). Shortness of breath. Coughing.
Skin contact:	Causes skin irritation. May cause allergic skin reaction. Prolonged contact with skin may cause dermatitis.
Eye contact:	Causes eye irritation. Excess tearing.
Ingestion:	Swallowing small amounts during normal handling is not likely to cause harmful effects; swallowing large amounts may be harmful.

Existing conditions aggravated by exposure: Eye, skin, and respiratory disorders. Skin allergies.

4. FIRST AID MEASURES

Inhalation:	Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. If symptoms develop and persist, get medical attention.
Skin contact:	Remove contaminated clothing and shoes. Immediately flush skin with plenty of water (using soap, if available). Get medical attention if symptoms develop and persist. Wash clothing before reuse. Thoroughly clean shoes before reuse.
Eye contact:	Check for and remove any contact lenses. Immediately flush eyes with plenty of water for at least 15 minutes. Get medical attention.
Ingestion:	DO NOT induce vomiting unless directed to do so by medical personnel. Give a conscious person several glasses of water. Never give anything by mouth to an unconscious person. Get medical attention if symptoms develop and persist.

5. FIRE-FIGHTING MEASURES

Flash point:	97°C (206°F) Setaflash Closed cup
Autoignition temperature:	Not available
Flammable/Explosive limits-lower %:	Not available
Flammable/Explosive limits-upper %:	Not available
Extinguishing media:	Water spray (fog), foam, dry chemical or carbon dioxide.
Special fire fighting procedures:	Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear. Use water spray to keep fire exposed containers cool.
Unusual fire or explosion hazards:	Vapors may accumulate in low or confined areas, travel considerable distance to source of ignition, and flash back.
Hazardous combustion products:	Oxides of carbon. Oxides of boron. Oxides of nitrogen. Hydrogen cyanide. Hydrocarbons.

6. ACCIDENTAL RELEASE MEASURES

Environmental precautions:	Prevent product from entering drains or open waters.
Clean-up methods:	Ensure adequate ventilation. Wear suitable protective clothing, gloves and eye/face protection. Scrape up spilled material and place in a closed container for disposal.

7. HANDLING AND STORAGE

Handling:	Use only with adequate ventilation. Avoid contact with eyes, skin and clothing. Do not taste or swallow. Do not breathe mist or vapors. Keep container closed. Wash thoroughly after handling.
Storage:	Keep in a cool, well ventilated area away from heat, sparks and open flame. Keep container tightly closed until ready for use. For safe storage, store between 5°C (41°F) and 10°C (50°F).
Incompatible products:	Refer to Section 10.

For information on product shelf life contact Henkel Customer Service at (626) 968-6511

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Engineering controls:	Local exhaust ventilation is recommended when general ventilation is not sufficient to control airborne contamination below occupational exposure limits.
Respiratory protection:	Use NIOSH approved respirator if there is potential to exceed exposure limit(s).
Skin protection:	Use chemical resistant, impermeable clothing including gloves and either an apron or body suit to prevent skin contact.

Eye/face protection: Chemical splash goggles or safety glasses with side shields.

See Section 2 for exposure limits.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state: Liquid/paste
Color: Light yellow
Odor: Mild, Characteristic
Vapor pressure: Not available
pH: Not applicable
Boiling point/range: Not available
Melting point/range: Not available
Specific gravity: 1.7
Vapor density: Not available
Evaporation rate: Not available
Solubility in water: Insoluble.
Partition coefficient (n-octanol/water): Not available
VOC content: 0.103%; 1.751 grams/liter (EPA Method 24)

10. STABILITY AND REACTIVITY

Stability: Stable at normal conditions

Hazardous polymerization: None under normal processing.

Hazardous decomposition products: Oxides of carbon. Boron oxides. Oxides of nitrogen. Hydrogen cyanide. Hydrocarbons.

Incompatibility: Strong oxidizers. Strong acids. Strong bases. Amines. Alkalis. Free radical initiators. Reducing agents. Heavy metals.

Conditions to avoid: Storage with incompatible materials. Heat, flames, sparks and other sources of ignition. Exposure to sunlight.

11. TOXICOLOGICAL INFORMATION

Carcinogen Status

Hazardous components	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen
Aluminum oxide 1344-28-1	No	No	No
Hydroxyalkyl methacrylate 27813-02-1	No	No	No
Boron Nitride Proprietary	No	No	No
Acrylonitrile Proprietary	No	No	No
1-Acetyl-2-phenylhydrazine 114-83-0	No	No	No

Literature Referenced Target Organ & Other Health Effects

Hazardous components	Health Effects/Target Organs
Aluminum oxide 1344-28-1	Corrosive, Irritant, Nuisance dust
Hydroxyalkyl methacrylate 27813-02-1	Allergen, Irritant
Boron Nitride Proprietary	Corrosive, Irritant
Acrylonitrile Proprietary	No data
1-Acetyl-2-phenylhydrazine 114-83-0	Allergen, Blood, Kidney, Mutagen, Some evidence of carcinogenicity

12. ECOLOGICAL INFORMATION

Ecological information: Not available

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Dispose of according to Federal, State and local governmental regulations.

EPA hazardous waste number: Not a RCRA hazardous waste.

14. TRANSPORT INFORMATION

The shipping classifications in this section are for non-bulk packaging only (unless otherwise specified). Shipping classification may be different for bulk packaging.

U.S. Department of Transportation Ground (49 CFR):

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

International Air Transportation (ICAO/IATA):

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

Water Transportation (IMO/IMDG):

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

15. REGULATORY INFORMATION

United States Regulatory Information

TSCA 8 (b) Inventory Status: All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.
TSCA 12 (b) Export Notification: None above reporting de minimus.

CERCLA/SARA Section 302 EHS: None above reporting de minimus.
CERCLA/SARA Section 311/312: Immediate Health Hazard, Delayed Health Hazard
CERCLA/SARA 313: None above reporting de minimus.

California Proposition 65: This product contains a chemical known to the State of California to cause cancer and birth defects or other reproductive harm.

Canada Regulatory Information

CEPA DSL/NDL Status: All components are listed on or are exempt from listing on the Domestic Substances List.
WHMIS hazard class: D.2.A, D.2.B

16. OTHER INFORMATION

This material safety data sheet contains changes from the previous version in sections: 15

Prepared by: Melissa Frisby, Product Safety and Regulatory Affairs Specialist
For Safety and Regulatory Information contact:
Product Safety and Regulatory Affairs,
Rocky Hill, CT.
860-571-5204

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation does not assume responsibility for any results obtained by persons over whose methods Henkel Corporation has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any of Henkel Corporation's products. In light of the foregoing, Henkel Corporation specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation further disclaims any liability for consequential or incidental damages of any kind, including lost profits.