



Revision Date: 10/23/2007

Issue date: 10/23/2007

1. CHEMICAL PRODUCT AND COMPANY IDENTIFICATION

Product name: 3876 30CC EFD PART B
Product type: Anaerobic
Company address: Henkel Corporation
15051 East Don Julian Road
Industry, California 91746

Item No. : TC3876B-V19 / IDH No. 995654
Region: United States
Contact Information:
Telephone: 626.968.6511
Emergency Telephone: 860.571.5100
Internet: www.electronics.henkel.us

2. COMPOSITION/INFORMATION ON INGREDIENTS

Table with 5 columns: Hazardous components, %, ACGIH TLV, OSHA PEL, OTHER. Rows include Aluminum oxide, Boron nitride, Polyurethane methacrylate resin, Hydroxyalkyl methacrylate, Urethane methacrylate polyester resin, Methacryloyloxyethyl Ester, High boiling methacrylate, Acrylic acid, and Soda lime borosilicate glass.

3. HAZARDS IDENTIFICATION

## EMERGENCY OVERVIEW

### HMIS:

**Physical state:** Liquid/paste  
**Color:** Light blue  
**Odor:** Mild, Characteristic

**HEALTH:** 3\*  
**FLAMMABILITY:** 1  
**PHYSICAL HAZARD:** 0  
**Personal Protection:** See Section 8

**WARNING:** CAUSES EYE, SKIN AND RESPIRATORY TRACT IRRITATION  
MAY CAUSE ALLERGIC SKIN REACTION.  
MAY BE HARMFUL IF SWALLOWED.

**Relevant routes of exposure:** Skin, Inhalation, Eyes, Ingestion

### Potential Health Effects

**Inhalation:** Causes respiratory tract irritation. Shortness of breath. Coughing.  
**Skin contact:** Causes skin irritation. May cause allergic skin reaction. Prolonged contact with skin may cause dermatitis. Itching. Redness.  
**Eye contact:** Causes eye irritation. Pain and discomfort. Blurred vision. Excess tearing.  
**Ingestion:** May be harmful if swallowed. Ingestion may cause gastrointestinal irritation, nausea, vomiting and diarrhea. Harmful to the liver or kidneys if swallowed.

**Existing conditions aggravated by exposure:** Eye, skin, and respiratory disorders. Skin allergies.

See Section 11 for additional toxicological information.

## 4. FIRST AID MEASURES

**Inhalation:** Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. If symptoms develop and persist, get medical attention.

**Skin contact:** Remove contaminated clothing and shoes. Immediately flush skin with plenty of water (using soap, if available). Get medical attention if symptoms develop and persist. Wash clothing before reuse. Thoroughly clean shoes before reuse.

**Eye contact:** Check for and remove any contact lenses. Immediately flush eyes with plenty of water for at least 15 minutes. If eye irritation persists, consult a specialist.

**Ingestion:** DO NOT induce vomiting unless directed to do so by medical personnel. Give a conscious person several glasses of water. Never give anything by mouth to an unconscious person. Get medical attention if symptoms develop and persist.

## 5. FIRE-FIGHTING MEASURES

**Flash point:** 107°C (224°F) Setafash Closed cup

**Autoignition temperature:** Not available

**Flammable/Explosive limits-lower %:** Not available

**Flammable/Explosive limits-upper %:** Not available

**Extinguishing media:** Water spray (fog), foam, dry chemical or carbon dioxide.

**Special fire fighting procedures:** Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear. Use water spray to keep fire exposed containers cool.

**Unusual fire or explosion hazards:** Vapors may accumulate in low or confined areas, travel considerable distance to source of ignition, and flash back.

**Hazardous combustion products:** Oxides of carbon. Oxides of nitrogen. Oxides of boron. Hydrocarbons.

## 6. ACCIDENTAL RELEASE MEASURES

**Environmental precautions:** Prevent product from entering drains or open waters.

**Clean-up methods:** Ensure adequate ventilation. Wear suitable protective clothing, gloves and eye/face protection. Scrape up spilled material and place in sealed container for disposal.

## 7. HANDLING AND STORAGE

**Handling:** Use only with adequate ventilation. Avoid contact with eyes, skin and clothing. Do not taste or swallow. Do not breathe mist or vapors. Keep container closed. Wash thoroughly after handling.

**Storage:** Keep in a cool, well ventilated area away from heat, sparks and open flame. Keep container tightly closed until ready for use. For safe storage, store between 5°C (41°F) and 10°C (50°F).

**Incompatible products:** Refer to Section 10.

For information on product shelf life contact Henkel Customer Service at (626) 968-6511

## 8. EXPOSURE CONTROLS / PERSONAL PROTECTION

**Engineering controls:** Local exhaust ventilation is recommended when general ventilation is not sufficient to control airborne contamination below occupational exposure limits.

**Respiratory protection:** Use NIOSH approved respirator if there is potential to exceed exposure limit(s).

**Skin protection:** Use chemical resistant, impermeable clothing including gloves and either an apron or body suit to prevent skin contact. Butyl rubber gloves.

**Eye/face protection:** Chemical splash goggles or safety glasses with side shields.

**See Section 2 for exposure limits.**

## 9. PHYSICAL AND CHEMICAL PROPERTIES

<b>Physical state:</b>	Liquid/paste
<b>Color:</b>	Light blue
<b>Odor:</b>	Mild, Characteristic
<b>Vapor pressure:</b>	Not available
<b>pH:</b>	Not applicable
<b>Boiling point/range:</b>	Not available
<b>Melting point/range:</b>	Not available
<b>Specific gravity:</b>	1.69
<b>Vapor density:</b>	Not available
<b>Evaporation rate:</b>	Not available
<b>Solubility in water:</b>	Insoluble.
<b>Partition coefficient (n-octanol/water):</b>	Not available
<b>VOC content:</b>	0.053%; 0.8957 grams/liter (EPA Method 24)

## 10. STABILITY AND REACTIVITY

**Stability:** Stable at normal conditions

**Hazardous polymerization:** None under normal processing.

**Hazardous decomposition products:** Oxides of carbon. Oxides of nitrogen. Boron oxides. Hydrocarbons.

**Incompatibility:** Strong oxidizers. Strong acids and strong bases. Free radical initiators. Reducing agents. Heavy metals.

**Conditions to avoid:** Storage with incompatible materials. Heat, flames, sparks and other sources of ignition. Ultraviolet radiation.

## 11. TOXICOLOGICAL INFORMATION

### Carcinogen Status

Hazardous components	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen
Aluminum oxide 1344-28-1	No	No	No
Boron nitride 10043-11-5	No	No	No
Polyurethane methacrylate resin Proprietary	No	No	No
Hydroxyalkyl methacrylate 27813-02-1	No	No	No
Urethane methacrylate polyester resin Unknown	No	No	No
Methacryloyloxyethyl Ester Proprietary	No	No	No
High boiling methacrylate Proprietary	No	No	No
Acrylic acid 79-10-7	No	No	No
Soda lime borosilicate glass 65997-17-3	Suspect Carcinogen	Group 2B	Yes

**Literature Referenced Target Organ & Other Health Effects**

Hazardous components	Health Effects/Target Organs
Aluminum oxide 1344-28-1	Corrosive, Irritant, Nuisance dust
Boron nitride 10043-11-5	Corrosive, Irritant
Polyurethane methacrylate resin Proprietary	Allergen, Irritant
Hydroxyalkyl methacrylate 27813-02-1	Allergen, Irritant
Urethane methacrylate polyester resin Unknown	Allergen, Irritant
Methacryloyloxyethyl Ester Proprietary	No Records
High boiling methacrylate Proprietary	Allergen, Irritant
Acrylic acid 79-10-7	Allergen, Corrosive, Irritant, Kidney, Liver
Soda lime borosilicate glass 65997-17-3	Allergen, Respiratory

**12. ECOLOGICAL INFORMATION**

**Ecological information:** Not available

**13. DISPOSAL CONSIDERATIONS**

**Information provided is for unused product only.**

**Recommended method of disposal:** Dispose of according to Federal, State and local governmental regulations.

**EPA hazardous waste number:** Not a RCRA hazardous waste.

**14. TRANSPORT INFORMATION**

**The shipping classifications in this section are for non-bulk packaging only (unless otherwise specified). Shipping classification may be different for bulk packaging.**

**U.S. Department of Transportation Ground (49 CFR):**

Proper shipping name: Not regulated  
Hazard class or division: None  
Identification number: None  
Packing group: None

**International Air Transportation (ICAO/IATA):**

Proper shipping name: Not regulated  
Hazard class or division: None  
Identification number: None  
Packing group: None

**Water Transportation (IMO/IMDG):**

Proper shipping name: Not regulated  
Hazard class or division: None  
Identification number: None  
Packing group: None

**15. REGULATORY INFORMATION**

**United States Regulatory Information**

**TSCA 8 (b) Inventory Status:** All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.  
**TSCA 12 (b) Export Notification:** None above reporting de minimus.

**CERCLA/SARA Section 302 EHS:** None above reporting de minimus.  
**CERCLA/SARA Section 311/312:** Immediate Health Hazard, Delayed Health Hazard  
**CERCLA/SARA 313:** This product contains the following toxic chemicals subject to the reporting requirements of section 313 of the Emergency Planning and Community Right-To-Know Act of 1986 (40 CFR 372). Acrylic acid (CAS# 79-10-7). Fatty acids, C6-C19 branched, cobalt(2+) salts (CAS # 68409-81-4).

**California Proposition 65:** This product contains a chemical known to the State of California to cause cancer and birth defects or other reproductive harm.

**Canada Regulatory Information**

**CEPA DSL/NDL Status:** One or more components are not listed on, and are not exempt from listing on either the Domestic Substances List or the Non-Domestic Substances List.  
**WHMIS hazard class:** D.2.A, D.2.B

**16. OTHER INFORMATION**

This material safety data sheet contains changes from the previous version in sections: 15

**Prepared by:** Melissa Frisby, Product Safety and Regulatory Affairs Specialist  
For Safety and Regulatory Information contact:  
Product Safety and Regulatory Affairs,  
Rocky Hill, CT.  
860-571-5204

**DISCLAIMER:** The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation does not assume responsibility for any results obtained by persons over whose methods Henkel Corporation has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any of Henkel Corporation's products. In light of the foregoing, Henkel Corporation specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation further disclaims any liability for consequential or incidental damages of any kind, including lost profits.