

# Current Probe - 1.5MHz



RoHS  
Compliant



## Description:

Active clamp style current probe has dual sensitivity ranges, 1V/A and 100mV/A for current measurements up to 4A or 40A, respectively. Bandwidth in both ranges up to 1.5MHz. Powered by 9V battery or included AC power adapter.  
Model 76-320 includes AC power adapter with North American style plugs.

## Features:

- Compact stylish body
- Dual sensitivity ranges
- 1.5MHz bandwidth (-3dB)
- Over-range indicator
- Accessories: Insulated BNC Cable, BNC to Banana Plugs Adapter, AC Power Adapter, and Instruction Manual.

## Specifications:

Type	: Active Current
Measurement Ranges	: 1V/A / 100mV/A
Current (DC + peak AC)	: 4A / 40A
DC Measurement Accuracy	: $\pm 3\% \pm 10\text{mA}$ @ 1 V/A (10mA to 8A peak) $\pm 4\% \pm 100\text{mA}$ @ 100mV/A (100mA to 80A peak)
Bandwidth	: DC - 1.5MHz
Rise and Fall Time	: 0.23 $\mu\text{s}$ (Typ.)
Max. Working Voltage	: 600V AC RMS CAT II 300V AC RMS CAT III
Max. Floating Voltage	: 600V AC RMS CAT II 300V AC RMS CAT III
Battery Life	: 4 hours
Operating Temperature/Humidity	: 0°C to +50°C / 0% to 95%
Max. Cable Diameter	: 10.3mm (0.4")
Dimensions	: 262mm $\times$ 81mm $\times$ 36mm (10.3" $\times$ 3.2" $\times$ 1.4")
Weight	: 310g w/o battery

## Part Number Table

Description	Part Number
Current Probe - 1.5MHz	76-320

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell plc 2012.

