# 280W 100V Hot Air Rework Station





## **Description:**

RoHS Compliant

The 21-10125 Hot Air Rework Station provides a wide range of temperature and temperature settings for flexibility in soldering and desoldering work of sensitive components. A closed-loop heat sensor provides accurate and consistent working temperature.

#### Features:

- · Lead free
- · ESD safe
- · Intelligent cooling system with auto off
- · Low vibration diaphragm air pump
- Temperature range: 210~896°F (100~480°C)
- 280 watt
- Max air volume: .81 cubic feet/min
- Nozzles included: SST 4.4mm, SST 7.5mm, SST 2.5mm, and QFP 14 × 14
- · Includes nozzles, handpiece, and holder

### **Replacement Nozzles:**

| MCM Part No. | Style | Туре   | Tip Size        |
|--------------|-------|--------|-----------------|
| 21-10160     | A1124 | Single | 2.5mm           |
| 21-10162     | A1125 | QFP    | 10.2mm × 10.2mm |
| 21-10164     | A1126 | QFP    | 15.2mm × 15.2mm |
| 21-10166     | A1129 | QFP    | 28.2mm × 28.2mm |
| 21-10168     | A1130 | Single | 4.4mm           |
| 21-10170     | A1170 | SOP    | 7.6mm × 12.7mm  |
| 21-10172     | A1257 | SOP    | 11.7mm × 21mm   |
| 21-10174     | A1258 | SOP    | 11.7mm × 8mm    |
| 21-10176     | A1131 | SOP    | 10mm × 4.8mm    |
| 21-10178     | A1132 | SOP    | 15mm × 5.7mm    |
| 21-10180     | A1133 | SOP    | 16mm × 7.2mm    |

## **Part Number Table**

| Description            | Part Number |
|------------------------|-------------|
| Hot Air Rework Station | 21-10125    |

Important Notice: This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell plc 2012.

www.element14.com www.farnell.com www.newark.com www.cpc.co.uk www.mcmelectronics.com

