
24 Hour Mechanical Time Switch

Model: NTT02 General Purpose Timer





NTT02 General Purpose Timer



Time control segments: 1 segment = 15 minutes, push segment down for ON, pull up for OFF.

Control switch:

1 = permanently ON, Timer symbol = timed control,

0 = permanently OFF.

1. General:

This time switch is a compact and easy to use segment timer, which fits on a single gang wall box. It can control outputs of up to 16A which makes it suitable for domestic immersion heaters.

2. Features:

Permanent ON/OFF facility. This enables the heater under control to be turned OFF when alternative methods of heating are available, or during a holiday period. It also enables the heater to be permanently turned ON.

Shortest switching time of 15 minutes increasing in 15 minute steps.

Up to 48 programmes per day.

3. Installation:

We recommend that this unit be fitted by a qualified electrician. Install in accordance to wiring and current building regulations. Please read the instructions carefully. If in any doubt contact the Timequard Helpline.

Important: Switch off mains electricity before commencing work.

Remove the two bezel fixing screws, and remove bezel from timer module and back plate. Separate the timer module from the back plate, and remove the wall fixing screws.

Ensuring that the free terminals on the back plate are at the top, connect the installation wiring to the terminal block, according to the legend on the wiring label.

The earth wires should be connected to the wall box earthing terminal, or should be connected together using a single way connector block if there is no suitable earth terminal in the back box.

Fit the wall mounting screws through the back plate into the wall box threaded holes, and tighten until the back plate is firmly fastened.

Fit the timer module to the back plate, ensuring the time indicator is on the bottom right hand side, and the locating holes on the timer are set correctly on the pegs on the back plate. Fit the bezel over the timer module, and secure to the back plate with the two screws provided.

For wiring, the terminals are marked as follows:

L Live supply.

Neutral supply.

S IN Live Input for volt free output (or a link can be added between L and S IN if volt free is not required).

S OUT Switch live output to heater or other appliance.

4. Programming the time switch:

- a) Decide what times you would like the time switch to switch ON and OFF.
- b) Push the required segments down for the duration of an ON period, and pull them up for the duration of an OFF period. The minimum switching interval is 15 minutes, and this can be increased in 15 minute steps.
- c) Set the correct time, by rotating the dial clockwise until the correct time is indicated by the triangular pointer. Note that as the dial is rotated there will be an increased resistance to turning as ON/OFF periods are passed.

Points to note:

The segment dial can be turned whilst the time controller is operating.

In case of power failure, re-adjust the time controller to the correct time of day by turning the dial in a clockwise direction until the correct time is indicated by the pointer.

5. Permanent Override:

The main slider on the timer can be set to permanent ON by sliding it to the left, aligning the arrow head to the 1 symbol.

In the middle position, with the arrow head pointing at the timer symbol, the timer is in automatic mode.

If the slider is moved to the right, and the arrow head points at the 0 symbol, the timer is permanently OFF.

6. Specifications:

Operating temperature: 0°C to 40°C
Operating voltage: 230V 50Hz
Switch rating: 16A resistive,
8A inductive.

1 HP, 750W incandescent,

750W halogen, 750W fluorescent, 100W compact fluorescent.

Minimum depth

of wall box: 32mm

Switch type: 22A micro switch

Voltage free contact: Yes

Contact type: Normally open

Power ON light: Yes
Time period: 24 hours

Note:

Product not suitable for discharge lighting.

3 Year Guarantee

In the unlikely event of this product becoming faulty due to defective material or manufacture within 3 years of the date of purchase, please return it to your supplier in the first year with proof of purchase and it will be replaced free of charge. For years 2 and 3 or any difficulty in the first year telephone the helpline on 020 8450 0515.

Note: a proof of purchase is required in all cases. For all eligible replacements (where agreed by Timeguard) the customer is responsible for all shipping/postage charges outside the UK. All shipping costs are to be paid in advance before a replacement is sent.

For assistance with the product please contact:

HELPLINE **020 8450 0515**

or email helpline@timeguard.com



For a product brochure please contact:

Timeguard Limited.

Victory Park, 400 Edgware Road, London NW2 6ND

Sales Office: 020 8452 1112 or email csc@timeguard.com

A **theben** Group Company

67 058 476 (issue 3)