

# PowerX

2013

## WATER SPRAY EXTINGUISHER - STORED PRESSURE

- Kitemarked to BS EN3
- High quality product
- Complete with wall bracket
- Nickel plated brass valve assembly
- Coated steel levers
- Polyester external coating
- Easy gauge testing (with needle test)
- Approved to the Pressure Equipment Directive
- Passed the 35kv conductivity discharge test
- 5 year warranty



Type	WATER SPRAY SP
Capacity (ltr)	6
Fire Rating	13A
Height	553
Cylinder Diameter (mm)	162
Overall Width (mm)	224
Filled Weight (kg)	9.5
Range of Throw (m)	>6
Duration of Discharge (secs)	20
Working Pressure (at 20°C)	12
Temperature Range (°C)	+5°C to +60°C
BS EN3 Approved	✓
MED Approved	
Part Number	81/03404
Model Number	EXWS6

Extinguisher images for illustration purposes only



Tel: 0161 654 2222 | Freefax: 0800 281 035  
Website: [www.thomas-glover.co.uk](http://www.thomas-glover.co.uk) | Email: [tgsales@tgproducts.co.uk](mailto:tgsales@tgproducts.co.uk)



TG Products Ltd, Parkfield House, Manchester Old Road, Middleton, Manchester, M24 4DY