

TECHNICAL DATA SHEET


CABLE REFERENCE : 1Pair(LSZH)

ISSUE NO. : 1

ISSUE DATE : 30 March, 2011.

CABLE CONSTRUCTION

| | | | | |
|---------------------------|--------------------------------|-------------------------------|---------------|--------|
| Category | 1Pair(LSZH) | | | |
| Test Standard | UL1581,UL758 | | | |
| 1.Conductor | Material | STRANDED-Tinned Copper | | |
| | Nom.O.D.(mm) | 7x0.203 | Up | +0.001 |
| | | | Down | -0.008 |
| 2.Insulation | Material | SPE | | |
| | Diameter | 1.25(+/-0.13)mmx2 | | |
| Color | red,black | | | |
| 3.Drain | Material | STRANDED-Tinned Copper | | |
| | Nom.O.D.(mm) | 7x 0.203 | Up | +0.001 |
| | | | Down | -0.008 |
| 4.Shield | Material | AL-foil | | |
| | Color | Blue | | |
| 5.Jacket | Extetal O.D. | 3.80(+/-0.18)mm | | |
| | Surface | Clean,Smooth | | |
| | Material | LSZH(complies RoHS) | | |
| | Color | Black | | |
| 6. CHARACTERISTICS | Item | Description | Standard | |
| | 1.Cond. Resistance | 20°C, Conductor DC Resistance | < 9.14 Ω/100M | |
| | 2.Min.Insulation DC Resistance | 20°C,Insulation DC Resistance | 200 MΩ*M | |
| | 3. Rated Voltage | ----- | 300 V | |
| | 4.Rated Temperature(°C) | ----- | 80°C | |



Information in this data sheet supplied to users is based on general experience and is given in good faith, but because of the many particular factors which are outside our knowledge which affect the use of the products, no warranty is given nor is to be implied with respect to such information. Users should make their own enquiries to determine the stability of products for any particular use.