


# Synchroflex Timing Pulleys T2.5

for 6mm wide belt

Centre drilled or Pilot Bore

in Aluminium with Zinc plated Steel Flanges



## Dimensions

Please note : All dimensions subject to change.

Pulleys may be Bored or Unbored.

If a dimension is critical to your application please contact our sales department for confirmation.  
for [special pulleys](#) or [reworked](#) pulleys please contact our manufacturing department

Code	Type	No. Teeth	De	Dp	Df	Dm	F	L	Bore d	No. Flanges
16T2.5/10-2	0F	10	7.45	7.96	13	13	9	16	-	2
16T2.5/12-2	0F	12	9.00	9.55	13	13	9	16	-	2
16T2.5/14-2	0F	14	10.60	11.14	15	15	9	16	-	2
16T2.5/15-2	0F	15	11.40	11.94	15	15	9	16	-	2
16T2.5/16-2	0F	16	12.20	12.73	16	16	9	16	-	2
16T2.5/18-2	1F	18	13.80	14.32	17.5	10	10	16	-	2
16T2.5/19-2	1F	19	14.60	15.12	20	10	10	16	-	2
16T2.5/20-2	1F	20	15.40	15.92	20	11	10	16	-	2
16T2.5/22-2	1F	22	17.00	17.51	22	11	10	16	-	2
16T2.5/24-2	1F	24	18.55	19.10	22	12	10	16	4	2
16T2.5/25-2	1F	25	19.35	19.89	25	13	10	16	4	2
16T2.5/26-2	1F	26	20.15	20.69	26	14	10	16	4	2
16T2.5/28-2	1F	28	21.75	22.28	26	14	10	16	4	2
16T2.5/30-2	1F	30	23.35	23.87	26	16	10	16	6	2
16T2.5/32-2	1F	32	24.95	25.46	32	16	10	16	6	2
16T2.5/36-2	1F	36	28.10	28.65	36	20	10	16	6	2
16T2.5/40-2	1F	40	31.30	31.83	38	22	10	16	6	2
16T2.5/44-0	2	44	34.50	35.01	-	24	10	16	6	0
16T2.5/48-0	2	48	37.70	38.20	-	26	10	16	6	0
16T2.5/60-0	2	60	47.25	47.75	-	34	10	16	8	0